

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332372

Luminaire Tested: **S123RDIP-S1165D805U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332372
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7783.3 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	96	93	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51																			
2	92	85	79	74	86	80	74	70	70	66	62	60	57	55	52	50	48	44																			
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38																			
4	78	67	59	54	72	63	56	51	56	50	46	48	44	41	42	39	36	33																			
5	71	60	52	46	67	57	50	44	50	44	40	44	39	36	38	35	32	29																			
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29	26																			
7	61	49	41	36	57	46	39	34	41	36	31	36	32	28	32	28	26	23																			
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	29	26	23	21																			
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19																			
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19763	19763	19763	19763
5°	23558	19847	17477	19847
10°	29415	19733	15789	19733
15°	34526	19531	14399	19531
20°	38533	19230	13216	19230
25°	37917	18912	12490	18912
30°	27256	18620	11742	18620
35°	18198	18239	11257	18239
40°	13408	17781	10756	17781
45°	11246	16978	10266	16978
50°	9923	15925	9582	15925
55°	8702	14720	8644	14720
60°	7750	13569	7918	13569
65°	6805	12332	7366	12332
70°	5344	11229	6729	11229
75°	4708	9807	6147	9807
80°	4091	8331	6044	8331
85°	3298	6694	6410	6694



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	2.3
10°-20°	564.1	7.2
20°-30°	886.2	11.4
30°-40°	924.6	11.9
40°-50°	791.2	10.2
50°-60°	603.1	7.7
60°-70°	386.5	5.0
70°-80°	186.0	2.4
80°-90°	52.2	0.7
90°-100°	38.3	0.5
100°-110°	182.3	2.3
110°-120°	438.0	5.6
120°-130°	557.7	7.2
130°-140°	595.9	7.7
140°-150°	557.2	7.2
150°-160°	449.5	5.8
160°-170°	290.1	3.7
170°-180°	100.0	1.3
0°-30°	1630.8	21.0
0°-40°	2555.4	32.8
0°-60°	3949.7	50.7
0°-90°	4574.3	58.8
90°-120°	658.6	8.5
90°-150°	2369.4	30.4
90°-180°	3209.0	41.2
0°-180°	7783.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1836	1836	1836	1836	1836	
5°	2180	1837	1618	1837	2180	225
15°	3098	1753	1292	1753	3098	879
25°	3193	1592	1052	1592	3193	1372
35°	1385	1388	857	1388	1385	908
45°	739	1115	674	1115	739	581
55°	464	784	461	784	464	419
65°	267	484	289	484	267	263
75°	113	236	148	236	113	121
85°	27	54	52	54	27	31
90°	24	1	24	1	24	12
95°	30	48	30	48	30	25
105°	34	233	34	233	34	79
115°	460	437	460	437	460	425
125°	629	616	629	616	629	561
135°	775	767	775	767	775	597
145°	894	885	894	885	894	558
155°	973	975	973	975	973	449
165°	1026	1028	1026	1028	1026	290
175°	1048	1052	1048	1052	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1955.5	1958.0	1949.8	1948.6	1939.1	1936.6	1936.6	1923.4	1915.2	1904.6	1898.3
5°	2180.3	2192.9	2186.6	2172.4	2148.8	2143.3	2128.4	2104.8	2078.1	2045.1	2029.4
7.5°	2461.0	2478.2	2471.6	2449.7	2425.0	2405.1	2362.9	2323.8	2268.9	2220.8	2179.6
10°	2691.2	2673.1	2658.9	2637.7	2614.9	2578.0	2534.0	2473.4	2403.5	2348.5	2287.2
12.5°	2863.4	2860.5	2842.5	2820.7	2788.5	2753.4	2699.3	2625.6	2544.3	2464.8	2394.7
15°	3098.3	3103.0	3091.2	3068.4	3022.8	2960.7	2879.0	2848.4	2732.0	2645.6	2559.1
17.5°	3260.8	3259.9	3258.3	3226.7	3180.2	3136.0	3060.2	2979.6	2874.3	2752.5	2636.0
20°	3363.9	3356.1	3357.7	3322.3	3287.7	3236.6	3162.7	3045.6	2959.2	2818.5	2698.2
22.5°	3361.4	3359.9	3365.8	3353.7	3328.6	3289.4	3231.3	3132.4	3022.1	2880.1	2744.8
25°	3192.6	3186.3	3223.3	3233.5	3273.6	3280.6	3263.3	3209.1	3104.6	2958.4	2791.0
27.5°	2672.0	2668.5	2737.1	2822.9	2931.7	3016.2	3098.0	3137.4	3104.6	2999.9	2832.2
30°	2192.9	2266.7	2301.3	2425.5	2563.8	2728.9	2873.5	3011.0	3044.8	2999.3	2861.7
32.5°	1820.6	1885.1	1914.0	2020.6	2149.5	2342.8	2559.7	2754.5	2892.1	2926.9	2844.1
35°	1384.9	1385.7	1451.7	1498.8	1618.3	1817.2	2027.8	2288.7	2548.1	2744.6	2765.0
37.5°	1105.1	1109.0	1148.9	1195.9	1285.5	1390.7	1576.2	1793.1	2092.7	2394.4	2571.2
40°	954.2	961.2	991.1	1037.5	1101.9	1181.3	1325.9	1530.3	1780.2	2115.8	2390.1
42.5°	857.3	868.8	884.2	919.9	959.8	1034.2	1151.1	1309.0	1536.3	1853.6	2170.1
45°	738.8	745.1	756.9	773.4	809.5	861.4	940.0	1046.1	1234.8	1490.2	1806.9
47.5°	651.7	648.4	660.8	674.2	698.3	733.6	786.3	872.9	1007.5	1212.4	1481.1
50°	592.6	591.8	600.5	610.7	633.5	659.4	702.7	767.9	874.8	1044.6	1290.6
52.5°	537.3	540.3	546.4	559.1	575.6	596.6	635.4	682.4	774.2	920.7	1125.8
55°	463.7	466.1	474.7	481.8	493.6	514.8	539.2	578.5	641.4	743.5	912.5
57.5°	401.5	400.4	408.7	410.4	423.8	441.1	459.9	490.4	536.0	612.0	725.8
60°	360.0	357.6	364.7	370.2	377.3	391.4	407.1	437.0	473.2	529.0	626.4
62.5°	322.2	321.1	326.3	331.8	337.7	350.5	363.7	386.7	415.3	462.3	539.6
65°	267.2	269.6	271.9	274.3	277.4	285.3	297.9	313.6	333.3	366.3	422.1
67.5°	210.0	212.4	213.2	218.0	224.8	229.7	237.4	251.4	265.0	292.9	324.6
70°	169.8	169.0	169.8	172.1	180.8	189.4	199.6	209.9	218.5	238.1	264.9
72.5°	145.9	144.5	146.5	147.0	151.2	153.6	160.0	169.6	180.8	194.1	213.3
75°	113.2	113.2	113.2	113.2	116.3	117.9	120.3	122.6	126.5	132.8	147.0
77.5°	83.6	83.8	84.9	85.7	86.3	87.2	88.7	91.0	92.4	95.7	101.9
80°	66.0	66.8	66.0	66.8	66.8	68.4	69.2	71.5	72.3	76.2	78.6
82.5°	49.7	49.2	49.7	50.5	50.5	52.0	52.2	53.9	54.1	56.1	58.5
85°	26.7	25.2	26.7	25.9	27.5	25.9	26.7	28.3	28.3	29.1	32.2
87.5°	11.0	12.2	10.8	11.4	11.3	11.9	11.7	11.6	12.7	11.9	12.1
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2	21.1	20.0	18.3
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0	26.6	25.2	37.7
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8	47.1	51.4	81.0
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7	291.3	313.8	311.3
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2	392.1	392.0	390.1
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6	505.2	503.8	503.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0	576.1	575.1	574.4
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3	674.8	674.2	673.4
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1	732.5	731.8	731.2
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8	813.0	812.1	811.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8	860.2	859.7	859.1
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3	921.0	920.6	920.3
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4	953.8	953.2	953.0
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5	993.5	992.4	992.6
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8	1013.6	1012.4	1012.6
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9	1034.9
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1	1045.7	1044.3	1044.2
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3	1052.2	1051.0	1050.9
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1895.8	1893.9	1885.1	1875.0	1861.8	1853.0	1846.1	1842.3	1831.0	1817.2	1807.7
5°	2012.9	1989.3	1964.1	1933.5	1905.2	1876.1	1858.0	1836.8	1810.9	1781.8	1761.4
7.5°	2138.3	2092.1	2042.3	1990.9	1940.1	1894.5	1854.3	1819.8	1778.5	1736.8	1707.6
10°	2234.5	2166.9	2097.0	2025.4	1960.2	1898.9	1851.7	1805.4	1755.9	1707.9	1671.8
12.5°	2321.9	2232.9	2152.3	2064.4	1981.0	1907.7	1839.8	1785.2	1725.7	1674.6	1633.4
15°	2432.6	2341.4	2243.9	2110.3	1999.5	1906.8	1824.2	1752.7	1680.4	1617.5	1577.4
17.5°	2536.0	2398.8	2267.8	2156.4	2012.4	1896.5	1795.8	1710.3	1630.9	1564.2	1514.9
20°	2578.8	2445.9	2303.7	2161.4	2019.9	1890.3	1773.1	1678.8	1596.3	1520.8	1475.3
22.5°	2604.5	2454.1	2304.3	2151.4	2001.1	1866.4	1750.5	1646.8	1557.3	1485.6	1429.4
25°	2634.6	2455.4	2290.3	2139.4	1986.1	1840.0	1702.4	1592.4	1495.7	1419.5	1359.7
27.5°	2654.4	2443.6	2248.5	2080.8	1925.3	1779.7	1653.7	1537.0	1439.0	1358.3	1294.2
30°	2658.1	2434.1	2216.4	2034.9	1876.9	1743.3	1609.7	1498.1	1394.3	1308.6	1248.9
32.5°	2663.2	2410.9	2173.0	1980.2	1818.4	1686.1	1565.0	1458.4	1352.2	1267.8	1206.8
35°	2642.4	2398.0	2107.2	1885.5	1723.6	1595.5	1486.3	1388.0	1283.5	1201.7	1139.7
37.5°	2553.1	2346.9	2039.0	1779.0	1609.7	1491.0	1402.0	1316.3	1220.5	1132.3	1073.8
40°	2463.2	2296.6	1986.1	1714.2	1537.4	1415.5	1335.4	1265.4	1172.7	1090.1	1027.3
42.5°	2329.3	2228.1	1935.8	1646.3	1455.6	1338.2	1270.6	1205.0	1123.6	1039.8	980.7
45°	2083.6	2097.0	1832.9	1538.1	1342.4	1224.5	1160.9	1115.3	1043.0	973.8	913.3
47.5°	1775.5	1900.5	1712.0	1422.9	1223.1	1112.5	1056.8	1017.0	968.3	900.4	845.2
50°	1574.3	1752.7	1615.2	1345.6	1148.3	1038.3	983.2	951.0	908.6	855.1	802.5
52.5°	1388.8	1580.4	1498.2	1259.4	1067.2	966.6	912.8	886.3	852.6	802.3	754.7
55°	1132.6	1326.7	1307.9	1129.4	945.5	855.1	814.3	784.4	761.6	723.9	686.2
57.5°	916.1	1100.2	1109.9	984.8	838.3	749.0	713.8	691.3	676.4	648.0	613.1
60°	779.7	948.7	981.7	887.4	761.6	683.0	648.4	630.3	618.6	595.8	569.0
62.5°	666.5	810.3	847.7	779.8	688.0	614.5	587.4	570.0	562.0	542.3	518.7
65°	510.1	629.6	665.7	628.0	580.0	521.1	499.1	484.2	477.1	466.1	448.8
67.5°	383.6	470.6	510.3	483.7	466.4	429.1	415.1	407.1	400.8	393.3	378.8
70°	308.1	372.5	413.4	406.3	392.2	372.5	362.3	356.8	350.5	344.3	331.7
72.5°	247.7	292.1	330.4	334.0	322.4	318.5	309.5	307.2	303.4	295.8	288.9
75°	164.3	194.9	221.6	231.9	236.6	240.5	236.6	235.8	235.0	228.7	224.8
77.5°	107.7	124.2	141.0	158.5	165.8	171.2	172.4	175.3	173.2	169.9	168.0
80°	82.5	86.5	98.2	113.2	125.0	129.7	132.8	134.4	133.6	132.8	129.7
82.5°	59.9	63.2	68.7	79.2	89.1	97.0	98.9	98.6	100.3	100.8	98.2
85°	32.2	33.0	34.6	36.2	41.7	50.3	52.7	54.2	55.8	55.8	51.1
87.5°	12.9	11.8	12.6	12.2	13.8	14.1	17.5	20.3	21.3	19.1	19.4
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5	14.1	13.6	13.1
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8	92.7	89.5	86.3
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4	175.9	178.4	180.9
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8	297.4	298.9	300.4
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8	379.0	380.3	381.5
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4	495.7	497.0	498.3
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3	567.6	568.9	570.2
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0	724.4	725.8	727.2
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5	805.8	807.1	808.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6	853.7	854.7	855.8
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5	916.3	917.1	917.9
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1	951.4	951.6	951.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3	993.3	993.3	993.2
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2	1014.8	1014.3	1013.9
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1	1037.4	1036.7	1036.0
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4	1046.6	1045.8	1044.9
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5	1052.9	1052.2	1051.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1804.6	1796.4	1790.8	1778.2	1770.0	1761.2	1752.4	1758.1	1757.4	1756.8	1756.8
5°	1744.1	1726.0	1709.5	1688.3	1674.9	1658.4	1645.8	1644.2	1647.4	1636.4	1630.1
7.5°	1684.0	1659.3	1635.9	1612.5	1587.7	1567.9	1555.4	1549.6	1541.6	1534.8	1527.8
10°	1641.9	1612.8	1590.0	1560.9	1534.2	1510.6	1495.7	1485.5	1480.0	1474.5	1464.3
12.5°	1598.5	1570.1	1541.0	1508.1	1482.7	1455.3	1444.1	1432.7	1422.1	1416.0	1402.0
15°	1535.0	1498.1	1467.4	1432.8	1404.5	1377.8	1362.1	1339.3	1336.1	1328.3	1314.1
17.5°	1471.3	1431.2	1389.0	1363.3	1331.4	1303.6	1279.7	1272.0	1249.5	1241.0	1228.8
20°	1421.0	1384.1	1351.9	1318.1	1271.7	1245.8	1226.9	1216.7	1198.6	1187.6	1179.7
22.5°	1377.6	1340.1	1302.8	1263.4	1225.2	1196.1	1182.3	1166.4	1156.5	1141.1	1132.6
25°	1315.7	1274.8	1230.0	1187.6	1160.1	1138.1	1116.1	1101.9	1087.8	1080.7	1065.0
27.5°	1243.7	1201.0	1159.1	1126.9	1093.1	1071.4	1051.5	1038.9	1021.9	1010.0	1001.3
30°	1204.1	1153.8	1117.6	1088.6	1045.3	1024.9	1010.0	994.3	981.7	969.1	960.5
32.5°	1158.2	1112.3	1078.0	1042.0	1008.9	986.5	967.2	953.4	942.7	930.7	922.1
35°	1086.2	1047.7	1012.3	976.2	951.8	929.0	906.2	894.4	884.2	873.2	865.4
37.5°	1021.1	985.1	951.5	917.2	887.0	868.5	850.1	841.1	827.3	819.9	811.9
40°	980.9	945.5	909.4	876.4	844.9	830.8	814.3	800.9	788.3	782.8	774.2
42.5°	936.9	901.5	871.0	835.5	809.7	790.5	775.3	760.7	751.2	743.2	738.3
45°	871.6	840.2	810.3	775.0	750.6	734.1	716.8	703.4	694.8	689.3	680.6
47.5°	808.3	776.9	746.5	715.7	692.1	673.3	656.0	646.7	635.2	628.5	622.6
50°	762.4	734.1	701.9	673.6	650.0	631.1	617.0	605.2	595.0	586.3	582.4
52.5°	720.3	690.1	662.3	635.8	611.0	589.6	576.7	564.3	556.6	546.7	542.2
55°	650.8	621.7	598.1	572.2	547.8	529.7	514.0	503.0	495.2	484.2	477.9
57.5°	585.5	559.5	531.3	508.8	483.7	468.4	455.4	440.5	430.9	422.2	416.1
60°	541.5	511.7	487.3	466.1	444.1	424.4	412.6	400.8	390.6	382.0	376.5
62.5°	495.6	469.5	446.4	423.3	403.2	386.1	372.4	362.5	353.5	348.0	342.5
65°	425.2	404.8	381.2	362.3	343.5	330.9	319.9	311.2	305.0	301.0	296.3
67.5°	360.4	340.6	320.0	301.5	288.9	279.3	272.1	264.7	261.6	256.5	253.4
70°	318.3	297.9	279.8	265.7	253.1	246.0	241.3	235.8	232.6	226.4	223.2
72.5°	272.4	257.6	244.6	233.0	222.9	216.5	210.5	203.7	198.7	191.8	188.6
75°	214.6	201.2	191.0	183.1	176.8	168.2	159.6	152.5	150.1	147.8	147.0
77.5°	158.9	150.4	143.0	136.4	128.6	122.3	120.4	118.8	118.4	117.1	117.1
80°	125.0	117.1	111.6	103.7	99.0	99.0	99.0	97.5	98.2	98.2	98.2
82.5°	92.9	85.7	82.7	79.9	78.9	79.5	79.5	79.9	79.4	80.6	80.0
85°	47.9	48.7	50.3	49.5	50.3	50.3	51.9	51.1	51.9	50.3	51.9
87.5°	19.2	21.4	22.5	23.6	24.7	24.5	25.3	25.4	26.2	26.3	26.4
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2	23.3	24.5	25.1
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0	29.3	30.7	31.5
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8	38.5	34.2	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7	246.2	223.6	200.7
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2	392.3	392.4	389.8
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6	508.0	509.3	510.1
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0	578.0	579.0	579.5
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3	675.9	676.4	676.5
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1	733.8	734.5	734.6
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8	814.6	815.5	815.7
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8	861.3	861.9	861.9
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3	921.7	922.0	921.8
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4	955.0	955.7	955.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5	995.5	996.6	996.4
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8	1016.0	1017.1	1017.2
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1	1048.5	1049.9	1049.8
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3	1054.4	1055.5	1055.4
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1749.3	1748.6	1749.3	1746.7	1749.3	1748.6	1749.3	1756.8	1756.8	1757.4	1758.1
5°	1627.7	1627.0	1624.6	1617.5	1624.6	1627.0	1627.7	1630.1	1636.4	1647.4	1644.2
7.5°	1521.6	1520.5	1513.6	1513.8	1513.6	1520.5	1521.6	1527.8	1534.8	1541.6	1549.6
10°	1458.8	1459.5	1450.1	1444.6	1450.1	1459.5	1458.8	1464.3	1474.5	1480.0	1485.5
12.5°	1397.8	1394.2	1386.6	1380.5	1386.6	1394.2	1397.8	1402.0	1416.0	1422.1	1432.7
15°	1317.3	1309.4	1290.6	1292.1	1290.6	1309.4	1317.3	1314.1	1328.3	1336.1	1339.3
17.5°	1222.5	1216.7	1216.4	1205.4	1216.4	1216.7	1222.5	1228.8	1241.0	1249.5	1272.0
20°	1167.2	1163.2	1164.8	1153.8	1164.8	1163.2	1167.2	1179.7	1187.6	1198.6	1216.7
22.5°	1123.8	1119.8	1113.2	1109.8	1113.2	1119.8	1123.8	1132.6	1141.1	1156.5	1166.4
25°	1060.3	1054.0	1047.7	1051.6	1047.7	1054.0	1060.3	1065.0	1080.7	1087.8	1101.9
27.5°	996.8	992.1	985.8	985.0	985.8	992.1	996.8	1001.3	1010.0	1021.9	1038.9
30°	956.5	951.8	948.7	944.7	948.7	951.8	956.5	960.5	969.1	981.7	994.3
32.5°	915.7	914.7	909.1	908.3	909.1	914.7	915.7	922.1	930.7	942.7	953.4
35°	862.2	857.5	855.9	856.7	855.9	857.5	862.2	865.4	873.2	884.2	894.4
37.5°	811.4	805.1	802.3	799.5	802.3	805.1	811.4	811.9	819.9	827.3	841.1
40°	775.0	768.7	767.1	765.5	767.1	768.7	775.0	774.2	782.8	788.3	800.9
42.5°	734.1	731.6	730.6	727.8	730.6	731.6	734.1	738.3	743.2	751.2	760.7
45°	678.3	677.5	672.8	674.4	672.8	677.5	678.3	680.6	689.3	694.8	703.4
47.5°	619.5	616.0	612.7	614.9	612.7	616.0	619.5	622.6	628.5	635.2	646.7
50°	579.3	577.7	570.6	572.2	570.6	577.7	579.3	582.4	586.3	595.0	605.2
52.5°	539.0	533.0	530.4	529.4	530.4	533.0	539.0	542.2	546.7	556.6	564.3
55°	472.4	465.3	462.1	460.6	462.1	465.3	472.4	477.9	484.2	495.2	503.0
57.5°	407.0	405.1	402.6	404.3	402.6	405.1	407.0	416.1	422.2	430.9	440.5
60°	368.6	368.6	368.6	367.8	368.6	368.6	368.6	376.5	382.0	390.6	400.8
62.5°	339.1	337.2	336.6	337.7	336.6	337.2	339.1	342.5	348.0	353.5	362.5
65°	294.0	293.2	290.0	289.2	290.0	293.2	294.0	296.3	301.0	305.0	311.2
67.5°	251.4	248.5	247.6	246.5	247.6	248.5	251.4	253.4	256.5	261.6	264.7
70°	219.3	217.7	213.0	213.8	213.0	217.7	219.3	223.2	226.4	232.6	235.8
72.5°	184.7	183.1	182.2	181.1	182.2	183.1	184.7	188.6	191.8	198.7	203.7
75°	146.2	145.4	144.6	147.8	144.6	145.4	146.2	147.0	147.8	150.1	152.5
77.5°	117.1	117.1	117.6	116.3	117.6	117.1	117.1	117.1	117.1	118.4	118.8
80°	98.2	98.2	97.5	97.5	97.5	98.2	98.2	98.2	98.2	98.2	97.5
82.5°	78.8	79.4	79.9	78.6	79.9	79.4	78.8	80.0	80.6	79.4	79.9
85°	51.9	51.1	52.7	51.9	52.7	51.1	51.9	51.9	50.3	51.9	51.1
87.5°	27.7	26.6	26.6	27.3	26.6	26.6	27.7	26.4	26.3	26.2	25.4
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	25.3	25.5	25.7	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2
95°	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7
97.5°	31.7	31.9	32.0	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0
100°	32.3	32.5	32.7	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6
102.5°	32.5	32.8	33.1	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8
105°	33.4	33.7	34.1	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7
107.5°	177.6	154.4	131.2	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7
110°	289.5	264.7	239.8	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	384.6	379.3	374.1	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2
115°	457.6	458.3	459.0	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2
117.5°	510.3	510.4	510.5	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6
120°	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2
122.5°	579.7	579.8	580.0	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0
125°	627.5	627.9	628.2	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1
127.5°	676.2	675.9	675.5	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3
130°	706.2	705.9	705.5	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0
132.5°	734.2	733.7	733.2	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1
135°	776.3	775.8	775.3	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8
137.5°	815.4	815.0	814.7	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8
140°	839.1	838.8	838.4	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9
142.5°	861.4	860.9	860.5	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8
145°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7
147.5°	921.0	920.2	919.4	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3
150°	938.9	938.4	937.9	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8
152.5°	954.8	954.0	953.2	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4
155°	976.5	975.4	974.4	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9
157.5°	995.1	993.7	992.4	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5
160°	1005.9	1004.7	1003.5	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1
162.5°	1016.1	1015.0	1014.0	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8
165°	1029.4	1028.1	1026.9	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7
167.5°	1039.1	1037.7	1036.3	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7
170°	1044.7	1043.3	1042.0	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3
172.5°	1048.3	1046.8	1045.2	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1
175°	1052.6	1051.2	1049.8	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6
177.5°	1054.0	1052.6	1051.2	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1752.4	1761.2	1770.0	1778.2	1790.8	1796.4	1804.6	1807.7	1817.2	1831.0	1842.3
5°	1645.8	1658.4	1674.9	1688.3	1709.5	1726.0	1744.1	1761.4	1781.8	1810.9	1836.8
7.5°	1555.4	1567.9	1587.7	1612.5	1635.9	1659.3	1684.0	1707.6	1736.8	1778.5	1819.8
10°	1495.7	1510.6	1534.2	1560.9	1590.0	1612.8	1641.9	1671.8	1707.9	1755.9	1805.4
12.5°	1444.1	1455.3	1482.7	1508.1	1541.0	1570.1	1598.5	1633.4	1674.6	1725.7	1785.2
15°	1362.1	1377.8	1404.5	1432.8	1467.4	1498.1	1535.0	1577.4	1617.5	1680.4	1752.7
17.5°	1279.7	1303.6	1331.4	1363.3	1389.0	1431.2	1471.3	1514.9	1564.2	1630.9	1710.3
20°	1226.9	1245.8	1271.7	1318.1	1351.9	1384.1	1421.0	1475.3	1520.8	1596.3	1678.8
22.5°	1182.3	1196.1	1225.2	1263.4	1302.8	1340.1	1377.6	1429.4	1485.6	1557.3	1646.8
25°	1116.1	1138.1	1160.1	1187.6	1230.0	1274.8	1315.7	1359.7	1419.5	1495.7	1592.4
27.5°	1051.5	1071.4	1093.1	1126.9	1159.1	1201.0	1243.7	1294.2	1358.3	1439.0	1537.0
30°	1010.0	1024.9	1045.3	1088.6	1117.6	1153.8	1204.1	1248.9	1308.6	1394.3	1498.1
32.5°	967.2	986.5	1008.9	1042.0	1078.0	1112.3	1158.2	1206.8	1267.8	1352.2	1458.4
35°	906.2	929.0	951.8	976.2	1012.3	1047.7	1086.2	1139.7	1201.7	1283.5	1388.0
37.5°	850.1	868.5	887.0	917.2	951.5	985.1	1021.1	1073.8	1132.3	1220.5	1316.3
40°	814.3	830.8	844.9	876.4	909.4	945.5	980.9	1027.3	1090.1	1172.7	1265.4
42.5°	775.3	790.5	809.7	835.5	871.0	901.5	936.9	980.7	1039.8	1123.6	1205.0
45°	716.8	734.1	750.6	775.0	810.3	840.2	871.6	913.3	973.8	1043.0	1115.3
47.5°	656.0	673.3	692.1	715.7	746.5	776.9	808.3	845.2	900.4	968.3	1017.0
50°	617.0	631.1	650.0	673.6	701.9	734.1	762.4	802.5	855.1	908.6	951.0
52.5°	576.7	589.6	611.0	635.8	662.3	690.1	720.3	754.7	802.3	852.6	886.3
55°	514.0	529.7	547.8	572.2	598.1	621.7	650.8	686.2	723.9	761.6	784.4
57.5°	455.4	468.4	483.7	508.8	531.3	559.5	585.5	613.1	648.0	676.4	691.3
60°	412.6	424.4	444.1	466.1	487.3	511.7	541.5	569.0	595.8	618.6	630.3
62.5°	372.4	386.1	403.2	423.3	446.4	469.5	495.6	518.7	542.3	562.0	570.0
65°	319.9	330.9	343.5	362.3	381.2	404.8	425.2	448.8	466.1	477.1	484.2
67.5°	272.1	279.3	288.9	301.5	320.0	340.6	360.4	378.8	393.3	400.8	407.1
70°	241.3	246.0	253.1	265.7	279.8	297.9	318.3	331.7	344.3	350.5	356.8
72.5°	210.5	216.5	222.9	233.0	244.6	257.6	272.4	288.9	295.8	303.4	307.2
75°	159.6	168.2	176.8	183.1	191.0	201.2	214.6	224.8	228.7	235.0	235.8
77.5°	120.4	122.3	128.6	136.4	143.0	150.4	158.9	168.0	169.9	173.2	175.3
80°	99.0	99.0	99.0	103.7	111.6	117.1	125.0	129.7	132.8	133.6	134.4
82.5°	79.5	79.5	78.9	79.9	82.7	85.7	92.9	98.2	100.8	100.3	98.6
85°	51.9	50.3	50.3	49.5	50.3	48.7	47.9	51.1	55.8	55.8	54.2
87.5°	25.3	24.5	24.7	23.6	22.5	21.4	19.2	19.4	19.1	21.3	20.3
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	21.1	20.0	18.3	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5
95°	25.5	24.2	22.3	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7
97.5°	26.6	25.2	37.7	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8
100°	27.2	25.8	52.9	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1
102.5°	47.1	51.4	81.0	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4
105°	140.5	171.2	186.8	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0
107.5°	291.3	313.8	311.3	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8
110°	346.9	352.6	350.7	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	392.1	392.0	390.1	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8
115°	450.5	448.8	447.2	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0
117.5°	505.2	503.8	503.0	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4
120°	540.8	539.4	538.9	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1
122.5°	576.1	575.1	574.4	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3
125°	625.8	625.4	624.7	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1
127.5°	674.8	674.2	673.4	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2
130°	704.3	703.6	702.9	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2
132.5°	732.5	731.8	731.2	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0
135°	775.3	774.8	774.1	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9
137.5°	813.0	812.1	811.7	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5
140°	837.2	836.5	836.0	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5
142.5°	860.2	859.7	859.1	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6
145°	892.4	892.0	891.7	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0
147.5°	921.0	920.6	920.3	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5
150°	938.5	938.2	937.8	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2
152.5°	953.8	953.2	953.0	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1
155°	975.0	974.1	973.9	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9
157.5°	993.5	992.4	992.6	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3
160°	1004.1	1003.0	1003.2	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
162.5°	1013.6	1012.4	1012.6	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2
165°	1026.3	1024.9	1025.1	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1
167.5°	1036.3	1034.9	1034.9	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1
170°	1042.0	1040.6	1040.6	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7
172.5°	1045.7	1044.3	1044.2	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4
175°	1050.4	1049.2	1049.0	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3
177.5°	1052.2	1051.0	1050.9	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1846.1	1853.0	1861.8	1875.0	1885.1	1893.9	1895.8	1898.3	1904.6	1915.2	1923.4
5°	1858.0	1876.1	1905.2	1933.5	1964.1	1989.3	2012.9	2029.4	2045.1	2078.1	2104.8
7.5°	1854.3	1894.5	1940.1	1990.9	2042.3	2092.1	2138.3	2179.6	2220.8	2268.9	2323.8
10°	1851.7	1898.9	1960.2	2025.4	2097.0	2166.9	2234.5	2287.2	2348.5	2403.5	2473.4
12.5°	1839.8	1907.7	1981.0	2064.4	2152.3	2232.9	2321.9	2394.7	2464.8	2544.3	2625.6
15°	1824.2	1906.8	1999.5	2110.3	2243.9	2341.4	2432.6	2559.1	2645.6	2732.0	2848.4
17.5°	1795.8	1896.5	2012.4	2156.4	2267.8	2398.8	2536.0	2636.0	2752.5	2874.3	2979.6
20°	1773.1	1890.3	2019.9	2161.4	2303.7	2445.9	2578.8	2698.2	2818.5	2959.2	3045.6
22.5°	1750.5	1866.4	2001.1	2151.4	2304.3	2454.1	2604.5	2744.8	2880.1	3022.1	3132.4
25°	1702.4	1840.0	1986.1	2139.4	2290.3	2455.4	2634.6	2791.0	2958.4	3104.6	3209.1
27.5°	1653.7	1779.7	1925.3	2080.8	2248.5	2443.6	2654.4	2832.2	2999.9	3104.6	3137.4
30°	1609.7	1743.3	1876.9	2034.9	2216.4	2434.1	2658.1	2861.7	2999.3	3044.8	3011.0
32.5°	1565.0	1686.1	1818.4	1980.2	2173.0	2410.9	2663.2	2844.1	2926.9	2892.1	2754.5
35°	1486.3	1595.5	1723.6	1885.5	2107.2	2398.0	2642.4	2765.0	2744.6	2548.1	2288.7
37.5°	1402.0	1491.0	1609.7	1779.0	2039.0	2346.9	2553.1	2571.2	2394.4	2092.7	1793.1
40°	1335.4	1415.5	1537.4	1714.2	1986.1	2296.6	2463.2	2390.1	2115.8	1780.2	1530.3
42.5°	1270.6	1338.2	1455.6	1646.3	1935.8	2228.1	2329.3	2170.1	1853.6	1536.3	1309.0
45°	1160.9	1224.5	1342.4	1538.1	1832.9	2097.0	2083.6	1806.9	1490.2	1234.8	1046.1
47.5°	1056.8	1112.5	1223.1	1422.9	1712.0	1900.5	1775.5	1481.1	1212.4	1007.5	872.9
50°	983.2	1038.3	1148.3	1345.6	1615.2	1752.7	1574.3	1290.6	1044.6	874.8	767.9
52.5°	912.8	966.6	1067.2	1259.4	1498.2	1580.4	1388.8	1125.8	920.7	774.2	682.4
55°	814.3	855.1	945.5	1129.4	1307.9	1326.7	1132.6	912.5	743.5	641.4	578.5
57.5°	713.8	749.0	838.3	984.8	1109.9	1100.2	916.1	725.8	612.0	536.0	490.4
60°	648.4	683.0	761.6	887.4	981.7	948.7	779.7	626.4	529.0	473.2	437.0
62.5°	587.4	614.5	688.0	779.8	847.7	810.3	666.5	539.6	462.3	415.3	386.7
65°	499.1	521.1	580.0	628.0	665.7	629.6	510.1	422.1	366.3	333.3	313.6
67.5°	415.1	429.1	466.4	483.7	510.3	470.6	383.6	324.6	292.9	265.0	251.4
70°	362.3	372.5	392.2	406.3	413.4	372.5	308.1	264.9	238.1	218.5	209.9
72.5°	309.5	318.5	322.4	334.0	330.4	292.1	247.7	213.3	194.1	180.8	169.6
75°	236.6	240.5	236.6	231.9	221.6	194.9	164.3	147.0	132.8	126.5	122.6
77.5°	172.4	171.2	165.8	158.5	141.0	124.2	107.7	101.9	95.7	92.4	91.0
80°	132.8	129.7	125.0	113.2	98.2	86.5	82.5	78.6	76.2	72.3	71.5
82.5°	98.9	97.0	89.1	79.2	68.7	63.2	59.9	58.5	56.1	54.1	53.9
85°	52.7	50.3	41.7	36.2	34.6	33.0	32.2	32.2	29.1	28.3	28.3
87.5°	17.5	14.1	13.8	12.2	12.6	11.8	12.9	12.1	11.9	12.7	11.6
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2
95°	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7
97.5°	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0
100°	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6
102.5°	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8
105°	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7
107.5°	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7
110°	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2
115°	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2
117.5°	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6
120°	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2
122.5°	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0
125°	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1
127.5°	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3
130°	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0
132.5°	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1
135°	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8
137.5°	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8
140°	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9
142.5°	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8
145°	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7
147.5°	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3
150°	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8
152.5°	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4
155°	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9
157.5°	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5
160°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1
162.5°	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8
165°	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7
167.5°	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7
170°	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3
172.5°	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1
175°	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6
177.5°	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1936.6	1936.6	1939.1	1948.6	1949.8	1958.0	1955.5
5°	2128.4	2143.3	2148.8	2172.4	2186.6	2192.9	2180.3
7.5°	2362.9	2405.1	2425.0	2449.7	2471.6	2478.2	2461.0
10°	2534.0	2578.0	2614.9	2637.7	2658.9	2673.1	2691.2
12.5°	2699.3	2753.4	2788.5	2820.7	2842.5	2860.5	2863.4
15°	2879.0	2960.7	3022.8	3068.4	3091.2	3103.0	3098.3
17.5°	3060.2	3136.0	3180.2	3226.7	3258.3	3259.9	3260.8
20°	3162.7	3236.6	3287.7	3322.3	3357.7	3356.1	3363.9
22.5°	3231.3	3289.4	3328.6	3353.7	3365.8	3359.9	3361.4
25°	3263.3	3280.6	3273.6	3233.5	3223.3	3186.3	3192.6
27.5°	3098.0	3016.2	2931.7	2822.9	2737.1	2668.5	2672.0
30°	2873.5	2728.9	2563.8	2425.5	2301.3	2266.7	2192.9
32.5°	2559.7	2342.8	2149.5	2020.6	1914.0	1885.1	1820.6
35°	2027.8	1817.2	1618.3	1498.8	1451.7	1385.7	1384.9
37.5°	1576.2	1390.7	1285.5	1195.9	1148.9	1109.0	1105.1
40°	1325.9	1181.3	1101.9	1037.5	991.1	961.2	954.2
42.5°	1151.1	1034.2	959.8	919.9	884.2	868.8	857.3
45°	940.0	861.4	809.5	773.4	756.9	745.1	738.8
47.5°	786.3	733.6	698.3	674.2	660.8	648.4	651.7
50°	702.7	659.4	633.5	610.7	600.5	591.8	592.6
52.5°	635.4	596.6	575.6	559.1	546.4	540.3	537.3
55°	539.2	514.8	493.6	481.8	474.7	466.1	463.7
57.5°	459.9	441.1	423.8	410.4	408.7	400.4	401.5
60°	407.1	391.4	377.3	370.2	364.7	357.6	360.0
62.5°	363.7	350.5	337.7	331.8	326.3	321.1	322.2
65°	297.9	285.3	277.4	274.3	271.9	269.6	267.2
67.5°	237.4	229.7	224.8	218.0	213.2	212.4	210.0
70°	199.6	189.4	180.8	172.1	169.8	169.0	169.8
72.5°	160.0	153.6	151.2	147.0	146.5	144.5	145.9
75°	120.3	117.9	116.3	113.2	113.2	113.2	113.2
77.5°	88.7	87.2	86.3	85.7	84.9	83.8	83.6
80°	69.2	68.4	66.8	66.8	66.0	66.8	66.0
82.5°	52.2	52.0	50.5	50.5	49.7	49.2	49.7
85°	26.7	25.9	27.5	25.9	26.7	25.2	26.7
87.5°	11.7	11.9	11.3	11.4	10.8	12.2	11.0
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P332372

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)