

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332373

Luminaire Tested: **S123RDIP-S1165D805U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332373  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D805U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7331.9 lumens  
Efficiency: N/A  
Efficacy: 120.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62																												
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54																												
2	93	86	80	75	87	81	76	71	71	67	64	62	60	57	54	52	50	46																												
3	85	76	69	63	80	72	65	60	63	59	55	56	52	49	49	46	44	40																												
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	35																												
5	72	61	53	47	68	58	50	45	51	46	41	46	41	37	40	37	34	31																												
6	67	55	47	41	63	52	45	40	47	41	36	41	37	33	37	33	30	27																												
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27	25																												
8	58	45	38	33	54	43	36	31	39	33	29	35	30	27	31	27	24	22																												
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22	20																												
10	50	38	31	26	47	37	30	26	33	28	24	30	25	22	27	23	20	18																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19763	19763	19763	19763
5°	23558	19847	17477	19847
10°	29415	19733	15789	19733
15°	34526	19531	14399	19531
20°	38533	19230	13216	19230
25°	37917	18912	12490	18912
30°	27256	18620	11742	18620
35°	18198	18239	11257	18239
40°	13408	17781	10756	17781
45°	11246	16978	10266	16978
50°	9923	15925	9582	15925
55°	8702	14720	8644	14720
60°	7750	13569	7918	13569
65°	6805	12332	7366	12332
70°	5344	11229	6729	11229
75°	4708	9807	6147	9807
80°	4091	8331	6044	8331
85°	3298	6694	6410	6694



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.6	2.5
10°-20°	564.1	7.7
20°-30°	886.2	12.1
30°-40°	924.6	12.6
40°-50°	791.2	10.8
50°-60°	603.1	8.2
60°-70°	386.5	5.3
70°-80°	186.0	2.5
80°-90°	52.2	0.7
90°-100°	64.8	0.9
100°-110°	194.1	2.6
110°-120°	330.1	4.5
120°-130°	434.2	5.9
130°-140°	488.0	6.7
140°-150°	479.7	6.5
150°-160°	403.8	5.5
160°-170°	268.8	3.7
170°-180°	94.1	1.3
0°-30°	1630.8	22.2
0°-40°	2555.4	34.9
0°-60°	3949.7	53.9
0°-90°	4574.3	62.4
90°-120°	589.0	8.0
90°-150°	1990.8	27.2
90°-180°	2758.0	37.6
0°-180°	7331.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1836	1836	1836	1836	1836	
5°	2180	1837	1618	1837	2180	225
15°	3098	1753	1292	1753	3098	879
25°	3193	1592	1052	1592	3193	1372
35°	1385	1388	857	1388	1385	908
45°	739	1115	674	1115	739	581
55°	464	784	461	784	464	419
65°	267	484	289	484	267	263
75°	113	236	148	236	113	121
85°	27	54	52	54	27	31
90°	24	1	24	1	24	12
95°	61	46	61	46	61	63
105°	186	176	186	176	186	197
115°	333	332	333	332	333	330
125°	481	486	481	486	481	430
135°	630	631	630	631	630	484
145°	765	765	765	765	765	478
155°	875	876	875	876	875	403
165°	952	955	952	955	952	268
175°	989	993	989	993	989	94
180°	995	995	995	995	995	



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1955.5	1958.0	1949.8	1948.6	1939.1	1936.6	1936.6	1923.4	1915.2	1904.6	1898.3
5°	2180.3	2192.9	2186.6	2172.4	2148.8	2143.3	2128.4	2104.8	2078.1	2045.1	2029.4
7.5°	2461.0	2478.2	2471.6	2449.7	2425.0	2405.1	2362.9	2323.8	2268.9	2220.8	2179.6
10°	2691.2	2673.1	2658.9	2637.7	2614.9	2578.0	2534.0	2473.4	2403.5	2348.5	2287.2
12.5°	2863.4	2860.5	2842.5	2820.7	2788.5	2753.4	2699.3	2625.6	2544.3	2464.8	2394.7
15°	3098.3	3103.0	3091.2	3068.4	3022.8	2960.7	2879.0	2848.4	2732.0	2645.6	2559.1
17.5°	3260.8	3259.9	3258.3	3226.7	3180.2	3136.0	3060.2	2979.6	2874.3	2752.5	2636.0
20°	3363.9	3356.1	3357.7	3322.3	3287.7	3236.6	3162.7	3045.6	2959.2	2818.5	2698.2
22.5°	3361.4	3359.9	3365.8	3353.7	3328.6	3289.4	3231.3	3132.4	3022.1	2880.1	2744.8
25°	3192.6	3186.3	3223.3	3233.5	3273.6	3280.6	3263.3	3209.1	3104.6	2958.4	2791.0
27.5°	2672.0	2668.5	2737.1	2822.9	2931.7	3016.2	3098.0	3137.4	3104.6	2999.9	2832.2
30°	2192.9	2266.7	2301.3	2425.5	2563.8	2728.9	2873.5	3011.0	3044.8	2999.3	2861.7
32.5°	1820.6	1885.1	1914.0	2020.6	2149.5	2342.8	2559.7	2754.5	2892.1	2926.9	2844.1
35°	1384.9	1385.7	1451.7	1498.8	1618.3	1817.2	2027.8	2288.7	2548.1	2744.6	2765.0
37.5°	1105.1	1109.0	1148.9	1195.9	1285.5	1390.7	1576.2	1793.1	2092.7	2394.4	2571.2
40°	954.2	961.2	991.1	1037.5	1101.9	1181.3	1325.9	1530.3	1780.2	2115.8	2390.1
42.5°	857.3	868.8	884.2	919.9	959.8	1034.2	1151.1	1309.0	1536.3	1853.6	2170.1
45°	738.8	745.1	756.9	773.4	809.5	861.4	940.0	1046.1	1234.8	1490.2	1806.9
47.5°	651.7	648.4	660.8	674.2	698.3	733.6	786.3	872.9	1007.5	1212.4	1481.1
50°	592.6	591.8	600.5	610.7	633.5	659.4	702.7	767.9	874.8	1044.6	1290.6
52.5°	537.3	540.3	546.4	559.1	575.6	596.6	635.4	682.4	774.2	920.7	1125.8
55°	463.7	466.1	474.7	481.8	493.6	514.8	539.2	578.5	641.4	743.5	912.5
57.5°	401.5	400.4	408.7	410.4	423.8	441.1	459.9	490.4	536.0	612.0	725.8
60°	360.0	357.6	364.7	370.2	377.3	391.4	407.1	437.0	473.2	529.0	626.4
62.5°	322.2	321.1	326.3	331.8	337.7	350.5	363.7	386.7	415.3	462.3	539.6
65°	267.2	269.6	271.9	274.3	277.4	285.3	297.9	313.6	333.3	366.3	422.1
67.5°	210.0	212.4	213.2	218.0	224.8	229.7	237.4	251.4	265.0	292.9	324.6
70°	169.8	169.0	169.8	172.1	180.8	189.4	199.6	209.9	218.5	238.1	264.9
72.5°	145.9	144.5	146.5	147.0	151.2	153.6	160.0	169.6	180.8	194.1	213.3
75°	113.2	113.2	113.2	113.2	116.3	117.9	120.3	122.6	126.5	132.8	147.0
77.5°	83.6	83.8	84.9	85.7	86.3	87.2	88.7	91.0	92.4	95.7	101.9
80°	66.0	66.8	66.0	66.8	66.8	68.4	69.2	71.5	72.3	76.2	78.6
82.5°	49.7	49.2	49.7	50.5	50.5	52.0	52.2	53.9	54.1	56.1	58.5
85°	26.7	25.2	26.7	25.9	27.5	25.9	26.7	28.3	28.3	29.1	32.2
87.5°	11.0	12.2	10.8	11.4	11.3	11.9	11.7	11.6	12.7	11.9	12.1
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1	30.6	30.0	28.7
95°	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2	58.6	57.9	56.5
97.5°	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1	91.3	90.5	89.5
100°	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0	115.5	114.9	114.1
102.5°	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5	143.0	142.5	141.3
105°	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5	184.5	184.5	183.0
107.5°	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9	228.4	227.8	227.2
110°	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6	257.9	257.2	256.9



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3	287.5	286.6	286.6
115°	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1	333.4
117.5°	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0	379.0	379.0	379.5
120°	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3	409.5	409.7	410.6
122.5°	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1	440.5	441.0	441.4
125°	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7	486.4	487.1	487.4
127.5°	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8	531.8	532.7	533.1
130°	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8	561.4	562.1	562.7
132.5°	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9	590.7	591.5	591.9
135°	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5	634.2	634.9	635.0
137.5°	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1	676.8	677.5	677.1
140°	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4	730.5	730.7	730.4
145°	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0	769.2	769.3	768.8
147.5°	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5	805.5	805.5	805.0
150°	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0	828.0	828.0	827.6
152.5°	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5	848.3	848.0	847.8
155°	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6	877.9	877.2	877.1
157.5°	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5	903.8	903.0	902.9
160°	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4	919.5	918.7	918.7
162.5°	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4	934.5	933.7	933.5
165°	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4	953.3	952.3	952.3
167.5°	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6	967.5
170°	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7	975.7
172.5°	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8	983.7	982.6	982.6
175°	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9	990.9	989.8	989.8
177.5°	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1	994.2	993.4	993.4
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1895.8	1893.9	1885.1	1875.0	1861.8	1853.0	1846.1	1842.3	1831.0	1817.2	1807.7
5°	2012.9	1989.3	1964.1	1933.5	1905.2	1876.1	1858.0	1836.8	1810.9	1781.8	1761.4
7.5°	2138.3	2092.1	2042.3	1990.9	1940.1	1894.5	1854.3	1819.8	1778.5	1736.8	1707.6
10°	2234.5	2166.9	2097.0	2025.4	1960.2	1898.9	1851.7	1805.4	1755.9	1707.9	1671.8
12.5°	2321.9	2232.9	2152.3	2064.4	1981.0	1907.7	1839.8	1785.2	1725.7	1674.6	1633.4
15°	2432.6	2341.4	2243.9	2110.3	1999.5	1906.8	1824.2	1752.7	1680.4	1617.5	1577.4
17.5°	2536.0	2398.8	2267.8	2156.4	2012.4	1896.5	1795.8	1710.3	1630.9	1564.2	1514.9
20°	2578.8	2445.9	2303.7	2161.4	2019.9	1890.3	1773.1	1678.8	1596.3	1520.8	1475.3
22.5°	2604.5	2454.1	2304.3	2151.4	2001.1	1866.4	1750.5	1646.8	1557.3	1485.6	1429.4
25°	2634.6	2455.4	2290.3	2139.4	1986.1	1840.0	1702.4	1592.4	1495.7	1419.5	1359.7
27.5°	2654.4	2443.6	2248.5	2080.8	1925.3	1779.7	1653.7	1537.0	1439.0	1358.3	1294.2
30°	2658.1	2434.1	2216.4	2034.9	1876.9	1743.3	1609.7	1498.1	1394.3	1308.6	1248.9
32.5°	2663.2	2410.9	2173.0	1980.2	1818.4	1686.1	1565.0	1458.4	1352.2	1267.8	1206.8
35°	2642.4	2398.0	2107.2	1885.5	1723.6	1595.5	1486.3	1388.0	1283.5	1201.7	1139.7
37.5°	2553.1	2346.9	2039.0	1779.0	1609.7	1491.0	1402.0	1316.3	1220.5	1132.3	1073.8
40°	2463.2	2296.6	1986.1	1714.2	1537.4	1415.5	1335.4	1265.4	1172.7	1090.1	1027.3
42.5°	2329.3	2228.1	1935.8	1646.3	1455.6	1338.2	1270.6	1205.0	1123.6	1039.8	980.7
45°	2083.6	2097.0	1832.9	1538.1	1342.4	1224.5	1160.9	1115.3	1043.0	973.8	913.3
47.5°	1775.5	1900.5	1712.0	1422.9	1223.1	1112.5	1056.8	1017.0	968.3	900.4	845.2
50°	1574.3	1752.7	1615.2	1345.6	1148.3	1038.3	983.2	951.0	908.6	855.1	802.5
52.5°	1388.8	1580.4	1498.2	1259.4	1067.2	966.6	912.8	886.3	852.6	802.3	754.7
55°	1132.6	1326.7	1307.9	1129.4	945.5	855.1	814.3	784.4	761.6	723.9	686.2
57.5°	916.1	1100.2	1109.9	984.8	838.3	749.0	713.8	691.3	676.4	648.0	613.1
60°	779.7	948.7	981.7	887.4	761.6	683.0	648.4	630.3	618.6	595.8	569.0
62.5°	666.5	810.3	847.7	779.8	688.0	614.5	587.4	570.0	562.0	542.3	518.7
65°	510.1	629.6	665.7	628.0	580.0	521.1	499.1	484.2	477.1	466.1	448.8
67.5°	383.6	470.6	510.3	483.7	466.4	429.1	415.1	407.1	400.8	393.3	378.8
70°	308.1	372.5	413.4	406.3	392.2	372.5	362.3	356.8	350.5	344.3	331.7
72.5°	247.7	292.1	330.4	334.0	322.4	318.5	309.5	307.2	303.4	295.8	288.9
75°	164.3	194.9	221.6	231.9	236.6	240.5	236.6	235.8	235.0	228.7	224.8
77.5°	107.7	124.2	141.0	158.5	165.8	171.2	172.4	175.3	173.2	169.9	168.0
80°	82.5	86.5	98.2	113.2	125.0	129.7	132.8	134.4	133.6	132.8	129.7
82.5°	59.9	63.2	68.7	79.2	89.1	97.0	98.9	98.6	100.3	100.8	98.2
85°	32.2	33.0	34.6	36.2	41.7	50.3	52.7	54.2	55.8	55.8	51.1
87.5°	12.9	11.8	12.6	12.2	13.8	14.1	17.5	20.3	21.3	19.1	19.4
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9	20.1	21.3	22.5
95°	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1	47.3	48.6	49.8
97.5°	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9	82.8	83.7	84.6
100°	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3	107.4	108.4	109.5
102.5°	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5	135.1	135.7	136.4
105°	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9	176.3	176.6	177.0
107.5°	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1	224.3	224.5	224.7
110°	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1	254.4	254.8	255.1





TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4	285.6	285.8	286.0
115°	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3	332.8	333.3	333.8
117.5°	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5	379.9	380.2	380.5
120°	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9	409.9	411.0	412.0
122.5°	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6	440.3	441.1	441.8
125°	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3	486.8	487.3	487.9
127.5°	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5	530.6	531.7	532.8
130°	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2	559.6	561.0	562.4
132.5°	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0	588.4	589.8	591.2
135°	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9	632.0	633.0	634.1
137.5°	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6	672.5	673.3	674.2
140°	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7	700.6	701.5	702.4
142.5°	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4	726.3	727.1	728.0
145°	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4	765.8	766.1	766.5
147.5°	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5	801.1	801.7	802.3
150°	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8	825.2	825.5	825.9
152.5°	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9	845.3	845.8	846.3
155°	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4	876.4	876.4	876.4
157.5°	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3	903.1	902.9	902.7
160°	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2	919.9	919.5	919.2
162.5°	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2	934.8	934.3	933.8
165°	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6	954.1	953.6	953.1
167.5°	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1	969.4	968.7	968.0
170°	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9	978.2	977.5	976.8
172.5°	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7	985.1	984.4	983.7
175°	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9	992.2	991.6	990.9
177.5°	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9	995.4	994.8	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1804.6	1796.4	1790.8	1778.2	1770.0	1761.2	1752.4	1758.1	1757.4	1756.8	1756.8
5°	1744.1	1726.0	1709.5	1688.3	1674.9	1658.4	1645.8	1644.2	1647.4	1636.4	1630.1
7.5°	1684.0	1659.3	1635.9	1612.5	1587.7	1567.9	1555.4	1549.6	1541.6	1534.8	1527.8
10°	1641.9	1612.8	1590.0	1560.9	1534.2	1510.6	1495.7	1485.5	1480.0	1474.5	1464.3
12.5°	1598.5	1570.1	1541.0	1508.1	1482.7	1455.3	1444.1	1432.7	1422.1	1416.0	1402.0
15°	1535.0	1498.1	1467.4	1432.8	1404.5	1377.8	1362.1	1339.3	1336.1	1328.3	1314.1
17.5°	1471.3	1431.2	1389.0	1363.3	1331.4	1303.6	1279.7	1272.0	1249.5	1241.0	1228.8
20°	1421.0	1384.1	1351.9	1318.1	1271.7	1245.8	1226.9	1216.7	1198.6	1187.6	1179.7
22.5°	1377.6	1340.1	1302.8	1263.4	1225.2	1196.1	1182.3	1166.4	1156.5	1141.1	1132.6
25°	1315.7	1274.8	1230.0	1187.6	1160.1	1138.1	1116.1	1101.9	1087.8	1080.7	1065.0
27.5°	1243.7	1201.0	1159.1	1126.9	1093.1	1071.4	1051.5	1038.9	1021.9	1010.0	1001.3
30°	1204.1	1153.8	1117.6	1088.6	1045.3	1024.9	1010.0	994.3	981.7	969.1	960.5
32.5°	1158.2	1112.3	1078.0	1042.0	1008.9	986.5	967.2	953.4	942.7	930.7	922.1
35°	1086.2	1047.7	1012.3	976.2	951.8	929.0	906.2	894.4	884.2	873.2	865.4
37.5°	1021.1	985.1	951.5	917.2	887.0	868.5	850.1	841.1	827.3	819.9	811.9
40°	980.9	945.5	909.4	876.4	844.9	830.8	814.3	800.9	788.3	782.8	774.2
42.5°	936.9	901.5	871.0	835.5	809.7	790.5	775.3	760.7	751.2	743.2	738.3
45°	871.6	840.2	810.3	775.0	750.6	734.1	716.8	703.4	694.8	689.3	680.6
47.5°	808.3	776.9	746.5	715.7	692.1	673.3	656.0	646.7	635.2	628.5	622.6
50°	762.4	734.1	701.9	673.6	650.0	631.1	617.0	605.2	595.0	586.3	582.4
52.5°	720.3	690.1	662.3	635.8	611.0	589.6	576.7	564.3	556.6	546.7	542.2
55°	650.8	621.7	598.1	572.2	547.8	529.7	514.0	503.0	495.2	484.2	477.9
57.5°	585.5	559.5	531.3	508.8	483.7	468.4	455.4	440.5	430.9	422.2	416.1
60°	541.5	511.7	487.3	466.1	444.1	424.4	412.6	400.8	390.6	382.0	376.5
62.5°	495.6	469.5	446.4	423.3	403.2	386.1	372.4	362.5	353.5	348.0	342.5
65°	425.2	404.8	381.2	362.3	343.5	330.9	319.9	311.2	305.0	301.0	296.3
67.5°	360.4	340.6	320.0	301.5	288.9	279.3	272.1	264.7	261.6	256.5	253.4
70°	318.3	297.9	279.8	265.7	253.1	246.0	241.3	235.8	232.6	226.4	223.2
72.5°	272.4	257.6	244.6	233.0	222.9	216.5	210.5	203.7	198.7	191.8	188.6
75°	214.6	201.2	191.0	183.1	176.8	168.2	159.6	152.5	150.1	147.8	147.0
77.5°	158.9	150.4	143.0	136.4	128.6	122.3	120.4	118.8	118.4	117.1	117.1
80°	125.0	117.1	111.6	103.7	99.0	99.0	99.0	97.5	98.2	98.2	98.2
82.5°	92.9	85.7	82.7	79.9	78.9	79.5	79.5	79.9	79.4	80.6	80.0
85°	47.9	48.7	50.3	49.5	50.3	50.3	51.9	51.1	51.9	50.3	51.9
87.5°	19.2	21.4	22.5	23.6	24.7	24.5	25.3	25.4	26.2	26.3	26.4
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1	31.7	32.2	32.4
95°	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2	59.9	60.6	61.0
97.5°	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1	92.9	93.7	94.1
100°	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0	116.5	117.0	117.5
102.5°	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5	144.0	144.5	144.8
105°	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5	184.5	184.5	184.7
107.5°	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9	229.5	230.1	230.2
110°	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6	259.3	260.0	260.2



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3	289.1	290.0	290.3
115°	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4	333.6	333.8	333.8
117.5°	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0	378.9	378.9	378.6
120°	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3	409.2	409.0	408.7
122.5°	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1	439.6	439.2	438.7
125°	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7	485.0	484.3	483.6
127.5°	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8	529.8	528.9	528.0
130°	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8	560.1	559.4	558.4
132.5°	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9	589.0	588.2	587.3
135°	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5	632.8	632.1	631.6
137.5°	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1	675.4	674.6	673.9
140°	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1	703.9	703.7	703.1
142.5°	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4	730.2	730.0	729.5
145°	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0	768.8	768.6	768.2
147.5°	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5	805.5	805.5	804.9
150°	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0	828.0	828.0	827.5
152.5°	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5	848.8	849.1	848.8
155°	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6	879.3	880.0	879.7
157.5°	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5	905.2	905.9	905.8
160°	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4	921.3	922.1	922.2
162.5°	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4	936.3	937.2	937.0
165°	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4	955.4	956.5	956.4
167.5°	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8	970.8	971.9	971.9
170°	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2	979.4	980.6	980.6
172.5°	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8	985.9	986.9	986.9
175°	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9	992.9	994.0	993.9
177.5°	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1	995.9	996.7	996.7
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1749.3	1748.6	1749.3	1746.7	1749.3	1748.6	1749.3	1756.8	1756.8	1757.4	1758.1
5°	1627.7	1627.0	1624.6	1617.5	1624.6	1627.0	1627.7	1630.1	1636.4	1647.4	1644.2
7.5°	1521.6	1520.5	1513.6	1513.8	1513.6	1520.5	1521.6	1527.8	1534.8	1541.6	1549.6
10°	1458.8	1459.5	1450.1	1444.6	1450.1	1459.5	1458.8	1464.3	1474.5	1480.0	1485.5
12.5°	1397.8	1394.2	1386.6	1380.5	1386.6	1394.2	1397.8	1402.0	1416.0	1422.1	1432.7
15°	1317.3	1309.4	1290.6	1292.1	1290.6	1309.4	1317.3	1314.1	1328.3	1336.1	1339.3
17.5°	1222.5	1216.7	1216.4	1205.4	1216.4	1216.7	1222.5	1228.8	1241.0	1249.5	1272.0
20°	1167.2	1163.2	1164.8	1153.8	1164.8	1163.2	1167.2	1179.7	1187.6	1198.6	1216.7
22.5°	1123.8	1119.8	1113.2	1109.8	1113.2	1119.8	1123.8	1132.6	1141.1	1156.5	1166.4
25°	1060.3	1054.0	1047.7	1051.6	1047.7	1054.0	1060.3	1065.0	1080.7	1087.8	1101.9
27.5°	996.8	992.1	985.8	985.0	985.8	992.1	996.8	1001.3	1010.0	1021.9	1038.9
30°	956.5	951.8	948.7	944.7	948.7	951.8	956.5	960.5	969.1	981.7	994.3
32.5°	915.7	914.7	909.1	908.3	909.1	914.7	915.7	922.1	930.7	942.7	953.4
35°	862.2	857.5	855.9	856.7	855.9	857.5	862.2	865.4	873.2	884.2	894.4
37.5°	811.4	805.1	802.3	799.5	802.3	805.1	811.4	811.9	819.9	827.3	841.1
40°	775.0	768.7	767.1	765.5	767.1	768.7	775.0	774.2	782.8	788.3	800.9
42.5°	734.1	731.6	730.6	727.8	730.6	731.6	734.1	738.3	743.2	751.2	760.7
45°	678.3	677.5	672.8	674.4	672.8	677.5	678.3	680.6	689.3	694.8	703.4
47.5°	619.5	616.0	612.7	614.9	612.7	616.0	619.5	622.6	628.5	635.2	646.7
50°	579.3	577.7	570.6	572.2	570.6	577.7	579.3	582.4	586.3	595.0	605.2
52.5°	539.0	533.0	530.4	529.4	530.4	533.0	539.0	542.2	546.7	556.6	564.3
55°	472.4	465.3	462.1	460.6	462.1	465.3	472.4	477.9	484.2	495.2	503.0
57.5°	407.0	405.1	402.6	404.3	402.6	405.1	407.0	416.1	422.2	430.9	440.5
60°	368.6	368.6	368.6	367.8	368.6	368.6	368.6	376.5	382.0	390.6	400.8
62.5°	339.1	337.2	336.6	337.7	336.6	337.2	339.1	342.5	348.0	353.5	362.5
65°	294.0	293.2	290.0	289.2	290.0	293.2	294.0	296.3	301.0	305.0	311.2
67.5°	251.4	248.5	247.6	246.5	247.6	248.5	251.4	253.4	256.5	261.6	264.7
70°	219.3	217.7	213.0	213.8	213.0	217.7	219.3	223.2	226.4	232.6	235.8
72.5°	184.7	183.1	182.2	181.1	182.2	183.1	184.7	188.6	191.8	198.7	203.7
75°	146.2	145.4	144.6	147.8	144.6	145.4	146.2	147.0	147.8	150.1	152.5
77.5°	117.1	117.1	117.6	116.3	117.6	117.1	117.1	117.1	117.1	118.4	118.8
80°	98.2	98.2	97.5	97.5	97.5	98.2	98.2	98.2	98.2	98.2	97.5
82.5°	78.8	79.4	79.9	78.6	79.9	79.4	78.8	80.0	80.6	79.4	79.9
85°	51.9	51.1	52.7	51.9	52.7	51.1	51.9	51.9	50.3	51.9	51.1
87.5°	27.7	26.6	26.6	27.3	26.6	26.6	27.7	26.4	26.3	26.2	25.4
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	32.2	32.0	31.8	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1
95°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2
97.5°	94.0	94.0	93.9	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1
100°	117.8	118.1	118.5	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0
102.5°	144.7	144.6	144.6	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5
105°	185.0	185.4	185.7	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5
107.5°	230.0	229.8	229.6	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9
110°	259.8	259.5	259.1	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	290.3	290.2	290.1	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3
115°	333.6	333.4	333.2	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4
117.5°	378.2	377.7	377.2	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0
120°	408.4	408.0	407.7	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3
122.5°	438.2	437.7	437.2	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1
125°	482.9	482.2	481.5	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7
127.5°	527.2	526.4	525.6	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8
130°	557.2	556.0	554.8	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8
132.5°	586.4	585.4	584.5	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9
135°	631.2	630.9	630.5	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5
137.5°	673.3	672.6	672.0	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1
140°	701.8	700.6	699.4	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1
142.5°	728.5	727.6	726.6	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4
145°	767.5	766.8	766.1	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0
147.5°	803.9	802.8	801.8	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5
150°	826.4	825.4	824.3	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0
152.5°	847.9	847.0	846.1	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5
155°	878.5	877.3	876.1	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6
157.5°	904.9	903.9	902.9	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5
160°	921.5	920.8	920.1	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4
162.5°	935.9	934.8	933.7	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4
165°	955.2	953.9	952.7	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4
167.5°	970.8	969.8	968.7	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8
170°	979.4	978.2	977.0	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2
172.5°	985.6	984.4	983.2	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8
175°	992.7	991.5	990.2	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9
177.5°	995.7	994.7	993.8	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1752.4	1761.2	1770.0	1778.2	1790.8	1796.4	1804.6	1807.7	1817.2	1831.0	1842.3
5°	1645.8	1658.4	1674.9	1688.3	1709.5	1726.0	1744.1	1761.4	1781.8	1810.9	1836.8
7.5°	1555.4	1567.9	1587.7	1612.5	1635.9	1659.3	1684.0	1707.6	1736.8	1778.5	1819.8
10°	1495.7	1510.6	1534.2	1560.9	1590.0	1612.8	1641.9	1671.8	1707.9	1755.9	1805.4
12.5°	1444.1	1455.3	1482.7	1508.1	1541.0	1570.1	1598.5	1633.4	1674.6	1725.7	1785.2
15°	1362.1	1377.8	1404.5	1432.8	1467.4	1498.1	1535.0	1577.4	1617.5	1680.4	1752.7
17.5°	1279.7	1303.6	1331.4	1363.3	1389.0	1431.2	1471.3	1514.9	1564.2	1630.9	1710.3
20°	1226.9	1245.8	1271.7	1318.1	1351.9	1384.1	1421.0	1475.3	1520.8	1596.3	1678.8
22.5°	1182.3	1196.1	1225.2	1263.4	1302.8	1340.1	1377.6	1429.4	1485.6	1557.3	1646.8
25°	1116.1	1138.1	1160.1	1187.6	1230.0	1274.8	1315.7	1359.7	1419.5	1495.7	1592.4
27.5°	1051.5	1071.4	1093.1	1126.9	1159.1	1201.0	1243.7	1294.2	1358.3	1439.0	1537.0
30°	1010.0	1024.9	1045.3	1088.6	1117.6	1153.8	1204.1	1248.9	1308.6	1394.3	1498.1
32.5°	967.2	986.5	1008.9	1042.0	1078.0	1112.3	1158.2	1206.8	1267.8	1352.2	1458.4
35°	906.2	929.0	951.8	976.2	1012.3	1047.7	1086.2	1139.7	1201.7	1283.5	1388.0
37.5°	850.1	868.5	887.0	917.2	951.5	985.1	1021.1	1073.8	1132.3	1220.5	1316.3
40°	814.3	830.8	844.9	876.4	909.4	945.5	980.9	1027.3	1090.1	1172.7	1265.4
42.5°	775.3	790.5	809.7	835.5	871.0	901.5	936.9	980.7	1039.8	1123.6	1205.0
45°	716.8	734.1	750.6	775.0	810.3	840.2	871.6	913.3	973.8	1043.0	1115.3
47.5°	656.0	673.3	692.1	715.7	746.5	776.9	808.3	845.2	900.4	968.3	1017.0
50°	617.0	631.1	650.0	673.6	701.9	734.1	762.4	802.5	855.1	908.6	951.0
52.5°	576.7	589.6	611.0	635.8	662.3	690.1	720.3	754.7	802.3	852.6	886.3
55°	514.0	529.7	547.8	572.2	598.1	621.7	650.8	686.2	723.9	761.6	784.4
57.5°	455.4	468.4	483.7	508.8	531.3	559.5	585.5	613.1	648.0	676.4	691.3
60°	412.6	424.4	444.1	466.1	487.3	511.7	541.5	569.0	595.8	618.6	630.3
62.5°	372.4	386.1	403.2	423.3	446.4	469.5	495.6	518.7	542.3	562.0	570.0
65°	319.9	330.9	343.5	362.3	381.2	404.8	425.2	448.8	466.1	477.1	484.2
67.5°	272.1	279.3	288.9	301.5	320.0	340.6	360.4	378.8	393.3	400.8	407.1
70°	241.3	246.0	253.1	265.7	279.8	297.9	318.3	331.7	344.3	350.5	356.8
72.5°	210.5	216.5	222.9	233.0	244.6	257.6	272.4	288.9	295.8	303.4	307.2
75°	159.6	168.2	176.8	183.1	191.0	201.2	214.6	224.8	228.7	235.0	235.8
77.5°	120.4	122.3	128.6	136.4	143.0	150.4	158.9	168.0	169.9	173.2	175.3
80°	99.0	99.0	99.0	103.7	111.6	117.1	125.0	129.7	132.8	133.6	134.4
82.5°	79.5	79.5	78.9	79.9	82.7	85.7	92.9	98.2	100.8	100.3	98.6
85°	51.9	50.3	50.3	49.5	50.3	48.7	47.9	51.1	55.8	55.8	54.2
87.5°	25.3	24.5	24.7	23.6	22.5	21.4	19.2	19.4	19.1	21.3	20.3
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	30.6	30.0	28.7	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9
95°	58.6	57.9	56.5	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1
97.5°	91.3	90.5	89.5	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9
100°	115.5	114.9	114.1	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3
102.5°	143.0	142.5	141.3	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5
105°	184.5	184.5	183.0	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9
107.5°	228.4	227.8	227.2	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1
110°	257.9	257.2	256.9	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.5	286.6	286.6	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4
115°	333.2	333.1	333.4	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3
117.5°	379.0	379.0	379.5	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5
120°	409.5	409.7	410.6	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9
122.5°	440.5	441.0	441.4	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6
125°	486.4	487.1	487.4	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3
127.5°	531.8	532.7	533.1	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5
130°	561.4	562.1	562.7	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2
132.5°	590.7	591.5	591.9	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0
135°	634.2	634.9	635.0	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9
137.5°	676.8	677.5	677.1	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6
140°	704.3	704.4	704.3	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7
142.5°	730.5	730.7	730.4	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4
145°	769.2	769.3	768.8	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4
147.5°	805.5	805.5	805.0	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5
150°	828.0	828.0	827.6	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8
152.5°	848.3	848.0	847.8	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9
155°	877.9	877.2	877.1	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4
157.5°	903.8	903.0	902.9	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3
160°	919.5	918.7	918.7	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2
162.5°	934.5	933.7	933.5	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2
165°	953.3	952.3	952.3	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6
167.5°	968.7	967.6	967.5	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1
170°	977.0	975.7	975.7	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9
172.5°	983.7	982.6	982.6	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7
175°	990.9	989.8	989.8	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9
177.5°	994.2	993.4	993.4	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1846.1	1853.0	1861.8	1875.0	1885.1	1893.9	1895.8	1898.3	1904.6	1915.2	1923.4
5°	1858.0	1876.1	1905.2	1933.5	1964.1	1989.3	2012.9	2029.4	2045.1	2078.1	2104.8
7.5°	1854.3	1894.5	1940.1	1990.9	2042.3	2092.1	2138.3	2179.6	2220.8	2268.9	2323.8
10°	1851.7	1898.9	1960.2	2025.4	2097.0	2166.9	2234.5	2287.2	2348.5	2403.5	2473.4
12.5°	1839.8	1907.7	1981.0	2064.4	2152.3	2232.9	2321.9	2394.7	2464.8	2544.3	2625.6
15°	1824.2	1906.8	1999.5	2110.3	2243.9	2341.4	2432.6	2559.1	2645.6	2732.0	2848.4
17.5°	1795.8	1896.5	2012.4	2156.4	2267.8	2398.8	2536.0	2636.0	2752.5	2874.3	2979.6
20°	1773.1	1890.3	2019.9	2161.4	2303.7	2445.9	2578.8	2698.2	2818.5	2959.2	3045.6
22.5°	1750.5	1866.4	2001.1	2151.4	2304.3	2454.1	2604.5	2744.8	2880.1	3022.1	3132.4
25°	1702.4	1840.0	1986.1	2139.4	2290.3	2455.4	2634.6	2791.0	2958.4	3104.6	3209.1
27.5°	1653.7	1779.7	1925.3	2080.8	2248.5	2443.6	2654.4	2832.2	2999.9	3104.6	3137.4
30°	1609.7	1743.3	1876.9	2034.9	2216.4	2434.1	2658.1	2861.7	2999.3	3044.8	3011.0
32.5°	1565.0	1686.1	1818.4	1980.2	2173.0	2410.9	2663.2	2844.1	2926.9	2892.1	2754.5
35°	1486.3	1595.5	1723.6	1885.5	2107.2	2398.0	2642.4	2765.0	2744.6	2548.1	2288.7
37.5°	1402.0	1491.0	1609.7	1779.0	2039.0	2346.9	2553.1	2571.2	2394.4	2092.7	1793.1
40°	1335.4	1415.5	1537.4	1714.2	1986.1	2296.6	2463.2	2390.1	2115.8	1780.2	1530.3
42.5°	1270.6	1338.2	1455.6	1646.3	1935.8	2228.1	2329.3	2170.1	1853.6	1536.3	1309.0
45°	1160.9	1224.5	1342.4	1538.1	1832.9	2097.0	2083.6	1806.9	1490.2	1234.8	1046.1
47.5°	1056.8	1112.5	1223.1	1422.9	1712.0	1900.5	1775.5	1481.1	1212.4	1007.5	872.9
50°	983.2	1038.3	1148.3	1345.6	1615.2	1752.7	1574.3	1290.6	1044.6	874.8	767.9
52.5°	912.8	966.6	1067.2	1259.4	1498.2	1580.4	1388.8	1125.8	920.7	774.2	682.4
55°	814.3	855.1	945.5	1129.4	1307.9	1326.7	1132.6	912.5	743.5	641.4	578.5
57.5°	713.8	749.0	838.3	984.8	1109.9	1100.2	916.1	725.8	612.0	536.0	490.4
60°	648.4	683.0	761.6	887.4	981.7	948.7	779.7	626.4	529.0	473.2	437.0
62.5°	587.4	614.5	688.0	779.8	847.7	810.3	666.5	539.6	462.3	415.3	386.7
65°	499.1	521.1	580.0	628.0	665.7	629.6	510.1	422.1	366.3	333.3	313.6
67.5°	415.1	429.1	466.4	483.7	510.3	470.6	383.6	324.6	292.9	265.0	251.4
70°	362.3	372.5	392.2	406.3	413.4	372.5	308.1	264.9	238.1	218.5	209.9
72.5°	309.5	318.5	322.4	334.0	330.4	292.1	247.7	213.3	194.1	180.8	169.6
75°	236.6	240.5	236.6	231.9	221.6	194.9	164.3	147.0	132.8	126.5	122.6
77.5°	172.4	171.2	165.8	158.5	141.0	124.2	107.7	101.9	95.7	92.4	91.0
80°	132.8	129.7	125.0	113.2	98.2	86.5	82.5	78.6	76.2	72.3	71.5
82.5°	98.9	97.0	89.1	79.2	68.7	63.2	59.9	58.5	56.1	54.1	53.9
85°	52.7	50.3	41.7	36.2	34.6	33.0	32.2	32.2	29.1	28.3	28.3
87.5°	17.5	14.1	13.8	12.2	12.6	11.8	12.9	12.1	11.9	12.7	11.6
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1
95°	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2
97.5°	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1
100°	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0
102.5°	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5
105°	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5
107.5°	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9
110°	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6





TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3
115°	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4
117.5°	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0
120°	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3
122.5°	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1
125°	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7
127.5°	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8
130°	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8
132.5°	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9
135°	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5
137.5°	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1
140°	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1
142.5°	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4
145°	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0
147.5°	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5
150°	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0
152.5°	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5
155°	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6
157.5°	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5
160°	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4
162.5°	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4
165°	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4
167.5°	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8
170°	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2
172.5°	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8
175°	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9
177.5°	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0	1836.0
2.5°	1936.6	1936.6	1939.1	1948.6	1949.8	1958.0	1955.5
5°	2128.4	2143.3	2148.8	2172.4	2186.6	2192.9	2180.3
7.5°	2362.9	2405.1	2425.0	2449.7	2471.6	2478.2	2461.0
10°	2534.0	2578.0	2614.9	2637.7	2658.9	2673.1	2691.2
12.5°	2699.3	2753.4	2788.5	2820.7	2842.5	2860.5	2863.4
15°	2879.0	2960.7	3022.8	3068.4	3091.2	3103.0	3098.3
17.5°	3060.2	3136.0	3180.2	3226.7	3258.3	3259.9	3260.8
20°	3162.7	3236.6	3287.7	3322.3	3357.7	3356.1	3363.9
22.5°	3231.3	3289.4	3328.6	3353.7	3365.8	3359.9	3361.4
25°	3263.3	3280.6	3273.6	3233.5	3223.3	3186.3	3192.6
27.5°	3098.0	3016.2	2931.7	2822.9	2737.1	2668.5	2672.0
30°	2873.5	2728.9	2563.8	2425.5	2301.3	2266.7	2192.9
32.5°	2559.7	2342.8	2149.5	2020.6	1914.0	1885.1	1820.6
35°	2027.8	1817.2	1618.3	1498.8	1451.7	1385.7	1384.9
37.5°	1576.2	1390.7	1285.5	1195.9	1148.9	1109.0	1105.1
40°	1325.9	1181.3	1101.9	1037.5	991.1	961.2	954.2
42.5°	1151.1	1034.2	959.8	919.9	884.2	868.8	857.3
45°	940.0	861.4	809.5	773.4	756.9	745.1	738.8
47.5°	786.3	733.6	698.3	674.2	660.8	648.4	651.7
50°	702.7	659.4	633.5	610.7	600.5	591.8	592.6
52.5°	635.4	596.6	575.6	559.1	546.4	540.3	537.3
55°	539.2	514.8	493.6	481.8	474.7	466.1	463.7
57.5°	459.9	441.1	423.8	410.4	408.7	400.4	401.5
60°	407.1	391.4	377.3	370.2	364.7	357.6	360.0
62.5°	363.7	350.5	337.7	331.8	326.3	321.1	322.2
65°	297.9	285.3	277.4	274.3	271.9	269.6	267.2
67.5°	237.4	229.7	224.8	218.0	213.2	212.4	210.0
70°	199.6	189.4	180.8	172.1	169.8	169.0	169.8
72.5°	160.0	153.6	151.2	147.0	146.5	144.5	145.9
75°	120.3	117.9	116.3	113.2	113.2	113.2	113.2
77.5°	88.7	87.2	86.3	85.7	84.9	83.8	83.6
80°	69.2	68.4	66.8	66.8	66.0	66.8	66.0
82.5°	52.2	52.0	50.5	50.5	49.7	49.2	49.7
85°	26.7	25.9	27.5	25.9	26.7	25.2	26.7
87.5°	11.7	11.9	11.3	11.4	10.8	12.2	11.0
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	259.3	260.0	260.2	259.8	259.5	259.1	258.8



TEST NUMBER: P332373

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)