

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332375-830

Luminaire Tested: **S123RDIP-S1165D805U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332375-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7154.3 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.4
10°-20°	477.3	6.7
20°-30°	687.3	9.6
30°-40°	774.2	10.8
40°-50°	740.6	10.4
50°-60°	606.5	8.5
60°-70°	409.2	5.7
70°-80°	205.9	2.9
80°-90°	57.2	0.8
90°-100°	36.1	0.5
100°-110°	171.9	2.4
110°-120°	412.8	5.8
120°-130°	525.7	7.3
130°-140°	561.7	7.9
140°-150°	525.2	7.3
150°-160°	423.7	5.9
160°-170°	273.4	3.8
170°-180°	94.2	1.3
0°-30°	1336.1	18.7
0°-40°	2110.3	29.5
0°-60°	3457.4	48.3
0°-90°	4129.7	57.7
90°-120°	620.7	8.7
90°-150°	2233.3	31.2
90°-180°	3025.0	42.3
0°-180°	7154.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	8	18	21	22	6
95°	45	17	23	28	28	56
105°	220	224	161	38	32	233
115°	412	416	423	430	433	406
125°	581	586	590	591	592	518
135°	723	727	730	732	730	556
145°	834	839	841	842	842	522
155°	919	918	918	921	917	423
165°	969	967	966	971	967	274
175°	992	988	989	993	988	94
180°	992	992	992	992	992	



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	26.0	23.5	20.9	18.3	17.2	17.6	18.1	18.5	18.9	18.9
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	13.7	13.3	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.9	19.9
95°	45.0	38.3	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.3	87.4	84.4	81.3	78.3	70.9	59.1	47.3	35.5	23.8	25.1
100°	124.5	127.8	131.1	134.3	137.6	126.5	100.9	75.4	49.9	24.3	25.6
102.5°	163.4	165.8	168.1	170.5	172.9	160.1	132.2	104.2	76.3	48.4	44.4
105°	219.6	221.4	223.2	225.0	226.8	220.4	205.6	190.9	176.1	161.4	132.4
107.5°	278.8	280.3	281.7	283.1	284.6	286.4	288.8	291.2	293.4	295.8	274.6
110°	318.3	319.6	320.9	322.3	323.6	325.1	327.0	328.8	330.5	332.3	327.0



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.1	357.2	358.4	359.6	360.8	362.2	364.1	365.9	367.7	369.5	369.6
115°	411.9	412.9	413.9	414.9	415.8	417.1	418.6	420.0	421.5	423.0	424.6
117.5°	466.0	467.2	468.4	469.7	470.8	471.8	472.6	473.3	474.1	474.9	476.2
120°	499.6	501.1	502.6	504.0	505.5	506.5	507.0	507.5	507.9	508.4	509.7
122.5°	533.8	535.0	536.2	537.4	538.7	539.5	540.2	540.8	541.4	542.1	543.0
125°	580.7	581.9	583.2	584.6	585.9	586.9	587.6	588.1	588.8	589.5	589.8
127.5°	626.0	627.4	628.7	630.0	631.3	632.4	633.1	634.0	634.7	635.5	636.0
130°	654.3	655.6	657.0	658.3	659.6	660.5	661.2	661.9	662.5	663.2	663.8
132.5°	681.5	682.8	684.1	685.4	686.7	687.6	688.2	688.6	689.2	689.8	690.4
135°	722.8	723.9	724.8	725.9	726.8	727.6	728.3	729.0	729.6	730.3	730.8
137.5°	758.3	759.5	760.7	762.0	763.2	764.0	764.4	764.8	765.1	765.4	766.3
140°	781.8	782.8	783.8	784.8	785.8	786.5	787.0	787.5	788.0	788.4	789.1
142.5°	803.6	804.6	805.6	806.6	807.6	808.3	808.8	809.3	809.7	810.3	810.8
145°	834.2	835.3	836.4	837.5	838.8	839.4	839.8	840.1	840.5	840.7	841.1
147.5°	862.9	863.7	864.4	865.2	865.9	866.5	866.8	867.0	867.4	867.7	868.1
150°	880.5	881.1	881.6	882.0	882.5	883.0	883.3	883.6	883.9	884.3	884.6
152.5°	896.5	896.7	896.9	897.2	897.4	897.6	897.8	898.0	898.2	898.4	899.0
155°	918.9	918.6	918.2	917.9	917.6	917.5	917.7	917.8	917.9	918.1	919.0
157.5°	936.2	936.2	936.2	936.1	936.1	936.0	935.9	935.8	935.6	935.4	936.4
160°	946.9	946.7	946.6	946.4	946.2	946.0	945.9	945.7	945.6	945.4	946.4
162.5°	956.9	956.5	956.0	955.6	955.2	954.9	954.7	954.6	954.4	954.2	955.4
165°	969.0	968.5	968.0	967.5	967.0	966.7	966.6	966.4	966.2	966.0	967.3
167.5°	978.5	977.8	977.1	976.5	975.8	975.4	975.4	975.4	975.4	975.4	976.8
170°	983.7	983.1	982.4	981.8	981.1	980.8	980.8	980.8	980.8	980.8	982.1
172.5°	987.2	986.5	985.7	984.9	984.1	983.8	983.9	984.0	984.2	984.3	985.6
175°	991.8	991.0	990.2	989.4	988.5	988.3	988.4	988.5	988.7	988.9	990.0
177.5°	993.0	992.4	991.7	991.1	990.4	990.1	990.2	990.4	990.5	990.6	991.7
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	18.7	18.6	18.4	18.3	18.1	17.8	17.6	17.4
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	20.9	22.0	23.1	23.7	23.8	24.0	24.2	24.5
95°	25.2	26.3	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.4	27.6	28.9	29.7	29.9	30.1	30.2	30.3
100°	27.0	28.3	29.6	30.3	30.4	30.6	30.8	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.6
105°	103.4	74.5	45.4	31.1	31.5	31.8	32.1	32.4
107.5°	253.3	232.1	210.8	189.2	167.4	145.5	123.7	101.8
110°	321.5	316.1	310.8	296.3	272.9	249.5	226.0	202.6



TEST NUMBER: P332375-830

CATALOG NUMBER: S123RDIP-S1165D805U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.7	369.8	369.9	367.4	362.5	357.5	352.6	347.7
115°	426.2	427.9	429.5	430.6	431.3	432.0	432.6	433.3
117.5°	477.5	478.8	480.0	480.8	481.0	481.1	481.2	481.4
120°	511.0	512.4	513.7	514.3	514.3	514.3	514.3	514.3
122.5°	543.8	544.8	545.7	546.2	546.4	546.5	546.7	546.8
125°	590.1	590.5	590.8	591.2	591.4	591.8	592.1	592.5
127.5°	636.5	637.1	637.5	637.6	637.3	637.1	636.7	636.4
130°	664.5	665.2	665.8	666.0	665.6	665.3	665.0	664.7
132.5°	691.0	691.6	692.3	692.4	692.0	691.5	691.1	690.6
135°	731.2	731.7	732.2	732.2	731.7	731.2	730.8	730.3
137.5°	767.0	767.8	768.6	768.8	768.5	768.2	767.9	767.5
140°	789.8	790.4	791.1	791.3	790.9	790.6	790.2	789.9
142.5°	811.3	811.8	812.4	812.4	811.9	811.4	811.1	810.6
145°	841.4	841.8	842.1	842.3	842.3	842.3	842.3	842.3
147.5°	868.4	868.7	869.0	868.8	868.1	867.3	866.6	865.8
150°	884.9	885.2	885.5	885.5	885.0	884.5	884.0	883.5
152.5°	899.6	900.1	900.8	900.7	899.9	899.2	898.4	897.7
155°	919.8	920.6	921.4	921.3	920.4	919.4	918.4	917.4
157.5°	937.4	938.3	939.3	939.1	937.9	936.6	935.4	934.1
160°	947.3	948.4	949.3	949.2	948.1	947.0	945.8	944.7
162.5°	956.5	957.6	958.7	958.8	957.7	956.7	955.7	954.7
165°	968.7	970.0	971.3	971.4	970.3	969.0	967.9	966.8
167.5°	978.1	979.4	980.7	980.7	979.4	978.1	976.8	975.4
170°	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8
172.5°	986.9	988.3	989.6	989.5	988.1	986.7	985.1	983.7
175°	991.2	992.3	993.4	993.3	992.1	990.8	989.5	988.2
177.5°	992.8	993.8	994.9	994.8	993.4	992.1	990.8	989.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8

(END OF REPORT)