

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332268-830

Luminaire Tested: **S123RDIP-S340D1195U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332268-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5089.9 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.0
10°-20°	141.5	2.8
20°-30°	203.7	4.0
30°-40°	229.5	4.5
40°-50°	219.5	4.3
50°-60°	179.8	3.5
60°-70°	121.3	2.4
70°-80°	61.0	1.2
80°-90°	20.3	0.4
90°-100°	90.8	1.8
100°-110°	271.8	5.3
110°-120°	462.3	9.1
120°-130°	608.1	11.9
130°-140°	683.5	13.4
140°-150°	671.9	13.2
150°-160°	565.6	11.1
160°-170°	376.5	7.4
170°-180°	131.8	2.6
0°-30°	396.1	7.8
0°-40°	625.5	12.3
0°-60°	1024.8	20.1
0°-90°	1227.4	24.1
90°-120°	825.0	16.2
90°-150°	2788.5	54.8
90°-180°	3863.0	75.9
0°-180°	5089.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	12	26	31	33	5
95°	65	72	81	85	85	73
105°	246	249	258	259	261	264
115°	465	468	467	468	467	460
125°	681	684	682	678	674	607
135°	884	890	889	885	883	681
145°	1072	1074	1078	1076	1072	669
155°	1228	1228	1229	1232	1225	565
165°	1337	1334	1334	1340	1333	377
175°	1391	1387	1386	1392	1385	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.7	8.3	7.9	7.5	7.2	7.3	7.9	8.6	9.2	9.8	9.9
90°	1.1	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2
92.5°	26.5	28.2	29.8	31.5	33.1	34.9	36.7	38.5	40.2	42.0	42.8
95°	64.7	66.4	68.1	69.7	71.4	73.2	75.2	77.1	79.1	81.1	82.0
97.5°	114.8	116.0	117.3	118.6	119.8	121.2	122.6	124.0	125.4	126.8	127.9
100°	148.9	150.4	151.8	153.4	154.8	156.1	157.3	158.5	159.8	161.0	161.7
102.5°	188.3	189.3	190.1	191.0	191.9	193.1	194.7	196.3	197.9	199.5	200.3
105°	246.4	246.9	247.4	247.9	248.4	249.7	251.8	254.1	256.3	258.4	258.4
107.5°	313.9	314.1	314.4	314.7	315.0	315.7	316.5	317.4	318.2	319.1	319.9
110°	355.9	356.4	356.8	357.4	357.9	358.4	358.8	359.3	359.8	360.3	361.3



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.7	400.0	400.3	400.6	400.9	401.1	401.1	401.2	401.3	401.4	402.7
115°	465.4	466.2	466.8	467.6	468.3	468.4	468.0	467.5	467.0	466.6	466.7
117.5°	531.6	532.1	532.5	533.0	533.5	533.5	532.8	532.2	531.6	530.9	530.8
120°	572.8	574.2	575.7	577.1	578.6	578.7	577.5	576.3	575.0	573.8	573.6
122.5°	615.7	616.7	617.8	618.9	620.0	620.2	619.5	618.9	618.3	617.6	617.0
125°	681.2	681.9	682.6	683.3	684.1	684.2	683.7	683.2	682.8	682.3	681.3
127.5°	741.6	743.2	744.7	746.3	747.8	748.4	747.8	747.2	746.8	746.2	744.9
130°	781.9	783.8	785.8	787.8	789.7	790.3	789.6	788.8	788.2	787.4	786.5
132.5°	822.2	824.2	826.1	828.0	830.0	830.8	830.2	829.6	829.1	828.6	827.4
135°	883.7	885.2	886.6	888.2	889.6	890.2	889.9	889.8	889.5	889.2	888.3
137.5°	940.8	941.9	943.1	944.3	945.6	946.5	947.2	947.7	948.4	949.0	948.0
140°	980.1	981.4	982.6	983.8	985.0	985.7	986.0	986.2	986.5	986.7	986.5
142.5°	1016.1	1017.3	1018.5	1019.7	1021.0	1021.7	1022.2	1022.7	1023.0	1023.5	1023.2
145°	1072.1	1072.6	1073.1	1073.6	1074.0	1074.7	1075.4	1076.1	1076.9	1077.6	1077.3
147.5°	1121.2	1122.1	1122.9	1123.8	1124.7	1125.5	1126.1	1126.8	1127.5	1128.2	1128.2
150°	1155.4	1155.8	1156.3	1156.8	1157.3	1157.8	1158.3	1158.8	1159.2	1159.7	1159.7
152.5°	1183.4	1184.1	1184.8	1185.4	1186.1	1186.6	1186.8	1187.2	1187.5	1187.8	1188.2
155°	1227.7	1227.7	1227.7	1227.7	1227.7	1227.8	1228.0	1228.2	1228.5	1228.7	1229.7
157.5°	1265.3	1265.0	1264.7	1264.4	1264.1	1264.0	1264.3	1264.5	1264.7	1264.9	1265.9
160°	1288.9	1288.5	1288.0	1287.5	1287.0	1286.8	1286.8	1286.8	1286.8	1286.8	1288.0
162.5°	1309.9	1309.3	1308.6	1308.0	1307.3	1307.0	1307.2	1307.4	1307.6	1307.8	1309.0
165°	1337.2	1336.4	1335.7	1334.9	1334.3	1333.9	1333.9	1333.9	1333.9	1333.9	1335.3
167.5°	1358.9	1357.8	1356.9	1355.9	1354.9	1354.5	1354.7	1354.9	1355.1	1355.3	1356.8
170°	1371.1	1370.1	1369.1	1368.2	1367.2	1366.7	1366.7	1366.7	1366.7	1366.7	1368.4
172.5°	1380.7	1379.8	1378.8	1377.8	1376.9	1376.4	1376.4	1376.4	1376.4	1376.4	1377.9
175°	1390.8	1389.9	1388.8	1387.9	1387.0	1386.4	1386.4	1386.4	1386.4	1386.4	1387.9
177.5°	1395.0	1394.2	1393.5	1392.6	1391.9	1391.5	1391.5	1391.5	1391.5	1391.5	1392.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	10.1	10.2	10.3	10.4	10.4	10.4	10.5	10.5
90°	28.3	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	43.6	44.4	45.1	45.4	45.1	44.9	44.5	44.2
95°	82.9	84.0	84.9	85.4	85.4	85.4	85.4	85.4
97.5°	129.0	130.2	131.3	131.8	131.7	131.6	131.5	131.4
100°	162.4	163.2	163.9	164.5	165.0	165.5	166.0	166.5
102.5°	201.0	201.7	202.5	202.7	202.6	202.6	202.5	202.4
105°	258.4	258.4	258.4	258.7	259.2	259.7	260.1	260.6
107.5°	320.7	321.5	322.3	322.4	322.2	321.9	321.6	321.3
110°	362.2	363.3	364.2	364.4	363.9	363.4	363.0	362.5



TEST NUMBER: P332268-830

CATALOG NUMBER: S123RDIP-S340D1195U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.8	405.0	406.1	406.7	406.6	406.5	406.4	406.3
115°	467.0	467.2	467.5	467.5	467.2	467.0	466.7	466.6
117.5°	530.8	530.7	530.7	530.4	529.7	529.0	528.3	527.6
120°	573.3	573.2	572.9	572.5	572.0	571.6	571.1	570.5
122.5°	616.4	615.8	615.1	614.4	613.8	613.1	612.4	611.7
125°	680.3	679.4	678.3	677.4	676.5	675.4	674.5	673.5
127.5°	743.5	742.2	740.7	739.5	738.4	737.3	736.1	735.1
130°	785.4	784.5	783.5	782.1	780.4	778.7	777.0	775.3
132.5°	826.2	825.1	823.9	822.7	821.3	820.0	818.7	817.4
135°	887.3	886.3	885.3	884.6	884.1	883.6	883.2	882.7
137.5°	947.0	945.9	944.9	944.0	943.0	942.2	941.2	940.3
140°	986.2	986.0	985.7	984.8	983.1	981.4	979.7	978.0
142.5°	1023.0	1022.8	1022.6	1021.7	1020.4	1019.1	1017.9	1016.5
145°	1077.1	1076.9	1076.7	1076.0	1075.1	1074.0	1073.1	1072.1
147.5°	1128.2	1128.2	1128.2	1127.5	1126.0	1124.5	1123.0	1121.6
150°	1159.7	1159.7	1159.7	1159.0	1157.5	1156.1	1154.6	1153.2
152.5°	1188.5	1188.9	1189.3	1188.9	1187.6	1186.4	1185.1	1183.8
155°	1230.7	1231.6	1232.7	1232.3	1230.6	1228.9	1227.2	1225.4
157.5°	1266.9	1267.9	1268.9	1268.8	1267.4	1266.0	1264.7	1263.3
160°	1289.2	1290.4	1291.7	1291.8	1290.8	1289.8	1288.8	1287.9
162.5°	1310.2	1311.5	1312.7	1312.5	1310.9	1309.4	1307.8	1306.3
165°	1336.8	1338.2	1339.7	1339.5	1337.8	1336.1	1334.5	1332.8
167.5°	1358.3	1359.8	1361.3	1361.3	1359.8	1358.3	1356.8	1355.3
170°	1370.1	1371.9	1373.6	1373.6	1371.9	1370.1	1368.4	1366.7
172.5°	1379.4	1380.9	1382.4	1382.3	1380.5	1378.8	1377.1	1375.5
175°	1389.3	1390.8	1392.2	1392.1	1390.4	1388.7	1387.0	1385.3
177.5°	1393.8	1395.0	1396.1	1396.0	1394.7	1393.3	1391.9	1390.6
180°	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1	1394.1

(END OF REPORT)