

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332376

Luminaire Tested: **S123RDIP-S1165D805U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332376  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D805U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7139.0 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	59	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	60	51	45	66	56	49	43	50	44	40	44	39	36	38	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	33	28	49	38	32	27	35	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.0	2.5
10°-20°	506.4	7.1
20°-30°	729.2	10.2
30°-40°	821.3	11.5
40°-50°	785.8	11.0
50°-60°	643.5	9.0
60°-70°	434.1	6.1
70°-80°	218.4	3.1
80°-90°	60.7	0.9
90°-100°	64.8	0.9
100°-110°	194.1	2.7
110°-120°	330.1	4.6
120°-130°	434.2	6.1
130°-140°	488.0	6.8
140°-150°	479.7	6.7
150°-160°	403.8	5.7
160°-170°	268.8	3.8
170°-180°	94.1	1.3
0°-30°	1417.6	19.9
0°-40°	2238.9	31.4
0°-60°	3668.1	51.4
0°-90°	4381.4	61.4
90°-120°	589.0	8.3
90°-150°	1990.8	27.9
90°-180°	2758.0	38.6
0°-180°	7139.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	9	19	22	24	7
95°	46	52	58	61	61	52
105°	176	178	184	185	186	188
115°	332	334	333	334	333	329
125°	486	488	487	484	481	434
135°	631	635	635	632	630	486
145°	765	767	769	768	765	478
155°	876	876	877	880	875	403
165°	955	952	952	956	952	269
175°	993	990	990	994	989	94
180°	995	995	995	995	995	



TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.3	27.6	24.9	22.2	19.4	18.3	18.7	19.2	19.6	20.1	20.0
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	18.9	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6
95°	46.1	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6
97.5°	81.9	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3
100°	106.3	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5
102.5°	134.5	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0
105°	175.9	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5
107.5°	224.1	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4
110°	254.1	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9



TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	285.4	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5
115°	332.3	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2
117.5°	379.5	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0
120°	408.9	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5
122.5°	439.6	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5
125°	486.3	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4
127.5°	529.5	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8
130°	558.2	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4
132.5°	587.0	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7
135°	630.9	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2
137.5°	671.6	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8
140°	699.7	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.4	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5
145°	765.4	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2
147.5°	800.5	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5
150°	824.8	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0
152.5°	844.9	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3
155°	876.4	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9
157.5°	903.3	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8
160°	920.2	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5
162.5°	935.2	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5
165°	954.6	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3
167.5°	970.1	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7
170°	978.9	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0
172.5°	985.7	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7
175°	992.9	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9
177.5°	995.9	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	19.8	19.7	19.5	19.4	19.2	18.9	18.7	18.5
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.1	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.2	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.1	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.0	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	143.5	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	228.9	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	258.6	259.3	260.0	260.2	259.8	259.5	259.1	258.8





TEST NUMBER: P332376

CATALOG NUMBER: S123RDIP-S1165D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.3	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	379.0	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.3	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	440.1	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.7	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	530.8	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.8	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.9	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	633.5	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	676.1	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	704.1	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.4	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	769.0	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.5	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	878.6	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	904.5	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	920.4	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	935.4	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	954.4	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	984.8	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	991.9	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.1	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)