

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832039

Luminaire Tested: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832039
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U835-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4996.5 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	37	37	37	30	
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	32	32	32	32	26	
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	28	22	
3	78	70	63	58	70	63	57	53	50	46	43	38	36	33	27	26	24	24	24	24	20	
4	72	62	55	49	64	56	50	45	45	40	37	34	31	29	25	23	22	22	22	22	17	
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	19	19	19	15	
6	61	50	42	37	55	45	39	34	36	32	28	28	25	23	21	19	17	17	17	17	14	
7	57	45	38	32	51	41	35	30	33	28	25	26	23	20	19	17	15	15	15	15	13	
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	14	14	14	12	
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	16	14	13	13	13	13	11	
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12	12	12	12	10	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11958	11958	11958	11958	11958
5°	14199	13746	12034	9728	9031
10°	12865	13962	11973	7794	6686
15°	8857	11972	11847	6370	5289
20°	6161	9216	11609	5371	4648
25°	4696	7024	11263	4774	4284
30°	4088	5615	10829	4432	3969
35°	3753	4737	10217	4144	3681
40°	3424	4231	9414	3863	3417
45°	3092	3870	8549	3596	3154
50°	2807	3570	7529	3332	2830
55°	2539	3278	6548	3078	2428
60°	2275	2982	5688	2794	2295
65°	2099	2646	4895	2511	2170
70°	1706	2285	4271	2272	1762
75°	1497	1817	3618	1884	1551
80°	1358	1537	2963	1581	1469
85°	1235	1346	2248	1433	1346

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 9021 cd/sqm



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	2.0
10°-20°	234.3	4.7
20°-30°	268.8	5.4
30°-40°	265.0	5.3
40°-50°	233.7	4.7
50°-60°	179.8	3.6
60°-70°	118.2	2.4
70°-80°	57.4	1.1
80°-90°	17.2	0.3
90°-100°	81.8	1.6
100°-110°	247.6	5.0
110°-120°	421.5	8.4
120°-130°	554.5	11.1
130°-140°	623.3	12.5
140°-150°	612.7	12.3
150°-160°	515.9	10.3
160°-170°	343.4	6.9
170°-180°	120.3	2.4
0°-30°	604.4	12.1
0°-40°	869.4	17.4
0°-60°	1282.9	25.7
0°-90°	1475.6	29.5
90°-120°	750.9	15.0
90°-150°	2541.3	50.9
90°-180°	3521.0	70.5
0°-180°	4996.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1111	1111	1111	1111	1111	
5°	1314	1272	1114	900	836	120
15°	795	1074	1063	572	475	224
25°	395	591	948	402	361	187
35°	286	360	778	315	280	178
45°	203	254	562	236	207	158
55°	135	175	349	164	129	121
65°	82	104	192	99	85	81
75°	36	44	87	45	37	39
85°	10	11	18	12	11	11
90°	30	24	1	24	30	15
95°	78	74	59	74	78	78
105°	238	236	225	236	238	252
115°	425	425	424	425	425	421
125°	614	622	621	622	614	549
135°	805	810	806	810	805	619
145°	977	982	977	982	977	610
155°	1117	1120	1119	1120	1117	515
165°	1215	1216	1219	1216	1215	343
175°	1263	1264	1268	1264	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1231.2	1227.3	1223.4	1222.3	1221.2	1217.5	1213.9	1205.7	1197.5	1189.0	1180.6
5°	1314.1	1314.5	1315.0	1313.8	1312.7	1307.9	1303.1	1293.1	1283.1	1272.2	1261.2
7.5°	1288.6	1295.9	1303.1	1304.5	1305.9	1309.5	1313.2	1310.9	1308.6	1304.5	1300.4
10°	1177.0	1176.5	1176.1	1184.3	1192.5	1216.8	1241.2	1253.7	1266.2	1277.4	1288.6
12.5°	994.8	995.5	996.1	1023.0	1049.9	1072.9	1095.9	1127.8	1159.7	1194.1	1228.4
15°	794.8	806.0	817.1	841.1	865.0	899.6	934.2	977.0	1019.8	1074.3	1128.7
17.5°	652.7	657.5	662.3	685.3	708.3	741.1	773.9	822.4	870.9	941.0	1011.2
20°	537.9	542.3	546.6	563.2	579.8	611.3	642.7	688.9	735.2	804.6	874.1
22.5°	449.1	457.5	466.0	477.1	488.3	511.1	533.8	581.0	628.1	691.4	754.7
25°	395.4	399.2	403.1	412.7	422.2	444.1	466.0	497.2	528.4	591.4	654.5
27.5°	358.9	360.1	361.2	368.3	375.3	389.4	403.6	432.5	461.4	513.3	565.3
30°	328.9	330.9	333.0	338.4	343.9	354.1	364.4	384.9	405.4	451.8	498.3
32.5°	305.6	306.8	307.9	312.5	317.0	324.5	332.0	348.2	364.4	399.9	435.4
35°	285.6	285.8	286.0	289.5	292.9	300.2	307.5	320.9	334.3	360.5	386.7
37.5°	262.8	264.4	266.0	268.5	271.0	277.4	283.8	294.7	305.6	327.3	348.9
40°	243.7	245.1	246.4	249.4	252.3	257.3	262.4	272.4	282.4	301.1	319.8
42.5°	224.6	225.5	226.4	229.3	232.3	238.4	244.6	252.6	260.5	276.0	291.5
45°	203.1	205.4	207.7	210.9	214.1	219.3	224.6	232.8	241.0	254.2	267.4
47.5°	185.4	186.5	187.7	190.4	193.1	199.5	205.9	213.2	220.5	232.8	245.1
50°	167.6	168.1	168.5	171.0	173.5	179.2	184.9	193.4	201.8	213.2	224.6
52.5°	150.8	151.9	153.0	155.5	158.1	161.9	165.8	174.5	183.1	194.3	205.4
55°	135.3	136.0	136.6	138.5	140.3	144.8	149.4	156.9	164.4	174.7	184.9
57.5°	120.7	121.6	122.5	123.9	125.3	129.4	133.5	140.1	146.7	156.9	167.2
60°	105.7	106.8	107.9	109.5	111.1	114.3	117.5	123.4	129.4	138.5	147.6
62.5°	94.7	95.0	95.2	96.6	97.9	100.2	102.5	107.3	112.0	121.2	130.3
65°	82.4	83.1	83.8	84.5	85.2	87.0	88.8	92.9	97.0	103.9	110.7
67.5°	69.7	70.4	71.1	72.2	73.3	74.9	76.5	79.3	82.0	88.4	94.7
70°	54.2	54.2	54.2	56.0	57.8	60.6	63.3	65.4	67.4	72.6	77.9
72.5°	44.2	44.4	44.6	44.9	45.1	46.7	48.3	51.7	55.1	58.3	61.5
75°	36.0	36.2	36.4	36.7	36.9	37.3	37.8	38.9	40.1	43.7	47.4
77.5°	28.7	28.9	29.2	29.4	29.6	30.1	30.5	31.0	31.4	32.8	34.2
80°	21.9	22.1	22.3	22.5	22.8	23.0	23.2	23.7	24.1	24.8	25.5
82.5°	15.9	15.9	15.9	15.9	15.9	16.4	16.9	16.9	16.9	17.3	17.8
85°	10.0	10.0	10.0	10.2	10.5	10.5	10.5	10.7	10.9	10.9	10.9
87.5°	4.6	4.3	4.1	4.3	4.6	4.6	4.6	4.8	5.0	5.0	5.0
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	42.9	43.4	43.8	44.3	44.7	44.6	43.9	43.3	42.6	41.9	40.6
95°	77.9	77.9	77.9	77.9	77.9	77.4	76.5	75.6	74.8	73.9	72.1
97.5°	111.8	112.0	112.2	112.5	112.7	112.2	111.1	110.0	108.9	107.8	106.5
100°	151.7	151.3	150.8	150.4	150.0	149.4	148.7	148.1	147.4	146.7	145.6
102.5°	192.7	192.9	193.1	193.3	193.5	193.3	192.7	192.0	191.3	190.7	189.1
105°	237.6	237.1	236.7	236.2	235.8	235.6	235.6	235.6	235.6	235.6	233.6
107.5°	283.5	283.7	283.9	284.2	284.4	284.2	283.5	282.8	282.2	281.5	280.6
110°	330.4	330.9	331.3	331.7	332.2	332.0	331.1	330.2	329.3	328.4	328.0



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	380.3	380.3	380.3	380.3	380.3	379.8	378.7	377.5	376.4	375.3	375.3
115°	425.2	425.5	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2	425.7
117.5°	471.2	471.8	472.5	473.2	473.8	474.1	474.1	474.1	474.1	474.1	474.6
120°	520.1	520.5	521.0	521.4	521.8	522.2	522.4	522.6	522.8	523.1	524.2
122.5°	567.0	567.6	568.3	569.0	569.6	570.3	571.0	571.6	572.3	573.0	573.4
125°	613.9	614.8	615.7	616.6	617.4	618.3	619.2	620.1	621.0	621.9	622.3
127.5°	660.8	661.7	662.6	663.5	664.4	665.5	666.8	668.1	669.5	670.8	671.2
130°	706.7	708.3	709.8	711.4	712.9	714.2	715.0	715.9	716.8	717.7	718.4
132.5°	754.6	755.8	756.9	758.0	759.1	760.2	761.3	762.4	763.5	764.6	765.1
135°	804.6	805.0	805.4	805.9	806.3	807.0	807.9	808.8	809.7	810.5	810.8
137.5°	848.5	849.1	849.8	850.5	851.1	852.0	853.1	854.2	855.4	856.5	855.8
140°	891.4	893.0	894.5	896.1	897.6	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	935.3	936.4	937.5	938.6	939.8	940.4	940.6	940.9	941.1	941.3	940.9
145°	977.2	978.1	979.0	979.9	980.8	981.3	981.6	981.8	982.0	982.2	981.6
147.5°	1015.2	1016.5	1017.8	1019.2	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1051.1	1052.4	1053.8	1055.1	1056.4	1057.1	1057.1	1057.1	1057.1	1057.1	1056.7
152.5°	1086.1	1087.2	1088.3	1089.4	1090.5	1090.8	1090.4	1089.9	1089.5	1089.0	1088.8
155°	1117.0	1118.5	1120.1	1121.7	1123.2	1123.5	1122.7	1121.8	1120.9	1120.0	1119.8
157.5°	1145.9	1147.3	1148.6	1149.9	1151.3	1151.5	1150.6	1149.7	1148.8	1147.9	1147.7
160°	1173.9	1174.8	1175.7	1176.6	1177.4	1177.3	1176.2	1175.1	1174.0	1172.9	1172.9
162.5°	1194.9	1196.4	1198.0	1199.5	1201.1	1201.3	1200.2	1199.1	1198.0	1196.9	1196.6
165°	1214.8	1216.4	1217.9	1219.5	1221.0	1221.1	1219.8	1218.5	1217.1	1215.8	1215.8
167.5°	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1	1236.8	1235.4	1234.1	1232.8	1232.6
170°	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8	1245.8
172.5°	1255.7	1257.3	1258.9	1260.4	1262.0	1262.1	1260.7	1259.4	1258.1	1256.7	1256.7
175°	1262.7	1264.3	1265.8	1267.4	1268.9	1269.1	1267.7	1266.4	1265.1	1263.7	1263.7
177.5°	1266.7	1268.3	1269.8	1271.4	1272.9	1273.0	1271.7	1270.4	1269.1	1267.7	1267.7
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1179.5	1178.3	1167.4	1156.5	1145.8	1135.1	1127.1	1119.1	1105.7	1092.3	1083.8
5°	1252.6	1243.9	1226.6	1209.3	1183.4	1157.4	1135.5	1113.7	1085.9	1058.1	1034.9
7.5°	1293.3	1286.3	1265.3	1244.4	1210.0	1175.6	1141.4	1107.3	1066.3	1025.3	990.2
10°	1294.5	1300.4	1283.1	1265.8	1227.1	1188.4	1141.9	1095.4	1040.3	985.2	939.9
12.5°	1254.0	1279.5	1275.8	1272.2	1232.8	1193.4	1136.9	1080.4	1012.8	945.1	888.4
15°	1178.1	1227.5	1242.1	1256.7	1224.1	1191.5	1127.3	1063.1	983.6	904.1	839.0
17.5°	1080.4	1149.6	1188.1	1226.6	1202.9	1179.3	1108.9	1038.5	949.0	859.5	788.7
20°	964.7	1055.4	1115.7	1176.1	1167.4	1158.8	1086.1	1013.5	916.9	820.3	743.6
22.5°	850.4	946.0	1029.4	1112.7	1121.6	1130.5	1057.2	983.8	878.2	772.5	694.4
25°	751.8	849.0	948.3	1047.6	1067.7	1087.7	1018.0	948.3	838.8	729.2	651.6
27.5°	657.7	750.2	859.5	968.8	1005.3	1041.7	977.9	914.2	800.1	686.0	608.5
30°	581.0	663.6	775.2	886.8	937.6	988.4	929.9	871.3	758.2	645.0	569.1
32.5°	509.5	583.5	695.5	807.6	866.6	925.5	875.0	824.4	715.6	606.7	531.8
35°	453.0	519.3	623.8	728.3	794.4	860.4	819.0	777.5	671.2	564.8	494.0
37.5°	404.5	460.0	558.2	656.4	726.5	796.6	762.0	727.4	627.4	527.5	460.5
40°	364.4	409.0	500.4	591.7	660.5	729.2	699.6	670.0	580.5	491.0	428.4
42.5°	330.0	368.5	450.5	532.5	595.5	658.6	639.0	619.5	538.4	457.3	399.2
45°	299.7	332.0	404.2	476.4	534.5	592.6	577.1	561.6	491.7	421.8	368.5
47.5°	272.8	300.6	365.1	429.5	481.7	533.8	519.5	505.1	447.3	389.4	340.9
50°	248.2	271.9	325.7	379.4	426.3	473.2	461.4	449.6	401.7	353.9	312.0
52.5°	225.0	244.6	292.9	341.2	379.0	416.8	407.7	398.5	361.7	324.8	286.7
55°	202.9	220.9	261.7	302.4	334.8	367.1	358.0	348.9	320.2	291.5	258.0
57.5°	182.9	198.6	231.6	264.6	290.4	316.1	311.8	307.5	283.5	259.6	232.1
60°	161.7	175.8	204.3	232.8	253.5	274.2	269.2	264.2	247.1	230.0	206.3
62.5°	142.8	155.3	178.1	200.9	217.7	234.6	230.9	227.3	214.3	201.3	181.7
65°	123.0	135.3	153.7	172.2	185.4	198.6	195.4	192.2	182.4	172.6	156.9
67.5°	105.0	115.2	131.2	147.1	156.0	164.9	163.1	161.2	153.7	146.2	133.9
70°	86.8	95.7	108.9	122.1	128.2	134.4	135.1	135.7	128.9	122.1	113.0
72.5°	68.6	75.6	87.9	100.2	105.0	109.8	109.5	109.3	105.2	101.1	92.9
75°	52.6	57.8	67.4	77.0	81.1	85.2	86.1	87.0	83.1	79.3	74.7
77.5°	37.8	41.4	48.7	56.0	60.6	65.1	65.6	66.0	64.2	62.4	58.1
80°	26.6	27.8	32.3	36.9	41.7	46.5	47.1	47.8	46.0	44.2	41.4
82.5°	18.4	19.1	20.7	22.3	26.2	30.1	31.0	31.9	31.0	30.1	27.1
85°	11.2	11.4	12.1	12.8	14.6	16.4	17.3	18.2	17.8	17.3	15.7
87.5°	5.0	5.0	5.2	5.5	5.9	6.4	7.5	8.7	8.0	7.3	6.6
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	39.3	37.9	36.6	35.3	33.9	32.6	31.3	29.9	31.3	32.6	33.9
95°	70.3	68.5	66.8	65.1	63.6	62.0	60.4	58.9	60.4	62.0	63.6
97.5°	105.1	103.8	102.5	101.3	100.2	99.0	97.9	96.8	97.9	99.0	100.2
100°	144.5	143.4	142.3	141.1	139.7	138.4	137.1	135.8	137.1	138.4	139.7
102.5°	187.6	186.0	184.4	183.3	182.7	182.0	181.3	180.7	181.3	182.0	182.7
105°	231.6	229.6	227.6	226.4	225.9	225.5	225.0	224.6	225.0	225.5	225.9
107.5°	279.7	278.8	277.9	277.4	277.2	276.9	276.7	276.5	276.7	276.9	277.2
110°	327.5	327.1	326.6	326.2	325.7	325.3	324.9	324.4	324.9	325.3	325.7



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.3	375.3	375.3	375.2	375.0	374.8	374.5	374.3	374.5	374.8	375.0
115°	426.1	426.6	427.0	426.9	426.2	425.6	424.9	424.2	424.9	425.6	426.2
117.5°	475.0	475.5	475.9	476.0	475.8	475.6	475.4	475.1	475.4	475.6	475.8
120°	525.3	526.4	527.5	527.4	526.1	524.7	523.4	522.1	523.4	524.7	526.1
122.5°	573.9	574.3	574.7	574.5	573.6	572.7	571.9	571.0	571.9	572.7	573.6
125°	622.8	623.2	623.7	623.5	622.9	622.2	621.6	620.9	621.6	622.2	622.9
127.5°	671.7	672.1	672.6	672.1	670.8	669.5	668.1	666.8	668.1	669.5	670.8
130°	719.0	719.7	720.4	719.8	718.0	716.3	714.5	712.7	714.5	716.3	718.0
132.5°	765.5	766.0	766.4	765.7	764.0	762.2	760.4	758.6	760.4	762.2	764.0
135°	811.0	811.2	811.4	810.9	809.5	808.2	806.9	805.6	806.9	808.2	809.5
137.5°	855.1	854.5	853.8	852.9	851.8	850.7	849.6	848.5	849.6	850.7	851.8
140°	898.9	898.7	898.5	897.8	896.7	895.6	894.5	893.4	894.5	895.6	896.7
142.5°	940.4	940.0	939.5	938.8	937.7	936.5	935.4	934.3	935.4	936.5	937.7
145°	980.9	980.2	979.6	979.0	978.6	978.1	977.7	977.2	977.7	978.1	978.6
147.5°	1019.8	1019.2	1018.5	1017.7	1016.8	1016.0	1015.1	1014.2	1015.1	1016.0	1016.8
150°	1056.2	1055.8	1055.3	1054.9	1054.4	1054.0	1053.6	1053.1	1053.6	1054.0	1054.4
152.5°	1088.6	1088.4	1088.2	1087.7	1087.0	1086.4	1085.7	1085.1	1085.7	1086.4	1087.0
155°	1119.5	1119.3	1119.1	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0
157.5°	1147.5	1147.3	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1147.7	1147.5	1147.3
160°	1172.9	1172.9	1172.9	1173.1	1173.6	1174.0	1174.4	1174.9	1174.4	1174.0	1173.6
162.5°	1196.4	1196.2	1196.0	1196.2	1196.9	1197.5	1198.2	1198.8	1198.2	1197.5	1196.9
165°	1215.8	1215.8	1215.8	1216.2	1216.8	1217.5	1218.1	1218.8	1218.1	1217.5	1216.8
167.5°	1232.3	1232.1	1231.9	1232.2	1233.1	1234.0	1234.9	1235.8	1234.9	1234.0	1233.1
170°	1245.8	1245.8	1245.8	1246.2	1247.1	1248.0	1248.9	1249.8	1248.9	1248.0	1247.1
172.5°	1256.7	1256.7	1256.7	1257.2	1258.1	1259.0	1259.8	1260.7	1259.8	1259.0	1258.1
175°	1263.7	1263.7	1263.7	1264.2	1265.1	1265.9	1266.8	1267.7	1266.8	1265.9	1265.1
177.5°	1267.7	1267.7	1267.7	1268.2	1269.1	1269.9	1270.8	1271.7	1270.8	1269.9	1269.1
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1075.4	1062.4	1049.4	1040.1	1030.8	1019.1	1007.5	1007.1	1006.6	998.0	989.3
5°	1011.6	989.1	966.5	944.4	922.4	900.3	878.2	873.2	868.2	860.6	853.1
7.5°	955.2	919.2	883.2	854.9	826.7	804.6	782.5	767.5	752.5	740.8	729.2
10°	894.6	849.9	805.3	771.1	737.0	713.1	689.1	671.8	654.5	646.3	638.1
12.5°	831.7	783.2	734.7	701.2	667.7	639.0	610.3	594.6	578.9	567.5	556.1
15°	773.9	721.7	669.6	634.0	598.5	571.6	544.8	529.0	513.3	501.9	490.6
17.5°	717.8	665.2	612.6	576.6	540.7	516.3	491.9	476.7	461.4	454.3	447.3
20°	666.8	613.8	560.7	526.8	492.8	468.9	445.0	436.8	428.6	422.0	415.4
22.5°	616.3	565.3	514.2	481.7	449.1	431.8	414.5	407.9	401.3	396.3	391.3
25°	573.9	523.1	472.3	443.9	415.4	402.0	388.5	384.2	379.9	374.9	369.9
27.5°	531.1	482.8	434.5	411.8	389.0	378.1	367.1	361.7	356.2	352.1	348.0
30°	493.3	448.7	404.0	385.1	366.2	356.6	347.1	341.2	335.2	331.4	327.5
32.5°	456.9	417.2	377.6	361.4	345.3	335.9	326.6	320.9	315.2	310.6	306.1
35°	423.1	388.8	354.4	339.6	324.8	315.4	306.1	300.4	294.7	290.1	285.6
37.5°	393.5	362.3	331.1	317.2	303.4	295.2	287.0	281.0	275.1	270.3	265.5
40°	365.8	338.2	310.6	297.2	283.8	274.9	266.0	260.8	255.5	251.2	246.9
42.5°	341.2	315.9	290.6	277.4	264.2	255.8	247.3	241.2	235.0	232.5	230.0
45°	315.2	292.9	270.6	257.8	245.1	236.2	227.3	222.0	216.8	214.5	212.3
47.5°	292.4	271.7	251.0	238.4	225.9	217.9	210.0	205.9	201.8	198.6	195.4
50°	270.1	250.1	230.0	217.9	205.9	199.0	192.2	187.2	182.2	179.9	177.6
52.5°	248.7	230.5	212.3	200.0	187.7	181.1	174.5	170.1	165.8	161.0	156.2
55°	224.6	208.6	192.7	181.7	170.8	164.0	157.1	152.1	147.1	142.1	137.1
57.5°	204.5	188.8	173.1	163.3	153.5	146.9	140.3	134.8	129.4	125.3	121.2
60°	182.6	169.0	155.3	145.8	136.2	129.8	123.4	118.2	113.0	110.9	108.9
62.5°	162.2	149.4	136.6	128.2	119.8	113.6	107.5	104.1	100.7	99.3	97.9
65°	141.2	130.3	119.3	111.6	103.9	98.6	93.4	91.8	90.2	89.0	87.9
67.5°	121.6	112.3	102.9	96.1	89.3	85.6	82.0	80.2	78.3	77.0	75.6
70°	103.9	95.7	87.5	81.5	75.6	72.2	68.8	67.2	65.6	63.1	60.6
72.5°	84.7	78.3	72.0	67.4	62.9	59.9	56.9	53.7	50.6	48.3	46.0
75°	70.1	63.8	57.4	53.1	48.7	45.3	41.9	40.8	39.6	38.9	38.3
77.5°	53.7	48.3	42.8	39.4	36.0	34.4	32.8	32.1	31.4	31.2	31.0
80°	38.7	34.2	29.6	27.8	26.0	25.5	25.1	24.6	24.1	23.9	23.7
82.5°	24.1	21.9	19.6	19.1	18.7	18.4	18.2	18.0	17.8	17.5	17.3
85°	14.1	13.2	12.3	12.1	11.8	11.6	11.4	11.4	11.4	11.4	11.4
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.7	5.5
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	35.3	36.6	37.9	39.3	40.6	41.9	42.6	43.3	43.9	44.6	44.7
95°	65.1	66.8	68.5	70.3	72.1	73.9	74.8	75.6	76.5	77.4	77.9
97.5°	101.3	102.5	103.8	105.1	106.5	107.8	108.9	110.0	111.1	112.2	112.7
100°	141.1	142.3	143.4	144.5	145.6	146.7	147.4	148.1	148.7	149.4	150.0
102.5°	183.3	184.4	186.0	187.6	189.1	190.7	191.3	192.0	192.7	193.3	193.5
105°	226.4	227.6	229.6	231.6	233.6	235.6	235.6	235.6	235.6	235.6	235.8
107.5°	277.4	277.9	278.8	279.7	280.6	281.5	282.2	282.8	283.5	284.2	284.4
110°	326.2	326.6	327.1	327.5	328.0	328.4	329.3	330.2	331.1	332.0	332.2



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.2	375.3	375.3	375.3	375.3	375.3	376.4	377.5	378.7	379.8	380.3
115°	426.9	427.0	426.6	426.1	425.7	425.2	425.5	425.7	425.9	426.1	426.1
117.5°	476.0	475.9	475.5	475.0	474.6	474.1	474.1	474.1	474.1	474.1	473.8
120°	527.4	527.5	526.4	525.3	524.2	523.1	522.8	522.6	522.4	522.2	521.8
122.5°	574.5	574.7	574.3	573.9	573.4	573.0	572.3	571.6	571.0	570.3	569.6
125°	623.5	623.7	623.2	622.8	622.3	621.9	621.0	620.1	619.2	618.3	617.4
127.5°	672.1	672.6	672.1	671.7	671.2	670.8	669.5	668.1	666.8	665.5	664.4
130°	719.8	720.4	719.7	719.0	718.4	717.7	716.8	715.9	715.0	714.2	712.9
132.5°	765.7	766.4	766.0	765.5	765.1	764.6	763.5	762.4	761.3	760.2	759.1
135°	810.9	811.4	811.2	811.0	810.8	810.5	809.7	808.8	807.9	807.0	806.3
137.5°	852.9	853.8	854.5	855.1	855.8	856.5	855.4	854.2	853.1	852.0	851.1
140°	897.8	898.5	898.7	898.9	899.2	899.4	899.2	898.9	898.7	898.5	897.6
142.5°	938.8	939.5	940.0	940.4	940.9	941.3	941.1	940.9	940.6	940.4	939.8
145°	979.0	979.6	980.2	980.9	981.6	982.2	982.0	981.8	981.6	981.3	980.8
147.5°	1017.7	1018.5	1019.2	1019.8	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1	1057.1	1057.1	1057.1	1056.4
152.5°	1087.7	1088.2	1088.4	1088.6	1088.8	1089.0	1089.5	1089.9	1090.4	1090.8	1090.5
155°	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9	1121.8	1122.7	1123.5	1123.2
157.5°	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1148.8	1149.7	1150.6	1151.5	1151.3
160°	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0	1175.1	1176.2	1177.3	1177.4
162.5°	1196.2	1196.0	1196.2	1196.4	1196.6	1196.9	1198.0	1199.1	1200.2	1201.3	1201.1
165°	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1	1218.5	1219.8	1221.1	1221.0
167.5°	1232.2	1231.9	1232.1	1232.3	1232.6	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1
170°	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0
172.5°	1257.2	1256.7	1256.7	1256.7	1256.7	1256.7	1258.1	1259.4	1260.7	1262.1	1262.0
175°	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1	1266.4	1267.7	1269.1	1268.9
177.5°	1268.2	1267.7	1267.7	1267.7	1267.7	1267.7	1269.1	1270.4	1271.7	1273.0	1272.9
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1110.9	1110.9	1110.9	1110.9
2.5°	987.0	984.8	983.8	982.9
5°	846.1	839.0	837.4	835.8
7.5°	726.3	723.3	713.5	703.7
10°	629.0	619.9	615.8	611.7
12.5°	547.7	539.3	537.9	536.6
15°	484.6	478.7	476.7	474.6
17.5°	443.2	439.1	436.6	434.1
20°	412.4	409.5	407.7	405.8
22.5°	389.0	386.7	385.3	384.0
25°	366.4	363.0	361.9	360.7
27.5°	345.0	342.1	340.9	339.8
30°	325.0	322.5	320.9	319.3
32.5°	303.1	300.2	299.3	298.3
35°	283.8	281.9	281.0	280.1
37.5°	263.3	261.0	259.6	258.3
40°	245.7	244.6	243.9	243.2
42.5°	228.0	225.9	225.7	225.5
45°	210.2	208.2	207.7	207.2
47.5°	193.6	191.8	191.5	191.3
50°	175.1	172.6	170.8	169.0
52.5°	154.0	151.7	150.1	148.5
55°	134.6	132.1	130.7	129.4
57.5°	120.0	118.9	118.2	117.5
60°	108.2	107.5	107.0	106.6
62.5°	97.2	96.6	96.6	96.6
65°	87.2	86.5	85.9	85.2
67.5°	74.2	72.9	72.6	72.4
70°	58.5	56.5	56.3	56.0
72.5°	45.8	45.5	45.1	44.6
75°	37.8	37.3	37.3	37.3
77.5°	30.5	30.1	30.1	30.1
80°	23.5	23.2	23.5	23.7
82.5°	17.3	17.3	17.1	16.9
85°	11.2	10.9	10.9	10.9
87.5°	5.5	5.5	5.5	5.5
90°	28.6	29.1	29.5	29.9
92.5°	44.3	43.8	43.4	42.9
95°	77.9	77.9	77.9	77.9
97.5°	112.5	112.2	112.0	111.8
100°	150.4	150.8	151.3	151.7
102.5°	193.3	193.1	192.9	192.7
105°	236.2	236.7	237.1	237.6
107.5°	284.2	283.9	283.7	283.5
110°	331.7	331.3	330.9	330.4



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	380.3	380.3	380.3	380.3
115°	425.9	425.7	425.5	425.2
117.5°	473.2	472.5	471.8	471.2
120°	521.4	521.0	520.5	520.1
122.5°	569.0	568.3	567.6	567.0
125°	616.6	615.7	614.8	613.9
127.5°	663.5	662.6	661.7	660.8
130°	711.4	709.8	708.3	706.7
132.5°	758.0	756.9	755.8	754.6
135°	805.9	805.4	805.0	804.6
137.5°	850.5	849.8	849.1	848.5
140°	896.1	894.5	893.0	891.4
142.5°	938.6	937.5	936.4	935.3
145°	979.9	979.0	978.1	977.2
147.5°	1019.2	1017.8	1016.5	1015.2
150°	1055.1	1053.8	1052.4	1051.1
152.5°	1089.4	1088.3	1087.2	1086.1
155°	1121.7	1120.1	1118.5	1117.0
157.5°	1149.9	1148.6	1147.3	1145.9
160°	1176.6	1175.7	1174.8	1173.9
162.5°	1199.5	1198.0	1196.4	1194.9
165°	1219.5	1217.9	1216.4	1214.8
167.5°	1236.8	1235.4	1234.1	1232.8
170°	1250.4	1248.9	1247.3	1245.8
172.5°	1260.4	1258.9	1257.3	1255.7
175°	1267.4	1265.8	1264.3	1262.7
177.5°	1271.4	1269.8	1268.3	1266.7
180°	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P832039

CATALOG NUMBER: S123RDIP-S340D1025U835-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.06	7.73	8.18	8.84	10.38	11.72	12.40	12.84	13.51	15.05
	3H	8.26	8.87	9.40	9.99	11.54	13.21	13.81	14.34	14.93	16.49
	4H	8.64	9.21	9.78	10.33	11.89	13.69	14.26	14.83	15.38	16.94
	6H	8.91	9.44	10.06	10.56	12.14	13.99	14.52	15.14	15.64	17.22
	8H	9.00	9.50	10.15	10.64	12.20	14.07	14.57	15.22	15.71	17.27
	12H	9.04	9.52	10.20	10.65	12.24	14.10	14.57	15.25	15.70	17.29
4H	2H	7.76	8.33	8.91	9.45	11.01	11.70	12.27	12.84	13.39	14.95
	3H	9.12	9.59	10.27	10.74	12.31	13.34	13.82	14.49	14.96	16.54
	4H	9.57	10.00	10.72	11.14	12.73	13.94	14.38	15.10	15.52	17.11
	6H	9.93	10.30	11.09	11.46	13.04	14.37	14.75	15.53	15.90	17.49
	8H	10.05	10.40	11.21	11.55	13.15	14.50	14.85	15.66	16.00	17.60
	12H	10.12	10.43	11.29	11.59	13.20	14.56	14.87	15.73	16.03	17.64
8H	4H	9.87	10.22	11.03	11.37	12.97	13.90	14.25	15.06	15.40	17.00
	6H	10.33	10.62	11.51	11.81	13.40	14.39	14.68	15.57	15.87	17.46
	8H	10.52	10.77	11.70	11.94	13.56	14.58	14.83	15.76	16.00	17.61
	12H	10.66	10.88	11.84	12.04	13.69	14.68	14.90	15.87	16.07	17.72
12H	4H	9.87	10.19	11.05	11.35	12.95	13.84	14.16	15.02	15.32	16.92
	6H	10.39	10.64	11.57	11.81	13.42	14.36	14.61	15.55	15.78	17.40
	8H	10.60	10.82	11.79	11.98	13.63	14.55	14.77	15.74	15.94	17.59