

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332244-830

Luminaire Tested: **S123RDIP-S340D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332244-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2399.4 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44				44
2	90	83	77	72	83	77	71	67	65	61	58	55	52	50	45	43	42	37				37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	32				32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	28				28
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27	24				24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21				21
7	59	47	39	34	55	44	37	32	38	32	28	33	28	25	27	24	22	19				19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17				17
9	51	39	32	27	47	37	30	25	32	27	23	27	23	20	23	20	18	15				15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	2.1
10°-20°	141.5	5.9
20°-30°	203.7	8.5
30°-40°	229.5	9.6
40°-50°	219.5	9.1
50°-60°	179.8	7.5
60°-70°	121.3	5.1
70°-80°	61.0	2.5
80°-90°	17.4	0.7
90°-100°	27.6	1.2
100°-110°	82.7	3.4
110°-120°	140.6	5.9
120°-130°	185.0	7.7
130°-140°	207.9	8.7
140°-150°	204.4	8.5
150°-160°	172.0	7.2
160°-170°	114.5	4.8
170°-180°	40.1	1.7
0°-30°	396.1	16.5
0°-40°	625.5	26.1
0°-60°	1024.8	42.7
0°-90°	1224.5	51.0
90°-120°	250.9	10.5
90°-150°	848.1	35.3
90°-180°	1175.0	49.0
0°-180°	2399.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	0	4	8	9	10	2
95°	20	22	25	26	26	22
105°	75	76	79	79	79	80
115°	142	142	142	142	142	140
125°	207	208	208	206	205	185
135°	269	271	270	269	268	207
145°	326	327	328	327	326	204
155°	373	373	374	375	373	172
165°	407	406	406	408	405	115
175°	423	422	422	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.5	7.8	7.1	6.4	5.7	5.4	5.6	5.7	5.9	6.1	6.1
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	8.1	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0
95°	19.7	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0
97.5°	34.9	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9
100°	45.3	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2
102.5°	57.3	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9
105°	74.9	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6
107.5°	95.5	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3
110°	108.3	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9



TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4
115°	141.6	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9
117.5°	161.6	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5
120°	174.2	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5
122.5°	187.3	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7
125°	207.2	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2
127.5°	225.6	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6
130°	237.8	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2
132.5°	250.1	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7
135°	268.8	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1
137.5°	286.2	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3
140°	298.1	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.1	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2
145°	326.1	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7
147.5°	341.0	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2
150°	351.4	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7
152.5°	360.0	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4
155°	373.4	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0
157.5°	384.8	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0
160°	392.0	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7
162.5°	398.4	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1
165°	406.7	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1
167.5°	413.3	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6
170°	417.0	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2
172.5°	420.0	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1
175°	423.0	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2
177.5°	424.2	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	6.1	6.1	6.1	6.0	6.0	5.9	5.9	5.8
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.3	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.3	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.2	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.4	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.2	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.6	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.2	110.5	110.7	110.8	110.7	110.6	110.4	110.3





TEST NUMBER: P332244-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.4	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.5	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.9	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	226.1	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.9	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	251.3	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.8	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	288.0	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.1	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.6	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.5	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.3	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.3	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.1	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.5	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	406.6	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	419.5	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	422.5	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.0	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)