

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332268

Luminaire Tested: **S123RDIP-S340D1195U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332268
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5400.2 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	150.1	2.8
20°-30°	216.1	4.0
30°-40°	243.5	4.5
40°-50°	232.9	4.3
50°-60°	190.7	3.5
60°-70°	128.7	2.4
70°-80°	64.7	1.2
80°-90°	21.5	0.4
90°-100°	96.4	1.8
100°-110°	288.4	5.3
110°-120°	490.5	9.1
120°-130°	645.2	11.9
130°-140°	725.2	13.4
140°-150°	712.8	13.2
150°-160°	600.1	11.1
160°-170°	399.5	7.4
170°-180°	139.9	2.6
0°-30°	420.2	7.8
0°-40°	663.7	12.3
0°-60°	1087.3	20.1
0°-90°	1302.2	24.1
90°-120°	875.3	16.2
90°-150°	2958.5	54.8
90°-180°	4098.0	75.9
0°-180°	5400.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	13	28	32	35	5
95°	69	77	86	90	91	77
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	723	726	724	719	715	644
135°	938	944	943	939	936	722
145°	1138	1140	1143	1142	1138	710
155°	1302	1303	1304	1308	1300	599
165°	1419	1415	1415	1421	1414	400
175°	1476	1471	1471	1477	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.2	8.8	8.4	8.0	7.6	7.7	8.4	9.1	9.8	10.4	10.5
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	28.1	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4
95°	68.6	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0
97.5°	121.8	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7
100°	158.0	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6
102.5°	199.8	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5
105°	261.4	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2
107.5°	333.0	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4
110°	377.6	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	424.1	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2
115°	493.8	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2
117.5°	564.0	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2
120°	607.7	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6
122.5°	653.2	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6
125°	722.7	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8
127.5°	786.8	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3
130°	829.6	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4
132.5°	872.3	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8
135°	937.6	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4
137.5°	998.1	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8
140°	1039.9	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.0	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6
145°	1137.5	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0
147.5°	1189.5	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0
150°	1225.8	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4
152.5°	1255.5	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6
155°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7
157.5°	1342.4	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1
160°	1367.5	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5
162.5°	1389.8	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8
165°	1418.7	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7
167.5°	1441.7	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5
170°	1454.7	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8
172.5°	1464.9	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9
175°	1475.6	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5
177.5°	1480.0	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	10.7	10.8	10.9	11.0	11.0	11.0	11.1	11.1
90°	30.0	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	46.3	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	88.0	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	136.9	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	172.3	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	213.2	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	340.2	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	384.3	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P332268

CATALOG NUMBER: S123RDIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.4	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.2	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.3	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	654.0	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	721.8	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	788.8	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	833.3	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	876.6	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	941.4	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1004.7	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.3	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.4	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.8	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.0	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1305.7	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1344.1	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1367.8	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1390.1	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1418.3	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1463.5	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1474.0	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1478.8	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)