

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332249-830

Luminaire Tested: **S123RDIP-S340D585U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332249-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3431.9 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36				
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31				
2	86	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26				
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27	22				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17				
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15				
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12				
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.5
10°-20°	141.5	4.1
20°-30°	203.7	5.9
30°-40°	229.5	6.7
40°-50°	219.5	6.4
50°-60°	179.8	5.2
60°-70°	121.3	3.5
70°-80°	61.0	1.8
80°-90°	18.2	0.5
90°-100°	26.3	0.8
100°-110°	125.4	3.7
110°-120°	301.2	8.8
120°-130°	383.5	11.2
130°-140°	409.8	11.9
140°-150°	383.2	11.2
150°-160°	309.1	9.0
160°-170°	199.5	5.8
170°-180°	68.7	2.0
0°-30°	396.1	11.5
0°-40°	625.5	18.2
0°-60°	1024.8	29.9
0°-90°	1225.3	35.7
90°-120°	452.8	13.2
90°-150°	1629.3	47.5
90°-180°	2207.0	64.3
0°-180°	3431.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	6	13	15	16	3
95°	33	12	17	20	20	41
105°	160	163	118	28	24	170
115°	300	304	309	314	316	297
125°	424	428	430	431	432	378
135°	527	531	533	534	533	406
145°	608	612	613	614	614	381
155°	670	669	670	672	669	309
165°	707	705	705	709	705	200
175°	724	721	721	725	721	69
180°	724	724	724	724	724	



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	7.9	7.3	6.7	6.0	5.9	6.2	6.5	6.9	7.2	7.2
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	10.0	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5
95°	32.8	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5
97.5°	65.9	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3
100°	90.9	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7
102.5°	119.2	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4
105°	160.2	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6
107.5°	203.4	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3
110°	232.2	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7
115°	300.5	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8
117.5°	340.0	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4
120°	364.5	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9
122.5°	389.5	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2
125°	423.6	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3
127.5°	456.8	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0
130°	477.4	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3
132.5°	497.2	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7
135°	527.4	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1
137.5°	553.2	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0
140°	570.3	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7
142.5°	586.3	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5
145°	608.5	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6
147.5°	629.5	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3
150°	642.4	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4
152.5°	654.0	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8
155°	670.3	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4
157.5°	683.1	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2
160°	690.8	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4
162.5°	698.1	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0
165°	706.9	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8
167.5°	713.8	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7
170°	717.7	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5
172.5°	720.3	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1
175°	723.6	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3
177.5°	724.4	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	7.2	7.2	7.3	7.3	7.2	7.2	7.2	7.1
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	15.3	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	18.4	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	19.2	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	19.6	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	29.4	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	75.4	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	184.7	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	234.6	230.6	226.7	216.1	199.1	182.0	164.9	147.8



TEST NUMBER: P332249-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.7	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	310.9	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	348.4	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	372.9	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	396.8	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.6	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.4	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	484.7	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.2	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	559.6	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.2	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	591.9	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	613.9	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.6	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.5	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.3	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.0	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	683.8	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.2	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	697.8	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	706.7	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	720.0	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	723.1	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	724.2	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)