

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332250-830

Luminaire Tested: **S123RDIP-S340D585U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332250-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3121.5 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29
3	80	71	64	58	72	65	58	54	53	49	45	42	39	37	33	31	29	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	1.6
10°-20°	141.5	4.5
20°-30°	203.7	6.5
30°-40°	229.5	7.4
40°-50°	219.5	7.0
50°-60°	179.8	5.8
60°-70°	121.3	3.9
70°-80°	61.0	2.0
80°-90°	18.2	0.6
90°-100°	44.6	1.4
100°-110°	133.4	4.3
110°-120°	227.0	7.3
120°-130°	298.5	9.6
130°-140°	335.6	10.7
140°-150°	329.8	10.6
150°-160°	277.7	8.9
160°-170°	184.8	5.9
170°-180°	64.7	2.1
0°-30°	396.1	12.7
0°-40°	625.5	20.0
0°-60°	1024.8	32.8
0°-90°	1225.3	39.3
90°-120°	405.0	13.0
90°-150°	1368.9	43.9
90°-180°	1896.0	60.7
0°-180°	3121.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	6	13	15	16	3
95°	32	36	40	42	42	36
105°	121	122	127	127	128	130
115°	228	230	229	230	229	226
125°	334	336	335	333	331	298
135°	434	437	437	434	433	334
145°	526	527	529	528	526	329
155°	603	603	603	605	602	277
165°	656	655	655	658	654	185
175°	683	681	681	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	7.9	7.3	6.7	6.0	5.9	6.2	6.5	6.9	7.2	7.2
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	13.0	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0
95°	31.8	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2
97.5°	56.4	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8
100°	73.1	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4
102.5°	92.5	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3
105°	120.9	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9
107.5°	154.1	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0
110°	174.7	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4



TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7
115°	228.5	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1
117.5°	261.0	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6
120°	281.2	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6
122.5°	302.3	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9
125°	334.4	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4
127.5°	364.1	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7
130°	383.9	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1
132.5°	403.6	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1
135°	433.9	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1
137.5°	461.8	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4
140°	481.2	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	498.8	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4
145°	526.3	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9
147.5°	550.4	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8
150°	567.2	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3
152.5°	581.0	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2
155°	602.7	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7
157.5°	621.1	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4
160°	632.7	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3
162.5°	643.1	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6
165°	656.4	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5
167.5°	667.0	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1
170°	673.1	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8
172.5°	677.8	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5
175°	682.8	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4
177.5°	684.9	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	7.2	7.2	7.3	7.3	7.2	7.2	7.2	7.1
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.4	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	40.7	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.3	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	79.7	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	98.7	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.4	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	177.9	178.3	178.8	178.9	178.7	178.4	178.2	178.0





TEST NUMBER: P332250-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.6	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.4	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.6	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.9	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	365.0	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.6	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.6	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.5	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.9	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.2	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.2	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.8	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.5	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.2	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.0	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	632.9	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.2	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	656.3	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.1	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.0	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.3	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)