

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332252-830

Luminaire Tested: **S123RDIP-S340D805U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332252-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U830-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4304.6 lumens  
Efficiency: N/A  
Efficacy: 138.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	94	90	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	26				
2	85	79	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	22				
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19				
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17				
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18	15				
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13				
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12				
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11				
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10				
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.4	1.2
10°-20°	157.6	3.7
20°-30°	247.6	5.8
30°-40°	258.3	6.0
40°-50°	221.1	5.1
50°-60°	168.5	3.9
60°-70°	108.0	2.5
70°-80°	52.0	1.2
80°-90°	16.5	0.4
90°-100°	36.1	0.8
100°-110°	171.9	4.0
110°-120°	412.8	9.6
120°-130°	525.7	12.2
130°-140°	561.7	13.0
140°-150°	525.2	12.2
150°-160°	423.7	9.8
160°-170°	273.4	6.4
170°-180°	94.2	2.2
0°-30°	455.6	10.6
0°-40°	714.0	16.6
0°-60°	1103.5	25.6
0°-90°	1280.0	29.7
90°-120°	620.7	14.4
90°-150°	2233.3	51.9
90°-180°	3025.0	70.3
0°-180°	4304.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	22	1	22	1	22	10
95°	28	45	28	45	28	23
105°	32	220	32	220	32	74
115°	433	412	433	412	433	400
125°	592	581	592	581	592	529
135°	730	723	730	723	730	563
145°	842	834	842	834	842	526
155°	917	919	917	919	917	423
165°	967	969	967	969	967	273
175°	988	992	988	992	988	94
180°	992	992	992	992	992	



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	6.2	6.5	6.0	6.1	6.1	6.1	6.0	5.9	6.1	5.8	5.6
90°	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0	18.4	17.7	15.6
92.5°	24.5	24.2	24.0	23.8	23.7	23.1	22.0	20.9	19.9	18.9	17.2
95°	28.0	28.0	28.0	28.0	28.0	27.4	26.3	25.2	24.0	22.8	21.0
97.5°	30.3	30.2	30.1	29.9	29.7	28.9	27.6	26.4	25.1	23.8	35.5
100°	30.9	30.8	30.6	30.4	30.3	29.6	28.3	27.0	25.6	24.3	49.9
102.5°	31.6	31.2	30.9	30.6	30.3	32.2	36.3	40.3	44.4	48.4	76.3
105°	32.4	32.1	31.8	31.5	31.1	45.4	74.5	103.4	132.4	161.4	176.1
107.5°	101.8	123.7	145.5	167.4	189.2	210.8	232.1	253.3	274.6	295.8	293.4
110°	202.6	226.0	249.5	272.9	296.3	310.8	316.1	321.5	327.0	332.3	330.5



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.7	352.6	357.5	362.5	367.4	369.9	369.8	369.7	369.6	369.5	367.7
115°	433.3	432.6	432.0	431.3	430.6	429.5	427.9	426.2	424.6	423.0	421.5
117.5°	481.4	481.2	481.1	481.0	480.8	480.0	478.8	477.5	476.2	474.9	474.1
120°	514.3	514.3	514.3	514.3	514.3	513.7	512.4	511.0	509.7	508.4	507.9
122.5°	546.8	546.7	546.5	546.4	546.2	545.7	544.8	543.8	543.0	542.1	541.4
125°	592.5	592.1	591.8	591.4	591.2	590.8	590.5	590.1	589.8	589.5	588.8
127.5°	636.4	636.7	637.1	637.3	637.6	637.5	637.1	636.5	636.0	635.5	634.7
130°	664.7	665.0	665.3	665.6	666.0	665.8	665.2	664.5	663.8	663.2	662.5
132.5°	690.6	691.1	691.5	692.0	692.4	692.3	691.6	691.0	690.4	689.8	689.2
135°	730.3	730.8	731.2	731.7	732.2	732.2	731.7	731.2	730.8	730.3	729.6
137.5°	767.5	767.9	768.2	768.5	768.8	768.6	767.8	767.0	766.3	765.4	765.1
140°	789.9	790.2	790.6	790.9	791.3	791.1	790.4	789.8	789.1	788.4	788.0
142.5°	810.6	811.1	811.4	811.9	812.4	812.4	811.8	811.3	810.8	810.3	809.7
145°	842.3	842.3	842.3	842.3	842.3	842.1	841.8	841.4	841.1	840.7	840.5
147.5°	865.8	866.6	867.3	868.1	868.8	869.0	868.7	868.4	868.1	867.7	867.4
150°	883.5	884.0	884.5	885.0	885.5	885.5	885.2	884.9	884.6	884.3	883.9
152.5°	897.7	898.4	899.2	899.9	900.7	900.8	900.1	899.6	899.0	898.4	898.2
155°	917.4	918.4	919.4	920.4	921.3	921.4	920.6	919.8	919.0	918.1	917.9
157.5°	934.1	935.4	936.6	937.9	939.1	939.3	938.3	937.4	936.4	935.4	935.6
160°	944.7	945.8	947.0	948.1	949.2	949.3	948.4	947.3	946.4	945.4	945.6
162.5°	954.7	955.7	956.7	957.7	958.8	958.7	957.6	956.5	955.4	954.2	954.4
165°	966.8	967.9	969.0	970.3	971.4	971.3	970.0	968.7	967.3	966.0	966.2
167.5°	975.4	976.8	978.1	979.4	980.7	980.7	979.4	978.1	976.8	975.4	975.4
170°	980.8	982.1	983.4	984.7	986.0	986.0	984.7	983.4	982.1	980.8	980.8
172.5°	983.7	985.1	986.7	988.1	989.5	989.6	988.3	986.9	985.6	984.3	984.2
175°	988.2	989.5	990.8	992.1	993.3	993.4	992.3	991.2	990.0	988.9	988.7
177.5°	989.5	990.8	992.1	993.4	994.8	994.9	993.8	992.8	991.7	990.6	990.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	5.5	4.9	4.8	4.4	4.6	4.5	5.2	5.7	6.3	5.9	6.2
90°	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8	2.4	4.1	5.7
92.5°	15.6	14.0	12.4	11.9	12.3	12.8	13.3	13.7	13.3	12.8	12.3
95°	19.2	17.4	15.6	18.1	24.8	31.5	38.3	45.0	38.3	31.5	24.8
97.5°	47.3	59.1	70.9	78.3	81.3	84.4	87.4	90.3	87.4	84.4	81.3
100°	75.4	100.9	126.5	137.6	134.3	131.1	127.8	124.5	127.8	131.1	134.3
102.5°	104.2	132.2	160.1	172.9	170.5	168.1	165.8	163.4	165.8	168.1	170.5
105°	190.9	205.6	220.4	226.8	225.0	223.2	221.4	219.6	221.4	223.2	225.0
107.5°	291.2	288.8	286.4	284.6	283.1	281.7	280.3	278.8	280.3	281.7	283.1
110°	328.8	327.0	325.1	323.6	322.3	320.9	319.6	318.3	319.6	320.9	322.3





TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	365.9	364.1	362.2	360.8	359.6	358.4	357.2	356.1	357.2	358.4	359.6
115°	420.0	418.6	417.1	415.8	414.9	413.9	412.9	411.9	412.9	413.9	414.9
117.5°	473.3	472.6	471.8	470.8	469.7	468.4	467.2	466.0	467.2	468.4	469.7
120°	507.5	507.0	506.5	505.5	504.0	502.6	501.1	499.6	501.1	502.6	504.0
122.5°	540.8	540.2	539.5	538.7	537.4	536.2	535.0	533.8	535.0	536.2	537.4
125°	588.1	587.6	586.9	585.9	584.6	583.2	581.9	580.7	581.9	583.2	584.6
127.5°	634.0	633.1	632.4	631.3	630.0	628.7	627.4	626.0	627.4	628.7	630.0
130°	661.9	661.2	660.5	659.6	658.3	657.0	655.6	654.3	655.6	657.0	658.3
132.5°	688.6	688.2	687.6	686.7	685.4	684.1	682.8	681.5	682.8	684.1	685.4
135°	729.0	728.3	727.6	726.8	725.9	724.8	723.9	722.8	723.9	724.8	725.9
137.5°	764.8	764.4	764.0	763.2	762.0	760.7	759.5	758.3	759.5	760.7	762.0
140°	787.5	787.0	786.5	785.8	784.8	783.8	782.8	781.8	782.8	783.8	784.8
142.5°	809.3	808.8	808.3	807.6	806.6	805.6	804.6	803.6	804.6	805.6	806.6
145°	840.1	839.8	839.4	838.8	837.5	836.4	835.3	834.2	835.3	836.4	837.5
147.5°	867.0	866.8	866.5	865.9	865.2	864.4	863.7	862.9	863.7	864.4	865.2
150°	883.6	883.3	883.0	882.5	882.0	881.6	881.1	880.5	881.1	881.6	882.0
152.5°	898.0	897.8	897.6	897.4	897.2	896.9	896.7	896.5	896.7	896.9	897.2
155°	917.8	917.7	917.5	917.6	917.9	918.2	918.6	918.9	918.6	918.2	917.9
157.5°	935.8	935.9	936.0	936.1	936.1	936.2	936.2	936.2	936.2	936.2	936.1
160°	945.7	945.9	946.0	946.2	946.4	946.6	946.7	946.9	946.7	946.6	946.4
162.5°	954.6	954.7	954.9	955.2	955.6	956.0	956.5	956.9	956.5	956.0	955.6
165°	966.4	966.6	966.7	967.0	967.5	968.0	968.5	969.0	968.5	968.0	967.5
167.5°	975.4	975.4	975.4	975.8	976.5	977.1	977.8	978.5	977.8	977.1	976.5
170°	980.8	980.8	980.8	981.1	981.8	982.4	983.1	983.7	983.1	982.4	981.8
172.5°	984.0	983.9	983.8	984.1	984.9	985.7	986.5	987.2	986.5	985.7	984.9
175°	988.5	988.4	988.3	988.5	989.4	990.2	991.0	991.8	991.0	990.2	989.4
177.5°	990.4	990.2	990.1	990.4	991.1	991.7	992.4	993.0	992.4	991.7	991.1
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	6.4	7.3	7.9	8.5	9.0	9.3	9.6	9.8	10.1	10.2	10.3
90°	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0	19.6	20.3	20.8
92.5°	11.9	12.4	14.0	15.6	17.2	18.9	19.9	20.9	22.0	23.1	23.7
95°	18.1	15.6	17.4	19.2	21.0	22.8	24.0	25.2	26.3	27.4	28.0
97.5°	78.3	70.9	59.1	47.3	35.5	23.8	25.1	26.4	27.6	28.9	29.7
100°	137.6	126.5	100.9	75.4	49.9	24.3	25.6	27.0	28.3	29.6	30.3
102.5°	172.9	160.1	132.2	104.2	76.3	48.4	44.4	40.3	36.3	32.2	30.3
105°	226.8	220.4	205.6	190.9	176.1	161.4	132.4	103.4	74.5	45.4	31.1
107.5°	284.6	286.4	288.8	291.2	293.4	295.8	274.6	253.3	232.1	210.8	189.2
110°	323.6	325.1	327.0	328.8	330.5	332.3	327.0	321.5	316.1	310.8	296.3



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	360.8	362.2	364.1	365.9	367.7	369.5	369.6	369.7	369.8	369.9	367.4
115°	415.8	417.1	418.6	420.0	421.5	423.0	424.6	426.2	427.9	429.5	430.6
117.5°	470.8	471.8	472.6	473.3	474.1	474.9	476.2	477.5	478.8	480.0	480.8
120°	505.5	506.5	507.0	507.5	507.9	508.4	509.7	511.0	512.4	513.7	514.3
122.5°	538.7	539.5	540.2	540.8	541.4	542.1	543.0	543.8	544.8	545.7	546.2
125°	585.9	586.9	587.6	588.1	588.8	589.5	589.8	590.1	590.5	590.8	591.2
127.5°	631.3	632.4	633.1	634.0	634.7	635.5	636.0	636.5	637.1	637.5	637.6
130°	659.6	660.5	661.2	661.9	662.5	663.2	663.8	664.5	665.2	665.8	666.0
132.5°	686.7	687.6	688.2	688.6	689.2	689.8	690.4	691.0	691.6	692.3	692.4
135°	726.8	727.6	728.3	729.0	729.6	730.3	730.8	731.2	731.7	732.2	732.2
137.5°	763.2	764.0	764.4	764.8	765.1	765.4	766.3	767.0	767.8	768.6	768.8
140°	785.8	786.5	787.0	787.5	788.0	788.4	789.1	789.8	790.4	791.1	791.3
142.5°	807.6	808.3	808.8	809.3	809.7	810.3	810.8	811.3	811.8	812.4	812.4
145°	838.8	839.4	839.8	840.1	840.5	840.7	841.1	841.4	841.8	842.1	842.3
147.5°	865.9	866.5	866.8	867.0	867.4	867.7	868.1	868.4	868.7	869.0	868.8
150°	882.5	883.0	883.3	883.6	883.9	884.3	884.6	884.9	885.2	885.5	885.5
152.5°	897.4	897.6	897.8	898.0	898.2	898.4	899.0	899.6	900.1	900.8	900.7
155°	917.6	917.5	917.7	917.8	917.9	918.1	919.0	919.8	920.6	921.4	921.3
157.5°	936.1	936.0	935.9	935.8	935.6	935.4	936.4	937.4	938.3	939.3	939.1
160°	946.2	946.0	945.9	945.7	945.6	945.4	946.4	947.3	948.4	949.3	949.2
162.5°	955.2	954.9	954.7	954.6	954.4	954.2	955.4	956.5	957.6	958.7	958.8
165°	967.0	966.7	966.6	966.4	966.2	966.0	967.3	968.7	970.0	971.3	971.4
167.5°	975.8	975.4	975.4	975.4	975.4	975.4	976.8	978.1	979.4	980.7	980.7
170°	981.1	980.8	980.8	980.8	980.8	980.8	982.1	983.4	984.7	986.0	986.0
172.5°	984.1	983.8	983.9	984.0	984.2	984.3	985.6	986.9	988.3	989.6	989.5
175°	988.5	988.3	988.4	988.5	988.7	988.9	990.0	991.2	992.3	993.4	993.3
177.5°	990.4	990.1	990.2	990.4	990.5	990.6	991.7	992.8	993.8	994.9	994.8
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	10.7	10.5	10.5	10.7	10.5	10.5	10.7	10.3	10.2	10.1	9.8
90°	21.1	21.5	21.8	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0
92.5°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	23.1	22.0	20.9
95°	28.0	28.0	28.0	28.0	28.0	28.0	28.0	28.0	27.4	26.3	25.2
97.5°	29.9	30.1	30.2	30.3	30.2	30.1	29.9	29.7	28.9	27.6	26.4
100°	30.4	30.6	30.8	30.9	30.8	30.6	30.4	30.3	29.6	28.3	27.0
102.5°	30.6	30.9	31.2	31.6	31.2	30.9	30.6	30.3	32.2	36.3	40.3
105°	31.5	31.8	32.1	32.4	32.1	31.8	31.5	31.1	45.4	74.5	103.4
107.5°	167.4	145.5	123.7	101.8	123.7	145.5	167.4	189.2	210.8	232.1	253.3
110°	272.9	249.5	226.0	202.6	226.0	249.5	272.9	296.3	310.8	316.1	321.5



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	362.5	357.5	352.6	347.7	352.6	357.5	362.5	367.4	369.9	369.8	369.7
115°	431.3	432.0	432.6	433.3	432.6	432.0	431.3	430.6	429.5	427.9	426.2
117.5°	481.0	481.1	481.2	481.4	481.2	481.1	481.0	480.8	480.0	478.8	477.5
120°	514.3	514.3	514.3	514.3	514.3	514.3	514.3	514.3	513.7	512.4	511.0
122.5°	546.4	546.5	546.7	546.8	546.7	546.5	546.4	546.2	545.7	544.8	543.8
125°	591.4	591.8	592.1	592.5	592.1	591.8	591.4	591.2	590.8	590.5	590.1
127.5°	637.3	637.1	636.7	636.4	636.7	637.1	637.3	637.6	637.5	637.1	636.5
130°	665.6	665.3	665.0	664.7	665.0	665.3	665.6	666.0	665.8	665.2	664.5
132.5°	692.0	691.5	691.1	690.6	691.1	691.5	692.0	692.4	692.3	691.6	691.0
135°	731.7	731.2	730.8	730.3	730.8	731.2	731.7	732.2	732.2	731.7	731.2
137.5°	768.5	768.2	767.9	767.5	767.9	768.2	768.5	768.8	768.6	767.8	767.0
140°	790.9	790.6	790.2	789.9	790.2	790.6	790.9	791.3	791.1	790.4	789.8
142.5°	811.9	811.4	811.1	810.6	811.1	811.4	811.9	812.4	812.4	811.8	811.3
145°	842.3	842.3	842.3	842.3	842.3	842.3	842.3	842.3	842.1	841.8	841.4
147.5°	868.1	867.3	866.6	865.8	866.6	867.3	868.1	868.8	869.0	868.7	868.4
150°	885.0	884.5	884.0	883.5	884.0	884.5	885.0	885.5	885.5	885.2	884.9
152.5°	899.9	899.2	898.4	897.7	898.4	899.2	899.9	900.7	900.8	900.1	899.6
155°	920.4	919.4	918.4	917.4	918.4	919.4	920.4	921.3	921.4	920.6	919.8
157.5°	937.9	936.6	935.4	934.1	935.4	936.6	937.9	939.1	939.3	938.3	937.4
160°	948.1	947.0	945.8	944.7	945.8	947.0	948.1	949.2	949.3	948.4	947.3
162.5°	957.7	956.7	955.7	954.7	955.7	956.7	957.7	958.8	958.7	957.6	956.5
165°	970.3	969.0	967.9	966.8	967.9	969.0	970.3	971.4	971.3	970.0	968.7
167.5°	979.4	978.1	976.8	975.4	976.8	978.1	979.4	980.7	980.7	979.4	978.1
170°	984.7	983.4	982.1	980.8	982.1	983.4	984.7	986.0	986.0	984.7	983.4
172.5°	988.1	986.7	985.1	983.7	985.1	986.7	988.1	989.5	989.6	988.3	986.9
175°	992.1	990.8	989.5	988.2	989.5	990.8	992.1	993.3	993.4	992.3	991.2
177.5°	993.4	992.1	990.8	989.5	990.8	992.1	993.4	994.8	994.9	993.8	992.8
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	9.6	9.3	9.0	8.5	7.9	7.3	6.4	6.2	5.9	6.3	5.7
90°	18.4	17.7	15.6	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8
92.5°	19.9	18.9	17.2	15.6	14.0	12.4	11.9	12.3	12.8	13.3	13.7
95°	24.0	22.8	21.0	19.2	17.4	15.6	18.1	24.8	31.5	38.3	45.0
97.5°	25.1	23.8	35.5	47.3	59.1	70.9	78.3	81.3	84.4	87.4	90.3
100°	25.6	24.3	49.9	75.4	100.9	126.5	137.6	134.3	131.1	127.8	124.5
102.5°	44.4	48.4	76.3	104.2	132.2	160.1	172.9	170.5	168.1	165.8	163.4
105°	132.4	161.4	176.1	190.9	205.6	220.4	226.8	225.0	223.2	221.4	219.6
107.5°	274.6	295.8	293.4	291.2	288.8	286.4	284.6	283.1	281.7	280.3	278.8
110°	327.0	332.3	330.5	328.8	327.0	325.1	323.6	322.3	320.9	319.6	318.3



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.6	369.5	367.7	365.9	364.1	362.2	360.8	359.6	358.4	357.2	356.1
115°	424.6	423.0	421.5	420.0	418.6	417.1	415.8	414.9	413.9	412.9	411.9
117.5°	476.2	474.9	474.1	473.3	472.6	471.8	470.8	469.7	468.4	467.2	466.0
120°	509.7	508.4	507.9	507.5	507.0	506.5	505.5	504.0	502.6	501.1	499.6
122.5°	543.0	542.1	541.4	540.8	540.2	539.5	538.7	537.4	536.2	535.0	533.8
125°	589.8	589.5	588.8	588.1	587.6	586.9	585.9	584.6	583.2	581.9	580.7
127.5°	636.0	635.5	634.7	634.0	633.1	632.4	631.3	630.0	628.7	627.4	626.0
130°	663.8	663.2	662.5	661.9	661.2	660.5	659.6	658.3	657.0	655.6	654.3
132.5°	690.4	689.8	689.2	688.6	688.2	687.6	686.7	685.4	684.1	682.8	681.5
135°	730.8	730.3	729.6	729.0	728.3	727.6	726.8	725.9	724.8	723.9	722.8
137.5°	766.3	765.4	765.1	764.8	764.4	764.0	763.2	762.0	760.7	759.5	758.3
140°	789.1	788.4	788.0	787.5	787.0	786.5	785.8	784.8	783.8	782.8	781.8
142.5°	810.8	810.3	809.7	809.3	808.8	808.3	807.6	806.6	805.6	804.6	803.6
145°	841.1	840.7	840.5	840.1	839.8	839.4	838.8	837.5	836.4	835.3	834.2
147.5°	868.1	867.7	867.4	867.0	866.8	866.5	865.9	865.2	864.4	863.7	862.9
150°	884.6	884.3	883.9	883.6	883.3	883.0	882.5	882.0	881.6	881.1	880.5
152.5°	899.0	898.4	898.2	898.0	897.8	897.6	897.4	897.2	896.9	896.7	896.5
155°	919.0	918.1	917.9	917.8	917.7	917.5	917.6	917.9	918.2	918.6	918.9
157.5°	936.4	935.4	935.6	935.8	935.9	936.0	936.1	936.1	936.2	936.2	936.2
160°	946.4	945.4	945.6	945.7	945.9	946.0	946.2	946.4	946.6	946.7	946.9
162.5°	955.4	954.2	954.4	954.6	954.7	954.9	955.2	955.6	956.0	956.5	956.9
165°	967.3	966.0	966.2	966.4	966.6	966.7	967.0	967.5	968.0	968.5	969.0
167.5°	976.8	975.4	975.4	975.4	975.4	975.4	975.8	976.5	977.1	977.8	978.5
170°	982.1	980.8	980.8	980.8	980.8	980.8	981.1	981.8	982.4	983.1	983.7
172.5°	985.6	984.3	984.2	984.0	983.9	983.8	984.1	984.9	985.7	986.5	987.2
175°	990.0	988.9	988.7	988.5	988.4	988.3	988.5	989.4	990.2	991.0	991.8
177.5°	991.7	990.6	990.5	990.4	990.2	990.1	990.4	991.1	991.7	992.4	993.0
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.2	4.5	4.6	4.4	4.8	4.9	5.5	5.6	5.8	6.1	5.9
90°	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0
92.5°	13.3	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.9	19.9	20.9
95°	38.3	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0	25.2
97.5°	87.4	84.4	81.3	78.3	70.9	59.1	47.3	35.5	23.8	25.1	26.4
100°	127.8	131.1	134.3	137.6	126.5	100.9	75.4	49.9	24.3	25.6	27.0
102.5°	165.8	168.1	170.5	172.9	160.1	132.2	104.2	76.3	48.4	44.4	40.3
105°	221.4	223.2	225.0	226.8	220.4	205.6	190.9	176.1	161.4	132.4	103.4
107.5°	280.3	281.7	283.1	284.6	286.4	288.8	291.2	293.4	295.8	274.6	253.3
110°	319.6	320.9	322.3	323.6	325.1	327.0	328.8	330.5	332.3	327.0	321.5





TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.2	358.4	359.6	360.8	362.2	364.1	365.9	367.7	369.5	369.6	369.7
115°	412.9	413.9	414.9	415.8	417.1	418.6	420.0	421.5	423.0	424.6	426.2
117.5°	467.2	468.4	469.7	470.8	471.8	472.6	473.3	474.1	474.9	476.2	477.5
120°	501.1	502.6	504.0	505.5	506.5	507.0	507.5	507.9	508.4	509.7	511.0
122.5°	535.0	536.2	537.4	538.7	539.5	540.2	540.8	541.4	542.1	543.0	543.8
125°	581.9	583.2	584.6	585.9	586.9	587.6	588.1	588.8	589.5	589.8	590.1
127.5°	627.4	628.7	630.0	631.3	632.4	633.1	634.0	634.7	635.5	636.0	636.5
130°	655.6	657.0	658.3	659.6	660.5	661.2	661.9	662.5	663.2	663.8	664.5
132.5°	682.8	684.1	685.4	686.7	687.6	688.2	688.6	689.2	689.8	690.4	691.0
135°	723.9	724.8	725.9	726.8	727.6	728.3	729.0	729.6	730.3	730.8	731.2
137.5°	759.5	760.7	762.0	763.2	764.0	764.4	764.8	765.1	765.4	766.3	767.0
140°	782.8	783.8	784.8	785.8	786.5	787.0	787.5	788.0	788.4	789.1	789.8
142.5°	804.6	805.6	806.6	807.6	808.3	808.8	809.3	809.7	810.3	810.8	811.3
145°	835.3	836.4	837.5	838.8	839.4	839.8	840.1	840.5	840.7	841.1	841.4
147.5°	863.7	864.4	865.2	865.9	866.5	866.8	867.0	867.4	867.7	868.1	868.4
150°	881.1	881.6	882.0	882.5	883.0	883.3	883.6	883.9	884.3	884.6	884.9
152.5°	896.7	896.9	897.2	897.4	897.6	897.8	898.0	898.2	898.4	899.0	899.6
155°	918.6	918.2	917.9	917.6	917.5	917.7	917.8	917.9	918.1	919.0	919.8
157.5°	936.2	936.2	936.1	936.1	936.0	935.9	935.8	935.6	935.4	936.4	937.4
160°	946.7	946.6	946.4	946.2	946.0	945.9	945.7	945.6	945.4	946.4	947.3
162.5°	956.5	956.0	955.6	955.2	954.9	954.7	954.6	954.4	954.2	955.4	956.5
165°	968.5	968.0	967.5	967.0	966.7	966.6	966.4	966.2	966.0	967.3	968.7
167.5°	977.8	977.1	976.5	975.8	975.4	975.4	975.4	975.4	975.4	976.8	978.1
170°	983.1	982.4	981.8	981.1	980.8	980.8	980.8	980.8	980.8	982.1	983.4
172.5°	986.5	985.7	984.9	984.1	983.8	983.9	984.0	984.2	984.3	985.6	986.9
175°	991.0	990.2	989.4	988.5	988.3	988.4	988.5	988.7	988.9	990.0	991.2
177.5°	992.4	991.7	991.1	990.4	990.1	990.2	990.4	990.5	990.6	991.7	992.8
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8	991.8



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	6.0	6.1	6.1	6.1	6.0	6.5	6.2
90°	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	22.0	23.1	23.7	23.8	24.0	24.2	24.5
95°	26.3	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	27.6	28.9	29.7	29.9	30.1	30.2	30.3
100°	28.3	29.6	30.3	30.4	30.6	30.8	30.9
102.5°	36.3	32.2	30.3	30.6	30.9	31.2	31.6
105°	74.5	45.4	31.1	31.5	31.8	32.1	32.4
107.5°	232.1	210.8	189.2	167.4	145.5	123.7	101.8
110°	316.1	310.8	296.3	272.9	249.5	226.0	202.6



TEST NUMBER: P332252-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.8	369.9	367.4	362.5	357.5	352.6	347.7
115°	427.9	429.5	430.6	431.3	432.0	432.6	433.3
117.5°	478.8	480.0	480.8	481.0	481.1	481.2	481.4
120°	512.4	513.7	514.3	514.3	514.3	514.3	514.3
122.5°	544.8	545.7	546.2	546.4	546.5	546.7	546.8
125°	590.5	590.8	591.2	591.4	591.8	592.1	592.5
127.5°	637.1	637.5	637.6	637.3	637.1	636.7	636.4
130°	665.2	665.8	666.0	665.6	665.3	665.0	664.7
132.5°	691.6	692.3	692.4	692.0	691.5	691.1	690.6
135°	731.7	732.2	732.2	731.7	731.2	730.8	730.3
137.5°	767.8	768.6	768.8	768.5	768.2	767.9	767.5
140°	790.4	791.1	791.3	790.9	790.6	790.2	789.9
142.5°	811.8	812.4	812.4	811.9	811.4	811.1	810.6
145°	841.8	842.1	842.3	842.3	842.3	842.3	842.3
147.5°	868.7	869.0	868.8	868.1	867.3	866.6	865.8
150°	885.2	885.5	885.5	885.0	884.5	884.0	883.5
152.5°	900.1	900.8	900.7	899.9	899.2	898.4	897.7
155°	920.6	921.4	921.3	920.4	919.4	918.4	917.4
157.5°	938.3	939.3	939.1	937.9	936.6	935.4	934.1
160°	948.4	949.3	949.2	948.1	947.0	945.8	944.7
162.5°	957.6	958.7	958.8	957.7	956.7	955.7	954.7
165°	970.0	971.3	971.4	970.3	969.0	967.9	966.8
167.5°	979.4	980.7	980.7	979.4	978.1	976.8	975.4
170°	984.7	986.0	986.0	984.7	983.4	982.1	980.8
172.5°	988.3	989.6	989.5	988.1	986.7	985.1	983.7
175°	992.3	993.4	993.3	992.1	990.8	989.5	988.2
177.5°	993.8	994.9	994.8	993.4	992.1	990.8	989.5
180°	991.8	991.8	991.8	991.8	991.8	991.8	991.8

(END OF REPORT)