

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832094

Luminaire Tested: S123RDIP-S340D365U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832094  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U835-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2787.0 lumens  
Efficiency: N/A  
Efficacy: 124.4 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 22.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				53
1	99	95	92	88	92	88	85	83	76	73	71	64	62	61	53	52	51	46				46
2	91	84	78	74	84	78	73	69	67	64	61	57	55	52	48	46	45	40				40
3	84	75	68	63	77	70	64	59	60	56	52	52	48	45	43	41	39	35				35
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	39	37	35	31				31
5	71	60	53	47	66	56	50	45	49	44	40	42	38	35	36	33	31	28				28
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25				25
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23				23
8	57	46	38	33	53	43	36	32	38	32	29	33	29	26	29	25	23	21				21
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	23	21	19				19
10	50	39	32	27	47	37	30	26	33	27	24	29	25	22	25	22	20	18				18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11958	11958	11958	11958	11958
5°	14199	13746	12034	9728	9031
10°	12865	13962	11973	7794	6686
15°	8857	11972	11847	6370	5289
20°	6161	9216	11609	5371	4648
25°	4696	7024	11263	4774	4284
30°	4088	5615	10829	4432	3969
35°	3753	4737	10217	4144	3681
40°	3424	4231	9414	3863	3417
45°	3092	3870	8549	3596	3154
50°	2807	3570	7529	3332	2830
55°	2539	3278	6548	3078	2428
60°	2275	2982	5688	2794	2295
65°	2099	2646	4895	2511	2170
70°	1706	2285	4271	2272	1762
75°	1497	1817	3618	1884	1551
80°	1358	1537	2963	1581	1469
85°	1235	1346	2248	1433	1346

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 9021 cd/sqm



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.3	3.6
10°-20°	234.3	8.4
20°-30°	268.8	9.6
30°-40°	265.0	9.5
40°-50°	233.7	8.4
50°-60°	179.8	6.5
60°-70°	118.2	4.2
70°-80°	57.4	2.1
80°-90°	15.4	0.6
90°-100°	94.7	3.4
100°-110°	277.3	10.0
110°-120°	270.8	9.7
120°-130°	215.7	7.7
130°-140°	170.2	6.1
140°-150°	126.9	4.6
150°-160°	88.5	3.2
160°-170°	52.0	1.9
170°-180°	16.9	0.6
0°-30°	604.4	21.7
0°-40°	869.4	31.2
0°-60°	1282.9	46.0
0°-90°	1473.9	52.9
90°-120°	642.9	23.1
90°-150°	1155.7	41.5
90°-180°	1313.0	47.1
0°-180°	2787.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1111	1111	1111	1111	1111	
5°	1314	1272	1114	900	836	120
15°	795	1074	1063	572	475	224
25°	395	591	948	402	361	187
35°	286	360	778	315	280	178
45°	203	254	562	236	207	158
55°	135	175	349	164	129	121
65°	82	104	192	99	85	81
75°	36	44	87	45	37	39
85°	10	11	18	12	11	11
90°	10	9	1	9	10	6
95°	41	210	12	210	41	67
105°	450	284	41	284	450	448
115°	547	217	72	217	547	533
125°	431	203	101	203	431	390
135°	350	200	118	200	350	271
145°	273	198	135	198	273	173
155°	226	191	153	191	226	106
165°	198	183	167	183	198	56
175°	178	176	174	176	178	17
180°	175	175	175	175	175	



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1231.2	1227.3	1223.4	1222.3	1221.2	1217.5	1213.9	1205.7	1197.5	1189.0	1180.6
5°	1314.1	1314.5	1315.0	1313.8	1312.7	1307.9	1303.1	1293.1	1283.1	1272.2	1261.2
7.5°	1288.6	1295.9	1303.1	1304.5	1305.9	1309.5	1313.2	1310.9	1308.6	1304.5	1300.4
10°	1177.0	1176.5	1176.1	1184.3	1192.5	1216.8	1241.2	1253.7	1266.2	1277.4	1288.6
12.5°	994.8	995.5	996.1	1023.0	1049.9	1072.9	1095.9	1127.8	1159.7	1194.1	1228.4
15°	794.8	806.0	817.1	841.1	865.0	899.6	934.2	977.0	1019.8	1074.3	1128.7
17.5°	652.7	657.5	662.3	685.3	708.3	741.1	773.9	822.4	870.9	941.0	1011.2
20°	537.9	542.3	546.6	563.2	579.8	611.3	642.7	688.9	735.2	804.6	874.1
22.5°	449.1	457.5	466.0	477.1	488.3	511.1	533.8	581.0	628.1	691.4	754.7
25°	395.4	399.2	403.1	412.7	422.2	444.1	466.0	497.2	528.4	591.4	654.5
27.5°	358.9	360.1	361.2	368.3	375.3	389.4	403.6	432.5	461.4	513.3	565.3
30°	328.9	330.9	333.0	338.4	343.9	354.1	364.4	384.9	405.4	451.8	498.3
32.5°	305.6	306.8	307.9	312.5	317.0	324.5	332.0	348.2	364.4	399.9	435.4
35°	285.6	285.8	286.0	289.5	292.9	300.2	307.5	320.9	334.3	360.5	386.7
37.5°	262.8	264.4	266.0	268.5	271.0	277.4	283.8	294.7	305.6	327.3	348.9
40°	243.7	245.1	246.4	249.4	252.3	257.3	262.4	272.4	282.4	301.1	319.8
42.5°	224.6	225.5	226.4	229.3	232.3	238.4	244.6	252.6	260.5	276.0	291.5
45°	203.1	205.4	207.7	210.9	214.1	219.3	224.6	232.8	241.0	254.2	267.4
47.5°	185.4	186.5	187.7	190.4	193.1	199.5	205.9	213.2	220.5	232.8	245.1
50°	167.6	168.1	168.5	171.0	173.5	179.2	184.9	193.4	201.8	213.2	224.6
52.5°	150.8	151.9	153.0	155.5	158.1	161.9	165.8	174.5	183.1	194.3	205.4
55°	135.3	136.0	136.6	138.5	140.3	144.8	149.4	156.9	164.4	174.7	184.9
57.5°	120.7	121.6	122.5	123.9	125.3	129.4	133.5	140.1	146.7	156.9	167.2
60°	105.7	106.8	107.9	109.5	111.1	114.3	117.5	123.4	129.4	138.5	147.6
62.5°	94.7	95.0	95.2	96.6	97.9	100.2	102.5	107.3	112.0	121.2	130.3
65°	82.4	83.1	83.8	84.5	85.2	87.0	88.8	92.9	97.0	103.9	110.7
67.5°	69.7	70.4	71.1	72.2	73.3	74.9	76.5	79.3	82.0	88.4	94.7
70°	54.2	54.2	54.2	56.0	57.8	60.6	63.3	65.4	67.4	72.6	77.9
72.5°	44.2	44.4	44.6	44.9	45.1	46.7	48.3	51.7	55.1	58.3	61.5
75°	36.0	36.2	36.4	36.7	36.9	37.3	37.8	38.9	40.1	43.7	47.4
77.5°	28.7	28.9	29.2	29.4	29.6	30.1	30.5	31.0	31.4	32.8	34.2
80°	21.9	22.1	22.3	22.5	22.8	23.0	23.2	23.7	24.1	24.8	25.5
82.5°	15.9	15.9	15.9	15.9	15.9	16.4	16.9	16.9	16.9	17.3	17.8
85°	10.0	10.0	10.0	10.2	10.5	10.5	10.5	10.7	10.9	10.9	10.9
87.5°	4.6	4.3	4.1	4.3	4.6	4.6	4.6	4.8	5.0	5.0	5.0
90°	10.2	10.6	10.2	9.9	10.2	9.5	9.2	8.8	8.5	8.8	7.8
92.5°	18.7	19.4	19.1	20.5	21.2	23.7	27.2	35.0	49.1	65.7	72.8
95°	41.0	42.4	44.9	48.1	54.8	67.5	86.2	127.2	170.0	209.6	186.6
97.5°	84.1	88.0	96.5	109.9	133.6	173.9	220.5	292.2	333.2	322.3	240.7
100°	221.6	221.2	235.0	260.8	296.5	346.7	388.0	416.6	404.3	334.7	226.2
102.5°	350.9	361.2	372.1	391.2	417.0	444.2	464.0	458.0	407.8	311.7	205.0
105°	449.5	451.3	462.6	476.0	492.3	501.4	494.7	459.4	385.5	284.1	188.4
107.5°	513.8	517.7	522.3	528.7	530.8	521.2	493.7	438.2	353.7	259.7	176.3
110°	550.6	551.3	552.0	549.2	539.3	514.5	470.0	405.0	324.1	239.6	170.0



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.0	557.6	554.1	543.9	523.7	490.1	438.9	372.1	298.3	226.2	166.4
115°	546.7	544.9	537.8	522.3	495.8	457.3	405.3	343.8	278.5	217.3	166.1
117.5°	521.9	519.5	508.9	491.6	464.0	424.1	376.4	321.9	265.4	211.3	166.4
120°	489.4	487.3	478.8	459.0	431.1	395.4	353.0	305.3	255.5	207.4	167.9
122.5°	459.0	456.2	446.7	429.4	405.3	372.8	334.3	292.2	247.4	205.0	170.3
125°	431.1	428.7	419.8	404.3	381.7	353.4	319.5	280.9	240.7	202.8	172.8
127.5°	407.1	405.0	396.8	383.4	362.9	336.8	305.7	270.7	234.3	201.8	175.6
130°	387.3	384.5	377.1	364.3	345.6	321.6	293.0	261.1	229.3	200.7	178.5
132.5°	367.9	366.1	359.7	347.0	329.7	307.1	280.9	252.3	224.8	200.4	180.6
135°	349.5	347.0	340.7	330.1	312.7	292.6	269.6	244.5	220.9	200.0	182.7
137.5°	330.1	327.9	322.6	311.7	296.8	278.8	258.3	237.1	217.3	199.3	184.1
140°	309.6	309.9	304.3	294.4	280.9	265.7	248.8	230.8	214.1	199.0	185.5
142.5°	290.5	290.8	285.9	277.4	266.4	253.7	239.6	224.8	211.3	198.2	186.6
145°	273.2	272.5	269.6	262.2	253.4	243.1	231.8	220.2	208.8	197.5	186.9
147.5°	258.3	258.0	255.1	249.8	242.8	235.4	225.8	216.3	206.4	196.5	186.9
150°	245.6	245.6	243.5	239.6	234.3	227.6	220.2	212.0	203.9	195.1	186.9
152.5°	235.0	235.0	233.9	230.4	226.5	221.2	214.9	208.1	201.1	193.3	185.9
155°	226.5	226.2	225.5	222.6	219.4	215.2	209.9	204.3	198.2	191.2	185.2
157.5°	218.4	218.4	217.7	215.6	212.7	209.2	205.0	200.0	195.1	189.4	184.1
160°	210.6	211.0	211.0	208.8	206.4	203.9	200.4	196.5	191.9	187.3	183.4
162.5°	203.5	203.9	203.9	202.1	200.7	198.6	195.4	192.2	188.7	185.2	182.0
165°	197.5	197.5	197.9	196.5	195.1	193.3	190.8	188.7	185.9	183.1	180.6
167.5°	191.5	191.5	191.9	190.8	190.1	188.7	187.3	185.5	183.1	180.9	179.2
170°	186.2	186.2	186.6	185.9	185.5	184.8	183.4	182.3	180.6	178.8	177.8
172.5°	181.3	181.6	182.3	181.6	181.6	181.3	180.2	179.5	178.1	177.0	176.7
175°	177.8	178.1	178.5	178.1	178.1	178.1	177.4	177.0	176.3	175.6	175.6
177.5°	175.3	175.3	176.0	175.6	176.0	176.0	175.6	175.3	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1179.5	1178.3	1167.4	1156.5	1145.8	1135.1	1127.1	1119.1	1105.7	1092.3	1083.8
5°	1252.6	1243.9	1226.6	1209.3	1183.4	1157.4	1135.5	1113.7	1085.9	1058.1	1034.9
7.5°	1293.3	1286.3	1265.3	1244.4	1210.0	1175.6	1141.4	1107.3	1066.3	1025.3	990.2
10°	1294.5	1300.4	1283.1	1265.8	1227.1	1188.4	1141.9	1095.4	1040.3	985.2	939.9
12.5°	1254.0	1279.5	1275.8	1272.2	1232.8	1193.4	1136.9	1080.4	1012.8	945.1	888.4
15°	1178.1	1227.5	1242.1	1256.7	1224.1	1191.5	1127.3	1063.1	983.6	904.1	839.0
17.5°	1080.4	1149.6	1188.1	1226.6	1202.9	1179.3	1108.9	1038.5	949.0	859.5	788.7
20°	964.7	1055.4	1115.7	1176.1	1167.4	1158.8	1086.1	1013.5	916.9	820.3	743.6
22.5°	850.4	946.0	1029.4	1112.7	1121.6	1130.5	1057.2	983.8	878.2	772.5	694.4
25°	751.8	849.0	948.3	1047.6	1067.7	1087.7	1018.0	948.3	838.8	729.2	651.6
27.5°	657.7	750.2	859.5	968.8	1005.3	1041.7	977.9	914.2	800.1	686.0	608.5
30°	581.0	663.6	775.2	886.8	937.6	988.4	929.9	871.3	758.2	645.0	569.1
32.5°	509.5	583.5	695.5	807.6	866.6	925.5	875.0	824.4	715.6	606.7	531.8
35°	453.0	519.3	623.8	728.3	794.4	860.4	819.0	777.5	671.2	564.8	494.0
37.5°	404.5	460.0	558.2	656.4	726.5	796.6	762.0	727.4	627.4	527.5	460.5
40°	364.4	409.0	500.4	591.7	660.5	729.2	699.6	670.0	580.5	491.0	428.4
42.5°	330.0	368.5	450.5	532.5	595.5	658.6	639.0	619.5	538.4	457.3	399.2
45°	299.7	332.0	404.2	476.4	534.5	592.6	577.1	561.6	491.7	421.8	368.5
47.5°	272.8	300.6	365.1	429.5	481.7	533.8	519.5	505.1	447.3	389.4	340.9
50°	248.2	271.9	325.7	379.4	426.3	473.2	461.4	449.6	401.7	353.9	312.0
52.5°	225.0	244.6	292.9	341.2	379.0	416.8	407.7	398.5	361.7	324.8	286.7
55°	202.9	220.9	261.7	302.4	334.8	367.1	358.0	348.9	320.2	291.5	258.0
57.5°	182.9	198.6	231.6	264.6	290.4	316.1	311.8	307.5	283.5	259.6	232.1
60°	161.7	175.8	204.3	232.8	253.5	274.2	269.2	264.2	247.1	230.0	206.3
62.5°	142.8	155.3	178.1	200.9	217.7	234.6	230.9	227.3	214.3	201.3	181.7
65°	123.0	135.3	153.7	172.2	185.4	198.6	195.4	192.2	182.4	172.6	156.9
67.5°	105.0	115.2	131.2	147.1	156.0	164.9	163.1	161.2	153.7	146.2	133.9
70°	86.8	95.7	108.9	122.1	128.2	134.4	135.1	135.7	128.9	122.1	113.0
72.5°	68.6	75.6	87.9	100.2	105.0	109.8	109.5	109.3	105.2	101.1	92.9
75°	52.6	57.8	67.4	77.0	81.1	85.2	86.1	87.0	83.1	79.3	74.7
77.5°	37.8	41.4	48.7	56.0	60.6	65.1	65.6	66.0	64.2	62.4	58.1
80°	26.6	27.8	32.3	36.9	41.7	46.5	47.1	47.8	46.0	44.2	41.4
82.5°	18.4	19.1	20.7	22.3	26.2	30.1	31.0	31.9	31.0	30.1	27.1
85°	11.2	11.4	12.1	12.8	14.6	16.4	17.3	18.2	17.8	17.3	15.7
87.5°	5.0	5.0	5.2	5.5	5.9	6.4	7.5	8.7	8.0	7.3	6.6
90°	6.7	5.7	4.6	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	54.4	35.7	24.4	18.0	14.5	11.3	7.8	5.3	7.8	11.3	14.5
95°	128.6	76.0	45.9	32.2	23.0	17.0	13.1	12.0	13.1	17.0	23.0
97.5°	143.1	82.0	52.3	37.1	27.9	22.6	19.4	19.1	19.4	22.6	27.9
100°	133.2	80.9	56.2	42.4	33.9	29.0	26.5	26.2	26.5	29.0	33.9
102.5°	124.7	82.3	60.8	48.4	41.0	36.4	34.3	33.6	34.3	36.4	41.0
105°	121.6	85.2	66.1	55.1	48.4	44.2	42.1	41.0	42.1	44.2	48.4
107.5°	120.9	89.8	72.8	62.5	56.2	51.9	49.8	48.8	49.8	51.9	56.2
110°	122.6	95.8	79.9	70.0	64.0	60.1	58.3	57.2	58.3	60.1	64.0





TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.2	101.8	87.3	77.7	71.7	67.8	66.1	65.0	66.1	67.8	71.7
115°	130.0	108.5	95.1	85.5	79.5	76.0	73.9	72.4	73.9	76.0	79.5
117.5°	135.0	115.6	102.1	93.3	86.6	83.4	81.6	79.9	81.6	83.4	86.6
120°	140.6	122.3	109.5	100.7	94.0	90.5	88.7	87.6	88.7	90.5	94.0
122.5°	145.9	129.3	117.0	107.4	101.1	97.2	95.4	94.4	95.4	97.2	101.1
125°	151.6	136.1	123.7	114.1	107.4	103.5	101.4	100.7	101.4	103.5	107.4
127.5°	156.2	142.1	130.0	120.5	113.1	109.2	106.7	105.7	106.7	109.2	113.1
130°	160.8	147.4	135.7	126.2	118.7	114.5	111.3	110.3	111.3	114.5	118.7
132.5°	165.0	152.0	140.6	131.5	124.0	118.7	115.2	113.8	115.2	118.7	124.0
135°	168.6	156.5	145.6	136.1	128.6	123.3	119.4	118.0	119.4	123.3	128.6
137.5°	171.4	159.7	149.1	140.3	132.9	127.2	123.3	121.9	123.3	127.2	132.9
140°	173.5	162.9	152.7	143.8	136.8	131.1	127.6	125.8	127.6	131.1	136.8
142.5°	175.6	165.4	155.5	147.4	140.3	135.3	131.5	130.0	131.5	135.3	140.3
145°	177.0	167.5	158.3	150.2	144.2	138.9	135.7	134.6	135.7	138.9	144.2
147.5°	178.1	169.3	160.8	153.7	147.7	143.1	139.9	139.2	139.9	143.1	147.7
150°	178.5	171.0	162.9	156.5	151.6	147.0	144.2	143.8	144.2	147.0	151.6
152.5°	179.2	172.1	165.4	159.4	155.1	151.2	148.4	148.4	148.4	151.2	155.1
155°	179.2	173.5	167.5	162.6	158.7	155.1	153.0	153.0	153.0	155.1	158.7
157.5°	179.5	174.2	169.3	165.4	161.8	158.7	156.9	156.5	156.9	158.7	161.8
160°	179.5	175.3	171.0	167.5	165.0	162.2	160.8	160.8	160.8	162.2	165.0
162.5°	179.2	175.6	172.1	169.3	167.1	165.0	164.0	164.0	164.0	165.0	167.1
165°	178.5	176.0	173.2	170.7	169.3	167.5	166.8	167.1	166.8	167.5	169.3
167.5°	178.1	176.0	173.9	172.1	171.0	169.6	169.3	169.6	169.3	169.6	171.0
170°	177.0	175.6	173.9	173.2	172.4	171.4	171.0	171.7	171.0	171.4	172.4
172.5°	176.7	175.6	174.2	173.9	173.5	172.8	172.8	173.2	172.8	172.8	173.5
175°	176.0	175.3	174.6	174.2	174.2	173.5	173.9	174.2	173.9	173.5	174.2
177.5°	175.6	174.9	174.6	174.6	174.6	174.2	174.6	174.9	174.6	174.2	174.6
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1075.4	1062.4	1049.4	1040.1	1030.8	1019.1	1007.5	1007.1	1006.6	998.0	989.3
5°	1011.6	989.1	966.5	944.4	922.4	900.3	878.2	873.2	868.2	860.6	853.1
7.5°	955.2	919.2	883.2	854.9	826.7	804.6	782.5	767.5	752.5	740.8	729.2
10°	894.6	849.9	805.3	771.1	737.0	713.1	689.1	671.8	654.5	646.3	638.1
12.5°	831.7	783.2	734.7	701.2	667.7	639.0	610.3	594.6	578.9	567.5	556.1
15°	773.9	721.7	669.6	634.0	598.5	571.6	544.8	529.0	513.3	501.9	490.6
17.5°	717.8	665.2	612.6	576.6	540.7	516.3	491.9	476.7	461.4	454.3	447.3
20°	666.8	613.8	560.7	526.8	492.8	468.9	445.0	436.8	428.6	422.0	415.4
22.5°	616.3	565.3	514.2	481.7	449.1	431.8	414.5	407.9	401.3	396.3	391.3
25°	573.9	523.1	472.3	443.9	415.4	402.0	388.5	384.2	379.9	374.9	369.9
27.5°	531.1	482.8	434.5	411.8	389.0	378.1	367.1	361.7	356.2	352.1	348.0
30°	493.3	448.7	404.0	385.1	366.2	356.6	347.1	341.2	335.2	331.4	327.5
32.5°	456.9	417.2	377.6	361.4	345.3	335.9	326.6	320.9	315.2	310.6	306.1
35°	423.1	388.8	354.4	339.6	324.8	315.4	306.1	300.4	294.7	290.1	285.6
37.5°	393.5	362.3	331.1	317.2	303.4	295.2	287.0	281.0	275.1	270.3	265.5
40°	365.8	338.2	310.6	297.2	283.8	274.9	266.0	260.8	255.5	251.2	246.9
42.5°	341.2	315.9	290.6	277.4	264.2	255.8	247.3	241.2	235.0	232.5	230.0
45°	315.2	292.9	270.6	257.8	245.1	236.2	227.3	222.0	216.8	214.5	212.3
47.5°	292.4	271.7	251.0	238.4	225.9	217.9	210.0	205.9	201.8	198.6	195.4
50°	270.1	250.1	230.0	217.9	205.9	199.0	192.2	187.2	182.2	179.9	177.6
52.5°	248.7	230.5	212.3	200.0	187.7	181.1	174.5	170.1	165.8	161.0	156.2
55°	224.6	208.6	192.7	181.7	170.8	164.0	157.1	152.1	147.1	142.1	137.1
57.5°	204.5	188.8	173.1	163.3	153.5	146.9	140.3	134.8	129.4	125.3	121.2
60°	182.6	169.0	155.3	145.8	136.2	129.8	123.4	118.2	113.0	110.9	108.9
62.5°	162.2	149.4	136.6	128.2	119.8	113.6	107.5	104.1	100.7	99.3	97.9
65°	141.2	130.3	119.3	111.6	103.9	98.6	93.4	91.8	90.2	89.0	87.9
67.5°	121.6	112.3	102.9	96.1	89.3	85.6	82.0	80.2	78.3	77.0	75.6
70°	103.9	95.7	87.5	81.5	75.6	72.2	68.8	67.2	65.6	63.1	60.6
72.5°	84.7	78.3	72.0	67.4	62.9	59.9	56.9	53.7	50.6	48.3	46.0
75°	70.1	63.8	57.4	53.1	48.7	45.3	41.9	40.8	39.6	38.9	38.3
77.5°	53.7	48.3	42.8	39.4	36.0	34.4	32.8	32.1	31.4	31.2	31.0
80°	38.7	34.2	29.6	27.8	26.0	25.5	25.1	24.6	24.1	23.9	23.7
82.5°	24.1	21.9	19.6	19.1	18.7	18.4	18.2	18.0	17.8	17.5	17.3
85°	14.1	13.2	12.3	12.1	11.8	11.6	11.4	11.4	11.4	11.4	11.4
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.7	5.5
90°	3.9	4.6	5.7	6.7	7.8	8.8	8.5	8.8	9.2	9.5	10.2
92.5°	18.0	24.4	35.7	54.4	72.8	65.7	49.1	35.0	27.2	23.7	21.2
95°	32.2	45.9	76.0	128.6	186.6	209.6	170.0	127.2	86.2	67.5	54.8
97.5°	37.1	52.3	82.0	143.1	240.7	322.3	333.2	292.2	220.5	173.9	133.6
100°	42.4	56.2	80.9	133.2	226.2	334.7	404.3	416.6	388.0	346.7	296.5
102.5°	48.4	60.8	82.3	124.7	205.0	311.7	407.8	458.0	464.0	444.2	417.0
105°	55.1	66.1	85.2	121.6	188.4	284.1	385.5	459.4	494.7	501.4	492.3
107.5°	62.5	72.8	89.8	120.9	176.3	259.7	353.7	438.2	493.7	521.2	530.8
110°	70.0	79.9	95.8	122.6	170.0	239.6	324.1	405.0	470.0	514.5	539.3



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	77.7	87.3	101.8	126.2	166.4	226.2	298.3	372.1	438.9	490.1	523.7
115°	85.5	95.1	108.5	130.0	166.1	217.3	278.5	343.8	405.3	457.3	495.8
117.5°	93.3	102.1	115.6	135.0	166.4	211.3	265.4	321.9	376.4	424.1	464.0
120°	100.7	109.5	122.3	140.6	167.9	207.4	255.5	305.3	353.0	395.4	431.1
122.5°	107.4	117.0	129.3	145.9	170.3	205.0	247.4	292.2	334.3	372.8	405.3
125°	114.1	123.7	136.1	151.6	172.8	202.8	240.7	280.9	319.5	353.4	381.7
127.5°	120.5	130.0	142.1	156.2	175.6	201.8	234.3	270.7	305.7	336.8	362.9
130°	126.2	135.7	147.4	160.8	178.5	200.7	229.3	261.1	293.0	321.6	345.6
132.5°	131.5	140.6	152.0	165.0	180.6	200.4	224.8	252.3	280.9	307.1	329.7
135°	136.1	145.6	156.5	168.6	182.7	200.0	220.9	244.5	269.6	292.6	312.7
137.5°	140.3	149.1	159.7	171.4	184.1	199.3	217.3	237.1	258.3	278.8	296.8
140°	143.8	152.7	162.9	173.5	185.5	199.0	214.1	230.8	248.8	265.7	280.9
142.5°	147.4	155.5	165.4	175.6	186.6	198.2	211.3	224.8	239.6	253.7	266.4
145°	150.2	158.3	167.5	177.0	186.9	197.5	208.8	220.2	231.8	243.1	253.4
147.5°	153.7	160.8	169.3	178.1	186.9	196.5	206.4	216.3	225.8	235.4	242.8
150°	156.5	162.9	171.0	178.5	186.9	195.1	203.9	212.0	220.2	227.6	234.3
152.5°	159.4	165.4	172.1	179.2	185.9	193.3	201.1	208.1	214.9	221.2	226.5
155°	162.6	167.5	173.5	179.2	185.2	191.2	198.2	204.3	209.9	215.2	219.4
157.5°	165.4	169.3	174.2	179.5	184.1	189.4	195.1	200.0	205.0	209.2	212.7
160°	167.5	171.0	175.3	179.5	183.4	187.3	191.9	196.5	200.4	203.9	206.4
162.5°	169.3	172.1	175.6	179.2	182.0	185.2	188.7	192.2	195.4	198.6	200.7
165°	170.7	173.2	176.0	178.5	180.6	183.1	185.9	188.7	190.8	193.3	195.1
167.5°	172.1	173.9	176.0	178.1	179.2	180.9	183.1	185.5	187.3	188.7	190.1
170°	173.2	173.9	175.6	177.0	177.8	178.8	180.6	182.3	183.4	184.8	185.5
172.5°	173.9	174.2	175.6	176.7	176.7	177.0	178.1	179.5	180.2	181.3	181.6
175°	174.2	174.6	175.3	176.0	175.6	175.6	176.3	177.0	177.4	178.1	178.1
177.5°	174.6	174.6	174.9	175.6	174.9	174.6	174.9	175.3	175.6	176.0	176.0
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1110.9	1110.9	1110.9	1110.9
2.5°	987.0	984.8	983.8	982.9
5°	846.1	839.0	837.4	835.8
7.5°	726.3	723.3	713.5	703.7
10°	629.0	619.9	615.8	611.7
12.5°	547.7	539.3	537.9	536.6
15°	484.6	478.7	476.7	474.6
17.5°	443.2	439.1	436.6	434.1
20°	412.4	409.5	407.7	405.8
22.5°	389.0	386.7	385.3	384.0
25°	366.4	363.0	361.9	360.7
27.5°	345.0	342.1	340.9	339.8
30°	325.0	322.5	320.9	319.3
32.5°	303.1	300.2	299.3	298.3
35°	283.8	281.9	281.0	280.1
37.5°	263.3	261.0	259.6	258.3
40°	245.7	244.6	243.9	243.2
42.5°	228.0	225.9	225.7	225.5
45°	210.2	208.2	207.7	207.2
47.5°	193.6	191.8	191.5	191.3
50°	175.1	172.6	170.8	169.0
52.5°	154.0	151.7	150.1	148.5
55°	134.6	132.1	130.7	129.4
57.5°	120.0	118.9	118.2	117.5
60°	108.2	107.5	107.0	106.6
62.5°	97.2	96.6	96.6	96.6
65°	87.2	86.5	85.9	85.2
67.5°	74.2	72.9	72.6	72.4
70°	58.5	56.5	56.3	56.0
72.5°	45.8	45.5	45.1	44.6
75°	37.8	37.3	37.3	37.3
77.5°	30.5	30.1	30.1	30.1
80°	23.5	23.2	23.5	23.7
82.5°	17.3	17.3	17.1	16.9
85°	11.2	10.9	10.9	10.9
87.5°	5.5	5.5	5.5	5.5
90°	9.9	10.2	10.6	10.2
92.5°	20.5	19.1	19.4	18.7
95°	48.1	44.9	42.4	41.0
97.5°	109.9	96.5	88.0	84.1
100°	260.8	235.0	221.2	221.6
102.5°	391.2	372.1	361.2	350.9
105°	476.0	462.6	451.3	449.5
107.5°	528.7	522.3	517.7	513.8
110°	549.2	552.0	551.3	550.6



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	543.9	554.1	557.6	558.0
115°	522.3	537.8	544.9	546.7
117.5°	491.6	508.9	519.5	521.9
120°	459.0	478.8	487.3	489.4
122.5°	429.4	446.7	456.2	459.0
125°	404.3	419.8	428.7	431.1
127.5°	383.4	396.8	405.0	407.1
130°	364.3	377.1	384.5	387.3
132.5°	347.0	359.7	366.1	367.9
135°	330.1	340.7	347.0	349.5
137.5°	311.7	322.6	327.9	330.1
140°	294.4	304.3	309.9	309.6
142.5°	277.4	285.9	290.8	290.5
145°	262.2	269.6	272.5	273.2
147.5°	249.8	255.1	258.0	258.3
150°	239.6	243.5	245.6	245.6
152.5°	230.4	233.9	235.0	235.0
155°	222.6	225.5	226.2	226.5
157.5°	215.6	217.7	218.4	218.4
160°	208.8	211.0	211.0	210.6
162.5°	202.1	203.9	203.9	203.5
165°	196.5	197.9	197.5	197.5
167.5°	190.8	191.9	191.5	191.5
170°	185.9	186.6	186.2	186.2
172.5°	181.6	182.3	181.6	181.3
175°	178.1	178.5	178.1	177.8
177.5°	175.6	176.0	175.3	175.3
180°	174.6	174.6	174.6	174.6



TEST NUMBER: P832094

CATALOG NUMBER: S123RDIP-S340D365U835-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.63	10.46	10.58	11.42	12.65	14.30	15.13	15.24	16.08	17.31
	3H	10.85	11.60	11.81	12.56	13.82	15.80	16.54	16.75	17.50	18.76
	4H	11.24	11.94	12.21	12.90	14.17	16.29	16.99	17.26	17.95	19.22
	6H	11.52	12.16	12.50	13.13	14.41	16.60	17.24	17.58	18.21	19.49
	8H	11.61	12.22	12.59	13.21	14.48	16.68	17.29	17.66	18.28	19.55
	12H	11.66	12.24	12.65	13.22	14.52	16.71	17.29	17.70	18.27	19.57
4H	2H	10.36	11.06	11.33	12.02	13.29	14.29	14.99	15.27	15.96	17.23
	3H	11.73	12.31	12.71	13.30	14.58	15.95	16.53	16.94	17.53	18.81
	4H	12.18	12.71	13.17	13.70	15.01	16.56	17.09	17.55	18.08	19.38
	6H	12.55	13.01	13.55	14.02	15.32	17.00	17.45	18.00	18.46	19.77
	8H	12.67	13.10	13.68	14.11	15.42	17.13	17.55	18.13	18.56	19.87
	12H	12.75	13.13	13.77	14.15	15.48	17.19	17.57	18.21	18.59	19.91
8H	4H	12.50	12.92	13.50	13.93	15.24	16.53	16.95	17.53	17.96	19.27
	6H	12.96	13.31	13.99	14.36	15.67	17.02	17.37	18.05	18.42	19.73
	8H	13.15	13.46	14.19	14.49	15.83	17.21	17.52	18.24	18.55	19.88
	12H	13.29	13.56	14.33	14.59	15.97	17.32	17.59	18.36	18.62	20.00
12H	4H	12.51	12.89	13.53	13.91	15.23	16.48	16.86	17.50	17.88	19.20
	6H	13.02	13.33	14.06	14.36	15.69	17.00	17.30	18.03	18.34	19.67
	8H	13.24	13.51	14.28	14.53	15.91	17.19	17.46	18.23	18.49	19.87