

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332257

Luminaire Tested: **S123RDIP-S340D805U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332257
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4206.6 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.3
10°-20°	150.1	3.6
20°-30°	216.1	5.1
30°-40°	243.5	5.8
40°-50°	232.9	5.5
50°-60°	190.7	4.5
60°-70°	128.7	3.1
70°-80°	64.7	1.5
80°-90°	20.1	0.5
90°-100°	214.9	5.1
100°-110°	608.6	14.5
110°-120°	598.7	14.2
120°-130°	477.5	11.4
130°-140°	376.5	9.0
140°-150°	281.0	6.7
150°-160°	195.9	4.7
160°-170°	115.1	2.7
170°-180°	37.4	0.9
0°-30°	420.2	10.0
0°-40°	663.7	15.8
0°-60°	1087.3	25.8
0°-90°	1300.9	30.9
90°-120°	1422.2	33.8
90°-150°	2557.3	60.8
90°-180°	2906.0	69.1
0°-180°	4206.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	2	9	20	22	23	3
95°	27	86	464	135	91	29
105°	91	134	629	1099	994	96
115°	160	200	481	1054	1210	159
125°	223	263	449	813	954	198
135°	261	312	442	670	773	202
145°	298	341	437	549	604	187
155°	338	365	423	481	501	156
165°	370	380	405	430	437	104
175°	385	386	389	394	393	37
180°	386	386	386	386	386	



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.3	8.7	8.1	7.6	7.0	6.9	7.3	7.8	8.3	8.8	8.5
90°	1.6	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8
92.5°	9.7	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7
95°	26.6	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1
97.5°	45.3	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7
100°	57.9	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4
102.5°	71.0	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7
105°	90.7	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0
107.5°	111.6	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5
110°	126.7	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	140.4	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3
115°	160.3	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1
117.5°	180.1	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8
120°	193.9	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3
122.5°	205.8	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9
125°	222.8	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4
127.5°	235.8	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2
130°	243.9	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4
132.5°	250.2	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3
135°	261.1	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6
137.5°	271.4	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4
140°	278.3	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8
142.5°	285.8	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8
145°	297.9	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1
147.5°	310.1	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5
150°	318.2	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1
152.5°	326.3	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1
155°	338.5	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6
157.5°	348.2	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2
160°	355.7	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5
162.5°	361.4	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9
165°	369.8	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2
167.5°	376.2	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9
170°	380.0	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5
172.5°	382.5	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1
175°	385.4	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1
177.5°	386.8	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	8.6	8.7	8.7	9.0	8.7	8.8	8.9	8.6
90°	19.5	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	65.8	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	281.5	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	701.6	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	921.8	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	994.9	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1016.4	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	954.8	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	896.0	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332257

CATALOG NUMBER: S123RDIP-S340D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	837.8	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	760.7	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	704.9	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	675.5	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	652.4	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	621.5	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	594.7	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	577.8	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	562.1	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	541.0	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	521.8	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	510.5	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	499.9	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	487.1	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	476.6	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	469.1	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	462.2	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	451.9	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	440.9	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	434.7	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	427.2	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	417.5	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	409.0	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	403.4	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	398.4	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	391.7	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	387.5	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)