

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332288

Luminaire Tested: **S123RDIP-S560D1025U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332288
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6328.6 lumens
Efficiency: N/A
Efficacy: 142.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32	26
3	79	70	64	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	46	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	16
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	13
9	49	37	30	25	45	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9630	9630	9630	9630
5°	11480	9672	8518	9672
10°	14335	9616	7695	9616
15°	16826	9518	7017	9518
20°	18778	9371	6441	9371
25°	18478	9216	6087	9216
30°	13282	9073	5722	9073
35°	8868	8888	5486	8888
40°	6534	8665	5243	8665
45°	5480	8273	5002	8273
50°	4836	7762	4669	7762
55°	4241	7174	4211	7174
60°	3776	6613	3860	6613
65°	3316	6008	3591	6008
70°	2603	5473	3279	5473
75°	2296	4779	2994	4779
80°	1996	4060	2944	4060
85°	1606	3260	3125	3260



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	1.4
10°-20°	274.9	4.3
20°-30°	431.9	6.8
30°-40°	450.6	7.1
40°-50°	385.6	6.1
50°-60°	293.9	4.6
60°-70°	188.4	3.0
70°-80°	90.6	1.4
80°-90°	27.7	0.4
90°-100°	48.8	0.8
100°-110°	232.8	3.7
110°-120°	559.2	8.8
120°-130°	712.1	11.3
130°-140°	760.8	12.0
140°-150°	711.5	11.2
150°-160°	573.9	9.1
160°-170°	370.4	5.9
170°-180°	127.6	2.0
0°-30°	794.7	12.6
0°-40°	1245.3	19.7
0°-60°	1924.8	30.4
0°-90°	2231.5	35.3
90°-120°	840.8	13.3
90°-150°	3025.2	47.8
90°-180°	4097.0	64.7
0°-180°	6328.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1062	895	788	895	1062	110
15°	1510	854	630	854	1510	428
25°	1556	776	512	776	1556	669
35°	675	676	418	676	675	442
45°	360	544	329	544	360	283
55°	226	382	224	382	226	204
65°	130	236	141	236	130	128
75°	55	115	72	115	55	59
85°	13	26	25	26	13	16
90°	30	1	30	1	30	14
95°	38	61	38	61	38	32
105°	44	297	44	297	44	100
115°	587	558	587	558	587	542
125°	802	786	802	786	802	717
135°	989	979	989	979	989	763
145°	1141	1130	1141	1130	1141	712
155°	1243	1245	1243	1245	1243	573
165°	1310	1313	1310	1313	1310	370
175°	1338	1344	1338	1344	1338	127
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	952.9	954.2	950.2	949.6	945.0	943.8	943.8	937.3	933.3	928.1	925.1
5°	1062.5	1068.6	1065.6	1058.7	1047.2	1044.5	1037.2	1025.7	1012.7	996.6	989.0
7.5°	1199.3	1207.7	1204.4	1193.8	1181.8	1172.0	1151.5	1132.4	1105.7	1082.3	1062.2
10°	1311.5	1302.6	1295.8	1285.4	1274.3	1256.3	1234.9	1205.4	1171.3	1144.5	1114.6
12.5°	1395.4	1394.0	1385.2	1374.6	1358.9	1341.8	1315.4	1279.5	1239.9	1201.1	1167.0
15°	1509.9	1512.2	1506.4	1495.3	1473.1	1442.8	1403.0	1388.1	1331.4	1289.2	1247.1
17.5°	1589.1	1588.6	1587.8	1572.4	1549.8	1528.2	1491.3	1452.0	1400.7	1341.3	1284.6
20°	1639.3	1635.5	1636.3	1619.0	1602.2	1577.3	1541.3	1484.2	1442.1	1373.5	1314.9
22.5°	1638.1	1637.3	1640.2	1634.3	1622.1	1603.0	1574.7	1526.5	1472.7	1403.5	1337.6
25°	1555.8	1552.8	1570.8	1575.7	1595.3	1598.7	1590.3	1563.9	1512.9	1441.7	1360.1
27.5°	1302.1	1300.4	1333.8	1375.6	1428.7	1469.9	1509.7	1528.9	1512.9	1461.9	1380.2
30°	1068.6	1104.6	1121.5	1182.0	1249.4	1329.8	1400.3	1467.3	1483.8	1461.6	1394.6
32.5°	887.2	918.6	932.7	984.7	1047.5	1141.7	1247.4	1342.3	1409.4	1426.4	1386.0
35°	674.9	675.3	707.4	730.4	788.6	885.5	988.2	1115.3	1241.7	1337.5	1347.5
37.5°	538.5	540.4	559.9	582.8	626.5	677.7	768.1	873.8	1019.8	1166.8	1253.0
40°	465.0	468.4	483.0	505.6	537.0	575.7	646.2	745.7	867.5	1031.1	1164.8
42.5°	417.8	423.4	430.9	448.3	467.7	504.0	561.0	637.9	748.6	903.3	1057.5
45°	360.0	363.1	368.8	376.9	394.5	419.8	458.1	509.8	601.7	726.2	880.6
47.5°	317.6	316.0	322.0	328.6	340.3	357.5	383.2	425.4	491.0	590.8	721.8
50°	288.8	288.4	292.6	297.6	308.7	321.4	342.4	374.2	426.3	509.0	628.9
52.5°	261.8	263.3	266.3	272.5	280.5	290.7	309.6	332.5	377.3	448.7	548.6
55°	226.0	227.1	231.3	234.8	240.5	250.9	262.8	281.9	312.5	362.3	444.7
57.5°	195.6	195.1	199.2	200.0	206.5	214.9	224.1	239.0	261.2	298.2	353.7
60°	175.4	174.3	177.7	180.4	183.8	190.7	198.4	213.0	230.6	257.8	305.3
62.5°	157.0	156.5	159.0	161.7	164.5	170.8	177.3	188.4	202.4	225.3	263.0
65°	130.2	131.4	132.5	133.7	135.2	139.0	145.2	152.8	162.4	178.5	205.7
67.5°	102.3	103.5	103.9	106.2	109.5	111.9	115.7	122.5	129.2	142.7	158.2
70°	82.7	82.3	82.7	83.9	88.1	92.3	97.3	102.3	106.5	116.1	129.1
72.5°	71.1	70.4	71.4	71.6	73.7	74.8	78.0	82.7	88.1	94.6	104.0
75°	55.2	55.2	55.2	55.2	56.7	57.5	58.6	59.8	61.7	64.7	71.6
77.5°	40.8	40.8	41.4	41.7	42.1	42.5	43.2	44.4	45.0	46.7	49.6
80°	32.2	32.6	32.2	32.6	32.6	33.3	33.7	34.9	35.2	37.2	38.3
82.5°	24.2	24.0	24.2	24.6	24.6	25.4	25.4	26.3	26.4	27.3	28.5
85°	13.0	12.3	13.0	12.6	13.4	12.6	13.0	13.8	13.8	14.2	15.7
87.5°	9.1	9.6	8.9	9.1	9.0	9.2	9.0	8.8	9.3	8.8	8.5
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4	27.0	25.6	23.4
95°	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0	32.5	30.9	28.5
97.5°	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7	33.9	32.1	48.1
100°	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5	34.7	32.9	67.5
102.5°	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7	60.2	65.7	103.5
105°	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1	179.3	218.6	238.6
107.5°	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1	371.9	400.7	397.5
110°	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5	442.8	450.2	447.7



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7	500.6	500.5	498.0
115°	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4	575.2	572.9	570.9
117.5°	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8	645.0	643.2	642.2
120°	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3	690.5	688.7	688.1
122.5°	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7	735.5	734.2	733.4
125°	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4	799.0	798.5	797.6
127.5°	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2	861.5	860.8	859.7
130°	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1	899.2	898.3	897.4
132.5°	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0	935.2	934.3	933.6
135°	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2	988.3
137.5°	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0	1037.9	1036.9	1036.4
140°	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8	1068.9	1068.0	1067.4
142.5°	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0	1098.3	1097.6	1096.9
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8	1139.3	1138.9	1138.4
147.5°	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3	1175.9	1175.4	1175.0
150°	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7	1198.2	1197.8	1197.3
152.5°	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5	1217.7	1216.9	1216.7
155°	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9	1244.8	1243.7	1243.5
157.5°	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7	1268.4	1267.0	1267.3
160°	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3	1282.0	1280.6	1280.8
162.5°	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6	1294.1	1292.6	1292.8
165°	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1	1310.3	1308.6	1308.8
167.5°	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3	1321.3
170°	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5	1328.5
172.5°	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9	1335.1	1333.3	1333.1
175°	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6	1341.1	1339.5	1339.3
177.5°	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7	1343.3	1341.9	1341.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	923.8	922.9	918.6	913.7	907.3	903.0	899.6	897.8	892.3	885.5	880.9
5°	980.9	969.4	957.2	942.2	928.4	914.3	905.5	895.1	882.5	868.3	858.3
7.5°	1042.0	1019.5	995.2	970.2	945.4	923.2	903.6	886.8	866.7	846.4	832.1
10°	1088.9	1056.0	1021.9	987.0	955.2	925.4	902.4	879.8	855.7	832.3	814.7
12.5°	1131.5	1088.2	1048.9	1006.0	965.4	929.7	896.6	870.0	841.0	816.1	796.0
15°	1185.4	1141.0	1093.5	1028.4	974.4	929.2	889.0	854.1	818.9	788.3	768.7
17.5°	1235.8	1169.0	1105.2	1050.8	980.7	924.2	875.1	833.4	794.8	762.3	738.2
20°	1256.7	1192.0	1122.6	1053.3	984.4	921.2	864.1	818.1	777.9	741.1	718.9
22.5°	1269.2	1195.9	1122.9	1048.4	975.2	909.5	853.1	802.5	758.9	724.0	696.6
25°	1283.9	1196.5	1116.1	1042.6	967.9	896.6	829.6	776.0	728.9	691.7	662.6
27.5°	1293.5	1190.8	1095.7	1014.0	938.2	867.3	805.9	749.0	701.2	661.9	630.7
30°	1295.4	1186.2	1080.1	991.6	914.6	849.5	784.4	730.0	679.5	637.7	608.6
32.5°	1297.8	1174.9	1059.0	965.0	886.2	821.7	762.7	710.7	658.9	617.8	588.1
35°	1287.7	1168.6	1026.9	918.9	840.0	777.5	724.3	676.4	625.5	585.6	555.4
37.5°	1244.2	1143.7	993.6	866.9	784.4	726.6	683.2	641.5	594.8	551.8	523.3
40°	1200.4	1119.2	967.9	835.4	749.2	689.8	650.7	616.7	571.5	531.2	500.6
42.5°	1135.1	1085.8	943.4	802.3	709.3	652.1	619.2	587.2	547.6	506.7	477.9
45°	1015.4	1021.9	893.2	749.6	654.2	596.7	565.7	543.5	508.3	474.6	445.1
47.5°	865.2	926.1	834.3	693.4	596.1	542.1	515.0	495.6	471.9	438.8	411.9
50°	767.2	854.1	787.1	655.7	559.6	506.0	479.2	463.5	442.8	416.7	391.1
52.5°	676.8	770.2	730.1	613.7	520.1	471.0	444.8	431.9	415.5	391.0	367.8
55°	551.9	646.5	637.3	550.4	460.8	416.7	396.8	382.3	371.1	352.8	334.4
57.5°	446.4	536.1	540.9	479.9	408.5	365.0	347.9	336.9	329.6	315.8	298.8
60°	380.0	462.3	478.4	432.4	371.1	332.8	316.0	307.2	301.4	290.3	277.3
62.5°	324.8	394.9	413.1	380.0	335.3	299.4	286.3	277.8	273.9	264.3	252.8
65°	248.6	306.8	324.4	306.0	282.7	253.9	243.2	235.9	232.5	227.1	218.7
67.5°	186.9	229.4	248.7	235.7	227.3	209.1	202.3	198.4	195.3	191.7	184.6
70°	150.1	181.6	201.5	198.0	191.1	181.6	176.6	173.9	170.8	167.8	161.6
72.5°	120.7	142.3	161.0	162.8	157.1	155.2	150.8	149.7	147.8	144.2	140.8
75°	80.1	95.0	108.0	113.0	115.3	117.2	115.3	114.9	114.5	111.5	109.5
77.5°	52.5	60.5	68.7	77.2	80.8	83.4	84.0	85.4	84.4	82.8	81.9
80°	40.2	42.1	47.9	55.2	60.9	63.2	64.7	65.5	65.1	64.7	63.2
82.5°	29.2	30.8	33.5	38.6	43.4	47.3	48.2	48.0	48.9	49.1	47.9
85°	15.7	16.1	16.9	17.6	20.3	24.5	25.7	26.4	27.2	27.2	24.9
87.5°	8.5	7.7	7.7	7.2	7.7	7.5	8.9	10.0	10.8	10.0	10.4
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6	17.9	17.3	16.7
95°	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9	51.8	42.7	33.6
97.5°	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4	118.3	114.2	110.1
100°	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7	173.1	177.6	182.0
102.5°	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4	224.6	227.8	231.0
105°	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4	299.9	302.3	304.8
107.5°	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7	379.7	381.6	383.6
110°	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2	433.0	434.7	436.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3	483.9	485.5	487.1
115°	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0	559.3	560.6	562.0
117.5°	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2	632.9	634.5	636.2
120°	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7	678.7	680.7	682.7
122.5°	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1	724.7	726.3	728.0
125°	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5	788.3	790.1	791.9
127.5°	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0	849.8	851.6	853.3
130°	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4	888.1	889.9	891.7
132.5°	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1	924.9	926.6	928.4
135°	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2	980.5	981.8	983.2
137.5°	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1	1028.8	1030.5	1032.2
140°	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0	1060.4	1061.7	1063.0
142.5°	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6	1089.9	1091.2	1092.6
145°	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9	1131.5	1133.0	1134.6
147.5°	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8	1169.9	1170.9	1171.9
150°	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8	1193.5	1194.1	1194.8
152.5°	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3	1214.7	1215.0	1215.3
155°	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7	1244.2	1243.8	1243.4
157.5°	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2	1268.2	1268.2	1268.1
160°	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6	1282.4	1282.2	1282.0
162.5°	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2	1295.6	1295.0	1294.5
165°	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6	1311.9	1311.2	1310.6
167.5°	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3	1324.5	1323.6	1322.7
170°	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5	1331.6	1330.8	1329.9
172.5°	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3	1336.3	1335.2	1334.1
175°	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5	1342.4	1341.3	1340.2
177.5°	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1	1344.2	1343.3	1342.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	879.4	875.4	872.7	866.5	862.6	858.3	854.0	856.7	856.4	856.1	856.1
5°	849.9	841.1	833.1	822.7	816.2	808.2	802.0	801.3	802.8	797.4	794.4
7.5°	820.7	808.6	797.2	785.8	773.7	764.0	758.0	755.2	751.3	748.0	744.5
10°	800.1	786.0	774.8	760.7	747.7	736.2	728.9	723.9	721.2	718.5	713.6
12.5°	779.0	765.1	750.9	734.9	722.5	709.2	703.8	698.2	693.0	690.0	683.2
15°	748.0	730.0	715.1	698.2	684.5	671.4	663.8	652.7	651.1	647.3	640.4
17.5°	717.0	697.5	676.9	664.4	648.8	635.3	623.6	619.9	608.9	604.8	598.8
20°	692.5	674.5	658.8	642.3	619.7	607.1	597.9	592.9	584.1	578.7	574.9
22.5°	671.4	653.0	634.9	615.7	597.0	582.9	576.1	568.4	563.6	556.1	551.9
25°	641.2	621.3	599.4	578.7	565.3	554.6	543.9	537.0	530.1	526.6	519.0
27.5°	606.1	585.3	564.9	549.2	532.7	522.1	512.4	506.3	498.0	492.2	488.0
30°	586.8	562.3	544.7	530.5	509.4	499.5	492.2	484.5	478.4	472.3	468.0
32.5°	564.4	542.0	525.3	507.8	491.6	480.8	471.3	464.6	459.4	453.6	449.4
35°	529.3	510.6	493.3	475.7	463.8	452.7	441.6	435.9	430.9	425.5	421.7
37.5°	497.6	480.1	463.7	447.0	432.3	423.2	414.3	409.9	403.2	399.6	395.7
40°	478.0	460.8	443.2	427.1	411.7	404.9	396.8	390.3	384.2	381.5	377.3
42.5°	456.6	439.3	424.5	407.1	394.6	385.2	377.8	370.7	366.1	362.2	359.8
45°	424.8	409.4	394.9	377.7	365.8	357.7	349.3	342.8	338.6	335.9	331.7
47.5°	393.9	378.6	363.8	348.8	337.3	328.1	319.7	315.1	309.6	306.3	303.4
50°	371.5	357.7	342.0	328.2	316.8	307.6	300.7	294.9	289.9	285.7	283.8
52.5°	351.0	336.3	322.7	309.9	297.8	287.3	281.1	275.0	271.3	266.4	264.2
55°	317.1	303.0	291.5	278.8	267.0	258.2	250.5	245.1	241.3	235.9	232.9
57.5°	285.3	272.6	258.9	248.0	235.7	228.3	221.9	214.6	210.0	205.8	202.8
60°	263.9	249.3	237.5	227.1	216.4	206.8	201.1	195.3	190.4	186.1	183.5
62.5°	241.5	228.8	217.6	206.3	196.5	188.1	181.5	176.6	172.3	169.6	166.9
65°	207.2	197.3	185.8	176.6	167.4	161.3	155.9	151.7	148.6	146.7	144.4
67.5°	175.7	166.0	156.0	146.9	140.8	136.1	132.6	129.0	127.5	125.0	123.5
70°	155.1	145.2	136.4	129.5	123.3	119.9	117.6	114.9	113.4	110.3	108.8
72.5°	132.8	125.6	119.2	113.5	108.6	105.5	102.6	99.3	96.8	93.5	91.9
75°	104.6	98.1	93.1	89.2	86.2	82.0	77.8	74.3	73.2	72.0	71.6
77.5°	77.4	73.3	69.7	66.5	62.7	59.6	58.7	57.9	57.7	57.1	57.1
80°	60.9	57.1	54.4	50.6	48.3	48.3	48.3	47.5	47.9	47.9	47.9
82.5°	45.3	41.7	40.3	38.9	38.5	38.8	38.8	38.9	38.7	39.3	39.0
85°	23.4	23.7	24.5	24.1	24.5	24.5	25.3	24.9	25.3	24.5	25.3
87.5°	10.6	12.0	12.9	13.7	14.6	14.9	15.4	15.6	16.0	16.2	16.4
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4	29.8	31.2	32.1
95°	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0	35.6	37.2	37.9
97.5°	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7	37.5	39.2	40.2
100°	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5	38.3	40.0	41.0
102.5°	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7	49.2	43.7	41.1
105°	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1	100.8	61.6	42.1
107.5°	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1	314.3	285.5	256.3
110°	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5	428.2	420.9	401.4



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7	500.9	501.0	497.7
115°	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4	579.6	581.8	583.4
117.5°	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8	648.5	650.3	651.3
120°	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3	694.0	695.8	696.7
122.5°	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7	738.0	739.2	739.9
125°	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4	799.8	800.3	800.7
127.5°	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2	862.9	863.6	863.8
130°	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1	901.0	901.9	902.1
132.5°	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0	936.9	937.8	937.9
135°	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5	991.2	991.8	991.8
137.5°	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0	1040.1	1041.1	1041.4
140°	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8	1070.7	1071.6	1071.8
142.5°	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0	1099.7	1100.4	1100.4
145°	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8	1140.2	1140.7	1140.9
147.5°	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3	1176.7	1177.2	1176.9
150°	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7	1199.1	1199.6	1199.4
152.5°	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5	1219.3	1220.1	1220.0
155°	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9	1247.0	1248.1	1248.0
157.5°	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7	1271.0	1272.4	1272.2
160°	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3	1284.6	1285.9	1285.8
162.5°	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6	1297.1	1298.6	1298.7
165°	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1	1313.9	1315.7	1315.8
167.5°	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4
170°	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6
172.5°	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9	1338.6	1340.4	1340.3
175°	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6	1344.2	1345.7	1345.6
177.5°	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7	1346.2	1347.6	1347.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	852.4	852.1	852.4	851.2	852.4	852.1	852.4	856.1	856.1	856.4	856.7
5°	793.2	792.8	791.7	788.3	791.7	792.8	793.2	794.4	797.4	802.8	801.3
7.5°	741.5	741.0	737.6	737.7	737.6	741.0	741.5	744.5	748.0	751.3	755.2
10°	710.9	711.3	706.7	704.0	706.7	711.3	710.9	713.6	718.5	721.2	723.9
12.5°	681.2	679.4	675.7	672.7	675.7	679.4	681.2	683.2	690.0	693.0	698.2
15°	641.9	638.1	628.9	629.7	628.9	638.1	641.9	640.4	647.3	651.1	652.7
17.5°	595.7	592.9	592.8	587.4	592.8	592.9	595.7	598.8	604.8	608.9	619.9
20°	568.8	566.9	567.6	562.3	567.6	566.9	568.8	574.9	578.7	584.1	592.9
22.5°	547.6	545.7	542.5	540.8	542.5	545.7	547.6	551.9	556.1	563.6	568.4
25°	516.7	513.6	510.6	512.5	510.6	513.6	516.7	519.0	526.6	530.1	537.0
27.5°	485.7	483.4	480.4	480.0	480.4	483.4	485.7	488.0	492.2	498.0	506.3
30°	466.1	463.8	462.3	460.4	462.3	463.8	466.1	468.0	472.3	478.4	484.5
32.5°	446.2	445.8	443.0	442.6	443.0	445.8	446.2	449.4	453.6	459.4	464.6
35°	420.2	417.9	417.1	417.5	417.1	417.9	420.2	421.7	425.5	430.9	435.9
37.5°	395.4	392.4	391.0	389.6	391.0	392.4	395.4	395.7	399.6	403.2	409.9
40°	377.7	374.6	373.8	373.1	373.8	374.6	377.7	377.3	381.5	384.2	390.3
42.5°	357.7	356.5	356.1	354.7	356.1	356.5	357.7	359.8	362.2	366.1	370.7
45°	330.5	330.2	327.9	328.6	327.9	330.2	330.5	331.7	335.9	338.6	342.8
47.5°	301.9	300.2	298.6	299.7	298.6	300.2	301.9	303.4	306.3	309.6	315.1
50°	282.3	281.5	278.1	278.8	278.1	281.5	282.3	283.8	285.7	289.9	294.9
52.5°	262.7	259.8	258.5	258.0	258.5	259.8	262.7	264.2	266.4	271.3	275.0
55°	230.2	226.7	225.2	224.4	225.2	226.7	230.2	232.9	235.9	241.3	245.1
57.5°	198.3	197.4	196.2	197.0	196.2	197.4	198.3	202.8	205.8	210.0	214.6
60°	179.6	179.6	179.6	179.3	179.6	179.6	179.6	183.5	186.1	190.4	195.3
62.5°	165.2	164.3	164.0	164.5	164.0	164.3	165.2	166.9	169.6	172.3	176.6
65°	143.2	142.9	141.3	141.0	141.3	142.9	143.2	144.4	146.7	148.6	151.7
67.5°	122.5	121.1	120.7	120.1	120.7	121.1	122.5	123.5	125.0	127.5	129.0
70°	106.9	106.1	103.8	104.2	103.8	106.1	106.9	108.8	110.3	113.4	114.9
72.5°	90.0	89.2	88.8	88.2	88.8	89.2	90.0	91.9	93.5	96.8	99.3
75°	71.2	70.9	70.5	72.0	70.5	70.9	71.2	71.6	72.0	73.2	74.3
77.5°	57.1	57.1	57.3	56.7	57.3	57.1	57.1	57.1	57.1	57.7	57.9
80°	47.9	47.9	47.5	47.5	47.5	47.9	47.9	47.9	47.9	47.9	47.5
82.5°	38.4	38.7	38.9	38.3	38.9	38.7	38.4	39.0	39.3	38.7	38.9
85°	25.3	24.9	25.7	25.3	25.7	24.9	25.3	25.3	24.5	25.3	24.9
87.5°	17.1	16.5	16.6	17.0	16.6	16.5	17.1	16.4	16.2	16.0	15.6
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7
92.5°	32.3	32.6	32.9	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4
95°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7
100°	41.3	41.5	41.7	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5
102.5°	41.5	41.9	42.3	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7
105°	42.6	43.0	43.5	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1
107.5°	226.7	197.1	167.5	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1
110°	369.6	337.9	306.2	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.0	484.3	477.6	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7
115°	584.2	585.1	586.0	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4
117.5°	651.5	651.6	651.8	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8
120°	696.7	696.7	696.7	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3
122.5°	740.1	740.3	740.4	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7
125°	801.2	801.6	802.1	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4
127.5°	863.3	862.9	862.4	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2
130°	901.7	901.2	900.8	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1
132.5°	937.3	936.7	936.1	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0
135°	991.2	990.5	989.8	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5
137.5°	1041.0	1040.6	1040.1	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0
140°	1071.3	1070.9	1070.5	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8
142.5°	1099.8	1099.2	1098.6	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8
147.5°	1175.9	1174.9	1173.8	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3
150°	1198.8	1198.1	1197.4	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7
152.5°	1219.0	1218.0	1217.0	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5
155°	1246.7	1245.4	1244.0	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9
157.5°	1270.4	1268.7	1267.0	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7
160°	1284.3	1282.7	1281.2	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3
162.5°	1297.3	1295.9	1294.6	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6
165°	1314.2	1312.7	1311.1	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1
167.5°	1326.7	1324.9	1323.1	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9
170°	1333.9	1332.1	1330.3	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1
172.5°	1338.4	1336.4	1334.5	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9
175°	1343.8	1342.1	1340.3	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6
177.5°	1345.6	1343.9	1342.1	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	854.0	858.3	862.6	866.5	872.7	875.4	879.4	880.9	885.5	892.3	897.8
5°	802.0	808.2	816.2	822.7	833.1	841.1	849.9	858.3	868.3	882.5	895.1
7.5°	758.0	764.0	773.7	785.8	797.2	808.6	820.7	832.1	846.4	866.7	886.8
10°	728.9	736.2	747.7	760.7	774.8	786.0	800.1	814.7	832.3	855.7	879.8
12.5°	703.8	709.2	722.5	734.9	750.9	765.1	779.0	796.0	816.1	841.0	870.0
15°	663.8	671.4	684.5	698.2	715.1	730.0	748.0	768.7	788.3	818.9	854.1
17.5°	623.6	635.3	648.8	664.4	676.9	697.5	717.0	738.2	762.3	794.8	833.4
20°	597.9	607.1	619.7	642.3	658.8	674.5	692.5	718.9	741.1	777.9	818.1
22.5°	576.1	582.9	597.0	615.7	634.9	653.0	671.4	696.6	724.0	758.9	802.5
25°	543.9	554.6	565.3	578.7	599.4	621.3	641.2	662.6	691.7	728.9	776.0
27.5°	512.4	522.1	532.7	549.2	564.9	585.3	606.1	630.7	661.9	701.2	749.0
30°	492.2	499.5	509.4	530.5	544.7	562.3	586.8	608.6	637.7	679.5	730.0
32.5°	471.3	480.8	491.6	507.8	525.3	542.0	564.4	588.1	617.8	658.9	710.7
35°	441.6	452.7	463.8	475.7	493.3	510.6	529.3	555.4	585.6	625.5	676.4
37.5°	414.3	423.2	432.3	447.0	463.7	480.1	497.6	523.3	551.8	594.8	641.5
40°	396.8	404.9	411.7	427.1	443.2	460.8	478.0	500.6	531.2	571.5	616.7
42.5°	377.8	385.2	394.6	407.1	424.5	439.3	456.6	477.9	506.7	547.6	587.2
45°	349.3	357.7	365.8	377.7	394.9	409.4	424.8	445.1	474.6	508.3	543.5
47.5°	319.7	328.1	337.3	348.8	363.8	378.6	393.9	411.9	438.8	471.9	495.6
50°	300.7	307.6	316.8	328.2	342.0	357.7	371.5	391.1	416.7	442.8	463.5
52.5°	281.1	287.3	297.8	309.9	322.7	336.3	351.0	367.8	391.0	415.5	431.9
55°	250.5	258.2	267.0	278.8	291.5	303.0	317.1	334.4	352.8	371.1	382.3
57.5°	221.9	228.3	235.7	248.0	258.9	272.6	285.3	298.8	315.8	329.6	336.9
60°	201.1	206.8	216.4	227.1	237.5	249.3	263.9	277.3	290.3	301.4	307.2
62.5°	181.5	188.1	196.5	206.3	217.6	228.8	241.5	252.8	264.3	273.9	277.8
65°	155.9	161.3	167.4	176.6	185.8	197.3	207.2	218.7	227.1	232.5	235.9
67.5°	132.6	136.1	140.8	146.9	156.0	166.0	175.7	184.6	191.7	195.3	198.4
70°	117.6	119.9	123.3	129.5	136.4	145.2	155.1	161.6	167.8	170.8	173.9
72.5°	102.6	105.5	108.6	113.5	119.2	125.6	132.8	140.8	144.2	147.8	149.7
75°	77.8	82.0	86.2	89.2	93.1	98.1	104.6	109.5	111.5	114.5	114.9
77.5°	58.7	59.6	62.7	66.5	69.7	73.3	77.4	81.9	82.8	84.4	85.4
80°	48.3	48.3	48.3	50.6	54.4	57.1	60.9	63.2	64.7	65.1	65.5
82.5°	38.8	38.8	38.5	38.9	40.3	41.7	45.3	47.9	49.1	48.9	48.0
85°	25.3	24.5	24.5	24.1	24.5	23.7	23.4	24.9	27.2	27.2	26.4
87.5°	15.4	14.9	14.6	13.7	12.9	12.0	10.6	10.4	10.0	10.8	10.0
90°	24.8	24.0	21.1	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6
95°	32.5	30.9	28.5	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9
97.5°	33.9	32.1	48.1	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4
100°	34.7	32.9	67.5	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7
102.5°	60.2	65.7	103.5	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4
105°	179.3	218.6	238.6	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4
107.5°	371.9	400.7	397.5	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7
110°	442.8	450.2	447.7	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.6	500.5	498.0	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3
115°	575.2	572.9	570.9	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0
117.5°	645.0	643.2	642.2	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2
120°	690.5	688.7	688.1	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7
122.5°	735.5	734.2	733.4	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1
125°	799.0	798.5	797.6	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5
127.5°	861.5	860.8	859.7	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0
130°	899.2	898.3	897.4	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4
132.5°	935.2	934.3	933.6	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1
135°	989.8	989.2	988.3	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2
137.5°	1037.9	1036.9	1036.4	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1
140°	1068.9	1068.0	1067.4	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0
142.5°	1098.3	1097.6	1096.9	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6
145°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9
147.5°	1175.9	1175.4	1175.0	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8
150°	1198.2	1197.8	1197.3	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8
152.5°	1217.7	1216.9	1216.7	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3
155°	1244.8	1243.7	1243.5	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7
157.5°	1268.4	1267.0	1267.3	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2
160°	1282.0	1280.6	1280.8	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6
162.5°	1294.1	1292.6	1292.8	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2
165°	1310.3	1308.6	1308.8	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6
167.5°	1323.1	1321.3	1321.3	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3
170°	1330.3	1328.5	1328.5	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5
172.5°	1335.1	1333.3	1333.1	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3
175°	1341.1	1339.5	1339.3	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5
177.5°	1343.3	1341.9	1341.7	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	899.6	903.0	907.3	913.7	918.6	922.9	923.8	925.1	928.1	933.3	937.3
5°	905.5	914.3	928.4	942.2	957.2	969.4	980.9	989.0	996.6	1012.7	1025.7
7.5°	903.6	923.2	945.4	970.2	995.2	1019.5	1042.0	1062.2	1082.3	1105.7	1132.4
10°	902.4	925.4	955.2	987.0	1021.9	1056.0	1088.9	1114.6	1144.5	1171.3	1205.4
12.5°	896.6	929.7	965.4	1006.0	1048.9	1088.2	1131.5	1167.0	1201.1	1239.9	1279.5
15°	889.0	929.2	974.4	1028.4	1093.5	1141.0	1185.4	1247.1	1289.2	1331.4	1388.1
17.5°	875.1	924.2	980.7	1050.8	1105.2	1169.0	1235.8	1284.6	1341.3	1400.7	1452.0
20°	864.1	921.2	984.4	1053.3	1122.6	1192.0	1256.7	1314.9	1373.5	1442.1	1484.2
22.5°	853.1	909.5	975.2	1048.4	1122.9	1195.9	1269.2	1337.6	1403.5	1472.7	1526.5
25°	829.6	896.6	967.9	1042.6	1116.1	1196.5	1283.9	1360.1	1441.7	1512.9	1563.9
27.5°	805.9	867.3	938.2	1014.0	1095.7	1190.8	1293.5	1380.2	1461.9	1512.9	1528.9
30°	784.4	849.5	914.6	991.6	1080.1	1186.2	1295.4	1394.6	1461.6	1483.8	1467.3
32.5°	762.7	821.7	886.2	965.0	1059.0	1174.9	1297.8	1386.0	1426.4	1409.4	1342.3
35°	724.3	777.5	840.0	918.9	1026.9	1168.6	1287.7	1347.5	1337.5	1241.7	1115.3
37.5°	683.2	726.6	784.4	866.9	993.6	1143.7	1244.2	1253.0	1166.8	1019.8	873.8
40°	650.7	689.8	749.2	835.4	967.9	1119.2	1200.4	1164.8	1031.1	867.5	745.7
42.5°	619.2	652.1	709.3	802.3	943.4	1085.8	1135.1	1057.5	903.3	748.6	637.9
45°	565.7	596.7	654.2	749.6	893.2	1021.9	1015.4	880.6	726.2	601.7	509.8
47.5°	515.0	542.1	596.1	693.4	834.3	926.1	865.2	721.8	590.8	491.0	425.4
50°	479.2	506.0	559.6	655.7	787.1	854.1	767.2	628.9	509.0	426.3	374.2
52.5°	444.8	471.0	520.1	613.7	730.1	770.2	676.8	548.6	448.7	377.3	332.5
55°	396.8	416.7	460.8	550.4	637.3	646.5	551.9	444.7	362.3	312.5	281.9
57.5°	347.9	365.0	408.5	479.9	540.9	536.1	446.4	353.7	298.2	261.2	239.0
60°	316.0	332.8	371.1	432.4	478.4	462.3	380.0	305.3	257.8	230.6	213.0
62.5°	286.3	299.4	335.3	380.0	413.1	394.9	324.8	263.0	225.3	202.4	188.4
65°	243.2	253.9	282.7	306.0	324.4	306.8	248.6	205.7	178.5	162.4	152.8
67.5°	202.3	209.1	227.3	235.7	248.7	229.4	186.9	158.2	142.7	129.2	122.5
70°	176.6	181.6	191.1	198.0	201.5	181.6	150.1	129.1	116.1	106.5	102.3
72.5°	150.8	155.2	157.1	162.8	161.0	142.3	120.7	104.0	94.6	88.1	82.7
75°	115.3	117.2	115.3	113.0	108.0	95.0	80.1	71.6	64.7	61.7	59.8
77.5°	84.0	83.4	80.8	77.2	68.7	60.5	52.5	49.6	46.7	45.0	44.4
80°	64.7	63.2	60.9	55.2	47.9	42.1	40.2	38.3	37.2	35.2	34.9
82.5°	48.2	47.3	43.4	38.6	33.5	30.8	29.2	28.5	27.3	26.4	26.3
85°	25.7	24.5	20.3	17.6	16.9	16.1	15.7	15.7	14.2	13.8	13.8
87.5°	8.9	7.5	7.7	7.2	7.7	7.7	8.5	8.5	8.8	9.3	8.8
90°	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7
92.5°	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4
95°	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0
97.5°	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7
100°	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5
102.5°	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7
105°	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1
107.5°	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1
110°	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7
115°	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4
117.5°	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8
120°	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3
122.5°	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7
125°	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4
127.5°	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2
130°	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1
132.5°	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0
135°	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5
137.5°	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0
140°	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8
142.5°	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0
145°	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8
147.5°	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3
150°	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7
152.5°	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5
155°	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9
157.5°	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7
160°	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3
162.5°	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6
165°	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1
167.5°	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9
170°	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1
172.5°	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9
175°	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6
177.5°	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	943.8	943.8	945.0	949.6	950.2	954.2	952.9
5°	1037.2	1044.5	1047.2	1058.7	1065.6	1068.6	1062.5
7.5°	1151.5	1172.0	1181.8	1193.8	1204.4	1207.7	1199.3
10°	1234.9	1256.3	1274.3	1285.4	1295.8	1302.6	1311.5
12.5°	1315.4	1341.8	1358.9	1374.6	1385.2	1394.0	1395.4
15°	1403.0	1442.8	1473.1	1495.3	1506.4	1512.2	1509.9
17.5°	1491.3	1528.2	1549.8	1572.4	1587.8	1588.6	1589.1
20°	1541.3	1577.3	1602.2	1619.0	1636.3	1635.5	1639.3
22.5°	1574.7	1603.0	1622.1	1634.3	1640.2	1637.3	1638.1
25°	1590.3	1598.7	1595.3	1575.7	1570.8	1552.8	1555.8
27.5°	1509.7	1469.9	1428.7	1375.6	1333.8	1300.4	1302.1
30°	1400.3	1329.8	1249.4	1182.0	1121.5	1104.6	1068.6
32.5°	1247.4	1141.7	1047.5	984.7	932.7	918.6	887.2
35°	988.2	885.5	788.6	730.4	707.4	675.3	674.9
37.5°	768.1	677.7	626.5	582.8	559.9	540.4	538.5
40°	646.2	575.7	537.0	505.6	483.0	468.4	465.0
42.5°	561.0	504.0	467.7	448.3	430.9	423.4	417.8
45°	458.1	419.8	394.5	376.9	368.8	363.1	360.0
47.5°	383.2	357.5	340.3	328.6	322.0	316.0	317.6
50°	342.4	321.4	308.7	297.6	292.6	288.4	288.8
52.5°	309.6	290.7	280.5	272.5	266.3	263.3	261.8
55°	262.8	250.9	240.5	234.8	231.3	227.1	226.0
57.5°	224.1	214.9	206.5	200.0	199.2	195.1	195.6
60°	198.4	190.7	183.8	180.4	177.7	174.3	175.4
62.5°	177.3	170.8	164.5	161.7	159.0	156.5	157.0
65°	145.2	139.0	135.2	133.7	132.5	131.4	130.2
67.5°	115.7	111.9	109.5	106.2	103.9	103.5	102.3
70°	97.3	92.3	88.1	83.9	82.7	82.3	82.7
72.5°	78.0	74.8	73.7	71.6	71.4	70.4	71.1
75°	58.6	57.5	56.7	55.2	55.2	55.2	55.2
77.5°	43.2	42.5	42.1	41.7	41.4	40.8	40.8
80°	33.7	33.3	32.6	32.6	32.2	32.6	32.2
82.5°	25.4	25.4	24.6	24.6	24.2	24.0	24.2
85°	13.0	12.6	13.4	12.6	13.0	12.3	13.0
87.5°	9.0	9.2	9.0	9.1	8.9	9.6	9.1
90°	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P332288

CATALOG NUMBER: S123RDIP-S560D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)