

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332275-830

Luminaire Tested: **S123RDIP-S560D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332275-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3250.3 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	60	51	46	67	56	49	44	50	44	40	44	39	36	39	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9582	9582	9582
5°	9619	9487	9541
10°	9565	9368	9335
15°	9461	9149	9052
20°	9321	8874	8668
25°	9175	8567	8291
30°	8983	8211	7762
35°	8784	7857	7276
40°	8604	7436	6674
45°	8363	7024	6132
50°	8100	6553	5526
55°	7833	6016	4960
60°	7584	5440	4336
65°	7264	4819	3713
70°	6861	4047	2999
75°	6276	3182	2824
80°	5597	2820	2591
85°	4730	2495	2322



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.6
10°-20°	232.6	7.2
20°-30°	334.9	10.3
30°-40°	377.3	11.6
40°-50°	360.9	11.1
50°-60°	295.6	9.1
60°-70°	199.4	6.1
70°-80°	100.3	3.1
80°-90°	27.8	0.9
90°-100°	91.6	2.8
100°-110°	259.3	8.0
110°-120°	255.1	7.8
120°-130°	203.5	6.3
130°-140°	160.4	4.9
140°-150°	119.7	3.7
150°-160°	83.4	2.6
160°-170°	49.0	1.5
170°-180°	16.0	0.5
0°-30°	651.1	20.0
0°-40°	1028.4	31.6
0°-60°	1684.8	51.8
0°-90°	2012.4	61.9
90°-120°	605.9	18.6
90°-150°	1089.5	33.5
90°-180°	1238.0	38.1
0°-180°	3250.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	890	890	890	890	890	
5°	890	886	878	884	883	84
15°	849	840	821	817	812	239
25°	772	754	721	706	698	355
35°	668	642	598	568	554	418
45°	549	516	461	422	403	424
55°	417	380	321	280	264	374
65°	285	245	189	155	146	282
75°	151	116	76	70	68	161
85°	38	23	20	19	19	43
90°	1	4	8	9	10	3
95°	11	37	198	58	39	12
105°	39	57	268	468	424	41
115°	68	85	205	449	515	68
125°	95	112	191	346	406	84
135°	111	133	188	285	329	86
145°	127	145	186	234	258	80
155°	144	156	180	205	214	66
165°	158	162	173	183	186	44
175°	164	164	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	893.2	892.6	892.1	891.6	891.1	890.0	888.5	886.9	885.4	883.9	885.3
5°	890.2	889.5	888.6	887.9	887.0	885.7	883.7	881.8	879.9	878.0	879.4
7.5°	882.0	881.2	880.2	879.4	878.5	876.8	874.4	871.9	869.3	866.9	867.6
10°	875.1	873.9	872.8	871.7	870.6	868.6	865.7	862.8	859.9	857.1	857.1
12.5°	865.3	864.0	862.7	861.5	860.3	857.9	854.3	850.8	847.3	843.8	843.7
15°	849.0	847.3	845.6	843.8	842.1	838.9	834.4	829.9	825.4	821.0	820.1
17.5°	828.7	826.7	824.6	822.6	820.5	816.6	810.9	805.2	799.5	793.8	792.1
20°	813.7	811.2	808.6	806.0	803.4	799.1	793.0	786.9	780.8	774.7	772.6
22.5°	796.9	794.0	791.1	788.1	785.1	780.4	773.9	767.4	761.0	754.5	751.9
25°	772.5	768.5	764.5	760.5	756.5	750.8	743.4	736.0	728.7	721.3	717.9
27.5°	742.9	738.5	734.1	729.6	725.2	718.9	710.7	702.5	694.3	686.1	681.4
30°	722.7	717.9	713.1	708.3	703.5	696.5	687.6	678.6	669.6	660.6	655.2
32.5°	702.5	697.1	691.6	686.2	680.7	673.3	663.7	654.2	644.7	635.2	629.2
35°	668.5	662.8	657.0	651.3	645.5	637.6	627.6	617.7	607.8	597.9	590.9
37.5°	634.2	627.8	621.4	614.9	608.5	600.0	589.4	578.8	568.2	557.5	549.7
40°	612.3	605.2	598.1	591.1	584.0	574.8	563.5	552.0	540.6	529.2	520.8
42.5°	587.4	580.3	573.3	566.3	559.2	549.8	538.0	526.2	514.4	502.7	493.5
45°	549.4	542.2	535.0	527.8	520.6	510.8	498.4	486.1	473.7	461.4	452.2
47.5°	511.4	503.5	495.6	487.7	479.8	469.7	457.2	444.9	432.5	420.2	410.3
50°	483.7	476.2	468.6	461.1	453.6	443.3	430.3	417.4	404.4	391.3	381.4
52.5°	458.9	450.7	442.5	434.3	426.2	415.7	402.7	389.9	377.0	364.2	353.8
55°	417.4	409.4	401.6	393.7	385.9	375.1	361.5	347.9	334.2	320.6	311.2
57.5°	378.9	370.3	361.7	353.2	344.6	333.5	319.8	306.1	292.4	278.7	269.9
60°	352.3	343.6	334.7	325.8	317.1	305.9	292.7	279.4	266.0	252.7	244.0
62.5°	325.7	317.0	308.1	299.3	290.5	279.4	266.1	252.8	239.4	226.1	218.0
65°	285.2	276.4	267.6	258.7	249.9	239.2	226.7	214.2	201.7	189.2	181.3
67.5°	244.6	235.7	226.8	217.8	209.0	198.5	186.4	174.5	162.5	150.4	144.6
70°	218.0	209.3	200.8	192.1	183.4	173.4	162.2	151.0	139.8	128.6	122.9
72.5°	191.4	182.9	174.4	165.9	157.3	148.0	137.8	127.5	117.3	107.2	102.5
75°	150.9	143.2	135.5	127.8	120.1	111.8	103.0	94.2	85.4	76.5	74.9
77.5°	114.0	107.0	100.0	93.0	86.1	79.7	74.1	68.4	62.7	57.0	56.2
80°	90.3	83.7	77.1	70.5	63.9	59.0	55.6	52.2	48.8	45.5	45.0
82.5°	67.8	62.0	56.4	50.7	45.0	41.4	39.8	38.3	36.7	35.1	34.6
85°	38.3	34.8	31.2	27.7	24.1	22.1	21.7	21.2	20.7	20.2	19.9
87.5°	13.9	12.7	11.4	10.2	9.0	8.4	8.6	8.8	9.0	9.1	9.0
90°	0.7	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0
92.5°	4.1	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6
95°	11.3	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2
97.5°	19.3	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4
100°	24.7	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1
102.5°	30.3	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7
105°	38.6	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4
107.5°	47.6	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8
110°	53.9	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.9	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0
115°	68.2	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5
117.5°	76.7	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3
120°	82.6	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8
122.5°	87.7	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7
125°	94.9	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9
127.5°	100.5	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9
130°	104.0	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1
132.5°	106.6	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7
135°	111.2	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2
137.5°	115.6	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2
140°	118.6	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8
142.5°	121.8	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7
145°	126.9	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8
147.5°	132.1	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1
150°	135.5	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2
152.5°	139.0	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0
155°	144.2	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8
157.5°	148.4	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2
160°	151.6	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9
162.5°	153.9	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4
165°	157.5	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2
167.5°	160.2	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1
170°	161.8	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2
172.5°	163.0	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3
175°	164.2	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2
177.5°	164.9	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	886.7	888.2	889.6	890.1	889.9	889.6	889.4	889.1
5°	880.8	882.3	883.7	884.3	884.0	883.6	883.4	883.0
7.5°	868.5	869.2	870.1	870.2	869.6	869.1	868.6	868.0
10°	857.3	857.5	857.6	857.3	856.6	855.7	855.0	854.1
12.5°	843.6	843.5	843.4	842.8	841.9	840.9	840.1	839.1
15°	819.4	818.5	817.7	816.7	815.6	814.5	813.4	812.3
17.5°	790.4	788.7	786.9	785.3	783.6	781.9	780.2	778.6
20°	770.5	768.5	766.4	764.4	762.4	760.5	758.6	756.7
22.5°	749.3	746.7	744.1	741.9	740.1	738.3	736.5	734.7
25°	714.5	711.1	707.8	705.2	703.5	701.7	699.9	698.1
27.5°	676.7	672.0	667.3	663.6	660.9	658.3	655.5	652.8
30°	649.7	644.2	638.9	634.8	632.3	629.7	627.1	624.5
32.5°	623.3	617.3	611.3	607.0	604.4	601.6	598.9	596.3
35°	584.0	577.1	570.2	565.3	562.4	559.6	556.7	553.7
37.5°	541.9	534.0	526.2	520.6	517.0	513.4	509.8	506.2
40°	512.6	504.2	495.9	489.8	486.2	482.5	478.8	475.0
42.5°	484.5	475.3	466.2	460.0	456.7	453.4	450.1	446.8
45°	443.1	433.9	424.8	418.3	414.4	410.6	406.7	402.8
47.5°	400.3	390.4	380.4	373.7	370.3	366.8	363.4	360.0
50°	371.5	361.5	351.6	344.7	341.0	337.3	333.7	330.0
52.5°	343.6	333.2	322.8	316.0	312.7	309.4	306.1	302.8
55°	302.0	292.7	283.3	277.1	273.9	270.7	267.5	264.3
57.5°	261.1	252.3	243.6	237.8	235.1	232.3	229.6	226.9
60°	235.4	226.7	218.0	212.4	209.6	206.9	204.2	201.4
62.5°	209.8	201.7	193.5	188.0	185.2	182.3	179.5	176.6
65°	173.4	165.6	157.7	152.9	151.2	149.4	147.6	145.8
67.5°	138.7	132.8	127.0	123.1	121.2	119.3	117.4	115.6
70°	117.3	111.7	106.0	102.4	100.6	98.9	97.1	95.3
72.5°	97.9	93.4	88.8	86.1	85.4	84.6	83.9	83.1
75°	73.3	71.7	70.1	69.2	68.8	68.5	68.1	67.9
77.5°	55.3	54.5	53.5	53.0	52.7	52.3	52.0	51.7
80°	44.5	44.0	43.5	43.2	42.9	42.5	42.2	41.8
82.5°	34.1	33.6	33.2	32.9	32.8	32.8	32.7	32.6
85°	19.6	19.2	18.9	18.8	18.8	18.8	18.8	18.8
87.5°	9.0	8.9	8.8	8.8	8.6	8.6	8.5	8.3
90°	8.3	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	28.1	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	119.9	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	298.9	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	392.7	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.9	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	433.0	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	406.7	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	381.7	443.0	484.9	508.3	517.6	520.3	519.6	519.0



TEST NUMBER: P332275-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	356.9	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	324.0	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	300.3	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	287.8	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	278.0	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	264.8	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	253.4	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	246.1	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	239.5	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	230.5	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	222.3	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	217.5	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	213.0	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	207.5	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	203.0	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	199.8	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	196.9	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	192.6	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	187.8	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	185.2	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	182.0	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	177.9	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	174.3	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	171.8	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	169.8	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	166.8	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.0	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)