

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332297

Luminaire Tested: **S123RDIP-S560D1195U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332297
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6906.9 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	1.3
10°-20°	246.8	3.6
20°-30°	355.3	5.1
30°-40°	400.3	5.8
40°-50°	382.9	5.5
50°-60°	313.6	4.5
60°-70°	211.6	3.1
70°-80°	106.4	1.5
80°-90°	32.5	0.5
90°-100°	56.9	0.8
100°-110°	271.0	3.9
110°-120°	650.9	9.4
120°-130°	828.8	12.0
130°-140°	885.6	12.8
140°-150°	828.1	12.0
150°-160°	668.0	9.7
160°-170°	431.1	6.2
170°-180°	148.6	2.2
0°-30°	690.8	10.0
0°-40°	1091.1	15.8
0°-60°	1787.6	25.9
0°-90°	2138.1	31.0
90°-120°	978.7	14.2
90°-150°	3521.2	51.0
90°-180°	4769.0	69.0
0°-180°	6906.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	1	13	28	32	35	5
95°	71	27	36	44	44	88
105°	346	352	254	60	51	367
115°	650	657	667	678	683	641
125°	916	925	929	932	934	817
135°	1140	1147	1151	1154	1151	877
145°	1315	1323	1326	1328	1328	823
155°	1449	1447	1448	1453	1446	667
165°	1528	1524	1523	1531	1524	431
175°	1564	1558	1559	1566	1558	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	14.9	14.0	13.0	12.0	11.0	10.9	11.5	12.2	12.9	13.5	13.6
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	21.6	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4
95°	70.9	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8
97.5°	142.4	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5
100°	196.3	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4
102.5°	257.7	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0
105°	346.2	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7
107.5°	439.6	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8
110°	501.9	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.4	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7
115°	649.5	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5
117.5°	734.7	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7
120°	787.7	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7
122.5°	841.6	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1
125°	915.5	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0
127.5°	987.1	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8
130°	1031.7	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7
132.5°	1074.4	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5
135°	1139.7	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1
137.5°	1195.5	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1
140°	1232.7	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2
142.5°	1267.1	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4
145°	1315.2	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1
147.5°	1360.5	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7
150°	1388.4	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7
152.5°	1413.5	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4
155°	1448.8	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9
157.5°	1476.2	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4
160°	1492.9	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2
162.5°	1508.7	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3
165°	1527.8	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2
167.5°	1542.7	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1
170°	1551.0	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4
172.5°	1556.6	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0
175°	1563.8	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0
177.5°	1565.7	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	13.7	13.8	13.8	13.8	13.8	13.8	13.7	13.7
90°	29.9	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	33.0	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	41.5	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	42.5	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	63.6	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	163.0	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	399.3	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	506.9	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P332297

CATALOG NUMBER: S123RDIP-S560D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	582.8	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	672.0	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	752.8	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	805.8	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	857.5	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	930.5	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1003.6	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1047.7	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1089.5	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1209.4	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1245.2	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1279.2	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1326.7	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.2	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.2	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1418.3	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1450.2	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1477.9	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1493.7	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1508.1	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1527.3	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1556.1	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1562.8	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1565.2	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)