

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332275

Luminaire Tested: **S123RDIP-S560D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332275
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3448.5 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	60	51	46	67	56	49	44	50	44	40	44	39	36	39	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	2.6
10°-20°	246.8	7.2
20°-30°	355.3	10.3
30°-40°	400.3	11.6
40°-50°	382.9	11.1
50°-60°	313.6	9.1
60°-70°	211.6	6.1
70°-80°	106.4	3.1
80°-90°	29.5	0.9
90°-100°	97.2	2.8
100°-110°	275.1	8.0
110°-120°	270.6	7.8
120°-130°	215.9	6.3
130°-140°	170.2	4.9
140°-150°	127.0	3.7
150°-160°	88.5	2.6
160°-170°	52.0	1.5
170°-180°	16.9	0.5
0°-30°	690.8	20.0
0°-40°	1091.1	31.6
0°-60°	1787.6	51.8
0°-90°	2135.1	61.9
90°-120°	642.9	18.6
90°-150°	1155.9	33.5
90°-180°	1313.0	38.1
0°-180°	3448.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	1	4	9	10	10	3
95°	12	39	210	61	41	13
105°	41	61	284	497	450	44
115°	72	90	217	477	547	72
125°	101	119	203	368	431	89
135°	118	141	200	303	350	91
145°	135	154	198	248	273	84
155°	153	165	191	217	226	70
165°	167	172	183	194	198	47
175°	174	174	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	14.8	13.5	12.1	10.8	9.5	8.9	9.1	9.3	9.5	9.7	9.5
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5
92.5°	4.4	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0
95°	12.0	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0
97.5°	20.5	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4
100°	26.2	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3
102.5°	32.1	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1
105°	41.0	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5
107.5°	50.5	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8
110°	57.2	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.5	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4
115°	72.4	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5
117.5°	81.4	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4
120°	87.6	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5
122.5°	93.0	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0
125°	100.7	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7
127.5°	106.6	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3
130°	110.3	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3
132.5°	113.1	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7
135°	118.0	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9
137.5°	122.7	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7
140°	125.8	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1
142.5°	129.2	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9
145°	134.6	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8
147.5°	140.2	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9
150°	143.8	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9
152.5°	147.5	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6
155°	153.0	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2
157.5°	157.4	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4
160°	160.8	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9
162.5°	163.3	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3
165°	167.1	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9
167.5°	170.0	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6
170°	171.7	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6
172.5°	172.9	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6
175°	174.2	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3
177.5°	174.9	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	9.5	9.4	9.3	9.3	9.1	9.1	9.0	8.8
90°	8.8	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	29.8	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	127.2	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	317.1	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	416.6	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	449.7	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	459.4	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	431.5	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	405.0	470.0	514.5	539.3	549.2	552.0	551.3	550.6



TEST NUMBER: P332275

CATALOG NUMBER: S123RDIP-S560D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	343.8	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	318.6	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	305.3	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	294.9	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	280.9	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	268.8	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	261.1	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	254.1	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	244.5	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	235.8	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	230.8	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	226.0	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	220.2	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	215.4	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	212.0	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	208.9	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	204.3	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	199.3	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	196.5	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	193.1	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	188.7	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	184.9	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	182.3	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.1	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.0	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.1	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)