

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332287-830

Luminaire Tested: **S123RDIP-S560D805U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332287-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4752.7 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	74	63	55	50	67	58	51	46	48	43	40	39	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	23	21	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9582	9582	9582
5°	9619	9487	9541
10°	9565	9368	9335
15°	9461	9149	9052
20°	9321	8874	8668
25°	9175	8567	8291
30°	8983	8211	7762
35°	8784	7857	7276
40°	8604	7436	6674
45°	8363	7024	6132
50°	8100	6553	5526
55°	7833	6016	4960
60°	7584	5440	4336
65°	7264	4819	3713
70°	6861	4047	2999
75°	6276	3182	2824
80°	5597	2820	2591
85°	4730	2495	2322



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.8
10°-20°	232.6	4.9
20°-30°	334.9	7.0
30°-40°	377.3	7.9
40°-50°	360.9	7.6
50°-60°	295.6	6.2
60°-70°	199.4	4.2
70°-80°	100.3	2.1
80°-90°	29.4	0.6
90°-100°	202.6	4.3
100°-110°	573.6	12.1
110°-120°	564.3	11.9
120°-130°	450.1	9.5
130°-140°	354.9	7.5
140°-150°	264.9	5.6
150°-160°	184.6	3.9
160°-170°	108.5	2.3
170°-180°	35.3	0.7
0°-30°	651.1	13.7
0°-40°	1028.4	21.6
0°-60°	1684.8	35.5
0°-90°	2013.9	42.4
90°-120°	1340.5	28.2
90°-150°	2410.4	50.7
90°-180°	2739.0	57.6
0°-180°	4752.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	890	890	890	890	890	
5°	890	886	878	884	883	84
15°	849	840	821	817	812	239
25°	772	754	721	706	698	355
35°	668	642	598	568	554	418
45°	549	516	461	422	403	424
55°	417	380	321	280	264	374
65°	285	245	189	155	146	282
75°	151	116	76	70	68	161
85°	38	23	20	19	19	43
90°	2	9	18	21	21	4
95°	25	81	437	127	86	27
105°	86	126	592	1036	937	91
115°	151	188	453	994	1140	150
125°	210	248	423	766	899	186
135°	246	294	417	631	729	190
145°	281	322	412	518	570	176
155°	319	344	399	453	472	147
165°	349	358	382	405	412	98
175°	363	364	366	371	371	34
180°	364	364	364	364	364	



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	893.2	892.6	892.1	891.6	891.1	890.0	888.5	886.9	885.4	883.9	885.3
5°	890.2	889.5	888.6	887.9	887.0	885.7	883.7	881.8	879.9	878.0	879.4
7.5°	882.0	881.2	880.2	879.4	878.5	876.8	874.4	871.9	869.3	866.9	867.6
10°	875.1	873.9	872.8	871.7	870.6	868.6	865.7	862.8	859.9	857.1	857.1
12.5°	865.3	864.0	862.7	861.5	860.3	857.9	854.3	850.8	847.3	843.8	843.7
15°	849.0	847.3	845.6	843.8	842.1	838.9	834.4	829.9	825.4	821.0	820.1
17.5°	828.7	826.7	824.6	822.6	820.5	816.6	810.9	805.2	799.5	793.8	792.1
20°	813.7	811.2	808.6	806.0	803.4	799.1	793.0	786.9	780.8	774.7	772.6
22.5°	796.9	794.0	791.1	788.1	785.1	780.4	773.9	767.4	761.0	754.5	751.9
25°	772.5	768.5	764.5	760.5	756.5	750.8	743.4	736.0	728.7	721.3	717.9
27.5°	742.9	738.5	734.1	729.6	725.2	718.9	710.7	702.5	694.3	686.1	681.4
30°	722.7	717.9	713.1	708.3	703.5	696.5	687.6	678.6	669.6	660.6	655.2
32.5°	702.5	697.1	691.6	686.2	680.7	673.3	663.7	654.2	644.7	635.2	629.2
35°	668.5	662.8	657.0	651.3	645.5	637.6	627.6	617.7	607.8	597.9	590.9
37.5°	634.2	627.8	621.4	614.9	608.5	600.0	589.4	578.8	568.2	557.5	549.7
40°	612.3	605.2	598.1	591.1	584.0	574.8	563.5	552.0	540.6	529.2	520.8
42.5°	587.4	580.3	573.3	566.3	559.2	549.8	538.0	526.2	514.4	502.7	493.5
45°	549.4	542.2	535.0	527.8	520.6	510.8	498.4	486.1	473.7	461.4	452.2
47.5°	511.4	503.5	495.6	487.7	479.8	469.7	457.2	444.9	432.5	420.2	410.3
50°	483.7	476.2	468.6	461.1	453.6	443.3	430.3	417.4	404.4	391.3	381.4
52.5°	458.9	450.7	442.5	434.3	426.2	415.7	402.7	389.9	377.0	364.2	353.8
55°	417.4	409.4	401.6	393.7	385.9	375.1	361.5	347.9	334.2	320.6	311.2
57.5°	378.9	370.3	361.7	353.2	344.6	333.5	319.8	306.1	292.4	278.7	269.9
60°	352.3	343.6	334.7	325.8	317.1	305.9	292.7	279.4	266.0	252.7	244.0
62.5°	325.7	317.0	308.1	299.3	290.5	279.4	266.1	252.8	239.4	226.1	218.0
65°	285.2	276.4	267.6	258.7	249.9	239.2	226.7	214.2	201.7	189.2	181.3
67.5°	244.6	235.7	226.8	217.8	209.0	198.5	186.4	174.5	162.5	150.4	144.6
70°	218.0	209.3	200.8	192.1	183.4	173.4	162.2	151.0	139.8	128.6	122.9
72.5°	191.4	182.9	174.4	165.9	157.3	148.0	137.8	127.5	117.3	107.2	102.5
75°	150.9	143.2	135.5	127.8	120.1	111.8	103.0	94.2	85.4	76.5	74.9
77.5°	114.0	107.0	100.0	93.0	86.1	79.7	74.1	68.4	62.7	57.0	56.2
80°	90.3	83.7	77.1	70.5	63.9	59.0	55.6	52.2	48.8	45.5	45.0
82.5°	67.8	62.0	56.4	50.7	45.0	41.4	39.8	38.3	36.7	35.1	34.6
85°	38.3	34.8	31.2	27.7	24.1	22.1	21.7	21.2	20.7	20.2	19.9
87.5°	14.1	13.0	11.9	10.9	9.8	9.4	9.9	10.3	10.7	11.2	10.9
90°	1.5	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7
92.5°	9.1	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5
95°	25.1	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5
97.5°	42.7	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5
100°	54.6	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0
102.5°	66.9	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9
105°	85.5	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0
107.5°	105.2	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3
110°	119.4	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.3	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7
115°	151.1	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7
117.5°	169.8	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3
120°	182.8	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8
122.5°	194.0	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2
125°	210.0	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8
127.5°	222.3	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5
130°	229.9	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2
132.5°	235.8	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6
135°	246.1	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5
137.5°	255.8	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9
140°	262.3	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6
142.5°	269.4	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9
145°	280.8	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5
147.5°	292.3	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3
150°	299.9	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2
152.5°	307.6	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5
155°	319.1	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4
157.5°	328.2	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5
160°	335.3	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1
162.5°	340.6	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8
165°	348.6	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6
167.5°	354.6	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7
170°	358.2	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5
172.5°	360.5	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4
175°	363.3	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7
177.5°	364.6	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
2.5°	886.7	888.2	889.6	890.1	889.9	889.6	889.4	889.1
5°	880.8	882.3	883.7	884.3	884.0	883.6	883.4	883.0
7.5°	868.5	869.2	870.1	870.2	869.6	869.1	868.6	868.0
10°	857.3	857.5	857.6	857.3	856.6	855.7	855.0	854.1
12.5°	843.6	843.5	843.4	842.8	841.9	840.9	840.1	839.1
15°	819.4	818.5	817.7	816.7	815.6	814.5	813.4	812.3
17.5°	790.4	788.7	786.9	785.3	783.6	781.9	780.2	778.6
20°	770.5	768.5	766.4	764.4	762.4	760.5	758.6	756.7
22.5°	749.3	746.7	744.1	741.9	740.1	738.3	736.5	734.7
25°	714.5	711.1	707.8	705.2	703.5	701.7	699.9	698.1
27.5°	676.7	672.0	667.3	663.6	660.9	658.3	655.5	652.8
30°	649.7	644.2	638.9	634.8	632.3	629.7	627.1	624.5
32.5°	623.3	617.3	611.3	607.0	604.4	601.6	598.9	596.3
35°	584.0	577.1	570.2	565.3	562.4	559.6	556.7	553.7
37.5°	541.9	534.0	526.2	520.6	517.0	513.4	509.8	506.2
40°	512.6	504.2	495.9	489.8	486.2	482.5	478.8	475.0
42.5°	484.5	475.3	466.2	460.0	456.7	453.4	450.1	446.8
45°	443.1	433.9	424.8	418.3	414.4	410.6	406.7	402.8
47.5°	400.3	390.4	380.4	373.7	370.3	366.8	363.4	360.0
50°	371.5	361.5	351.6	344.7	341.0	337.3	333.7	330.0
52.5°	343.6	333.2	322.8	316.0	312.7	309.4	306.1	302.8
55°	302.0	292.7	283.3	277.1	273.9	270.7	267.5	264.3
57.5°	261.1	252.3	243.6	237.8	235.1	232.3	229.6	226.9
60°	235.4	226.7	218.0	212.4	209.6	206.9	204.2	201.4
62.5°	209.8	201.7	193.5	188.0	185.2	182.3	179.5	176.6
65°	173.4	165.6	157.7	152.9	151.2	149.4	147.6	145.8
67.5°	138.7	132.8	127.0	123.1	121.2	119.3	117.4	115.6
70°	117.3	111.7	106.0	102.4	100.6	98.9	97.1	95.3
72.5°	97.9	93.4	88.8	86.1	85.4	84.6	83.9	83.1
75°	73.3	71.7	70.1	69.2	68.8	68.5	68.1	67.9
77.5°	55.3	54.5	53.5	53.0	52.7	52.3	52.0	51.7
80°	44.5	44.0	43.5	43.2	42.9	42.5	42.2	41.8
82.5°	34.1	33.6	33.2	32.9	32.8	32.8	32.7	32.6
85°	19.6	19.2	18.9	18.8	18.8	18.8	18.8	18.8
87.5°	10.9	10.9	10.9	11.1	10.8	10.8	10.9	10.7
90°	18.4	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	62.0	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	265.3	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	661.3	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	868.8	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	937.7	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	958.0	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	899.9	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	844.5	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P332287-830

CATALOG NUMBER: S123RDIP-S560D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.7	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	717.0	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	664.4	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	636.7	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	614.9	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	585.8	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	560.5	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	544.6	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	529.8	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	509.9	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	491.8	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	481.2	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	471.2	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	459.1	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	449.2	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	442.1	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	435.6	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	425.9	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	415.6	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	409.7	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	402.7	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	393.5	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	385.5	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	380.2	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	375.5	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.2	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.2	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)