

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332279

Luminaire Tested: **S123RDIP-S560D585U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332279
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4477.0 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	2.0
10°-20°	246.8	5.5
20°-30°	355.3	7.9
30°-40°	400.3	8.9
40°-50°	382.9	8.6
50°-60°	313.6	7.0
60°-70°	211.6	4.7
70°-80°	106.4	2.4
80°-90°	30.3	0.7
90°-100°	27.9	0.6
100°-110°	133.0	3.0
110°-120°	319.5	7.1
120°-130°	406.9	9.1
130°-140°	434.7	9.7
140°-150°	406.5	9.1
150°-160°	327.9	7.3
160°-170°	211.6	4.7
170°-180°	72.9	1.6
0°-30°	690.8	15.4
0°-40°	1091.1	24.4
0°-60°	1787.6	39.9
0°-90°	2135.9	47.7
90°-120°	480.5	10.7
90°-150°	1728.6	38.6
90°-180°	2341.0	52.3
0°-180°	4477.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	1	6	14	16	17	4
95°	35	13	18	21	22	43
105°	170	173	125	30	25	180
115°	319	322	327	333	335	315
125°	449	454	456	457	459	401
135°	560	563	565	567	565	431
145°	646	650	651	652	652	404
155°	711	710	711	713	710	328
165°	750	748	748	752	748	212
175°	768	765	765	769	765	73
180°	768	768	768	768	768	



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	14.8	13.6	12.3	11.1	9.8	9.4	9.7	10.0	10.4	10.7	10.7
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	10.6	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4
95°	34.8	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6
97.5°	69.9	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4
100°	96.4	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8
102.5°	126.5	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4
105°	170.0	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5
107.5°	215.8	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5
110°	246.4	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1
115°	318.8	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7
117.5°	360.7	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6
120°	386.7	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6
122.5°	413.2	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3
125°	449.4	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5
127.5°	484.6	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3
130°	506.5	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8
132.5°	527.5	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4
135°	559.5	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6
137.5°	586.9	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1
140°	605.1	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8
142.5°	622.0	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6
145°	645.6	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0
147.5°	667.9	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9
150°	681.6	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7
152.5°	693.9	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8
155°	711.2	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3
157.5°	724.7	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8
160°	732.9	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5
162.5°	740.7	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5
165°	750.0	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8
167.5°	757.3	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1
170°	761.4	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2
172.5°	764.2	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9
175°	767.7	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3
177.5°	768.6	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	10.6	10.6	10.6	10.5	10.4	10.3	10.2	10.2
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	16.2	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	19.5	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	20.4	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	20.8	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	31.2	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	80.0	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	196.0	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	248.9	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P332279

CATALOG NUMBER: S123RDIP-S560D585U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	286.1	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	329.9	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	369.6	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	395.6	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.0	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	456.8	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	492.7	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.3	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	534.9	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	593.7	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.3	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.0	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.3	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.2	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	684.9	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.3	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	711.9	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	725.5	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	733.3	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	740.3	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	749.8	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	763.9	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	767.2	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	768.4	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)