

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332305-830

Luminaire Tested: **S123RDIP-S775D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332305-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3988.2 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	90	87	83	81	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	72	73	69	66	66	62	60	58	56	54	50
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	52	49	46	43
4	79	68	60	54	74	65	57	52	58	52	48	52	48	44	47	43	40	37
5	73	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	33
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	39	35	31	29
7	62	50	42	36	59	47	40	35	43	37	33	39	34	30	35	31	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	2.9
10°-20°	317.9	8.0
20°-30°	457.8	11.5
30°-40°	515.7	12.9
40°-50°	493.3	12.4
50°-60°	404.0	10.1
60°-70°	272.6	6.8
70°-80°	137.1	3.4
80°-90°	37.6	0.9
90°-100°	91.6	2.3
100°-110°	259.3	6.5
110°-120°	255.1	6.4
120°-130°	203.5	5.1
130°-140°	160.4	4.0
140°-150°	119.7	3.0
150°-160°	83.4	2.1
160°-170°	49.0	1.2
170°-180°	16.0	0.4
0°-30°	890.0	22.3
0°-40°	1405.7	35.2
0°-60°	2303.0	57.7
0°-90°	2750.3	69.0
90°-120°	605.9	15.2
90°-150°	1089.5	27.3
90°-180°	1238.0	31.0
0°-180°	3988.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	1	4	8	9	10	3
95°	11	37	198	58	39	12
105°	39	57	268	468	424	41
115°	68	85	205	449	515	68
125°	95	112	191	346	406	84
135°	111	133	188	285	329	86
145°	127	145	186	234	258	80
155°	144	156	180	205	214	66
165°	158	162	173	183	186	44
175°	164	164	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.0	17.2	15.5	13.8	12.0	11.1	11.3	11.5	11.7	12.0	11.7
90°	0.7	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0
92.5°	4.1	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6
95°	11.3	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2
97.5°	19.3	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4
100°	24.7	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1
102.5°	30.3	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7
105°	38.6	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4
107.5°	47.6	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8
110°	53.9	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.9	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0
115°	68.2	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5
117.5°	76.7	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3
120°	82.6	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8
122.5°	87.7	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7
125°	94.9	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9
127.5°	100.5	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9
130°	104.0	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1
132.5°	106.6	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7
135°	111.2	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2
137.5°	115.6	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2
140°	118.6	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8
142.5°	121.8	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7
145°	126.9	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8
147.5°	132.1	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1
150°	135.5	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2
152.5°	139.0	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0
155°	144.2	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8
157.5°	148.4	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2
160°	151.6	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9
162.5°	153.9	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4
165°	157.5	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2
167.5°	160.2	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1
170°	161.8	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2
172.5°	163.0	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3
175°	164.2	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2
177.5°	164.9	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	11.6	11.5	11.4	11.3	11.1	10.9	10.8	10.7
90°	8.3	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	28.1	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	119.9	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	298.9	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	392.7	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.9	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	433.0	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	406.7	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	381.7	443.0	484.9	508.3	517.6	520.3	519.6	519.0



TEST NUMBER: P332305-830

CATALOG NUMBER: S123RDIP-S775D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	356.9	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	324.0	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	300.3	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	287.8	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	278.0	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	264.8	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	253.4	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	246.1	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	239.5	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	230.5	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	222.3	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	217.5	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	213.0	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	207.5	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	203.0	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	199.8	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	196.9	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	192.6	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	187.8	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	185.2	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	182.0	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	177.9	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	174.3	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	171.8	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	169.8	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	166.8	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.0	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)