

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332316-830

Luminaire Tested: **S123RDIP-S775D805U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332316-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5350.9 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	46	44	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	2.1
10°-20°	317.9	5.9
20°-30°	457.8	8.6
30°-40°	515.7	9.6
40°-50°	493.3	9.2
50°-60°	404.0	7.5
60°-70°	272.6	5.1
70°-80°	137.1	2.6
80°-90°	39.1	0.7
90°-100°	61.1	1.1
100°-110°	182.9	3.4
110°-120°	311.1	5.8
120°-130°	409.2	7.6
130°-140°	460.0	8.6
140°-150°	452.1	8.4
150°-160°	380.6	7.1
160°-170°	253.4	4.7
170°-180°	88.7	1.7
0°-30°	890.0	16.6
0°-40°	1405.7	26.3
0°-60°	2303.0	43.0
0°-90°	2751.8	51.4
90°-120°	555.1	10.4
90°-150°	1876.4	35.1
90°-180°	2599.0	48.6
0°-180°	5350.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	1	8	18	21	22	5
95°	44	49	55	57	58	49
105°	166	168	174	174	175	178
115°	313	315	314	315	314	310
125°	458	460	459	456	453	409
135°	595	599	598	596	594	458
145°	721	723	725	724	721	450
155°	826	826	827	829	825	380
165°	900	898	898	901	897	254
175°	936	933	933	937	932	89
180°	938	938	938	938	938	



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.1	17.5	15.9	14.3	12.7	12.1	12.5	12.9	13.4	13.8	13.8
90°	0.8	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4
92.5°	17.8	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8
95°	43.5	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2
97.5°	77.2	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1
100°	100.2	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9
102.5°	126.8	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8
105°	165.8	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9
107.5°	211.2	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3
110°	239.5	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.0	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0
115°	313.2	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1
117.5°	357.7	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2
120°	385.4	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0
122.5°	414.3	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2
125°	458.4	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5
127.5°	499.1	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2
130°	526.1	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1
132.5°	553.3	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8
135°	594.7	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8
137.5°	633.0	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9
140°	659.5	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	683.7	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5
145°	721.4	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0
147.5°	754.5	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2
150°	777.4	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4
152.5°	796.4	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6
155°	826.0	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5
157.5°	851.4	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9
160°	867.3	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7
162.5°	881.5	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8
165°	899.8	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5
167.5°	914.4	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0
170°	922.7	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9
172.5°	929.1	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2
175°	935.9	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0
177.5°	938.7	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	13.7	13.7	13.7	13.6	13.5	13.3	13.2	13.1
90°	19.0	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.3	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	55.8	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	86.8	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.3	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.3	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	215.7	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	243.7	244.4	245.1	245.2	244.9	244.6	244.2	243.9



TEST NUMBER: P332316-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.7	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.2	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.8	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.8	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.8	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	500.3	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	528.6	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	556.0	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	597.1	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	637.3	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.6	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.4	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.8	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	799.7	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.1	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	852.5	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	867.5	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	881.7	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	899.6	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	928.2	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	934.9	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	937.9	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)