

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332322

Luminaire Tested: **S123RDIP-S775D1025U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332322  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1025U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6441.1 lumens  
Efficiency: N/A  
Efficacy: 123.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45					45			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39					39			
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33					33			
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28					28			
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24					24			
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21					21			
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19					19			
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17					17			
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15					15			
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14					14			
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	1.9
10°-20°	337.3	5.2
20°-30°	485.7	7.5
30°-40°	547.1	8.5
40°-50°	523.4	8.1
50°-60°	428.6	6.7
60°-70°	289.2	4.5
70°-80°	145.5	2.3
80°-90°	42.3	0.7
90°-100°	82.8	1.3
100°-110°	247.8	3.8
110°-120°	421.4	6.5
120°-130°	554.3	8.6
130°-140°	623.0	9.7
140°-150°	612.4	9.5
150°-160°	515.6	8.0
160°-170°	343.2	5.3
170°-180°	120.2	1.9
0°-30°	944.3	14.7
0°-40°	1491.4	23.2
0°-60°	2443.4	37.9
0°-90°	2920.3	45.3
90°-120°	752.0	11.7
90°-150°	2541.8	39.5
90°-180°	3521.0	54.7
0°-180°	6441.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	11	24	28	30	6
95°	59	66	74	78	78	66
105°	225	227	236	236	238	241
115°	424	427	425	426	425	420
125°	621	624	622	618	614	553
135°	806	811	810	807	805	621
145°	977	979	982	981	977	610
155°	1119	1119	1120	1123	1117	515
165°	1219	1216	1216	1221	1215	344
175°	1268	1264	1264	1269	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.7	17.1	15.5	13.9	13.4	14.0	14.5	15.1	15.7	15.7
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	24.2	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0
95°	58.9	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8
97.5°	104.6	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6
100°	135.8	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4
102.5°	171.7	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5
105°	224.6	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6
107.5°	286.1	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6
110°	324.4	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3



TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.3	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0
115°	424.2	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5
117.5°	484.5	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9
120°	522.1	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8
122.5°	561.2	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4
125°	620.9	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0
127.5°	676.0	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9
130°	712.7	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8
132.5°	749.5	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2
135°	805.6	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7
137.5°	857.5	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1
140°	893.4	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.1	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7
145°	977.2	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0
147.5°	1022.0	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4
150°	1053.1	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1
152.5°	1078.7	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0
155°	1119.0	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9
157.5°	1153.3	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9
160°	1174.9	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0
162.5°	1194.1	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2
165°	1218.8	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1
167.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8
170°	1249.8	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3
172.5°	1258.5	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9
175°	1267.7	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1
177.5°	1271.5	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	15.7	15.7	15.6	15.6	15.5	15.4	15.3	15.2
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	39.8	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	75.6	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	117.6	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.1	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.2	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	292.3	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	330.2	331.1	332.0	332.2	331.7	331.3	330.9	330.4





TEST NUMBER: P332322

CATALOG NUMBER: S123RDIP-S775D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.1	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.6	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.8	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	620.1	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	677.7	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.9	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	753.1	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	808.8	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	863.2	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.9	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.5	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.8	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.4	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1121.8	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1154.8	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1175.1	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1194.3	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1218.5	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1257.3	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1266.4	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1270.5	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)