

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332317-830

Luminaire Tested: **S123RDIP-S775D805U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332317-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U830-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5490.6 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	34	29	25	29	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	2.1
10°-20°	317.9	5.8
20°-30°	457.8	8.3
30°-40°	515.7	9.4
40°-50°	493.3	9.0
50°-60°	404.0	7.4
60°-70°	272.6	5.0
70°-80°	137.1	2.5
80°-90°	39.1	0.7
90°-100°	202.6	3.7
100°-110°	573.6	10.4
110°-120°	564.3	10.3
120°-130°	450.1	8.2
130°-140°	354.9	6.5
140°-150°	264.9	4.8
150°-160°	184.6	3.4
160°-170°	108.5	2.0
170°-180°	35.3	0.6
0°-30°	890.0	16.2
0°-40°	1405.7	25.6
0°-60°	2303.0	41.9
0°-90°	2751.8	50.1
90°-120°	1340.5	24.4
90°-150°	2410.4	43.9
90°-180°	2739.0	49.9
0°-180°	5490.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	2	9	18	21	21	4
95°	25	81	437	127	86	27
105°	86	126	592	1036	937	91
115°	151	188	453	994	1140	150
125°	210	248	423	766	899	186
135°	246	294	417	631	729	190
145°	281	322	412	518	570	176
155°	319	344	399	453	472	147
165°	349	358	382	405	412	98
175°	363	364	366	371	371	34
180°	364	364	364	364	364	



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.2	17.6	15.9	14.5	12.8	12.2	12.6	13.1	13.5	13.9	13.7
90°	1.5	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7
92.5°	9.1	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5
95°	25.1	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5
97.5°	42.7	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5
100°	54.6	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0
102.5°	66.9	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9
105°	85.5	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0
107.5°	105.2	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3
110°	119.4	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.3	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7
115°	151.1	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7
117.5°	169.8	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3
120°	182.8	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8
122.5°	194.0	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2
125°	210.0	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8
127.5°	222.3	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5
130°	229.9	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2
132.5°	235.8	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6
135°	246.1	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5
137.5°	255.8	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9
140°	262.3	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6
142.5°	269.4	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9
145°	280.8	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5
147.5°	292.3	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3
150°	299.9	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2
152.5°	307.6	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5
155°	319.1	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4
157.5°	328.2	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5
160°	335.3	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1
162.5°	340.6	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8
165°	348.6	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6
167.5°	354.6	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7
170°	358.2	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5
172.5°	360.5	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4
175°	363.3	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7
177.5°	364.6	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	13.6	13.6	13.6	13.7	13.4	13.3	13.3	12.9
90°	18.4	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	62.0	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	265.3	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	661.3	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	868.8	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	937.7	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	958.0	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	899.9	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	844.5	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P332317-830

CATALOG NUMBER: S123RDIP-S775D805U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.7	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	717.0	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	664.4	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	636.7	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	614.9	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	585.8	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	560.5	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	544.6	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	529.8	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	509.9	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	491.8	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	481.2	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	471.2	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	459.1	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	449.2	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	442.1	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	435.6	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	425.9	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	415.6	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	409.7	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	402.7	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	393.5	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	385.5	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	380.2	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	375.5	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.2	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.2	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)