

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332329

Luminaire Tested: **S123RDIP-S775D1195U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332329
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7239.2 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30	25				
4	73	63	55	49	66	58	51	46	48	43	39	38	35	32	30	28	26	22				
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	22	19				
6	62	50	42	37	56	46	39	34	39	33	29	31	27	25	25	22	20	17				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13				
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	26	21	27	22	19	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	1.7
10°-20°	337.3	4.7
20°-30°	485.7	6.7
30°-40°	547.1	7.6
40°-50°	523.4	7.2
50°-60°	428.6	5.9
60°-70°	289.2	4.0
70°-80°	145.5	2.0
80°-90°	42.9	0.6
90°-100°	319.4	4.4
100°-110°	904.4	12.5
110°-120°	889.7	12.3
120°-130°	709.7	9.8
130°-140°	559.5	7.7
140°-150°	417.6	5.8
150°-160°	291.1	4.0
160°-170°	171.0	2.4
170°-180°	55.6	0.8
0°-30°	944.3	13.0
0°-40°	1491.4	20.6
0°-60°	2443.4	33.8
0°-90°	2921.0	40.4
90°-120°	2113.6	29.2
90°-150°	3800.4	52.5
90°-180°	4318.0	59.6
0°-180°	7239.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	2	14	29	33	34	5
95°	40	128	689	201	135	43
105°	135	199	934	1634	1478	143
115°	238	297	714	1567	1797	236
125°	331	391	667	1208	1418	294
135°	388	463	658	995	1149	300
145°	443	507	650	816	898	277
155°	503	543	629	715	745	231
165°	550	565	602	638	650	155
175°	573	573	577	586	584	54
180°	574	574	574	574	574	



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.6	19.0	17.4	16.1	14.5	13.9	14.6	15.3	16.0	16.7	16.3
90°	2.3	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9
92.5°	14.4	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8
95°	39.5	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8
97.5°	67.4	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3
100°	86.0	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2
102.5°	105.5	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4
105°	134.8	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6
107.5°	165.9	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5
110°	188.2	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.7	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6
115°	238.2	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5
117.5°	267.7	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0
120°	288.1	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0
122.5°	305.8	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6
125°	331.1	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2
127.5°	350.4	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1
130°	362.5	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0
132.5°	371.8	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0
135°	388.1	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2
137.5°	403.4	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4
140°	413.6	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1
142.5°	424.8	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6
145°	442.7	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7
147.5°	460.8	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9
150°	472.9	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4
152.5°	485.0	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0
155°	503.1	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8
157.5°	517.5	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2
160°	528.6	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9
162.5°	537.0	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5
165°	549.6	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1
167.5°	559.1	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2
170°	564.7	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7
172.5°	568.4	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2
175°	572.8	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8
177.5°	574.9	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	16.3	16.4	16.4	16.7	16.3	16.3	16.4	16.0
90°	29.0	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	97.8	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	418.3	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	1042.6	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1369.8	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1478.6	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1510.4	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1418.8	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1331.5	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P332329

CATALOG NUMBER: S123RDIP-S775D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1245.0	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1130.5	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1047.5	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1003.8	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	969.4	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	923.7	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	883.7	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	858.6	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	835.4	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	804.0	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	775.4	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	758.7	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	742.9	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	723.8	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	708.3	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	697.1	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	686.9	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	671.5	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	655.3	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	646.0	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	634.8	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	620.4	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	607.9	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	599.5	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	592.1	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	582.1	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	575.8	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)