

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332036-930

Luminaire Tested: **S123DIP-S1000D1195U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332036-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7347.8 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12326	12326	12326	12326
5°	14699	12379	10970	12379
10°	18398	12316	9908	12316
15°	22566	12217	9225	12217
20°	26882	12062	8782	12062
25°	28544	11873	8684	11873
30°	24467	11737	8730	11737
35°	17015	11540	8821	11540
40°	12816	11311	8793	11311
45°	10641	10971	8681	10971
50°	9532	10275	8602	10275
55°	8912	9526	8496	9526
60°	8359	8742	8409	8742
65°	7857	7969	8140	7969
70°	7371	7091	7751	7091
75°	6600	6209	7107	6209
80°	5777	5089	6118	5089
85°	4520	3693	4113	3693



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.5
10°-20°	361.7	4.9
20°-30°	607.1	8.3
30°-40°	687.4	9.4
40°-50°	616.4	8.4
50°-60°	497.4	6.8
60°-70°	346.6	4.7
70°-80°	182.2	2.5
80°-90°	48.1	0.7
90°-100°	46.4	0.6
100°-110°	220.9	3.0
110°-120°	530.6	7.2
120°-130°	675.7	9.2
130°-140°	722.0	9.8
140°-150°	675.1	9.2
150°-160°	544.6	7.4
160°-170°	351.5	4.8
170°-180°	121.1	1.6
0°-30°	1081.6	14.7
0°-40°	1768.9	24.1
0°-60°	2882.8	39.2
0°-90°	3459.8	47.1
90°-120°	797.9	10.9
90°-150°	2870.8	39.1
90°-180°	3888.0	52.9
0°-180°	7347.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1360	1146	1015	1146	1360	141
15°	2025	1096	828	1096	2025	585
25°	2403	1000	731	1000	2403	1054
35°	1295	878	671	878	1295	841
45°	699	721	570	721	699	553
55°	475	508	453	508	475	426
65°	308	313	320	313	308	307
75°	159	149	171	149	159	170
85°	37	30	33	30	37	44
90°	28	1	28	1	28	15
95°	36	58	36	58	36	30
105°	42	282	42	282	42	95
115°	557	530	557	530	557	515
125°	762	746	762	746	762	680
135°	939	929	939	929	939	724
145°	1083	1072	1083	1072	1083	676
155°	1179	1181	1179	1181	1179	544
165°	1243	1246	1243	1246	1243	351
175°	1270	1275	1270	1275	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1215.2	1214.4	1212.1	1213.9	1210.4	1205.5	1205.0	1200.6	1187.7	1186.8	1183.3
5°	1360.4	1355.9	1355.4	1354.9	1347.0	1336.5	1316.5	1314.9	1288.3	1275.0	1258.8
7.5°	1548.3	1550.7	1542.5	1535.5	1511.7	1496.1	1474.6	1447.2	1414.5	1381.4	1359.3
10°	1683.3	1701.6	1678.9	1663.3	1648.9	1621.7	1590.1	1550.7	1511.3	1465.3	1430.3
12.5°	1828.0	1837.0	1832.4	1817.8	1795.4	1754.0	1697.9	1654.6	1618.3	1541.6	1510.6
15°	2025.0	2058.9	2037.3	1987.3	1988.4	1949.1	1875.8	1795.4	1752.6	1685.5	1594.0
17.5°	2235.0	2239.2	2230.0	2188.3	2160.6	2106.5	2038.9	1961.8	1875.3	1794.0	1697.0
20°	2346.8	2343.5	2324.1	2302.4	2254.7	2212.6	2138.8	2052.8	1941.8	1861.9	1756.0
22.5°	2409.0	2403.4	2394.2	2376.1	2336.4	2291.2	2224.9	2130.9	2025.3	1915.2	1792.8
25°	2403.4	2410.6	2411.7	2406.8	2392.9	2365.7	2313.5	2238.6	2133.2	1991.8	1864.2
27.5°	2185.9	2196.2	2225.8	2252.1	2281.5	2311.5	2307.5	2270.3	2192.3	2070.0	1914.1
30°	1968.5	1946.3	2001.2	2070.5	2117.7	2200.9	2247.5	2250.3	2206.4	2101.6	1949.5
32.5°	1666.6	1691.0	1715.3	1800.7	1903.7	1997.2	2089.9	2164.6	2173.2	2103.4	1970.4
35°	1294.9	1325.4	1369.8	1414.2	1525.2	1620.6	1783.7	1925.7	2038.9	2053.9	1972.3
37.5°	1043.5	1058.6	1086.6	1131.1	1203.7	1316.9	1443.1	1622.6	1786.6	1908.5	1913.8
40°	912.1	916.6	948.2	982.0	1040.8	1134.0	1247.7	1406.4	1602.8	1773.2	1844.2
42.5°	813.6	823.3	836.7	869.3	916.1	986.2	1091.9	1223.1	1403.1	1599.1	1738.1
45°	699.0	710.1	718.4	740.1	773.4	820.5	894.4	1014.2	1151.2	1353.7	1540.7
47.5°	623.4	624.3	630.5	646.8	669.4	704.8	757.0	834.0	959.8	1124.1	1316.0
50°	569.2	578.1	580.3	593.0	610.8	636.9	680.2	745.7	848.9	993.1	1169.5
52.5°	531.1	533.7	540.0	549.2	564.7	585.0	622.5	673.8	754.7	877.7	1039.9
55°	474.9	474.9	481.0	488.2	497.1	515.4	540.4	578.1	639.7	735.2	869.4
57.5°	423.0	425.7	430.1	432.3	439.9	451.9	472.8	501.4	547.4	620.9	727.6
60°	388.3	393.4	392.8	397.2	403.9	413.4	431.0	454.4	495.5	554.2	644.2
62.5°	358.2	357.8	357.8	363.1	369.7	378.7	390.3	410.4	445.3	497.4	574.0
65°	308.5	307.4	311.3	314.5	316.8	323.4	332.3	350.1	373.4	412.2	471.6
67.5°	264.3	261.1	263.2	264.3	268.1	273.3	281.6	292.6	311.1	342.3	387.0
70°	234.2	231.4	230.8	231.9	235.2	239.1	245.2	255.8	273.0	297.9	330.7
72.5°	203.1	201.1	201.1	203.5	205.0	207.6	211.9	221.6	235.2	254.0	284.5
75°	158.7	158.7	158.7	159.2	160.9	163.1	166.4	171.5	182.0	195.3	215.8
77.5°	119.0	118.9	118.1	118.1	120.5	121.5	122.3	126.9	132.8	141.8	156.8
80°	93.2	90.4	91.6	93.2	94.3	94.9	96.5	97.7	102.6	107.6	118.1
82.5°	69.2	66.9	67.1	69.7	69.9	70.4	72.2	73.7	75.6	80.1	85.8
85°	36.6	36.6	37.2	37.2	37.7	37.2	38.8	39.4	39.4	42.2	45.5
87.5°	19.0	18.0	18.4	18.8	18.2	18.5	18.8	19.1	19.3	19.6	19.6
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.4	23.6	22.7	20.0
92.5°	31.5	31.2	31.0	30.7	30.4	29.7	28.3	26.9	25.6	24.2	22.2
95°	36.0	36.0	36.0	36.0	36.0	35.2	33.8	32.3	30.8	29.4	27.1
97.5°	39.1	38.8	38.6	38.4	38.2	37.3	35.5	33.8	32.2	30.5	45.7
100°	39.8	39.5	39.4	39.1	39.0	38.0	36.3	34.7	32.9	31.2	64.1
102.5°	40.5	40.2	39.8	39.4	39.1	41.4	46.6	51.9	57.1	62.3	98.2
105°	41.7	41.3	40.8	40.4	40.0	58.4	95.6	132.9	170.2	207.4	226.4
107.5°	130.9	159.0	187.0	215.2	243.2	270.9	298.2	325.5	352.9	380.3	377.2
110°	260.5	290.6	320.7	350.8	380.9	399.4	406.3	413.3	420.3	427.2	424.9



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.9	453.2	459.6	465.9	472.3	475.5	475.3	475.2	475.1	474.9	472.6
115°	556.9	556.1	555.3	554.4	553.6	552.1	550.0	547.9	545.8	543.7	541.8
117.5°	618.7	618.6	618.4	618.2	618.1	617.1	615.5	613.8	612.0	610.4	609.4
120°	661.1	661.1	661.1	661.1	661.1	660.3	658.6	657.0	655.3	653.5	653.0
122.5°	702.9	702.7	702.5	702.3	702.1	701.5	700.3	699.1	698.0	696.8	695.9
125°	761.6	761.2	760.8	760.3	759.9	759.5	759.0	758.6	758.2	757.7	756.9
127.5°	818.0	818.5	818.9	819.3	819.7	819.5	818.9	818.2	817.6	816.8	815.9
130°	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2	853.4	852.5	851.7
132.5°	887.7	888.4	888.9	889.5	890.1	890.0	889.2	888.3	887.5	886.6	885.9
135°	938.7	939.3	940.0	940.6	941.3	941.3	940.6	940.0	939.3	938.7	937.8
137.5°	986.6	987.1	987.5	987.9	988.3	988.0	987.0	986.0	985.0	984.0	983.5
140°	1015.5	1015.9	1016.3	1016.7	1017.1	1016.9	1016.0	1015.2	1014.4	1013.5	1012.9
142.5°	1042.0	1042.5	1043.1	1043.7	1044.3	1044.2	1043.6	1042.9	1042.3	1041.5	1041.0
145°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.5	1082.1	1081.7	1081.2	1080.8	1080.4
147.5°	1113.0	1113.9	1114.9	1115.9	1116.9	1117.1	1116.7	1116.3	1115.9	1115.4	1115.0
150°	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5	1137.1	1136.7	1136.3
152.5°	1153.9	1154.9	1155.8	1156.8	1157.8	1157.9	1157.2	1156.3	1155.6	1154.9	1154.6
155°	1179.3	1180.6	1181.9	1183.1	1184.3	1184.5	1183.4	1182.3	1181.3	1180.2	1180.1
157.5°	1200.7	1202.3	1204.0	1205.7	1207.3	1207.5	1206.2	1204.9	1203.7	1202.4	1202.6
160°	1214.3	1215.8	1217.3	1218.8	1220.3	1220.3	1219.0	1217.8	1216.6	1215.3	1215.5
162.5°	1227.2	1228.5	1229.8	1231.1	1232.4	1232.4	1230.9	1229.6	1228.1	1226.6	1226.9
165°	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.8	1245.2	1243.5	1241.8	1242.0
167.5°	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9	1253.9
170°	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8	1260.8
172.5°	1264.5	1266.4	1268.3	1270.1	1271.9	1272.0	1270.3	1268.7	1267.0	1265.3	1265.1
175°	1270.2	1271.9	1273.6	1275.3	1276.9	1277.1	1275.6	1274.1	1272.7	1271.1	1271.0
177.5°	1271.9	1273.6	1275.3	1277.0	1278.6	1278.8	1277.5	1276.1	1274.8	1273.4	1273.3
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1180.6	1177.0	1173.5	1167.3	1162.0	1154.5	1152.2	1149.6	1141.6	1134.5	1129.1
5°	1252.7	1239.4	1220.0	1202.2	1187.8	1168.4	1157.3	1145.7	1129.0	1114.0	1101.9
7.5°	1328.2	1302.0	1271.9	1239.2	1208.8	1179.5	1155.8	1134.8	1111.5	1089.4	1072.2
10°	1388.1	1350.4	1308.2	1262.7	1223.9	1186.2	1154.5	1126.8	1096.8	1070.7	1049.1
12.5°	1456.5	1400.5	1342.4	1287.1	1241.2	1188.9	1150.6	1115.2	1081.3	1049.9	1025.6
15°	1537.3	1466.3	1397.6	1321.5	1251.6	1186.2	1140.7	1096.3	1056.9	1024.7	993.7
17.5°	1611.0	1530.6	1439.9	1347.5	1263.1	1185.5	1121.9	1071.6	1022.4	983.0	952.0
20°	1652.8	1561.2	1458.6	1362.6	1269.4	1182.8	1113.0	1053.0	999.7	958.1	923.2
22.5°	1688.7	1581.6	1475.4	1372.8	1268.9	1175.7	1096.5	1034.9	977.1	936.4	899.2
25°	1726.0	1597.8	1491.3	1370.9	1255.0	1158.5	1069.7	999.7	942.1	894.4	856.1
27.5°	1757.9	1596.8	1470.3	1340.8	1233.0	1136.2	1041.5	966.5	905.2	853.4	814.6
30°	1779.2	1599.0	1448.6	1320.5	1211.7	1111.8	1019.7	944.3	880.0	827.2	790.6
32.5°	1792.6	1597.6	1428.6	1292.0	1177.9	1089.6	996.2	918.1	852.0	800.1	764.8
35°	1800.3	1587.9	1394.2	1233.3	1123.5	1037.5	959.3	878.2	808.9	760.7	720.7
37.5°	1784.8	1567.3	1354.3	1176.7	1056.5	971.8	906.0	837.0	770.6	717.5	683.1
40°	1760.4	1554.0	1323.2	1136.8	1010.3	928.7	872.7	805.0	739.6	689.1	656.9
42.5°	1713.8	1526.9	1289.1	1092.4	962.4	880.8	829.2	772.7	710.7	663.3	631.1
45°	1600.0	1468.0	1237.8	1025.8	891.5	807.2	761.7	720.7	664.6	618.6	590.8
47.5°	1442.3	1379.3	1163.7	955.6	817.7	736.5	689.3	656.2	615.3	578.1	551.5
50°	1332.6	1306.6	1113.5	907.7	768.4	689.1	643.6	613.6	584.2	547.1	522.6
52.5°	1206.2	1222.2	1054.9	857.9	718.3	640.3	597.5	573.6	546.9	516.4	495.1
55°	1028.1	1086.3	953.7	774.5	643.6	569.2	528.7	507.6	492.1	469.4	451.0
57.5°	861.3	935.4	844.3	688.5	570.2	506.1	467.2	444.3	434.3	422.4	408.0
60°	762.3	835.5	766.2	630.8	521.0	459.9	425.5	406.1	396.2	387.8	375.6
62.5°	674.0	748.1	689.8	572.3	472.5	416.0	386.0	367.0	359.3	355.0	344.5
65°	552.6	616.4	577.6	481.0	403.3	353.4	326.2	312.9	305.7	304.0	297.3
67.5°	449.7	498.3	470.0	399.0	337.9	294.7	271.7	260.3	254.8	254.2	249.2
70°	382.3	427.8	406.1	341.8	289.0	255.2	235.2	225.3	221.9	221.4	218.6
72.5°	329.9	361.6	344.4	290.7	250.0	219.2	204.6	194.2	190.4	191.2	189.3
75°	244.1	268.0	258.0	220.8	188.1	168.1	155.9	149.3	145.9	147.6	145.4
77.5°	175.6	190.8	181.7	156.0	135.8	121.4	112.4	108.3	105.3	105.2	104.2
80°	132.6	141.5	136.5	120.9	104.3	92.1	84.9	82.1	80.5	79.9	79.3
82.5°	94.4	102.0	96.1	85.4	74.1	66.8	62.7	59.0	57.8	58.1	57.6
85°	47.7	50.5	48.3	41.6	37.2	33.8	31.6	29.9	28.9	29.4	28.3
87.5°	19.9	19.7	17.9	15.7	14.3	12.6	12.1	10.8	10.4	10.8	10.8
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	20.1	18.1	16.0	15.2	15.8	16.5	17.0	17.6	17.0	16.5	15.8
95°	24.7	22.4	20.1	23.2	31.9	40.5	49.2	57.8	49.2	40.5	31.9
97.5°	60.8	76.0	91.2	100.6	104.5	108.4	112.3	116.1	112.3	108.4	104.5
100°	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.0	164.3	168.5	172.7
102.5°	134.0	169.9	205.8	222.3	219.2	216.1	213.1	210.1	213.1	216.1	219.2
105°	245.3	264.2	283.2	291.6	289.2	286.9	284.6	282.3	284.6	286.9	289.2
107.5°	374.2	371.3	368.3	365.8	363.9	362.2	360.3	358.4	360.3	362.2	363.9
110°	422.6	420.3	417.9	416.0	414.3	412.5	410.9	409.2	410.9	412.5	414.3



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	470.3	468.0	465.7	463.7	462.3	460.7	459.2	457.7	459.2	460.7	462.3
115°	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5	530.8	532.0	533.3
117.5°	608.5	607.5	606.5	605.3	603.7	602.1	600.5	599.0	600.5	602.1	603.7
120°	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2	644.1	646.0	647.9
122.5°	695.2	694.4	693.6	692.4	690.8	689.3	687.7	686.2	687.7	689.3	690.8
125°	756.1	755.2	754.4	753.2	751.5	749.7	748.1	746.4	748.1	749.7	751.5
127.5°	814.9	813.8	812.9	811.5	809.8	808.1	806.4	804.8	806.4	808.1	809.8
130°	850.8	849.9	849.1	847.8	846.2	844.5	842.9	841.1	842.9	844.5	846.2
132.5°	885.3	884.6	883.9	882.7	881.0	879.4	877.7	876.0	877.7	879.4	881.0
135°	937.0	936.2	935.3	934.3	933.0	931.7	930.5	929.2	930.5	931.7	933.0
137.5°	983.1	982.6	982.1	981.1	979.5	977.9	976.3	974.7	976.3	977.9	979.5
140°	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.2	1005.0	1006.2	1007.5	1008.8
142.5°	1040.3	1039.7	1039.0	1038.1	1036.8	1035.6	1034.3	1033.1	1034.3	1035.6	1036.8
145°	1079.9	1079.5	1079.1	1078.2	1076.7	1075.2	1073.7	1072.3	1073.7	1075.2	1076.7
147.5°	1114.6	1114.2	1113.8	1113.0	1112.1	1111.2	1110.2	1109.2	1110.2	1111.2	1112.1
150°	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.5	1132.0	1132.5	1133.2	1133.8
152.5°	1154.4	1154.1	1153.8	1153.6	1153.2	1153.0	1152.7	1152.4	1152.7	1153.0	1153.2
155°	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2	1180.8	1180.3	1179.9
157.5°	1202.8	1203.1	1203.2	1203.4	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4
160°	1215.7	1215.9	1216.1	1216.3	1216.6	1216.8	1217.0	1217.2	1217.0	1216.8	1216.6
162.5°	1227.1	1227.3	1227.5	1227.8	1228.4	1229.0	1229.6	1230.0	1229.6	1229.0	1228.4
165°	1242.2	1242.4	1242.7	1243.1	1243.7	1244.3	1245.0	1245.6	1245.0	1244.3	1243.7
167.5°	1253.9	1253.9	1253.9	1254.3	1255.2	1256.1	1256.9	1257.8	1256.9	1256.1	1255.2
170°	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5	1263.7	1262.9	1262.0
172.5°	1264.9	1264.8	1264.6	1265.0	1266.1	1267.1	1268.1	1269.1	1268.1	1267.1	1266.1
175°	1270.7	1270.6	1270.3	1270.7	1271.8	1272.8	1273.9	1275.0	1273.9	1272.8	1271.8
177.5°	1273.1	1272.9	1272.8	1273.1	1274.0	1274.8	1275.6	1276.5	1275.6	1274.8	1274.0
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1126.0	1122.9	1118.5	1111.8	1106.5	1098.0	1098.0	1099.4	1099.4	1098.9	1098.0
5°	1091.8	1083.5	1073.6	1061.9	1049.7	1037.5	1035.3	1030.9	1027.5	1025.2	1022.5
7.5°	1055.8	1041.1	1026.5	1010.2	995.3	983.0	974.4	967.4	962.8	957.9	954.4
10°	1031.4	1013.1	995.9	978.7	959.8	944.9	935.4	928.7	923.7	919.3	917.1
12.5°	1002.5	981.5	962.6	946.2	925.6	910.2	901.2	898.1	892.3	882.9	878.0
15°	960.3	940.9	918.2	893.2	883.2	864.4	853.9	848.9	845.5	838.3	836.1
17.5°	924.3	898.9	873.3	854.8	836.2	820.9	815.0	808.8	804.4	798.5	796.7
20°	895.4	872.7	849.4	829.4	810.0	793.4	788.4	783.9	779.5	776.7	774.5
22.5°	866.2	843.4	824.1	805.4	784.7	773.8	768.4	763.5	760.4	758.6	756.3
25°	825.0	805.0	783.4	766.7	750.1	742.9	739.6	736.8	734.6	731.8	731.2
27.5°	788.1	766.4	748.9	733.4	721.4	715.3	712.2	710.8	711.3	712.2	712.9
30°	760.7	740.7	726.3	712.9	701.8	696.3	695.7	695.7	698.0	698.5	699.6
32.5°	735.3	718.9	704.5	691.6	683.2	679.4	681.5	681.5	683.3	684.8	686.7
35°	698.5	684.0	672.9	661.9	654.7	656.3	657.5	658.5	661.3	664.6	666.9
37.5°	663.3	650.8	639.3	630.6	627.3	630.2	632.9	635.3	638.5	641.0	643.3
40°	638.1	628.6	617.5	609.8	610.8	612.5	614.7	617.5	620.3	621.9	624.2
42.5°	614.5	604.6	596.2	589.8	591.3	593.5	594.8	596.2	599.4	602.4	603.7
45°	578.7	570.9	563.1	559.2	560.4	561.5	562.6	564.3	567.0	569.2	569.8
47.5°	538.3	533.0	527.7	524.0	525.7	525.3	526.8	530.3	531.2	532.5	535.6
50°	512.7	507.6	501.6	500.4	500.4	500.4	501.0	505.4	505.4	507.6	509.9
52.5°	484.2	481.0	477.1	475.2	474.3	474.3	476.5	478.8	479.7	482.8	485.0
55°	442.2	438.9	435.5	433.8	432.8	433.8	438.3	439.4	442.2	443.8	445.5
57.5°	398.4	395.8	393.1	392.2	392.0	393.5	395.9	399.3	399.9	405.0	407.6
60°	369.5	365.6	363.4	363.4	362.3	367.3	366.2	371.7	372.8	376.2	380.0
62.5°	339.7	334.5	333.6	333.6	335.3	336.6	338.2	340.6	343.6	347.7	350.7
65°	291.8	289.0	292.9	292.4	291.3	294.6	294.6	297.3	300.7	304.6	310.7
67.5°	246.5	245.0	245.3	245.3	247.0	248.9	250.5	252.9	256.9	261.0	265.0
70°	215.8	217.5	214.7	217.0	218.6	219.2	220.3	223.6	228.0	230.8	235.2
72.5°	186.1	186.0	186.3	187.2	188.8	189.9	190.9	194.8	199.6	201.9	205.5
75°	143.2	142.6	144.2	144.2	147.0	148.1	149.3	150.9	155.3	158.7	161.4
77.5°	104.5	105.2	104.8	106.7	106.0	106.2	109.7	111.3	111.8	118.3	119.8
80°	78.8	79.9	80.5	81.0	81.5	80.5	84.3	86.0	86.0	89.8	92.6
82.5°	56.6	57.2	58.7	59.3	59.4	60.5	60.8	62.0	63.3	65.1	68.6
85°	28.3	29.9	30.5	29.9	30.5	29.4	31.1	31.6	32.2	32.2	32.2
87.5°	10.8	11.7	11.8	12.8	12.9	13.9	14.0	13.3	13.5	15.0	13.4
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4	25.3	26.1	26.7
92.5°	15.2	16.0	18.1	20.1	22.2	24.2	25.6	26.9	28.3	29.7	30.4
95°	23.2	20.1	22.4	24.7	27.1	29.4	30.8	32.3	33.8	35.2	36.0
97.5°	100.6	91.2	76.0	60.8	45.7	30.5	32.2	33.8	35.5	37.3	38.2
100°	176.9	162.6	129.8	96.9	64.1	31.2	32.9	34.7	36.3	38.0	39.0
102.5°	222.3	205.8	169.9	134.0	98.2	62.3	57.1	51.9	46.6	41.4	39.1
105°	291.6	283.2	264.2	245.3	226.4	207.4	170.2	132.9	95.6	58.4	40.0
107.5°	365.8	368.3	371.3	374.2	377.2	380.3	352.9	325.5	298.2	270.9	243.2
110°	416.0	417.9	420.3	422.6	424.9	427.2	420.3	413.3	406.3	399.4	380.9



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	463.7	465.7	468.0	470.3	472.6	474.9	475.1	475.2	475.3	475.5	472.3
115°	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9	550.0	552.1	553.6
117.5°	605.3	606.5	607.5	608.5	609.4	610.4	612.0	613.8	615.5	617.1	618.1
120°	649.8	651.1	651.7	652.3	653.0	653.5	655.3	657.0	658.6	660.3	661.1
122.5°	692.4	693.6	694.4	695.2	695.9	696.8	698.0	699.1	700.3	701.5	702.1
125°	753.2	754.4	755.2	756.1	756.9	757.7	758.2	758.6	759.0	759.5	759.9
127.5°	811.5	812.9	813.8	814.9	815.9	816.8	817.6	818.2	818.9	819.5	819.7
130°	847.8	849.1	849.9	850.8	851.7	852.5	853.4	854.2	855.0	855.9	856.1
132.5°	882.7	883.9	884.6	885.3	885.9	886.6	887.5	888.3	889.2	890.0	890.1
135°	934.3	935.3	936.2	937.0	937.8	938.7	939.3	940.0	940.6	941.3	941.3
137.5°	981.1	982.1	982.6	983.1	983.5	984.0	985.0	986.0	987.0	988.0	988.3
140°	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2	1016.0	1016.9	1017.1
142.5°	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3	1042.9	1043.6	1044.2	1044.3
145°	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.7	1082.1	1082.5	1082.6
147.5°	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9	1116.3	1116.7	1117.1	1116.9
150°	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1	1137.5	1137.9	1138.3	1138.2
152.5°	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6	1156.3	1157.2	1157.9	1157.8
155°	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3	1182.3	1183.4	1184.5	1184.3
157.5°	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7	1204.9	1206.2	1207.5	1207.3
160°	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6	1217.8	1219.0	1220.3	1220.3
162.5°	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1	1229.6	1230.9	1232.4	1232.4
165°	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2	1246.8	1248.5	1248.6
167.5°	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7
170°	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5
172.5°	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0	1268.7	1270.3	1272.0	1271.9
175°	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7	1274.1	1275.6	1277.1	1276.9
177.5°	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8	1276.1	1277.5	1278.8	1278.6
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1094.9	1094.5	1097.6	1095.4	1097.6	1094.5	1094.9	1098.0	1098.9	1099.4	1099.4
5°	1019.2	1020.8	1015.3	1015.3	1015.3	1020.8	1019.2	1022.5	1025.2	1027.5	1030.9
7.5°	951.7	949.3	949.5	946.5	949.5	949.3	951.7	954.4	957.9	962.8	967.4
10°	910.4	907.1	906.0	906.5	906.0	907.1	910.4	917.1	919.3	923.7	928.7
12.5°	876.3	875.6	868.3	868.4	868.3	875.6	876.3	878.0	882.9	892.3	898.1
15°	836.1	825.6	824.4	827.8	824.4	825.6	836.1	836.1	838.3	845.5	848.9
17.5°	795.8	790.3	790.6	789.0	790.6	790.3	795.8	796.7	798.5	804.4	808.8
20°	774.5	771.2	770.6	766.7	770.6	771.2	774.5	774.5	776.7	779.5	783.9
22.5°	755.0	753.9	754.2	749.9	754.2	753.9	755.0	756.3	758.6	760.4	763.5
25°	730.7	733.4	731.2	731.2	731.2	733.4	730.7	731.2	731.8	734.6	736.8
27.5°	714.3	714.1	713.1	713.1	713.1	714.1	714.3	712.9	712.2	711.3	710.8
30°	701.8	701.2	702.4	702.4	702.4	701.2	701.8	699.6	698.5	698.0	695.7
32.5°	689.4	690.2	690.4	690.8	690.4	690.2	689.4	686.7	684.8	683.3	681.5
35°	670.2	670.7	672.5	671.3	672.5	670.7	670.2	666.9	664.6	661.3	658.5
37.5°	644.2	646.8	646.2	647.1	646.2	646.8	644.2	643.3	641.0	638.5	635.3
40°	624.7	626.4	625.8	625.8	625.8	626.4	624.7	624.2	621.9	620.3	617.5
42.5°	604.7	605.9	604.5	603.6	604.5	605.9	604.7	603.7	602.4	599.4	596.2
45°	572.0	570.9	572.6	570.3	572.6	570.9	572.0	569.8	569.2	567.0	564.3
47.5°	535.4	536.5	537.0	538.6	537.0	536.5	535.4	535.6	532.5	531.2	530.3
50°	510.9	514.3	514.3	513.7	514.3	514.3	510.9	509.9	507.6	505.4	505.4
52.5°	487.0	488.5	490.8	490.6	490.8	488.5	487.0	485.0	482.8	479.7	478.8
55°	450.0	451.0	452.2	452.7	452.2	451.0	450.0	445.5	443.8	442.2	439.4
57.5°	411.6	411.1	413.8	414.6	413.8	411.1	411.6	407.6	405.0	399.9	399.3
60°	384.5	384.5	388.9	390.6	388.9	384.5	384.5	380.0	376.2	372.8	371.7
62.5°	355.6	357.4	361.8	359.5	361.8	357.4	355.6	350.7	347.7	343.6	340.6
65°	313.5	317.9	317.3	319.6	317.3	317.9	313.5	310.7	304.6	300.7	297.3
67.5°	269.4	272.1	276.1	276.5	276.1	272.1	269.4	265.0	261.0	256.9	252.9
70°	239.7	242.5	244.7	246.3	244.7	242.5	239.7	235.2	230.8	228.0	223.6
72.5°	210.8	212.3	217.6	215.2	217.6	212.3	210.8	205.5	201.9	199.6	194.8
75°	165.3	169.2	172.5	170.9	172.5	169.2	165.3	161.4	158.7	155.3	150.9
77.5°	122.3	126.1	127.7	126.3	127.7	126.1	122.3	119.8	118.3	111.8	111.3
80°	96.5	96.0	99.3	98.7	99.3	96.0	96.5	92.6	89.8	86.0	86.0
82.5°	70.8	70.3	71.8	72.2	71.8	70.3	70.8	68.6	65.1	63.3	62.0
85°	34.4	36.0	33.8	33.3	33.8	36.0	34.4	32.2	32.2	32.2	31.6
87.5°	13.5	13.5	13.1	12.8	13.1	13.5	13.5	13.4	15.0	13.5	13.3
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.4
92.5°	30.7	31.0	31.2	31.5	31.2	31.0	30.7	30.4	29.7	28.3	26.9
95°	36.0	36.0	36.0	36.0	36.0	36.0	36.0	36.0	35.2	33.8	32.3
97.5°	38.4	38.6	38.8	39.1	38.8	38.6	38.4	38.2	37.3	35.5	33.8
100°	39.1	39.4	39.5	39.8	39.5	39.4	39.1	39.0	38.0	36.3	34.7
102.5°	39.4	39.8	40.2	40.5	40.2	39.8	39.4	39.1	41.4	46.6	51.9
105°	40.4	40.8	41.3	41.7	41.3	40.8	40.4	40.0	58.4	95.6	132.9
107.5°	215.2	187.0	159.0	130.9	159.0	187.0	215.2	243.2	270.9	298.2	325.5
110°	350.8	320.7	290.6	260.5	290.6	320.7	350.8	380.9	399.4	406.3	413.3



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	465.9	459.6	453.2	446.9	453.2	459.6	465.9	472.3	475.5	475.3	475.2
115°	554.4	555.3	556.1	556.9	556.1	555.3	554.4	553.6	552.1	550.0	547.9
117.5°	618.2	618.4	618.6	618.7	618.6	618.4	618.2	618.1	617.1	615.5	613.8
120°	661.1	661.1	661.1	661.1	661.1	661.1	661.1	661.1	660.3	658.6	657.0
122.5°	702.3	702.5	702.7	702.9	702.7	702.5	702.3	702.1	701.5	700.3	699.1
125°	760.3	760.8	761.2	761.6	761.2	760.8	760.3	759.9	759.5	759.0	758.6
127.5°	819.3	818.9	818.5	818.0	818.5	818.9	819.3	819.7	819.5	818.9	818.2
130°	855.7	855.2	854.8	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2
132.5°	889.5	888.9	888.4	887.7	888.4	888.9	889.5	890.1	890.0	889.2	888.3
135°	940.6	940.0	939.3	938.7	939.3	940.0	940.6	941.3	941.3	940.6	940.0
137.5°	987.9	987.5	987.1	986.6	987.1	987.5	987.9	988.3	988.0	987.0	986.0
140°	1016.7	1016.3	1015.9	1015.5	1015.9	1016.3	1016.7	1017.1	1016.9	1016.0	1015.2
142.5°	1043.7	1043.1	1042.5	1042.0	1042.5	1043.1	1043.7	1044.3	1044.2	1043.6	1042.9
145°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.5	1082.1	1081.7
147.5°	1115.9	1114.9	1113.9	1113.0	1113.9	1114.9	1115.9	1116.9	1117.1	1116.7	1116.3
150°	1137.6	1137.0	1136.4	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5
152.5°	1156.8	1155.8	1154.9	1153.9	1154.9	1155.8	1156.8	1157.8	1157.9	1157.2	1156.3
155°	1183.1	1181.9	1180.6	1179.3	1180.6	1181.9	1183.1	1184.3	1184.5	1183.4	1182.3
157.5°	1205.7	1204.0	1202.3	1200.7	1202.3	1204.0	1205.7	1207.3	1207.5	1206.2	1204.9
160°	1218.8	1217.3	1215.8	1214.3	1215.8	1217.3	1218.8	1220.3	1220.3	1219.0	1217.8
162.5°	1231.1	1229.8	1228.5	1227.2	1228.5	1229.8	1231.1	1232.4	1232.4	1230.9	1229.6
165°	1247.2	1245.7	1244.2	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.8	1245.2
167.5°	1259.0	1257.3	1255.6	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3
170°	1265.8	1264.1	1262.4	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1
172.5°	1270.1	1268.3	1266.4	1264.5	1266.4	1268.3	1270.1	1271.9	1272.0	1270.3	1268.7
175°	1275.3	1273.6	1271.9	1270.2	1271.9	1273.6	1275.3	1276.9	1277.1	1275.6	1274.1
177.5°	1277.0	1275.3	1273.6	1271.9	1273.6	1275.3	1277.0	1278.6	1278.8	1277.5	1276.1
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1098.0	1098.0	1106.5	1111.8	1118.5	1122.9	1126.0	1129.1	1134.5	1141.6	1149.6
5°	1035.3	1037.5	1049.7	1061.9	1073.6	1083.5	1091.8	1101.9	1114.0	1129.0	1145.7
7.5°	974.4	983.0	995.3	1010.2	1026.5	1041.1	1055.8	1072.2	1089.4	1111.5	1134.8
10°	935.4	944.9	959.8	978.7	995.9	1013.1	1031.4	1049.1	1070.7	1096.8	1126.8
12.5°	901.2	910.2	925.6	946.2	962.6	981.5	1002.5	1025.6	1049.9	1081.3	1115.2
15°	853.9	864.4	883.2	893.2	918.2	940.9	960.3	993.7	1024.7	1056.9	1096.3
17.5°	815.0	820.9	836.2	854.8	873.3	898.9	924.3	952.0	983.0	1022.4	1071.6
20°	788.4	793.4	810.0	829.4	849.4	872.7	895.4	923.2	958.1	999.7	1053.0
22.5°	768.4	773.8	784.7	805.4	824.1	843.4	866.2	899.2	936.4	977.1	1034.9
25°	739.6	742.9	750.1	766.7	783.4	805.0	825.0	856.1	894.4	942.1	999.7
27.5°	712.2	715.3	721.4	733.4	748.9	766.4	788.1	814.6	853.4	905.2	966.5
30°	695.7	696.3	701.8	712.9	726.3	740.7	760.7	790.6	827.2	880.0	944.3
32.5°	681.5	679.4	683.2	691.6	704.5	718.9	735.3	764.8	800.1	852.0	918.1
35°	657.5	656.3	654.7	661.9	672.9	684.0	698.5	720.7	760.7	808.9	878.2
37.5°	632.9	630.2	627.3	630.6	639.3	650.8	663.3	683.1	717.5	770.6	837.0
40°	614.7	612.5	610.8	609.8	617.5	628.6	638.1	656.9	689.1	739.6	805.0
42.5°	594.8	593.5	591.3	589.8	596.2	604.6	614.5	631.1	663.3	710.7	772.7
45°	562.6	561.5	560.4	559.2	563.1	570.9	578.7	590.8	618.6	664.6	720.7
47.5°	526.8	525.3	525.7	524.0	527.7	533.0	538.3	551.5	578.1	615.3	656.2
50°	501.0	500.4	500.4	500.4	501.6	507.6	512.7	522.6	547.1	584.2	613.6
52.5°	476.5	474.3	474.3	475.2	477.1	481.0	484.2	495.1	516.4	546.9	573.6
55°	438.3	433.8	432.8	433.8	435.5	438.9	442.2	451.0	469.4	492.1	507.6
57.5°	395.9	393.5	392.0	392.2	393.1	395.8	398.4	408.0	422.4	434.3	444.3
60°	366.2	367.3	362.3	363.4	363.4	365.6	369.5	375.6	387.8	396.2	406.1
62.5°	338.2	336.6	335.3	333.6	333.6	334.5	339.7	344.5	355.0	359.3	367.0
65°	294.6	294.6	291.3	292.4	292.9	289.0	291.8	297.3	304.0	305.7	312.9
67.5°	250.5	248.9	247.0	245.3	245.3	245.0	246.5	249.2	254.2	254.8	260.3
70°	220.3	219.2	218.6	217.0	214.7	217.5	215.8	218.6	221.4	221.9	225.3
72.5°	190.9	189.9	188.8	187.2	186.3	186.0	186.1	189.3	191.2	190.4	194.2
75°	149.3	148.1	147.0	144.2	144.2	142.6	143.2	145.4	147.6	145.9	149.3
77.5°	109.7	106.2	106.0	106.7	104.8	105.2	104.5	104.2	105.2	105.3	108.3
80°	84.3	80.5	81.5	81.0	80.5	79.9	78.8	79.3	79.9	80.5	82.1
82.5°	60.8	60.5	59.4	59.3	58.7	57.2	56.6	57.6	58.1	57.8	59.0
85°	31.1	29.4	30.5	29.9	30.5	29.9	28.3	28.3	29.4	28.9	29.9
87.5°	14.0	13.9	12.9	12.8	11.8	11.7	10.8	10.8	10.8	10.4	10.8
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	25.6	24.2	22.2	20.1	18.1	16.0	15.2	15.8	16.5	17.0	17.6
95°	30.8	29.4	27.1	24.7	22.4	20.1	23.2	31.9	40.5	49.2	57.8
97.5°	32.2	30.5	45.7	60.8	76.0	91.2	100.6	104.5	108.4	112.3	116.1
100°	32.9	31.2	64.1	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.0
102.5°	57.1	62.3	98.2	134.0	169.9	205.8	222.3	219.2	216.1	213.1	210.1
105°	170.2	207.4	226.4	245.3	264.2	283.2	291.6	289.2	286.9	284.6	282.3
107.5°	352.9	380.3	377.2	374.2	371.3	368.3	365.8	363.9	362.2	360.3	358.4
110°	420.3	427.2	424.9	422.6	420.3	417.9	416.0	414.3	412.5	410.9	409.2



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	475.1	474.9	472.6	470.3	468.0	465.7	463.7	462.3	460.7	459.2	457.7
115°	545.8	543.7	541.8	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5
117.5°	612.0	610.4	609.4	608.5	607.5	606.5	605.3	603.7	602.1	600.5	599.0
120°	655.3	653.5	653.0	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2
122.5°	698.0	696.8	695.9	695.2	694.4	693.6	692.4	690.8	689.3	687.7	686.2
125°	758.2	757.7	756.9	756.1	755.2	754.4	753.2	751.5	749.7	748.1	746.4
127.5°	817.6	816.8	815.9	814.9	813.8	812.9	811.5	809.8	808.1	806.4	804.8
130°	853.4	852.5	851.7	850.8	849.9	849.1	847.8	846.2	844.5	842.9	841.1
132.5°	887.5	886.6	885.9	885.3	884.6	883.9	882.7	881.0	879.4	877.7	876.0
135°	939.3	938.7	937.8	937.0	936.2	935.3	934.3	933.0	931.7	930.5	929.2
137.5°	985.0	984.0	983.5	983.1	982.6	982.1	981.1	979.5	977.9	976.3	974.7
140°	1014.4	1013.5	1012.9	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.2	1005.0
142.5°	1042.3	1041.5	1041.0	1040.3	1039.7	1039.0	1038.1	1036.8	1035.6	1034.3	1033.1
145°	1081.2	1080.8	1080.4	1079.9	1079.5	1079.1	1078.2	1076.7	1075.2	1073.7	1072.3
147.5°	1115.9	1115.4	1115.0	1114.6	1114.2	1113.8	1113.0	1112.1	1111.2	1110.2	1109.2
150°	1137.1	1136.7	1136.3	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.5	1132.0
152.5°	1155.6	1154.9	1154.6	1154.4	1154.1	1153.8	1153.6	1153.2	1153.0	1152.7	1152.4
155°	1181.3	1180.2	1180.1	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2
157.5°	1203.7	1202.4	1202.6	1202.8	1203.1	1203.2	1203.4	1203.4	1203.5	1203.5	1203.5
160°	1216.6	1215.3	1215.5	1215.7	1215.9	1216.1	1216.3	1216.6	1216.8	1217.0	1217.2
162.5°	1228.1	1226.6	1226.9	1227.1	1227.3	1227.5	1227.8	1228.4	1229.0	1229.6	1230.0
165°	1243.5	1241.8	1242.0	1242.2	1242.4	1242.7	1243.1	1243.7	1244.3	1245.0	1245.6
167.5°	1255.6	1253.9	1253.9	1253.9	1253.9	1253.9	1254.3	1255.2	1256.1	1256.9	1257.8
170°	1262.4	1260.8	1260.8	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5
172.5°	1267.0	1265.3	1265.1	1264.9	1264.8	1264.6	1265.0	1266.1	1267.1	1268.1	1269.1
175°	1272.7	1271.1	1271.0	1270.7	1270.6	1270.3	1270.7	1271.8	1272.8	1273.9	1275.0
177.5°	1274.8	1273.4	1273.3	1273.1	1272.9	1272.8	1273.1	1274.0	1274.8	1275.6	1276.5
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1152.2	1154.5	1162.0	1167.3	1173.5	1177.0	1180.6	1183.3	1186.8	1187.7	1200.6
5°	1157.3	1168.4	1187.8	1202.2	1220.0	1239.4	1252.7	1258.8	1275.0	1288.3	1314.9
7.5°	1155.8	1179.5	1208.8	1239.2	1271.9	1302.0	1328.2	1359.3	1381.4	1414.5	1447.2
10°	1154.5	1186.2	1223.9	1262.7	1308.2	1350.4	1388.1	1430.3	1465.3	1511.3	1550.7
12.5°	1150.6	1188.9	1241.2	1287.1	1342.4	1400.5	1456.5	1510.6	1541.6	1618.3	1654.6
15°	1140.7	1186.2	1251.6	1321.5	1397.6	1466.3	1537.3	1594.0	1685.5	1752.6	1795.4
17.5°	1121.9	1185.5	1263.1	1347.5	1439.9	1530.6	1611.0	1697.0	1794.0	1875.3	1961.8
20°	1113.0	1182.8	1269.4	1362.6	1458.6	1561.2	1652.8	1756.0	1861.9	1941.8	2052.8
22.5°	1096.5	1175.7	1268.9	1372.8	1475.4	1581.6	1688.7	1792.8	1915.2	2025.3	2130.9
25°	1069.7	1158.5	1255.0	1370.9	1491.3	1597.8	1726.0	1864.2	1991.8	2133.2	2238.6
27.5°	1041.5	1136.2	1233.0	1340.8	1470.3	1596.8	1757.9	1914.1	2070.0	2192.3	2270.3
30°	1019.7	1111.8	1211.7	1320.5	1448.6	1599.0	1779.2	1949.5	2101.6	2206.4	2250.3
32.5°	996.2	1089.6	1177.9	1292.0	1428.6	1597.6	1792.6	1970.4	2103.4	2173.2	2164.6
35°	959.3	1037.5	1123.5	1233.3	1394.2	1587.9	1800.3	1972.3	2053.9	2038.9	1925.7
37.5°	906.0	971.8	1056.5	1176.7	1354.3	1567.3	1784.8	1913.8	1908.5	1786.6	1622.6
40°	872.7	928.7	1010.3	1136.8	1323.2	1554.0	1760.4	1844.2	1773.2	1602.8	1406.4
42.5°	829.2	880.8	962.4	1092.4	1289.1	1526.9	1713.8	1738.1	1599.1	1403.1	1223.1
45°	761.7	807.2	891.5	1025.8	1237.8	1468.0	1600.0	1540.7	1353.7	1151.2	1014.2
47.5°	689.3	736.5	817.7	955.6	1163.7	1379.3	1442.3	1316.0	1124.1	959.8	834.0
50°	643.6	689.1	768.4	907.7	1113.5	1306.6	1332.6	1169.5	993.1	848.9	745.7
52.5°	597.5	640.3	718.3	857.9	1054.9	1222.2	1206.2	1039.9	877.7	754.7	673.8
55°	528.7	569.2	643.6	774.5	953.7	1086.3	1028.1	869.4	735.2	639.7	578.1
57.5°	467.2	506.1	570.2	688.5	844.3	935.4	861.3	727.6	620.9	547.4	501.4
60°	425.5	459.9	521.0	630.8	766.2	835.5	762.3	644.2	554.2	495.5	454.4
62.5°	386.0	416.0	472.5	572.3	689.8	748.1	674.0	574.0	497.4	445.3	410.4
65°	326.2	353.4	403.3	481.0	577.6	616.4	552.6	471.6	412.2	373.4	350.1
67.5°	271.7	294.7	337.9	399.0	470.0	498.3	449.7	387.0	342.3	311.1	292.6
70°	235.2	255.2	289.0	341.8	406.1	427.8	382.3	330.7	297.9	273.0	255.8
72.5°	204.6	219.2	250.0	290.7	344.4	361.6	329.9	284.5	254.0	235.2	221.6
75°	155.9	168.1	188.1	220.8	258.0	268.0	244.1	215.8	195.3	182.0	171.5
77.5°	112.4	121.4	135.8	156.0	181.7	190.8	175.6	156.8	141.8	132.8	126.9
80°	84.9	92.1	104.3	120.9	136.5	141.5	132.6	118.1	107.6	102.6	97.7
82.5°	62.7	66.8	74.1	85.4	96.1	102.0	94.4	85.8	80.1	75.6	73.7
85°	31.6	33.8	37.2	41.6	48.3	50.5	47.7	45.5	42.2	39.4	39.4
87.5°	12.1	12.6	14.3	15.7	17.9	19.7	19.9	19.6	19.6	19.3	19.1
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4
92.5°	17.0	16.5	15.8	15.2	16.0	18.1	20.1	22.2	24.2	25.6	26.9
95°	49.2	40.5	31.9	23.2	20.1	22.4	24.7	27.1	29.4	30.8	32.3
97.5°	112.3	108.4	104.5	100.6	91.2	76.0	60.8	45.7	30.5	32.2	33.8
100°	164.3	168.5	172.7	176.9	162.6	129.8	96.9	64.1	31.2	32.9	34.7
102.5°	213.1	216.1	219.2	222.3	205.8	169.9	134.0	98.2	62.3	57.1	51.9
105°	284.6	286.9	289.2	291.6	283.2	264.2	245.3	226.4	207.4	170.2	132.9
107.5°	360.3	362.2	363.9	365.8	368.3	371.3	374.2	377.2	380.3	352.9	325.5
110°	410.9	412.5	414.3	416.0	417.9	420.3	422.6	424.9	427.2	420.3	413.3



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.2	460.7	462.3	463.7	465.7	468.0	470.3	472.6	474.9	475.1	475.2
115°	530.8	532.0	533.3	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9
117.5°	600.5	602.1	603.7	605.3	606.5	607.5	608.5	609.4	610.4	612.0	613.8
120°	644.1	646.0	647.9	649.8	651.1	651.7	652.3	653.0	653.5	655.3	657.0
122.5°	687.7	689.3	690.8	692.4	693.6	694.4	695.2	695.9	696.8	698.0	699.1
125°	748.1	749.7	751.5	753.2	754.4	755.2	756.1	756.9	757.7	758.2	758.6
127.5°	806.4	808.1	809.8	811.5	812.9	813.8	814.9	815.9	816.8	817.6	818.2
130°	842.9	844.5	846.2	847.8	849.1	849.9	850.8	851.7	852.5	853.4	854.2
132.5°	877.7	879.4	881.0	882.7	883.9	884.6	885.3	885.9	886.6	887.5	888.3
135°	930.5	931.7	933.0	934.3	935.3	936.2	937.0	937.8	938.7	939.3	940.0
137.5°	976.3	977.9	979.5	981.1	982.1	982.6	983.1	983.5	984.0	985.0	986.0
140°	1006.2	1007.5	1008.8	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2
142.5°	1034.3	1035.6	1036.8	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3	1042.9
145°	1073.7	1075.2	1076.7	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.7
147.5°	1110.2	1111.2	1112.1	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9	1116.3
150°	1132.5	1133.2	1133.8	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1	1137.5
152.5°	1152.7	1153.0	1153.2	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6	1156.3
155°	1180.8	1180.3	1179.9	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3	1182.3
157.5°	1203.5	1203.5	1203.4	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7	1204.9
160°	1217.0	1216.8	1216.6	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6	1217.8
162.5°	1229.6	1229.0	1228.4	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1	1229.6
165°	1245.0	1244.3	1243.7	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2
167.5°	1256.9	1256.1	1255.2	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6	1257.3
170°	1263.7	1262.9	1262.0	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1
172.5°	1268.1	1267.1	1266.1	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0	1268.7
175°	1273.9	1272.8	1271.8	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7	1274.1
177.5°	1275.6	1274.8	1274.0	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8	1276.1
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1205.0	1205.5	1210.4	1213.9	1212.1	1214.4	1215.2
5°	1316.5	1336.5	1347.0	1354.9	1355.4	1355.9	1360.4
7.5°	1474.6	1496.1	1511.7	1535.5	1542.5	1550.7	1548.3
10°	1590.1	1621.7	1648.9	1663.3	1678.9	1701.6	1683.3
12.5°	1697.9	1754.0	1795.4	1817.8	1832.4	1837.0	1828.0
15°	1875.8	1949.1	1988.4	1987.3	2037.3	2058.9	2025.0
17.5°	2038.9	2106.5	2160.6	2188.3	2230.0	2239.2	2235.0
20°	2138.8	2212.6	2254.7	2302.4	2324.1	2343.5	2346.8
22.5°	2224.9	2291.2	2336.4	2376.1	2394.2	2403.4	2409.0
25°	2313.5	2365.7	2392.9	2406.8	2411.7	2410.6	2403.4
27.5°	2307.5	2311.5	2281.5	2252.1	2225.8	2196.2	2185.9
30°	2247.5	2200.9	2117.7	2070.5	2001.2	1946.3	1968.5
32.5°	2089.9	1997.2	1903.7	1800.7	1715.3	1691.0	1666.6
35°	1783.7	1620.6	1525.2	1414.2	1369.8	1325.4	1294.9
37.5°	1443.1	1316.9	1203.7	1131.1	1086.6	1058.6	1043.5
40°	1247.7	1134.0	1040.8	982.0	948.2	916.6	912.1
42.5°	1091.9	986.2	916.1	869.3	836.7	823.3	813.6
45°	894.4	820.5	773.4	740.1	718.4	710.1	699.0
47.5°	757.0	704.8	669.4	646.8	630.5	624.3	623.4
50°	680.2	636.9	610.8	593.0	580.3	578.1	569.2
52.5°	622.5	585.0	564.7	549.2	540.0	533.7	531.1
55°	540.4	515.4	497.1	488.2	481.0	474.9	474.9
57.5°	472.8	451.9	439.9	432.3	430.1	425.7	423.0
60°	431.0	413.4	403.9	397.2	392.8	393.4	388.3
62.5°	390.3	378.7	369.7	363.1	357.8	357.8	358.2
65°	332.3	323.4	316.8	314.5	311.3	307.4	308.5
67.5°	281.6	273.3	268.1	264.3	263.2	261.1	264.3
70°	245.2	239.1	235.2	231.9	230.8	231.4	234.2
72.5°	211.9	207.6	205.0	203.5	201.1	201.1	203.1
75°	166.4	163.1	160.9	159.2	158.7	158.7	158.7
77.5°	122.3	121.5	120.5	118.1	118.1	118.9	119.0
80°	96.5	94.9	94.3	93.2	91.6	90.4	93.2
82.5°	72.2	70.4	69.9	69.7	67.1	66.9	69.2
85°	38.8	37.2	37.7	37.2	37.2	36.6	36.6
87.5°	18.8	18.5	18.2	18.8	18.4	18.0	19.0
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	28.3	29.7	30.4	30.7	31.0	31.2	31.5
95°	33.8	35.2	36.0	36.0	36.0	36.0	36.0
97.5°	35.5	37.3	38.2	38.4	38.6	38.8	39.1
100°	36.3	38.0	39.0	39.1	39.4	39.5	39.8
102.5°	46.6	41.4	39.1	39.4	39.8	40.2	40.5
105°	95.6	58.4	40.0	40.4	40.8	41.3	41.7
107.5°	298.2	270.9	243.2	215.2	187.0	159.0	130.9
110°	406.3	399.4	380.9	350.8	320.7	290.6	260.5



TEST NUMBER: P332036-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	475.3	475.5	472.3	465.9	459.6	453.2	446.9
115°	550.0	552.1	553.6	554.4	555.3	556.1	556.9
117.5°	615.5	617.1	618.1	618.2	618.4	618.6	618.7
120°	658.6	660.3	661.1	661.1	661.1	661.1	661.1
122.5°	700.3	701.5	702.1	702.3	702.5	702.7	702.9
125°	759.0	759.5	759.9	760.3	760.8	761.2	761.6
127.5°	818.9	819.5	819.7	819.3	818.9	818.5	818.0
130°	855.0	855.9	856.1	855.7	855.2	854.8	854.4
132.5°	889.2	890.0	890.1	889.5	888.9	888.4	887.7
135°	940.6	941.3	941.3	940.6	940.0	939.3	938.7
137.5°	987.0	988.0	988.3	987.9	987.5	987.1	986.6
140°	1016.0	1016.9	1017.1	1016.7	1016.3	1015.9	1015.5
142.5°	1043.6	1044.2	1044.3	1043.7	1043.1	1042.5	1042.0
145°	1082.1	1082.5	1082.6	1082.6	1082.6	1082.6	1082.6
147.5°	1116.7	1117.1	1116.9	1115.9	1114.9	1113.9	1113.0
150°	1137.9	1138.3	1138.2	1137.6	1137.0	1136.4	1135.7
152.5°	1157.2	1157.9	1157.8	1156.8	1155.8	1154.9	1153.9
155°	1183.4	1184.5	1184.3	1183.1	1181.9	1180.6	1179.3
157.5°	1206.2	1207.5	1207.3	1205.7	1204.0	1202.3	1200.7
160°	1219.0	1220.3	1220.3	1218.8	1217.3	1215.8	1214.3
162.5°	1230.9	1232.4	1232.4	1231.1	1229.8	1228.5	1227.2
165°	1246.8	1248.5	1248.6	1247.2	1245.7	1244.2	1242.8
167.5°	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9
170°	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8
172.5°	1270.3	1272.0	1271.9	1270.1	1268.3	1266.4	1264.5
175°	1275.6	1277.1	1276.9	1275.3	1273.6	1271.9	1270.2
177.5°	1277.5	1278.8	1278.6	1277.0	1275.3	1273.6	1271.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0

(END OF REPORT)