

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332310

Luminaire Tested: **S123RDIP-S775D585U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332310  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D585U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4930.5 lumens  
Efficiency: N/A  
Efficacy: 122.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	2.5
10°-20°	337.3	6.8
20°-30°	485.7	9.9
30°-40°	547.1	11.1
40°-50°	523.4	10.6
50°-60°	428.6	8.7
60°-70°	289.2	5.9
70°-80°	145.5	3.0
80°-90°	40.6	0.8
90°-100°	47.3	1.0
100°-110°	141.6	2.9
110°-120°	240.8	4.9
120°-130°	316.7	6.4
130°-140°	356.0	7.2
140°-150°	349.9	7.1
150°-160°	294.6	6.0
160°-170°	196.1	4.0
170°-180°	68.7	1.4
0°-30°	944.3	19.2
0°-40°	1491.4	30.2
0°-60°	2443.4	49.6
0°-90°	2918.7	59.2
90°-120°	429.7	8.7
90°-150°	1452.4	29.5
90°-180°	2012.0	40.8
0°-180°	4930.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	6	14	16	17	5
95°	34	38	42	44	44	38
105°	128	130	135	135	136	137
115°	242	244	243	244	243	240
125°	355	356	355	353	351	316
135°	460	464	463	461	460	355
145°	558	560	561	561	558	349
155°	639	639	640	642	638	294
165°	696	695	695	698	694	196
175°	724	722	722	725	722	69
180°	726	726	726	726	726	



TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.2	18.4	16.6	14.8	13.0	12.3	12.6	13.0	13.3	13.6	13.5
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	13.8	14.7	15.5	16.4	17.3	18.2	19.1	20.0	21.0	21.9	22.3
95°	33.7	34.5	35.4	36.3	37.2	38.2	39.2	40.2	41.2	42.2	42.7
97.5°	59.8	60.4	61.1	61.8	62.4	63.1	63.8	64.6	65.3	66.1	66.6
100°	77.6	78.3	79.1	79.9	80.6	81.3	81.9	82.6	83.2	83.8	84.2
102.5°	98.1	98.6	99.0	99.5	99.9	100.6	101.4	102.3	103.1	103.9	104.3
105°	128.3	128.6	128.8	129.1	129.4	130.0	131.2	132.3	133.5	134.6	134.6
107.5°	163.5	163.6	163.8	163.9	164.1	164.4	164.8	165.3	165.8	166.2	166.6
110°	185.4	185.6	185.9	186.1	186.4	186.6	186.9	187.2	187.4	187.7	188.2



TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.2	208.3	208.5	208.6	208.8	208.9	209.0	209.0	209.1	209.1	209.7
115°	242.4	242.8	243.2	243.6	243.9	244.0	243.7	243.5	243.2	243.0	243.1
117.5°	276.9	277.1	277.4	277.6	277.9	277.8	277.5	277.2	276.9	276.5	276.5
120°	298.3	299.1	299.8	300.6	301.4	301.4	300.8	300.2	299.5	298.9	298.8
122.5°	320.7	321.2	321.8	322.3	322.9	323.0	322.7	322.4	322.0	321.7	321.4
125°	354.8	355.2	355.5	355.9	356.3	356.4	356.1	355.9	355.6	355.4	354.8
127.5°	386.3	387.1	387.9	388.7	389.5	389.8	389.5	389.2	388.9	388.7	388.0
130°	407.3	408.3	409.3	410.3	411.3	411.6	411.3	410.9	410.5	410.1	409.6
132.5°	428.2	429.3	430.3	431.3	432.3	432.7	432.4	432.1	431.8	431.6	430.9
135°	460.3	461.1	461.8	462.6	463.3	463.7	463.5	463.4	463.3	463.2	462.7
137.5°	490.0	490.6	491.2	491.9	492.5	493.0	493.3	493.6	494.0	494.3	493.8
140°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.8
142.5°	529.2	529.8	530.5	531.1	531.7	532.2	532.4	532.6	532.9	533.1	533.0
145°	558.4	558.7	558.9	559.2	559.4	559.7	560.1	560.5	560.9	561.3	561.1
147.5°	584.0	584.4	584.9	585.3	585.8	586.2	586.6	586.9	587.3	587.6	587.6
150°	601.8	602.0	602.3	602.5	602.8	603.0	603.3	603.5	603.8	604.0	604.0
152.5°	616.4	616.7	617.1	617.4	617.8	618.0	618.2	618.3	618.5	618.6	618.8
155°	639.4	639.4	639.4	639.4	639.4	639.5	639.6	639.7	639.9	640.0	640.5
157.5°	659.0	658.9	658.7	658.6	658.4	658.4	658.5	658.6	658.7	658.8	659.3
160°	671.3	671.1	670.8	670.6	670.3	670.2	670.2	670.2	670.2	670.2	670.8
162.5°	682.3	681.9	681.6	681.2	680.9	680.8	680.9	681.0	681.1	681.2	681.8
165°	696.4	696.1	695.7	695.3	694.9	694.7	694.7	694.7	694.7	694.7	695.5
167.5°	707.7	707.2	706.7	706.2	705.7	705.5	705.6	705.7	705.8	705.9	706.7
170°	714.1	713.6	713.1	712.6	712.1	711.8	711.8	711.8	711.8	711.8	712.7
172.5°	719.1	718.6	718.1	717.6	717.1	716.9	716.9	716.9	716.9	716.9	717.7
175°	724.4	723.9	723.4	722.9	722.4	722.1	722.1	722.1	722.1	722.1	722.9
177.5°	726.6	726.2	725.8	725.3	724.9	724.7	724.7	724.7	724.7	724.7	725.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	13.5	13.4	13.3	13.2	13.0	12.9	12.8	12.6
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	22.7	23.1	23.5	23.7	23.5	23.3	23.2	23.0
95°	43.2	43.7	44.2	44.5	44.5	44.5	44.5	44.5
97.5°	67.2	67.8	68.4	68.6	68.6	68.5	68.5	68.4
100°	84.6	85.0	85.4	85.7	85.9	86.2	86.4	86.7
102.5°	104.7	105.1	105.4	105.6	105.6	105.5	105.5	105.4
105°	134.6	134.6	134.6	134.7	135.0	135.2	135.5	135.8
107.5°	167.0	167.4	167.8	168.0	167.8	167.7	167.5	167.4
110°	188.7	189.2	189.7	189.8	189.6	189.3	189.1	188.8





TEST NUMBER: P332310

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	210.9	211.5	211.8	211.8	211.7	211.7	211.6
115°	243.2	243.4	243.5	243.5	243.4	243.2	243.1	243.0
117.5°	276.5	276.4	276.4	276.2	275.9	275.5	275.2	274.8
120°	298.6	298.5	298.4	298.2	297.9	297.7	297.4	297.2
122.5°	321.0	320.7	320.4	320.0	319.7	319.3	319.0	318.6
125°	354.3	353.8	353.3	352.8	352.3	351.8	351.3	350.8
127.5°	387.2	386.5	385.8	385.2	384.6	384.0	383.4	382.8
130°	409.1	408.6	408.1	407.4	406.5	405.6	404.7	403.8
132.5°	430.3	429.7	429.1	428.5	427.8	427.1	426.4	425.7
135°	462.1	461.6	461.1	460.7	460.5	460.2	460.0	459.7
137.5°	493.2	492.7	492.2	491.7	491.2	490.7	490.2	489.7
140°	513.7	513.5	513.4	512.9	512.0	511.1	510.2	509.4
142.5°	532.8	532.7	532.6	532.2	531.5	530.8	530.1	529.4
145°	561.0	560.9	560.8	560.4	559.9	559.4	558.9	558.4
147.5°	587.6	587.6	587.6	587.2	586.5	585.7	585.0	584.2
150°	604.0	604.0	604.0	603.7	602.9	602.1	601.4	600.6
152.5°	619.1	619.3	619.5	619.2	618.6	617.9	617.3	616.6
155°	641.0	641.5	642.0	641.8	640.9	640.0	639.2	638.3
157.5°	659.9	660.4	660.9	660.8	660.1	659.4	658.7	658.0
160°	671.5	672.1	672.7	672.8	672.3	671.8	671.3	670.8
162.5°	682.4	683.1	683.7	683.6	682.8	682.0	681.2	680.4
165°	696.3	697.0	697.8	697.7	696.8	695.9	695.1	694.2
167.5°	707.5	708.3	709.1	709.1	708.3	707.5	706.7	705.9
170°	713.6	714.5	715.4	715.4	714.5	713.6	712.7	711.8
172.5°	718.4	719.2	720.0	720.0	719.1	718.2	717.3	716.4
175°	723.6	724.4	725.2	725.1	724.2	723.3	722.4	721.5
177.5°	726.0	726.6	727.2	727.1	726.4	725.7	725.0	724.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1

(END OF REPORT)