

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332311

Luminaire Tested: **S123RDIP-S775D585U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332311  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D585U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5038.6 lumens  
Efficiency: N/A  
Efficacy: 125.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	55	54	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	66	55	48	43	49	43	39	42	38	34	37	33	30	27
6	65	53	45	39	61	50	43	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	2.4
10°-20°	337.3	6.7
20°-30°	485.7	9.6
30°-40°	547.1	10.9
40°-50°	523.4	10.4
50°-60°	428.6	8.5
60°-70°	289.2	5.7
70°-80°	145.5	2.9
80°-90°	40.7	0.8
90°-100°	156.8	3.1
100°-110°	444.0	8.8
110°-120°	436.8	8.7
120°-130°	348.4	6.9
130°-140°	274.7	5.5
140°-150°	205.0	4.1
150°-160°	142.9	2.8
160°-170°	83.9	1.7
170°-180°	27.3	0.5
0°-30°	944.3	18.7
0°-40°	1491.4	29.6
0°-60°	2443.4	48.5
0°-90°	2918.8	57.9
90°-120°	1037.6	20.6
90°-150°	1865.7	37.0
90°-180°	2120.0	42.1
0°-180°	5038.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	7	14	16	16	4
95°	19	63	338	99	66	21
105°	66	98	459	802	726	70
115°	117	146	351	769	882	116
125°	163	192	327	593	696	144
135°	190	227	323	489	564	147
145°	217	249	319	401	441	136
155°	247	266	309	351	366	114
165°	270	278	296	313	319	76
175°	281	282	284	288	287	27
180°	282	282	282	282	282	



TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.5	16.7	15.0	13.2	12.4	12.7	13.1	13.4	13.7	13.4
90°	1.1	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7
92.5°	7.1	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2
95°	19.4	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3
97.5°	33.1	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8
100°	42.2	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5
102.5°	51.8	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1
105°	66.2	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3
107.5°	81.4	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4
110°	92.4	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0



TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.4	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7
115°	116.9	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5
117.5°	131.4	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2
120°	141.5	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4
122.5°	150.1	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9
125°	162.6	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4
127.5°	172.0	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6
130°	178.0	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2
132.5°	182.5	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2
135°	190.5	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5
137.5°	198.0	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8
140°	203.1	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6
142.5°	208.5	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0
145°	217.3	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1
147.5°	226.2	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3
150°	232.1	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1
152.5°	238.1	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5
155°	247.0	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0
157.5°	254.0	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8
160°	259.5	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7
162.5°	263.6	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6
165°	269.8	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0
167.5°	274.5	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7
170°	277.2	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5
172.5°	279.0	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3
175°	281.2	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6
177.5°	282.2	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	13.4	13.3	13.2	13.3	13.0	12.9	12.8	12.5
90°	14.3	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	48.0	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	205.3	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	511.9	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	672.5	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	725.9	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	741.5	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	696.5	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	653.6	758.6	830.5	870.4	886.4	890.9	889.8	888.6





TEST NUMBER: P332311

CATALOG NUMBER: S123RDIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.2	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	555.0	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	514.2	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	492.8	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	475.9	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	453.4	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	433.8	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	421.5	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	410.1	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	394.7	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	380.7	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	372.5	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	364.7	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	355.3	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	347.7	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	342.2	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	337.2	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	329.7	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	321.7	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	317.1	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	311.7	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	304.6	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	298.4	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	294.3	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	290.7	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	285.8	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	282.7	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)