

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332044-930

Luminaire Tested: **S123DIP-S1000D1195U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332044-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D1195U930-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6882.3 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41				
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34				
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29				
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29	25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17				
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	1.8
10°-20°	343.3	5.0
20°-30°	507.0	7.4
30°-40°	592.3	8.6
40°-50°	595.5	8.7
50°-60°	523.1	7.6
60°-70°	389.7	5.7
70°-80°	222.0	3.2
80°-90°	67.3	1.0
90°-100°	260.4	3.8
100°-110°	737.4	10.7
110°-120°	725.4	10.5
120°-130°	578.6	8.4
130°-140°	456.2	6.6
140°-150°	340.5	4.9
150°-160°	237.3	3.4
160°-170°	139.4	2.0
170°-180°	45.4	0.7
0°-30°	971.9	14.1
0°-40°	1564.1	22.7
0°-60°	2682.6	39.0
0°-90°	3361.7	48.8
90°-120°	1723.2	25.0
90°-150°	3098.5	45.0
90°-180°	3521.0	51.2
0°-180°	6882.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	2	11	24	27	28	5
95°	32	105	562	164	110	35
105°	110	162	762	1332	1205	117
115°	194	242	582	1277	1465	192
125°	270	319	544	985	1156	239
135°	316	378	536	811	937	244
145°	361	414	530	665	732	226
155°	410	442	512	583	607	189
165°	448	461	491	520	530	126
175°	467	468	471	477	476	44
180°	468	468	468	468	468	



TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.5	23.2	23.1	23.0	22.8	22.7	23.2	23.6	23.9	24.3	23.9
90°	1.9	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7
92.5°	11.7	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9
95°	32.2	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6
97.5°	55.0	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3
100°	70.1	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7
102.5°	86.0	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2
105°	109.9	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5
107.5°	135.3	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3
110°	153.4	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6



TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3
115°	194.2	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4
117.5°	218.3	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0
120°	234.9	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9
122.5°	249.3	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4
125°	269.9	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1
127.5°	285.7	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4
130°	295.5	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7
132.5°	303.1	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0
135°	316.4	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1
137.5°	328.9	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8
140°	337.2	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1
142.5°	346.3	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9
145°	360.9	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9
147.5°	375.7	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9
150°	385.6	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6
152.5°	395.4	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5
155°	410.2	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4
157.5°	421.9	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1
160°	431.0	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4
162.5°	437.8	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5
165°	448.1	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2
167.5°	455.8	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3
170°	460.4	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0
172.5°	463.4	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7
175°	467.0	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7
177.5°	468.7	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	23.9	23.9	23.9	24.1	24.0	24.1	24.3	24.1
90°	23.6	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	79.7	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	341.0	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	850.0	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1116.8	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1205.5	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1231.4	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1156.7	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1085.6	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9





TEST NUMBER: P332044-930

CATALOG NUMBER: S123DIP-S1000D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1015.0	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	921.7	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	854.0	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	818.4	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	790.4	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	753.1	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	720.5	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	700.0	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	681.1	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	655.5	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	632.2	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	618.6	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	605.7	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	590.1	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	577.5	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	568.3	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	560.0	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	547.5	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	534.3	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	526.7	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	517.6	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	505.8	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	495.6	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	488.8	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	482.7	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	474.6	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	469.4	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)