

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831114

Luminaire Tested: S123DIP-S1000D365U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831114
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U930-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4941.6 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	80	80	80	76	
1	104	100	96	93	99	96	92	89	87	85	82	79	77	75	72	71	69	69	69	69	66	
2	96	89	83	77	91	85	79	75	77	73	69	71	67	64	64	62	60	60	60	60	56	
3	88	79	72	66	84	75	69	64	69	64	60	63	59	56	58	55	52	52	52	52	49	
4	81	71	63	57	77	68	61	55	62	56	52	57	53	49	53	49	46	46	46	46	43	
5	75	64	56	50	71	61	54	48	56	50	46	52	47	43	48	44	41	41	41	41	38	
6	70	58	50	44	66	56	48	43	51	45	41	48	42	39	44	40	36	36	36	36	34	
7	65	53	45	39	62	51	44	38	47	41	37	44	39	35	41	36	33	33	33	33	31	
8	61	48	41	35	58	47	40	35	44	37	33	41	35	32	38	33	30	30	30	30	28	
9	57	45	37	32	54	43	36	32	40	34	30	38	33	29	35	31	28	28	28	28	26	
10	54	42	34	30	51	40	33	29	38	32	28	35	30	27	33	29	25	25	25	25	24	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	25168	25168	25168	25168	25168
5°	31829	30041	25393	20464	18805
10°	32138	33111	25224	16312	14255
15°	24206	30741	25052	13814	12055
20°	16866	24876	24733	12080	10950
25°	12860	19130	24188	11114	10271
30°	11125	15198	23317	10432	9723
35°	10322	12832	22312	9938	9339
40°	9773	11511	20903	9468	9208
45°	9447	10653	19110	9100	9150
50°	9284	9975	16988	8766	9103
55°	8938	9479	14904	8450	9143
60°	8620	8947	12848	8153	8992
65°	8097	8443	11082	7834	8815
70°	7478	7802	9426	7308	8299
75°	6771	6995	8077	6791	7582
80°	5585	6118	6391	5920	6391
85°	4421	4952	4693	5027	5088

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 21818 cd/sqm



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	4.5
10°-20°	549.9	11.1
20°-30°	651.1	13.2
30°-40°	654.7	13.2
40°-50°	600.7	12.2
50°-60°	495.8	10.0
60°-70°	350.7	7.1
70°-80°	187.2	3.8
80°-90°	48.3	1.0
90°-100°	13.7	0.3
100°-110°	66.1	1.3
110°-120°	162.0	3.3
120°-130°	205.7	4.2
130°-140°	219.7	4.4
140°-150°	205.5	4.2
150°-160°	165.7	3.4
160°-170°	106.9	2.2
170°-180°	36.9	0.7
0°-30°	1422.1	28.8
0°-40°	2076.8	42.0
0°-60°	3173.3	64.2
0°-90°	3759.5	76.1
90°-120°	241.8	4.9
90°-150°	872.6	17.7
90°-180°	1182.0	23.9
0°-180°	4941.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2338	2338	2338	2338	2338	
5°	2946	2780	2350	1894	1740	281
15°	2172	2759	2248	1240	1082	600
25°	1083	1611	2037	936	865	511
35°	786	976	1698	756	711	494
45°	621	700	1255	598	601	481
55°	476	505	794	450	487	426
65°	318	332	435	308	346	316
75°	163	168	194	163	182	171
85°	36	40	38	41	41	40
90°	9	7	0	7	9	6
95°	11	9	18	9	11	9
105°	13	63	86	63	13	26
115°	169	165	161	165	169	159
125°	232	230	227	230	232	207
135°	286	286	283	286	286	220
145°	329	329	326	329	329	206
155°	359	359	359	359	359	165
165°	378	378	379	378	378	107
175°	386	387	388	387	386	37
180°	388	388	388	388	388	



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2635.5	2632.8	2630.1	2616.5	2602.9	2596.4	2589.9	2570.4	2550.9	2529.2	2507.5
5°	2945.8	2953.4	2961.0	2952.3	2943.6	2917.1	2890.5	2855.2	2819.9	2780.3	2740.7
7.5°	3089.0	3093.4	3097.7	3092.3	3086.9	3079.8	3072.8	3041.3	3009.8	2969.1	2928.5
10°	2940.4	2950.2	2959.9	2981.1	3002.2	3026.1	3050.0	3045.6	3041.3	3029.4	3017.4
12.5°	2613.8	2625.7	2637.7	2680.0	2722.3	2776.5	2830.8	2877.5	2924.1	2956.7	2989.2
15°	2172.2	2205.3	2238.4	2276.9	2315.4	2395.2	2474.9	2573.1	2671.3	2758.6	2846.0
17.5°	1789.2	1801.7	1814.1	1855.4	1896.6	1997.0	2097.3	2210.7	2324.1	2468.9	2613.8
20°	1472.4	1483.8	1495.1	1549.4	1603.6	1682.3	1761.0	1888.5	2016.0	2171.7	2327.4
22.5°	1236.9	1254.8	1272.7	1303.1	1333.5	1408.9	1484.3	1597.7	1711.1	1883.0	2055.0
25°	1082.8	1095.9	1108.9	1127.3	1145.8	1206.0	1266.2	1359.5	1452.8	1610.7	1768.6
27.5°	977.6	983.0	988.4	1006.9	1025.3	1064.4	1103.5	1183.7	1264.0	1398.0	1532.0
30°	895.1	898.9	902.7	919.0	935.3	961.9	988.4	1046.5	1104.5	1222.8	1341.1
32.5°	837.6	840.3	843.1	855.5	868.0	887.0	906.0	948.3	990.6	1088.3	1185.9
35°	785.5	787.2	788.8	798.0	807.2	821.4	835.5	867.5	899.5	976.5	1053.5
37.5°	740.0	742.1	744.3	749.7	755.2	767.6	780.1	805.6	831.1	890.3	949.4
40°	695.5	699.3	703.1	706.9	710.7	721.0	731.3	750.8	770.4	819.2	868.0
42.5°	657.5	661.3	665.1	666.7	668.4	674.3	680.3	698.2	716.1	752.5	788.8
45°	620.6	622.3	623.9	625.5	627.1	632.0	636.9	652.6	668.4	699.8	731.3
47.5°	587.0	587.0	587.0	588.1	589.2	593.5	597.8	609.2	620.6	645.0	669.5
50°	554.4	554.4	554.4	552.8	551.2	553.9	556.6	565.3	574.0	595.7	617.4
52.5°	515.4	515.4	515.4	515.9	516.5	516.5	516.5	524.1	531.7	551.2	570.7
55°	476.3	478.5	480.7	479.0	477.4	478.5	479.6	484.5	489.3	505.1	520.8
57.5°	437.3	438.3	439.4	438.9	438.3	438.9	439.4	443.8	448.1	460.0	472.0
60°	400.4	400.4	400.4	399.3	398.2	399.3	400.4	402.5	404.7	415.6	426.4
62.5°	359.1	359.7	360.2	360.8	361.3	360.2	359.1	361.9	364.6	372.7	380.8
65°	317.9	318.5	319.0	320.6	322.2	321.2	320.1	322.8	325.5	331.5	337.4
67.5°	281.0	279.9	278.8	279.4	279.9	281.6	283.2	283.7	284.3	290.8	297.3
70°	237.6	238.7	239.8	239.2	238.7	239.2	239.8	241.4	243.0	247.9	252.8
72.5°	198.6	199.1	199.6	199.6	199.6	200.7	201.8	203.4	205.1	207.8	210.5
75°	162.8	162.8	162.8	163.8	164.9	165.5	166.0	166.0	166.0	168.2	170.3
77.5°	123.7	126.4	129.1	128.6	128.0	129.1	130.2	131.8	133.5	134.5	135.6
80°	90.1	90.1	90.1	90.6	91.1	92.8	94.4	95.5	96.6	98.7	100.9
82.5°	57.5	58.0	58.6	60.2	61.8	62.9	64.0	65.6	67.3	67.3	67.3
85°	35.8	34.7	33.6	34.7	35.8	36.9	38.0	38.5	39.1	40.1	41.2
87.5°	17.4	17.4	17.4	17.4	17.4	17.9	18.4	18.4	18.4	18.4	18.4
90°	8.6	8.5	8.4	8.3	8.1	7.9	7.7	7.4	7.2	6.9	6.1
92.5°	9.8	9.7	9.7	9.6	9.5	9.3	8.8	8.4	7.9	7.5	6.9
95°	10.9	10.9	10.9	10.9	10.9	10.7	10.3	9.8	9.4	8.9	8.2
97.5°	11.8	11.7	11.7	11.6	11.6	11.3	10.8	10.2	9.7	9.2	12.5
100°	12.1	12.0	12.0	11.9	11.8	11.6	11.0	10.5	10.0	9.5	19.5
102.5°	12.4	12.3	12.1	12.0	11.9	12.9	15.0	17.1	19.2	21.3	32.5
105°	12.7	12.5	12.4	12.3	12.2	17.8	29.1	40.4	51.8	63.1	68.9
107.5°	30.0	38.3	46.7	55.1	63.5	72.6	82.5	92.4	102.2	112.1	111.1
110°	79.2	88.4	97.5	106.7	115.8	121.5	123.6	125.7	127.8	129.9	129.2



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.1	150.2	150.4	150.5	150.6	150.4	149.8	149.2	148.7	148.1	147.4
115°	169.4	169.1	168.9	168.6	168.4	167.9	167.3	166.7	166.0	165.4	164.8
117.5°	185.0	184.9	184.8	184.8	184.7	184.4	183.9	183.4	182.9	182.4	182.0
120°	201.1	201.1	201.1	201.1	201.1	200.8	200.3	199.8	199.3	198.8	198.6
122.5°	216.9	216.9	216.8	216.7	216.7	216.5	216.2	215.9	215.5	215.2	215.0
125°	231.6	231.5	231.4	231.2	231.1	231.0	230.9	230.7	230.6	230.5	230.2
127.5°	246.0	246.2	246.3	246.4	246.6	246.5	246.3	246.1	245.9	245.8	245.4
130°	259.9	260.0	260.1	260.3	260.4	260.3	260.1	259.8	259.5	259.3	259.0
132.5°	272.5	272.7	272.9	273.1	273.3	273.3	273.0	272.8	272.5	272.3	272.1
135°	285.5	285.7	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5	285.3
137.5°	297.9	298.0	298.2	298.3	298.4	298.3	298.0	297.7	297.4	297.0	296.9
140°	308.8	309.0	309.1	309.2	309.4	309.3	309.0	308.8	308.5	308.3	308.1
142.5°	318.9	319.1	319.3	319.5	319.7	319.7	319.5	319.3	319.1	318.9	318.7
145°	329.3	329.3	329.3	329.3	329.3	329.2	329.1	329.0	328.9	328.7	328.6
147.5°	336.8	337.1	337.4	337.8	338.1	338.2	338.0	337.9	337.8	337.7	337.5
150°	345.4	345.6	345.8	346.0	346.2	346.2	346.1	346.0	345.8	345.7	345.6
152.5°	352.3	352.7	353.0	353.3	353.6	353.7	353.4	353.1	352.9	352.6	352.6
155°	358.7	359.1	359.5	359.8	360.2	360.3	359.9	359.6	359.3	359.0	358.9
157.5°	364.2	364.7	365.2	365.7	366.2	366.3	365.9	365.5	365.1	364.7	364.8
160°	369.3	369.8	370.2	370.7	371.1	371.2	370.8	370.4	370.0	369.6	369.7
162.5°	374.2	374.6	375.0	375.4	375.8	375.7	375.3	374.9	374.4	374.0	374.0
165°	378.0	378.4	378.9	379.3	379.8	379.7	379.2	378.7	378.2	377.7	377.8
167.5°	380.9	381.4	381.9	382.4	382.9	382.9	382.4	381.9	381.4	380.9	380.9
170°	383.5	384.0	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.5	383.5
172.5°	384.9	385.5	386.1	386.6	387.2	387.2	386.7	386.2	385.7	385.2	385.1
175°	386.3	386.9	387.4	387.9	388.4	388.4	388.0	387.5	387.1	386.6	386.6
177.5°	386.6	387.3	387.9	388.6	389.2	389.3	388.7	388.2	387.7	387.2	387.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2501.0	2494.4	2470.6	2446.7	2419.6	2392.5	2372.4	2352.3	2322.5	2292.6	2268.2
5°	2710.4	2680.0	2629.5	2579.1	2510.7	2442.4	2396.3	2350.1	2288.3	2226.4	2177.1
7.5°	2876.4	2824.3	2753.8	2683.2	2593.7	2504.2	2419.6	2334.9	2240.6	2146.2	2069.1
10°	2982.2	2946.9	2865.5	2784.1	2664.2	2544.4	2426.1	2307.8	2186.3	2064.8	1962.8
12.5°	2992.5	2995.7	2920.9	2846.0	2710.4	2574.7	2431.0	2287.2	2134.2	1981.2	1862.4
15°	2901.9	2957.7	2916.5	2875.3	2738.6	2601.9	2425.0	2248.1	2071.8	1895.5	1758.3
17.5°	2733.7	2853.6	2859.6	2865.5	2728.8	2592.1	2396.3	2200.4	2000.8	1801.1	1656.8
20°	2504.2	2681.1	2741.8	2802.6	2691.4	2580.2	2369.7	2159.2	1935.7	1712.2	1560.8
22.5°	2269.8	2484.7	2595.9	2707.1	2624.6	2542.2	2318.1	2094.1	1858.1	1622.1	1468.6
25°	2002.9	2237.3	2408.2	2579.1	2528.6	2478.2	2257.4	2036.6	1785.4	1534.2	1377.4
27.5°	1770.2	2008.4	2214.5	2420.7	2409.8	2399.0	2179.8	1960.6	1703.5	1446.3	1295.0
30°	1563.0	1784.8	2015.4	2246.0	2272.6	2299.1	2087.6	1876.0	1618.3	1360.6	1214.7
32.5°	1379.6	1573.3	1820.7	2068.0	2120.1	2172.2	1981.2	1790.3	1535.3	1280.3	1139.8
35°	1229.3	1405.1	1652.5	1899.9	1965.0	2030.1	1864.1	1698.0	1449.6	1201.1	1067.1
37.5°	1096.4	1243.4	1484.8	1726.3	1806.0	1885.8	1737.1	1588.5	1355.7	1123.0	999.8
40°	986.3	1104.5	1326.4	1548.3	1640.5	1732.8	1610.2	1487.6	1266.8	1046.0	932.6
42.5°	894.1	999.3	1200.6	1401.8	1490.3	1578.7	1475.1	1371.5	1175.1	978.7	875.1
45°	815.4	899.5	1082.3	1265.1	1349.2	1433.3	1344.3	1255.4	1082.3	909.2	812.7
47.5°	741.6	813.8	970.0	1126.2	1201.1	1276.0	1206.5	1137.1	990.6	844.1	756.8
50°	675.4	733.5	870.2	1006.9	1072.0	1137.1	1075.8	1014.5	894.1	773.6	697.7
52.5°	617.9	665.1	779.6	894.1	949.9	1005.8	953.2	900.6	805.1	709.6	643.4
55°	561.0	601.1	700.4	799.7	837.6	875.6	834.9	794.2	717.2	640.2	584.3
57.5°	507.8	543.6	625.0	706.3	735.6	764.9	728.0	691.2	633.1	575.1	528.4
60°	455.7	485.0	552.8	620.6	638.5	656.4	626.6	596.8	556.1	515.4	473.6
62.5°	407.4	434.0	484.5	534.9	546.8	558.8	536.0	513.2	482.3	451.4	418.8
65°	357.5	377.6	418.8	460.0	467.6	475.2	455.2	435.1	411.8	388.4	364.6
67.5°	311.4	325.5	359.1	392.8	393.3	393.9	377.6	361.3	348.3	335.3	316.3
70°	266.4	279.9	302.2	324.4	325.0	325.5	312.5	299.5	289.7	279.9	265.8
72.5°	220.3	230.0	246.8	263.7	262.6	261.5	253.4	245.2	237.6	230.0	219.7
75°	178.5	186.6	198.0	209.4	206.2	202.9	198.6	194.2	187.7	181.2	174.7
77.5°	140.5	145.4	151.9	158.4	156.2	154.1	150.3	146.5	141.6	136.7	134.0
80°	103.1	105.2	109.6	113.9	112.8	111.8	107.4	103.1	102.0	100.9	97.1
82.5°	70.0	72.7	73.8	74.9	74.3	73.8	70.5	67.3	66.2	65.1	64.6
85°	41.8	42.3	42.9	43.4	41.8	40.1	39.1	38.0	38.0	38.0	37.4
87.5°	19.0	19.5	19.5	19.5	19.0	18.4	17.4	16.3	16.8	17.4	17.4
90°	5.2	4.4	3.6	2.8	2.2	1.6	0.9	0.3	0.9	1.6	2.2
92.5°	6.3	5.8	5.2	5.1	5.5	5.9	6.2	6.6	6.2	5.9	5.5
95°	7.5	6.8	6.1	7.1	9.7	12.3	14.9	17.6	14.9	12.3	9.7
97.5°	15.7	19.0	22.3	24.8	26.6	28.4	30.2	32.0	30.2	28.4	26.6
100°	29.5	39.5	49.5	53.8	52.5	51.3	50.0	48.7	50.0	51.3	52.5
102.5°	43.6	54.7	65.9	71.0	70.2	69.4	68.5	67.7	68.5	69.4	70.2
105°	74.6	80.4	86.1	88.7	88.0	87.3	86.6	85.9	86.6	87.3	88.0
107.5°	110.2	109.2	108.2	107.5	106.9	106.3	105.7	105.2	105.7	106.3	106.9
110°	128.5	127.8	127.1	126.5	126.0	125.5	125.0	124.5	125.0	125.5	126.0



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	146.7	146.0	145.3	144.7	144.2	143.8	143.3	142.9	143.3	143.8	144.2
115°	164.2	163.6	163.1	162.6	162.2	161.8	161.4	161.0	161.4	161.8	162.2
117.5°	181.7	181.4	181.1	180.7	180.3	179.8	179.4	178.9	179.4	179.8	180.3
120°	198.4	198.2	198.0	197.6	197.1	196.5	195.9	195.3	195.9	196.5	197.1
122.5°	214.7	214.4	214.2	213.8	213.4	212.9	212.5	212.0	212.5	212.9	213.4
125°	230.0	229.7	229.5	229.1	228.6	228.0	227.5	227.0	227.5	228.0	228.6
127.5°	245.1	244.8	244.5	244.1	243.5	243.0	242.5	242.0	242.5	243.0	243.5
130°	258.8	258.5	258.3	257.9	257.4	256.9	256.3	255.8	256.3	256.9	257.4
132.5°	271.9	271.7	271.5	271.1	270.6	270.1	269.6	269.1	269.6	270.1	270.6
135°	285.0	284.7	284.5	284.2	283.8	283.4	283.0	282.6	283.0	283.4	283.8
137.5°	296.8	296.6	296.5	296.2	295.7	295.2	294.7	294.2	294.7	295.2	295.7
140°	307.9	307.7	307.5	307.2	306.8	306.4	306.1	305.7	306.1	306.4	306.8
142.5°	318.5	318.4	318.2	317.9	317.5	317.1	316.7	316.3	316.7	317.1	317.5
145°	328.5	328.3	328.2	327.9	327.5	327.0	326.6	326.1	326.6	327.0	327.5
147.5°	337.4	337.3	337.1	336.9	336.6	336.3	336.0	335.6	336.0	336.3	336.6
150°	345.5	345.3	345.2	345.0	344.9	344.7	344.5	344.3	344.5	344.7	344.9
152.5°	352.5	352.4	352.4	352.3	352.3	352.2	352.1	352.1	352.1	352.2	352.3
155°	358.8	358.8	358.7	358.8	358.9	359.0	359.1	359.3	359.1	359.0	358.9
157.5°	364.9	364.9	365.0	365.0	365.0	365.0	365.0	365.0	365.0	365.0	365.0
160°	369.8	369.8	369.9	370.0	370.0	370.1	370.1	370.2	370.1	370.1	370.0
162.5°	374.1	374.1	374.2	374.3	374.5	374.7	374.9	375.1	374.9	374.7	374.5
165°	377.8	377.9	378.0	378.1	378.3	378.5	378.7	378.9	378.7	378.5	378.3
167.5°	380.9	380.9	380.9	381.0	381.3	381.5	381.8	382.0	381.8	381.5	381.3
170°	383.5	383.5	383.5	383.6	383.8	384.1	384.4	384.6	384.4	384.1	383.8
172.5°	385.1	385.0	384.9	385.1	385.4	385.7	386.0	386.3	386.0	385.7	385.4
175°	386.5	386.4	386.4	386.5	386.8	387.1	387.5	387.8	387.5	387.1	386.8
177.5°	387.1	387.0	387.0	387.1	387.4	387.7	388.0	388.4	388.0	387.7	387.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2	2338.2
2.5°	2243.8	2222.6	2201.5	2185.2	2168.9	2141.3	2113.6	2107.1	2100.6	2091.4	2082.1
5°	2127.7	2075.6	2023.5	1976.9	1930.2	1893.9	1857.5	1833.7	1809.8	1792.4	1775.1
7.5°	1992.1	1914.0	1835.8	1780.5	1725.2	1672.5	1619.9	1603.1	1586.3	1563.5	1540.7
10°	1860.8	1774.5	1688.3	1616.1	1544.0	1492.4	1440.9	1420.3	1399.7	1370.9	1342.2
12.5°	1743.6	1649.2	1554.8	1482.1	1409.4	1359.5	1309.6	1279.8	1249.9	1233.7	1217.4
15°	1621.0	1520.1	1419.2	1351.9	1284.7	1239.6	1194.6	1168.6	1142.5	1126.8	1111.1
17.5°	1512.5	1412.7	1312.9	1248.3	1183.7	1142.5	1101.3	1078.5	1055.7	1043.8	1031.8
20°	1409.4	1311.8	1214.1	1151.2	1088.3	1054.6	1021.0	1006.3	991.7	981.9	972.2
22.5°	1315.0	1219.0	1123.0	1069.3	1015.6	988.4	961.3	951.0	940.7	932.6	924.4
25°	1220.6	1134.9	1049.2	1003.6	958.1	935.8	913.6	903.3	893.0	884.8	876.7
27.5°	1143.6	1061.7	979.8	940.7	901.6	884.3	866.9	858.8	850.7	843.1	835.5
30°	1068.7	995.5	922.3	888.6	855.0	839.3	823.5	815.4	807.2	800.2	793.1
32.5°	999.3	936.4	873.4	842.5	811.6	798.6	785.5	775.8	766.0	760.6	755.2
35°	933.1	876.7	820.3	794.8	769.3	756.3	743.2	735.1	727.0	722.6	718.3
37.5°	876.7	826.2	775.8	751.4	727.0	714.5	702.0	695.0	687.9	686.3	684.6
40°	819.2	775.8	732.4	708.5	684.6	673.8	662.9	658.6	654.3	653.2	652.1
42.5°	771.4	729.1	686.8	665.1	643.4	634.2	625.0	622.8	620.6	622.3	623.9
45°	716.1	680.8	645.6	625.5	605.4	597.8	590.2	588.6	587.0	590.2	593.5
47.5°	669.5	636.9	604.4	585.4	566.4	561.0	555.5	555.0	554.4	558.8	563.1
50°	621.7	590.2	558.8	543.6	528.4	523.5	518.6	520.3	521.9	528.9	536.0
52.5°	577.2	547.9	518.6	504.5	490.4	487.2	483.9	487.7	491.5	499.1	506.7
55°	528.4	501.8	475.2	464.4	453.5	450.3	447.0	454.6	462.2	469.3	476.3
57.5°	481.7	458.4	435.1	425.3	415.6	415.0	414.5	421.5	428.6	436.2	443.8
60°	431.8	412.3	392.8	385.2	377.6	378.7	379.8	387.9	396.0	402.0	408.0
62.5°	386.3	370.0	353.7	346.7	339.6	342.3	345.0	353.2	361.3	368.4	375.4
65°	340.7	327.1	313.6	308.7	303.8	307.6	311.4	318.5	325.5	330.4	335.3
67.5°	297.3	285.9	274.5	270.7	266.9	270.7	274.5	281.6	288.6	293.5	298.4
70°	251.7	242.5	233.3	230.6	227.9	232.2	236.5	242.5	248.5	253.4	258.2
72.5°	209.4	202.4	195.3	194.8	194.2	198.0	201.8	207.8	213.7	217.0	220.3
75°	168.2	164.4	160.6	160.0	159.5	163.3	167.1	170.3	173.6	176.3	179.0
77.5°	131.3	128.0	124.8	125.3	125.9	128.6	131.3	134.5	137.8	139.4	141.1
80°	93.3	92.2	91.1	92.2	93.3	95.5	97.7	99.8	102.0	103.1	104.2
82.5°	64.0	62.9	61.8	63.5	65.1	66.7	68.4	70.0	71.6	72.2	72.7
85°	36.9	38.5	40.1	40.1	40.1	40.7	41.2	41.8	42.3	41.8	41.2
87.5°	17.4	17.9	18.4	18.4	18.4	19.0	19.5	19.5	19.5	19.0	18.4
90°	2.8	3.6	4.4	5.2	6.1	6.9	7.2	7.4	7.7	7.9	8.1
92.5°	5.1	5.2	5.8	6.3	6.9	7.5	7.9	8.4	8.8	9.3	9.5
95°	7.1	6.1	6.8	7.5	8.2	8.9	9.4	9.8	10.3	10.7	10.9
97.5°	24.8	22.3	19.0	15.7	12.5	9.2	9.7	10.2	10.8	11.3	11.6
100°	53.8	49.5	39.5	29.5	19.5	9.5	10.0	10.5	11.0	11.6	11.8
102.5°	71.0	65.9	54.7	43.6	32.5	21.3	19.2	17.1	15.0	12.9	11.9
105°	88.7	86.1	80.4	74.6	68.9	63.1	51.8	40.4	29.1	17.8	12.2
107.5°	107.5	108.2	109.2	110.2	111.1	112.1	102.2	92.4	82.5	72.6	63.5
110°	126.5	127.1	127.8	128.5	129.2	129.9	127.8	125.7	123.6	121.5	115.8

TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	144.7	145.3	146.0	146.7	147.4	148.1	148.7	149.2	149.8	150.4	150.6
115°	162.6	163.1	163.6	164.2	164.8	165.4	166.0	166.7	167.3	167.9	168.4
117.5°	180.7	181.1	181.4	181.7	182.0	182.4	182.9	183.4	183.9	184.4	184.7
120°	197.6	198.0	198.2	198.4	198.6	198.8	199.3	199.8	200.3	200.8	201.1
122.5°	213.8	214.2	214.4	214.7	215.0	215.2	215.5	215.9	216.2	216.5	216.7
125°	229.1	229.5	229.7	230.0	230.2	230.5	230.6	230.7	230.9	231.0	231.1
127.5°	244.1	244.5	244.8	245.1	245.4	245.8	245.9	246.1	246.3	246.5	246.6
130°	257.9	258.3	258.5	258.8	259.0	259.3	259.5	259.8	260.1	260.3	260.4
132.5°	271.1	271.5	271.7	271.9	272.1	272.3	272.5	272.8	273.0	273.3	273.3
135°	284.2	284.5	284.7	285.0	285.3	285.5	285.7	285.9	286.1	286.3	286.3
137.5°	296.2	296.5	296.6	296.8	296.9	297.0	297.4	297.7	298.0	298.3	298.4
140°	307.2	307.5	307.7	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.4
142.5°	317.9	318.2	318.4	318.5	318.7	318.9	319.1	319.3	319.5	319.7	319.7
145°	327.9	328.2	328.3	328.5	328.6	328.7	328.9	329.0	329.1	329.2	329.3
147.5°	336.9	337.1	337.3	337.4	337.5	337.7	337.8	337.9	338.0	338.2	338.1
150°	345.0	345.2	345.3	345.5	345.6	345.7	345.8	346.0	346.1	346.2	346.2
152.5°	352.3	352.4	352.4	352.5	352.6	352.6	352.9	353.1	353.4	353.7	353.6
155°	358.8	358.7	358.8	358.8	358.9	359.0	359.3	359.6	359.9	360.3	360.2
157.5°	365.0	365.0	364.9	364.9	364.8	364.7	365.1	365.5	365.9	366.3	366.2
160°	370.0	369.9	369.8	369.8	369.7	369.6	370.0	370.4	370.8	371.2	371.1
162.5°	374.3	374.2	374.1	374.1	374.0	374.0	374.4	374.9	375.3	375.7	375.8
165°	378.1	378.0	377.9	377.8	377.8	377.7	378.2	378.7	379.2	379.7	379.8
167.5°	381.0	380.9	380.9	380.9	380.9	380.9	381.4	381.9	382.4	382.9	382.9
170°	383.6	383.5	383.5	383.5	383.5	383.5	384.0	384.5	385.0	385.5	385.5
172.5°	385.1	384.9	385.0	385.1	385.1	385.2	385.7	386.2	386.7	387.2	387.2
175°	386.5	386.4	386.4	386.5	386.6	386.6	387.1	387.5	388.0	388.4	388.4
177.5°	387.1	387.0	387.0	387.1	387.1	387.2	387.7	388.2	388.7	389.3	389.2
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2338.2	2338.2	2338.2	2338.2
2.5°	2078.3	2074.5	2059.4	2044.2
5°	1762.1	1749.0	1744.7	1740.4
7.5°	1539.6	1538.5	1515.8	1493.0
10°	1343.8	1345.4	1324.8	1304.2
12.5°	1203.8	1190.3	1188.6	1187.0
15°	1098.6	1086.1	1083.9	1081.8
17.5°	1024.3	1016.7	1014.5	1012.3
20°	967.8	963.5	959.7	955.9
22.5°	919.0	913.6	910.3	907.1
25°	871.8	866.9	865.8	864.8
27.5°	829.5	823.5	823.5	823.5
30°	789.3	785.5	783.9	782.3
32.5°	751.9	748.7	748.7	748.7
35°	716.7	715.0	712.9	710.7
37.5°	684.6	684.6	683.6	682.5
40°	653.7	655.3	655.3	655.3
42.5°	625.5	627.1	627.1	627.1
45°	596.2	598.9	600.0	601.1
47.5°	567.5	571.8	572.9	574.0
50°	539.3	542.5	543.0	543.6
52.5°	510.5	514.3	517.0	519.7
55°	480.1	483.9	485.5	487.2
57.5°	447.6	451.4	451.9	452.5
60°	411.8	415.6	416.6	417.7
62.5°	377.6	379.8	380.8	381.9
65°	338.5	341.8	343.9	346.1
67.5°	301.1	303.8	303.8	303.8
70°	259.3	260.4	262.0	263.7
72.5°	220.8	221.3	221.3	221.3
75°	180.1	181.2	181.7	182.3
77.5°	141.6	142.1	142.1	142.1
80°	103.6	103.1	103.1	103.1
82.5°	71.1	69.4	69.4	69.4
85°	40.7	40.1	40.7	41.2
87.5°	18.4	18.4	18.4	18.4
90°	8.3	8.4	8.5	8.6
92.5°	9.6	9.7	9.7	9.8
95°	10.9	10.9	10.9	10.9
97.5°	11.6	11.7	11.7	11.8
100°	11.9	12.0	12.0	12.1
102.5°	12.0	12.1	12.3	12.4
105°	12.3	12.4	12.5	12.7
107.5°	55.1	46.7	38.3	30.0
110°	106.7	97.5	88.4	79.2



TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	150.5	150.4	150.2	150.1
115°	168.6	168.9	169.1	169.4
117.5°	184.8	184.8	184.9	185.0
120°	201.1	201.1	201.1	201.1
122.5°	216.7	216.8	216.9	216.9
125°	231.2	231.4	231.5	231.6
127.5°	246.4	246.3	246.2	246.0
130°	260.3	260.1	260.0	259.9
132.5°	273.1	272.9	272.7	272.5
135°	286.1	285.9	285.7	285.5
137.5°	298.3	298.2	298.0	297.9
140°	309.2	309.1	309.0	308.8
142.5°	319.5	319.3	319.1	318.9
145°	329.3	329.3	329.3	329.3
147.5°	337.8	337.4	337.1	336.8
150°	346.0	345.8	345.6	345.4
152.5°	353.3	353.0	352.7	352.3
155°	359.8	359.5	359.1	358.7
157.5°	365.7	365.2	364.7	364.2
160°	370.7	370.2	369.8	369.3
162.5°	375.4	375.0	374.6	374.2
165°	379.3	378.9	378.4	378.0
167.5°	382.4	381.9	381.4	380.9
170°	385.0	384.5	384.0	383.5
172.5°	386.6	386.1	385.5	384.9
175°	387.9	387.4	386.9	386.3
177.5°	388.6	387.9	387.3	386.6
180°	387.8	387.8	387.8	387.8

TEST NUMBER: P831114

CATALOG NUMBER: S123DIP-S1000D365U930-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.94	18.03	17.64	18.75	19.59	19.17	20.27	19.88	20.98	21.83
	3H	18.60	19.58	19.32	20.31	21.19	20.61	21.59	21.33	22.32	23.20
	4H	19.19	20.11	19.92	20.85	21.74	21.08	22.00	21.81	22.73	23.63
	6H	19.57	20.42	20.32	21.17	22.07	21.36	22.21	22.11	22.96	23.86
	8H	19.67	20.48	20.43	21.25	22.16	21.43	22.24	22.19	23.01	23.91
	12H	19.73	20.50	20.49	21.26	22.19	21.46	22.23	22.22	22.99	23.92
4H	2H	17.54	18.46	18.28	19.20	20.09	19.36	20.29	20.10	21.02	21.91
	3H	19.39	20.15	20.14	20.93	21.84	21.00	21.77	21.75	22.54	23.45
	4H	20.09	20.79	20.86	21.56	22.50	21.59	22.29	22.36	23.07	24.00
	6H	20.58	21.18	21.37	21.98	22.93	22.01	22.61	22.80	23.41	24.36
	8H	20.72	21.28	21.51	22.08	23.04	22.13	22.69	22.92	23.48	24.44
	12H	20.80	21.30	21.61	22.12	23.08	22.18	22.69	22.99	23.51	24.47
8H	4H	20.38	20.94	21.16	21.73	22.69	21.72	22.28	22.51	23.07	24.03
	6H	20.97	21.44	21.79	22.28	23.23	22.23	22.69	23.05	23.53	24.49
	8H	21.18	21.59	22.01	22.43	23.41	22.41	22.82	23.24	23.66	24.63
	12H	21.32	21.68	22.15	22.50	23.54	22.52	22.88	23.35	23.71	24.74
12H	4H	20.39	20.89	21.20	21.71	22.67	21.70	22.21	22.51	23.02	23.99
	6H	21.03	21.44	21.85	22.27	23.25	22.24	22.66	23.07	23.49	24.47
	8H	21.27	21.63	22.10	22.46	23.49	22.45	22.82	23.28	23.64	24.67