

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832418

Luminaire Tested: S123RDIP-S775D805U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832418
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U835-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6217.3 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 46.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53		
1	99	95	92	88	92	89	85	83	76	74	72	64	63	61	54	53	52	47		
2	91	84	79	74	84	78	74	69	68	64	61	58	55	53	48	46	45	40		
3	84	75	68	63	78	70	64	59	60	56	52	52	48	46	44	41	39	35		
4	77	67	60	54	72	63	56	51	54	49	45	47	43	40	40	37	35	31		
5	71	60	53	47	66	57	50	45	49	44	40	43	39	35	36	33	31	28		
6	66	55	47	41	61	51	44	39	45	40	36	39	35	32	33	30	28	25		
7	61	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	25	23		
8	57	46	38	33	53	43	36	32	38	33	29	33	29	26	29	26	23	21		
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21	19		
10	50	39	32	27	47	37	30	26	33	28	24	29	25	22	25	22	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	26872	26872	26872	26872	26872
5°	31907	30889	27041	21860	20294
10°	28909	31376	26906	17514	15024
15°	19904	26902	26622	14315	11886
20°	13846	20711	26087	12071	10447
25°	10552	15785	25310	10728	9628
30°	9185	12621	24337	9962	8918
35°	8433	10646	22959	9314	8272
40°	7694	9507	21157	8679	7680
45°	6949	8694	19212	8079	7089
50°	6308	8021	16918	7490	6358
55°	5705	7366	14713	6915	5455
60°	5113	6699	12781	6280	5156
65°	4720	5945	11000	5644	4875
70°	3833	5139	9599	5105	3962
75°	3365	4088	8131	4234	3489
80°	3044	3459	6664	3552	3298
85°	2779	3038	5051	3223	3038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 20272 cd/sqm



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.6	3.7
10°-20°	526.5	8.5
20°-30°	604.1	9.7
30°-40°	595.5	9.6
40°-50°	525.1	8.4
50°-60°	404.0	6.5
60°-70°	265.6	4.3
70°-80°	129.0	2.1
80°-90°	34.7	0.6
90°-100°	209.6	3.4
100°-110°	613.6	9.9
110°-120°	599.2	9.6
120°-130°	477.2	7.7
130°-140°	376.5	6.1
140°-150°	280.9	4.5
150°-160°	195.8	3.1
160°-170°	115.0	1.9
170°-180°	37.4	0.6
0°-30°	1358.2	21.8
0°-40°	1953.7	31.4
0°-60°	2882.8	46.4
0°-90°	3312.1	53.3
90°-120°	1422.4	22.9
90°-150°	2556.9	41.1
90°-180°	2905.0	46.7
0°-180°	6217.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2496	2496	2496	2496	2496	
5°	2953	2859	2503	2023	1878	270
15°	1786	2414	2389	1285	1067	504
25°	888	1329	2131	903	811	420
35°	642	810	1747	709	630	400
45°	456	571	1262	531	466	354
55°	304	392	784	368	291	273
65°	185	233	432	222	191	182
75°	81	98	196	102	84	87
85°	22	25	41	26	25	24
90°	23	20	2	20	23	13
95°	91	464	27	464	91	147
105°	994	629	91	629	994	992
115°	1210	481	160	481	1210	1179
125°	954	449	223	449	954	863
135°	773	442	261	442	773	600
145°	604	437	298	437	604	384
155°	501	423	338	423	501	233
165°	437	405	370	405	437	125
175°	393	389	385	389	393	38
180°	386	386	386	386	386	



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5
2.5°	2766.7	2758.0	2749.3	2746.7	2744.2	2736.0	2727.8	2709.4	2690.9	2672.0	2653.1
5°	2953.0	2954.0	2955.0	2952.5	2949.9	2939.2	2928.4	2905.9	2883.4	2858.8	2834.2
7.5°	2895.7	2912.0	2928.4	2931.5	2934.6	2942.7	2950.9	2945.8	2940.7	2931.5	2922.3
10°	2644.9	2643.9	2642.8	2661.3	2679.7	2734.5	2789.2	2817.4	2845.5	2870.6	2895.7
12.5°	2235.5	2237.0	2238.5	2298.9	2359.3	2411.0	2462.7	2534.3	2606.0	2683.3	2760.6
15°	1786.1	1811.2	1836.3	1890.0	1943.7	2021.5	2099.3	2195.5	2291.8	2414.1	2536.4
17.5°	1466.8	1477.5	1488.3	1540.0	1591.6	1665.3	1739.0	1848.0	1957.1	2114.7	2272.3
20°	1208.8	1218.6	1228.3	1265.6	1303.0	1373.6	1444.2	1548.1	1652.0	1808.1	1964.2
22.5°	1009.2	1028.2	1047.1	1072.2	1097.3	1148.4	1199.6	1305.6	1411.5	1553.8	1696.0
25°	888.5	897.2	905.9	927.3	948.8	998.0	1047.1	1117.2	1187.3	1329.1	1470.9
27.5°	806.6	809.1	811.7	827.6	843.4	875.1	906.9	971.9	1036.9	1153.6	1270.2
30°	739.0	743.6	748.2	760.5	772.8	795.8	818.9	864.9	911.0	1015.4	1119.8
32.5°	686.8	689.4	691.9	702.2	712.4	729.3	746.2	782.5	818.9	898.7	978.5
35°	641.8	642.3	642.8	650.5	658.2	674.5	690.9	721.1	751.3	810.2	869.0
37.5°	590.6	594.2	597.8	603.4	609.0	623.4	637.7	662.2	686.8	735.4	784.0
40°	547.6	550.7	553.7	560.4	567.1	578.3	589.6	612.1	634.6	676.6	718.5
42.5°	504.6	506.7	508.7	515.4	522.0	535.8	549.7	567.6	585.5	620.3	655.1
45°	456.5	461.6	466.7	473.9	481.1	492.8	504.6	523.0	541.5	571.1	600.8
47.5°	416.6	419.1	421.7	427.8	434.0	448.3	462.7	479.0	495.4	523.0	550.7
50°	376.7	377.7	378.7	384.3	390.0	402.8	415.6	434.5	453.4	479.0	504.6
52.5°	338.8	341.4	343.9	349.5	355.2	363.9	372.6	392.0	411.5	436.6	461.6
55°	304.0	305.5	307.1	311.2	315.3	325.5	335.7	352.6	369.5	392.5	415.6
57.5°	271.2	273.3	275.3	278.4	281.5	290.7	299.9	314.7	329.6	352.6	375.6
60°	237.5	240.0	242.6	246.2	249.7	256.9	264.1	277.4	290.7	311.2	331.6
62.5°	212.9	213.4	213.9	217.0	220.1	225.2	230.3	241.0	251.8	272.3	292.7
65°	185.3	186.8	188.3	189.9	191.4	195.5	199.6	208.8	218.0	233.4	248.7
67.5°	156.6	158.1	159.7	162.2	164.8	168.4	172.0	178.1	184.2	198.6	212.9
70°	121.8	121.8	121.8	125.9	130.0	136.1	142.3	146.9	151.5	163.3	175.0
72.5°	99.3	99.8	100.3	100.8	101.3	104.9	108.5	116.2	123.9	131.0	138.2
75°	80.9	81.4	81.9	82.4	82.9	83.9	85.0	87.5	90.1	98.3	106.5
77.5°	64.5	65.0	65.5	66.0	66.5	67.6	68.6	69.6	70.6	73.7	76.8
80°	49.1	49.6	50.2	50.7	51.2	51.7	52.2	53.2	54.2	55.8	57.3
82.5°	35.8	35.8	35.8	35.8	35.8	36.8	37.9	37.9	37.9	38.9	39.9
85°	22.5	22.5	22.5	23.0	23.5	23.5	23.5	24.1	24.6	24.6	24.6
87.5°	10.2	9.7	9.2	9.7	10.2	10.2	10.2	10.7	11.3	11.3	11.3
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	41.4	43.0	42.2	45.3	46.9	52.4	60.2	77.4	108.7	145.4	161.1
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	186.1	194.7	213.4	243.1	295.5	384.7	487.9	646.6	737.3	713.0	532.4
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	776.3	799.0	823.3	865.5	922.5	982.7	1026.5	1013.2	902.2	689.6	453.5
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1136.8	1145.4	1155.5	1169.6	1174.3	1153.2	1092.2	969.5	782.6	574.6	390.1
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1234.5	1233.7	1225.9	1203.2	1158.7	1084.4	971.0	823.3	659.9	500.4	368.2
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1154.7	1149.3	1125.8	1087.5	1026.5	938.2	832.6	712.2	587.1	467.5	368.2
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1015.6	1009.3	988.2	949.9	896.7	824.8	739.6	646.6	547.3	453.5	376.8
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	900.7	896.0	878.0	848.3	802.9	745.1	676.3	598.9	518.3	446.4	388.6
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	813.9	810.0	795.9	767.7	729.4	679.4	621.5	558.2	497.2	443.3	399.5
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	730.2	725.5	713.8	689.6	656.7	616.9	571.5	524.6	480.8	440.9	407.3
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	642.7	643.4	632.5	613.7	589.5	561.3	530.1	497.2	467.5	438.6	412.8
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	571.5	570.7	564.5	552.7	537.1	520.7	499.6	478.5	456.6	434.7	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	519.9	519.9	517.6	509.7	501.1	489.4	475.3	460.5	444.9	427.7	411.2
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	483.2	483.2	481.6	476.9	470.7	462.8	453.5	442.5	431.6	419.1	407.3
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	450.3	451.1	451.1	447.2	444.1	439.4	432.3	425.3	417.5	409.7	402.6
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	423.7	423.7	424.5	422.2	420.6	417.5	414.4	410.5	405.0	400.3	396.4
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	401.1	401.9	403.4	401.9	401.9	401.1	398.7	397.2	394.0	391.7	390.9
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.8	387.8	389.3	388.6	389.3	389.3	388.6	387.8	387.0	386.2	387.0
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5
2.5°	2650.5	2648.0	2623.4	2598.8	2574.8	2550.7	2532.8	2514.9	2484.7	2454.5	2435.6
5°	2814.8	2795.4	2756.5	2717.6	2659.2	2600.9	2551.7	2502.6	2440.2	2377.7	2325.5
7.5°	2906.4	2890.5	2843.5	2796.4	2719.1	2641.8	2565.1	2488.3	2396.2	2304.0	2225.2
10°	2909.0	2922.3	2883.4	2844.5	2757.5	2670.5	2566.1	2461.7	2337.8	2214.0	2112.1
12.5°	2817.9	2875.2	2867.0	2858.8	2770.3	2681.7	2554.8	2427.9	2275.9	2123.9	1996.5
15°	2647.4	2758.5	2791.3	2824.0	2750.8	2677.6	2533.3	2389.0	2210.4	2031.8	1885.4
17.5°	2427.9	2583.5	2670.0	2756.5	2703.2	2650.0	2491.9	2333.7	2132.6	1931.5	1772.3
20°	2167.9	2371.6	2507.2	2642.8	2623.4	2603.9	2440.7	2277.4	2060.4	1843.4	1671.0
22.5°	1911.0	2125.9	2313.3	2500.6	2520.5	2540.5	2375.7	2210.9	1973.4	1736.0	1560.4
25°	1689.4	1907.9	2131.1	2354.2	2399.2	2444.3	2287.7	2131.1	1884.9	1638.7	1464.2
27.5°	1478.0	1685.8	1931.5	2177.1	2259.0	2340.9	2197.6	2054.3	1797.9	1541.5	1367.5
30°	1305.6	1491.3	1742.1	1992.9	2107.0	2221.1	2089.6	1958.1	1703.7	1449.4	1278.9
32.5°	1144.9	1311.2	1563.0	1814.8	1947.3	2079.9	1966.3	1852.7	1608.0	1363.4	1195.0
35°	1017.9	1166.9	1401.8	1636.7	1785.1	1933.5	1840.4	1747.2	1508.2	1269.2	1110.1
37.5°	908.9	1033.8	1254.4	1475.0	1632.6	1790.2	1712.4	1634.6	1410.0	1185.3	1034.8
40°	818.9	919.2	1124.4	1329.6	1484.2	1638.7	1572.2	1505.7	1304.5	1103.4	962.7
42.5°	741.6	828.1	1012.3	1196.5	1338.3	1480.1	1436.1	1392.0	1209.9	1027.7	897.2
45°	673.5	746.2	908.4	1070.6	1201.2	1331.7	1296.9	1262.1	1104.9	947.8	828.1
47.5°	613.1	675.6	820.4	965.2	1082.4	1199.6	1167.4	1135.1	1005.1	875.1	766.1
50°	557.8	611.1	731.8	852.6	958.1	1063.5	1036.9	1010.3	902.8	795.3	701.1
52.5°	505.6	549.7	658.2	766.6	851.6	936.6	916.1	895.6	812.7	729.8	644.3
55°	456.0	496.4	588.0	679.6	752.3	825.0	804.5	784.0	719.6	655.1	579.8
57.5°	411.0	446.3	520.5	594.7	652.5	710.4	700.6	690.9	637.2	583.4	521.5
60°	363.4	395.1	459.1	523.0	569.6	616.2	604.9	593.7	555.3	516.9	463.7
62.5°	320.9	349.0	400.2	451.4	489.3	527.1	518.9	510.8	481.6	452.4	408.4
65°	276.4	304.0	345.5	386.9	416.6	446.3	439.1	431.9	409.9	387.9	352.6
67.5°	235.9	259.0	294.8	330.6	350.6	370.5	366.4	362.3	345.5	328.6	300.9
70°	195.0	214.9	244.6	274.3	288.1	302.0	303.5	305.0	289.7	274.3	253.8
72.5°	154.0	169.9	197.5	225.2	235.9	246.7	246.2	245.7	236.4	227.2	208.8
75°	118.2	130.0	151.5	173.0	182.2	191.4	193.5	195.5	186.8	178.1	167.9
77.5°	85.0	93.1	109.5	125.9	136.1	146.4	147.4	148.4	144.3	140.2	130.5
80°	59.9	62.4	72.7	82.9	93.7	104.4	105.9	107.5	103.4	99.3	93.1
82.5°	41.5	43.0	46.6	50.2	58.9	67.6	69.6	71.6	69.6	67.6	60.9
85°	25.1	25.6	27.1	28.7	32.8	36.8	38.9	40.9	39.9	38.9	35.3
87.5°	11.3	11.3	11.8	12.3	13.3	14.3	16.9	19.4	17.9	16.4	14.8
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	120.4	79.0	53.9	39.9	32.1	25.0	17.2	11.7	17.2	25.0	32.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	316.6	181.4	115.7	82.1	61.8	50.0	43.0	42.2	43.0	50.0	61.8
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	276.0	182.2	134.5	107.1	90.7	80.5	75.8	74.3	75.8	80.5	90.7
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	267.4	198.6	161.1	138.4	124.3	114.9	110.2	107.9	110.2	114.9	124.3
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.1	225.2	193.1	172.0	158.7	150.1	146.2	143.9	146.2	150.1	158.7
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	298.7	255.7	225.9	206.4	191.5	184.5	180.6	176.7	180.6	184.5	191.5
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	322.9	286.1	258.8	237.7	223.6	215.0	211.1	208.7	211.1	215.0	223.6
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	345.6	314.3	287.7	266.6	250.2	241.6	236.1	233.8	236.1	241.6	250.2
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	365.1	336.2	311.2	290.8	274.4	262.7	254.9	251.7	254.9	262.7	274.4
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	379.2	353.4	329.9	310.4	294.0	281.5	272.9	269.7	272.9	281.5	294.0
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	388.6	365.9	344.0	326.0	310.4	299.4	290.8	287.7	290.8	299.4	310.4
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.0	374.5	355.7	340.1	326.8	316.6	309.6	308.0	309.6	316.6	326.8
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.4	380.7	365.9	352.6	343.2	334.6	328.4	328.4	328.4	334.6	343.2
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.4	374.5	365.9	358.1	351.0	347.1	346.3	347.1	351.0	358.1
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.4	388.6	380.7	374.5	369.8	365.1	362.8	362.8	362.8	365.1	369.8
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	394.0	389.3	384.7	380.7	378.4	375.3	374.5	375.3	374.5	375.3	378.4
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	390.9	388.6	385.4	384.7	383.9	382.3	382.3	383.1	382.3	382.3	383.9
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.6	387.0	386.2	386.2	386.2	385.4	386.2	387.0	386.2	385.4	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5	2496.5
2.5°	2416.6	2387.5	2358.3	2337.3	2316.3	2290.2	2264.1	2263.1	2262.1	2242.6	2223.2
5°	2273.3	2222.7	2172.0	2122.4	2072.7	2023.1	1973.4	1962.2	1950.9	1934.0	1917.1
7.5°	2146.4	2065.6	1984.7	1921.2	1857.8	1808.1	1758.5	1724.7	1690.9	1664.8	1638.7
10°	2010.3	1910.0	1809.7	1732.9	1656.1	1602.4	1548.7	1509.8	1470.9	1452.4	1434.0
12.5°	1869.0	1760.0	1651.0	1575.8	1500.5	1436.1	1371.6	1336.3	1300.9	1275.4	1249.8
15°	1739.0	1621.8	1504.6	1424.8	1345.0	1284.6	1224.2	1188.9	1153.6	1128.0	1102.4
17.5°	1613.1	1494.9	1376.7	1295.8	1215.0	1160.2	1105.4	1071.2	1036.9	1021.0	1005.1
20°	1498.5	1379.3	1260.0	1183.8	1107.5	1053.8	1000.0	981.6	963.2	948.3	933.5
22.5°	1384.9	1270.2	1155.6	1082.4	1009.2	970.3	931.4	916.6	901.8	890.5	879.2
25°	1289.7	1175.6	1061.4	997.5	933.5	903.3	873.1	863.4	853.7	842.4	831.1
27.5°	1193.5	1085.0	976.5	925.3	874.1	849.6	825.0	812.7	800.4	791.2	782.0
30°	1108.5	1008.2	907.9	865.4	822.9	801.5	780.0	766.6	753.3	744.6	735.9
32.5°	1026.6	937.6	848.5	812.2	775.9	754.9	733.9	721.1	708.3	698.1	687.8
35°	950.9	873.6	796.3	763.1	729.8	708.8	687.8	675.0	662.2	652.0	641.8
37.5°	884.4	814.2	744.1	712.9	681.7	663.3	644.8	631.5	618.2	607.5	596.7
40°	821.9	760.0	698.1	667.9	637.7	617.7	597.8	586.0	574.2	564.5	554.8
42.5°	766.6	709.8	653.0	623.4	593.7	574.7	555.8	542.0	528.2	522.5	516.9
45°	708.3	658.2	608.0	579.3	550.7	530.7	510.8	499.0	487.2	482.1	477.0
47.5°	657.1	610.6	564.0	535.8	507.7	489.8	471.9	462.7	453.4	446.3	439.1
50°	607.0	561.9	516.9	489.8	462.7	447.3	431.9	420.7	409.4	404.3	399.2
52.5°	558.9	517.9	477.0	449.3	421.7	406.9	392.0	382.3	372.6	361.8	351.1
55°	504.6	468.8	433.0	408.4	383.8	368.5	353.1	341.9	330.6	319.4	308.1
57.5°	459.6	424.3	389.0	366.9	344.9	330.1	315.3	303.0	290.7	281.5	272.3
60°	410.4	379.7	349.0	327.5	306.0	291.7	277.4	265.6	253.8	249.2	244.6
62.5°	364.4	335.7	307.1	288.1	269.2	255.4	241.6	233.9	226.2	223.1	220.1
65°	317.3	292.7	268.2	250.8	233.4	221.6	209.8	206.2	202.7	200.1	197.5
67.5°	273.3	252.3	231.3	216.0	200.6	192.4	184.2	180.1	176.1	173.0	169.9
70°	233.4	214.9	196.5	183.2	169.9	162.2	154.6	151.0	147.4	141.8	136.1
72.5°	190.4	176.1	161.7	151.5	141.3	134.6	127.9	120.8	113.6	108.5	103.4
75°	157.6	143.3	129.0	119.2	109.5	101.8	94.2	91.6	89.1	87.5	86.0
77.5°	120.8	108.5	96.2	88.5	80.9	77.3	73.7	72.2	70.6	70.1	69.6
80°	87.0	76.8	66.5	62.4	58.3	57.3	56.3	55.3	54.2	53.7	53.2
82.5°	54.2	49.1	44.0	43.0	42.0	41.5	40.9	40.4	39.9	39.4	38.9
85°	31.7	29.7	27.6	27.1	26.6	26.1	25.6	25.6	25.6	25.6	25.6
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	12.8	12.3
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	39.9	53.9	79.0	120.4	161.1	145.4	108.7	77.4	60.2	52.4	46.9
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	82.1	115.7	181.4	316.6	532.4	713.0	737.3	646.6	487.9	384.7	295.5
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	107.1	134.5	182.2	276.0	453.5	689.6	902.2	1013.2	1026.5	982.7	922.5
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	138.4	161.1	198.6	267.4	390.1	574.6	782.6	969.5	1092.2	1153.2	1174.3
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	172.0	193.1	225.2	279.1	368.2	500.4	659.9	823.3	971.0	1084.4	1158.7
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	206.4	225.9	255.7	298.7	368.2	467.5	587.1	712.2	832.6	938.2	1026.5
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	237.7	258.8	286.1	322.9	376.8	453.5	547.3	646.6	739.6	824.8	896.7
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	266.6	287.7	314.3	345.6	388.6	446.4	518.3	598.9	676.3	745.1	802.9
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	290.8	311.2	336.2	365.1	399.5	443.3	497.2	558.2	621.5	679.4	729.4
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	310.4	329.9	353.4	379.2	407.3	440.9	480.8	524.6	571.5	616.9	656.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	326.0	344.0	365.9	388.6	412.8	438.6	467.5	497.2	530.1	561.3	589.5
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	340.1	355.7	374.5	394.0	413.6	434.7	456.6	478.5	499.6	520.7	537.1
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	352.6	365.9	380.7	396.4	411.2	427.7	444.9	460.5	475.3	489.4	501.1
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	365.9	374.5	385.4	397.2	407.3	419.1	431.6	442.5	453.5	462.8	470.7
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	374.5	380.7	388.6	396.4	402.6	409.7	417.5	425.3	432.3	439.4	444.1
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	380.7	384.7	389.3	394.0	396.4	400.3	405.0	410.5	414.4	417.5	420.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.7	385.4	388.6	390.9	390.9	391.7	394.0	397.2	398.7	401.1	401.9
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	387.0	388.6	387.0	386.2	387.0	387.8	388.6	389.3	389.3
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2496.5	2496.5	2496.5	2496.5
2.5°	2218.1	2212.9	2210.9	2208.9
5°	1901.3	1885.4	1881.8	1878.2
7.5°	1632.1	1625.4	1603.4	1581.4
10°	1413.5	1393.1	1383.9	1374.6
12.5°	1230.8	1211.9	1208.8	1205.8
15°	1089.1	1075.8	1071.2	1066.6
17.5°	995.9	986.7	981.1	975.5
20°	926.8	920.2	916.1	912.0
22.5°	874.1	869.0	865.9	862.9
25°	823.5	815.8	813.2	810.7
27.5°	775.3	768.7	766.1	763.6
30°	730.3	724.7	721.1	717.5
32.5°	681.2	674.5	672.5	670.4
35°	637.7	633.6	631.5	629.5
37.5°	591.6	586.5	583.4	580.4
40°	552.2	549.7	548.1	546.6
42.5°	512.3	507.7	507.2	506.7
45°	472.4	467.8	466.7	465.7
47.5°	435.0	430.9	430.4	429.9
50°	393.6	387.9	383.8	379.7
52.5°	346.0	340.8	337.3	333.7
55°	302.5	296.8	293.8	290.7
57.5°	269.7	267.2	265.6	264.1
60°	243.1	241.6	240.5	239.5
62.5°	218.5	217.0	217.0	217.0
65°	196.0	194.5	192.9	191.4
67.5°	166.8	163.8	163.3	162.7
70°	131.5	126.9	126.4	125.9
72.5°	102.9	102.4	101.3	100.3
75°	85.0	83.9	83.9	83.9
77.5°	68.6	67.6	67.6	67.6
80°	52.7	52.2	52.7	53.2
82.5°	38.9	38.9	38.4	37.9
85°	25.1	24.6	24.6	24.6
87.5°	12.3	12.3	12.3	12.3
90°	21.9	22.7	23.5	22.7
92.5°	45.3	42.2	43.0	41.4
95°	106.3	99.3	93.8	90.7
97.5°	243.1	213.4	194.7	186.1
100°	577.0	519.9	489.4	490.2
102.5°	865.5	823.3	799.0	776.3
105°	1053.1	1023.4	998.4	994.5
107.5°	1169.6	1155.5	1145.4	1136.8
110°	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1203.2	1225.9	1233.7	1234.5
115°	1155.5	1189.9	1205.6	1209.5
117.5°	1087.5	1125.8	1149.3	1154.7
120°	1015.6	1059.4	1078.1	1082.8
122.5°	949.9	988.2	1009.3	1015.6
125°	894.4	928.8	948.3	953.8
127.5°	848.3	878.0	896.0	900.7
130°	806.1	834.2	850.6	856.9
132.5°	767.7	795.9	810.0	813.9
135°	730.2	753.7	767.7	773.2
137.5°	689.6	713.8	725.5	730.2
140°	651.3	673.1	685.7	684.9
142.5°	613.7	632.5	643.4	642.7
145°	580.1	596.5	602.8	604.3
147.5°	552.7	564.5	570.7	571.5
150°	530.1	538.7	543.4	543.4
152.5°	509.7	517.6	519.9	519.9
155°	492.5	498.8	500.4	501.1
157.5°	476.9	481.6	483.2	483.2
160°	462.1	466.7	466.7	466.0
162.5°	447.2	451.1	451.1	450.3
165°	434.7	437.8	437.0	437.0
167.5°	422.2	424.5	423.7	423.7
170°	411.2	412.8	412.0	412.0
172.5°	401.9	403.4	401.9	401.1
175°	394.0	394.8	394.0	393.3
177.5°	388.6	389.3	387.8	387.8
180°	386.2	386.2	386.2	386.2



TEST NUMBER: P832418

CATALOG NUMBER: S123RDIP-S775D805U835-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	13.32	13.42	14.27	15.49	17.15	17.98	18.09	18.93	20.16
	3H	13.71	14.45	14.66	15.41	16.66	18.65	19.39	19.60	20.35	21.60
	4H	14.09	14.79	15.05	15.75	17.01	19.14	19.84	20.10	20.80	22.06
	6H	14.37	15.02	15.35	15.98	17.26	19.45	20.10	20.43	21.06	22.34
	8H	14.46	15.07	15.44	16.06	17.33	19.53	20.14	20.51	21.13	22.40
	12H	14.51	15.09	15.50	16.07	17.36	19.56	20.14	20.55	21.12	22.42
4H	2H	13.21	13.91	14.18	14.87	16.13	17.14	17.85	18.11	18.81	20.07
	3H	14.58	15.16	15.56	16.15	17.43	18.80	19.38	19.78	20.38	21.65
	4H	15.03	15.57	16.02	16.55	17.85	19.41	19.94	20.40	20.93	22.22
	6H	15.40	15.86	16.40	16.87	18.16	19.85	20.30	20.85	21.31	22.61
	8H	15.53	15.95	16.53	16.95	18.27	19.98	20.40	20.98	21.41	22.72
	12H	15.60	15.99	16.62	17.00	18.32	20.04	20.42	21.06	21.44	22.76
8H	4H	15.35	15.77	16.35	16.78	18.09	19.37	19.80	20.38	20.80	22.11
	6H	15.81	16.16	16.84	17.21	18.52	19.87	20.22	20.90	21.27	22.58
	8H	16.00	16.31	17.04	17.34	18.67	20.06	20.37	21.09	21.40	22.73
	12H	16.14	16.42	17.18	17.44	18.81	20.17	20.45	21.21	21.47	22.84
12H	4H	15.36	15.74	16.38	16.76	18.08	19.33	19.71	20.34	20.73	22.04
	6H	15.87	16.18	16.90	17.21	18.54	19.85	20.16	20.88	21.19	22.51
	8H	16.09	16.36	17.12	17.38	18.76	20.04	20.31	21.08	21.34	22.71