

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332009-930

Luminaire Tested: **S123DIP-S1000D585U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332009-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5366.6 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332009-930
CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	51	46	50	45	42	44	40	38	34
5	71	60	52	45	67	57	49	44	50	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	43	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12326	12326	12326	12326
5°	14699	12379	10970	12379
10°	18398	12316	9908	12316
15°	22566	12217	9225	12217
20°	26882	12062	8782	12062
25°	28544	11873	8684	11873
30°	24467	11737	8730	11737
35°	17015	11540	8821	11540
40°	12816	11311	8793	11311
45°	10641	10971	8681	10971
50°	9532	10275	8602	10275
55°	8912	9526	8496	9526
60°	8359	8742	8409	8742
65°	7857	7969	8140	7969
70°	7371	7091	7751	7091
75°	6600	6209	7107	6209
80°	5777	5089	6118	5089
85°	4520	3693	4113	3693



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	2.1
10°-20°	361.7	6.7
20°-30°	607.1	11.3
30°-40°	687.4	12.8
40°-50°	616.4	11.5
50°-60°	497.4	9.3
60°-70°	346.6	6.5
70°-80°	182.2	3.4
80°-90°	46.3	0.9
90°-100°	22.8	0.4
100°-110°	108.4	2.0
110°-120°	260.5	4.9
120°-130°	331.7	6.2
130°-140°	354.4	6.6
140°-150°	331.4	6.2
150°-160°	267.4	5.0
160°-170°	172.6	3.2
170°-180°	59.5	1.1
0°-30°	1081.6	20.2
0°-40°	1768.9	33.0
0°-60°	2882.8	53.7
0°-90°	3457.9	64.4
90°-120°	391.7	7.3
90°-150°	1409.3	26.3
90°-180°	1909.0	35.6
0°-180°	5366.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1360	1146	1015	1146	1360	141
15°	2025	1096	828	1096	2025	585
25°	2403	1000	731	1000	2403	1054
35°	1295	878	671	878	1295	841
45°	699	721	570	721	699	553
55°	475	508	453	508	475	426
65°	308	313	320	313	308	307
75°	159	149	171	149	159	170
85°	37	30	33	30	37	44
90°	14	0	14	0	14	8
95°	18	28	18	28	18	15
105°	20	139	20	139	20	47
115°	274	260	274	260	274	253
125°	374	366	374	366	374	334
135°	461	456	461	456	461	355
145°	532	526	532	526	532	332
155°	579	580	579	580	579	267
165°	610	612	610	612	610	172
175°	624	626	624	626	624	59
180°	626	626	626	626	626	



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1215.2	1214.4	1212.1	1213.9	1210.4	1205.5	1205.0	1200.6	1187.7	1186.8	1183.3
5°	1360.4	1355.9	1355.4	1354.9	1347.0	1336.5	1316.5	1314.9	1288.3	1275.0	1258.8
7.5°	1548.3	1550.7	1542.5	1535.5	1511.7	1496.1	1474.6	1447.2	1414.5	1381.4	1359.3
10°	1683.3	1701.6	1678.9	1663.3	1648.9	1621.7	1590.1	1550.7	1511.3	1465.3	1430.3
12.5°	1828.0	1837.0	1832.4	1817.8	1795.4	1754.0	1697.9	1654.6	1618.3	1541.6	1510.6
15°	2025.0	2058.9	2037.3	1987.3	1988.4	1949.1	1875.8	1795.4	1752.6	1685.5	1594.0
17.5°	2235.0	2239.2	2230.0	2188.3	2160.6	2106.5	2038.9	1961.8	1875.3	1794.0	1697.0
20°	2346.8	2343.5	2324.1	2302.4	2254.7	2212.6	2138.8	2052.8	1941.8	1861.9	1756.0
22.5°	2409.0	2403.4	2394.2	2376.1	2336.4	2291.2	2224.9	2130.9	2025.3	1915.2	1792.8
25°	2403.4	2410.6	2411.7	2406.8	2392.9	2365.7	2313.5	2238.6	2133.2	1991.8	1864.2
27.5°	2185.9	2196.2	2225.8	2252.1	2281.5	2311.5	2307.5	2270.3	2192.3	2070.0	1914.1
30°	1968.5	1946.3	2001.2	2070.5	2117.7	2200.9	2247.5	2250.3	2206.4	2101.6	1949.5
32.5°	1666.6	1691.0	1715.3	1800.7	1903.7	1997.2	2089.9	2164.6	2173.2	2103.4	1970.4
35°	1294.9	1325.4	1369.8	1414.2	1525.2	1620.6	1783.7	1925.7	2038.9	2053.9	1972.3
37.5°	1043.5	1058.6	1086.6	1131.1	1203.7	1316.9	1443.1	1622.6	1786.6	1908.5	1913.8
40°	912.1	916.6	948.2	982.0	1040.8	1134.0	1247.7	1406.4	1602.8	1773.2	1844.2
42.5°	813.6	823.3	836.7	869.3	916.1	986.2	1091.9	1223.1	1403.1	1599.1	1738.1
45°	699.0	710.1	718.4	740.1	773.4	820.5	894.4	1014.2	1151.2	1353.7	1540.7
47.5°	623.4	624.3	630.5	646.8	669.4	704.8	757.0	834.0	959.8	1124.1	1316.0
50°	569.2	578.1	580.3	593.0	610.8	636.9	680.2	745.7	848.9	993.1	1169.5
52.5°	531.1	533.7	540.0	549.2	564.7	585.0	622.5	673.8	754.7	877.7	1039.9
55°	474.9	474.9	481.0	488.2	497.1	515.4	540.4	578.1	639.7	735.2	869.4
57.5°	423.0	425.7	430.1	432.3	439.9	451.9	472.8	501.4	547.4	620.9	727.6
60°	388.3	393.4	392.8	397.2	403.9	413.4	431.0	454.4	495.5	554.2	644.2
62.5°	358.2	357.8	357.8	363.1	369.7	378.7	390.3	410.4	445.3	497.4	574.0
65°	308.5	307.4	311.3	314.5	316.8	323.4	332.3	350.1	373.4	412.2	471.6
67.5°	264.3	261.1	263.2	264.3	268.1	273.3	281.6	292.6	311.1	342.3	387.0
70°	234.2	231.4	230.8	231.9	235.2	239.1	245.2	255.8	273.0	297.9	330.7
72.5°	203.1	201.1	201.1	203.5	205.0	207.6	211.9	221.6	235.2	254.0	284.5
75°	158.7	158.7	158.7	159.2	160.9	163.1	166.4	171.5	182.0	195.3	215.8
77.5°	119.0	118.9	118.1	118.1	120.5	121.5	122.3	126.9	132.8	141.8	156.8
80°	93.2	90.4	91.6	93.2	94.3	94.9	96.5	97.7	102.6	107.6	118.1
82.5°	69.2	66.9	67.1	69.7	69.9	70.4	72.2	73.7	75.6	80.1	85.8
85°	36.6	36.6	37.2	37.2	37.7	37.2	38.8	39.4	39.4	42.2	45.5
87.5°	16.1	15.2	15.6	16.0	15.5	15.9	16.2	16.6	17.0	17.3	17.5
90°	13.9	13.8	13.5	13.4	13.1	12.8	12.4	12.0	11.6	11.2	9.8
92.5°	15.4	15.3	15.2	15.1	14.9	14.5	13.9	13.2	12.6	11.9	10.9
95°	17.7	17.7	17.7	17.7	17.7	17.3	16.6	15.9	15.2	14.4	13.3
97.5°	19.2	19.1	18.9	18.8	18.8	18.3	17.4	16.6	15.8	15.0	22.4
100°	19.6	19.4	19.3	19.2	19.1	18.7	17.9	17.0	16.1	15.3	31.5
102.5°	19.9	19.7	19.6	19.3	19.2	20.4	22.9	25.4	28.0	30.6	48.2
105°	20.5	20.2	20.1	19.8	19.6	28.7	47.0	65.2	83.6	101.8	111.1
107.5°	64.2	78.0	91.8	105.6	119.4	133.0	146.4	159.8	173.3	186.6	185.2
110°	127.8	142.7	157.4	172.2	186.9	196.1	199.5	202.9	206.3	209.7	208.6



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.4	222.5	225.6	228.8	231.9	233.4	233.3	233.3	233.3	233.2	232.0
115°	273.5	273.0	272.6	272.1	271.7	271.1	270.0	269.0	268.0	266.9	266.0
117.5°	303.8	303.7	303.6	303.5	303.5	303.0	302.1	301.3	300.5	299.6	299.2
120°	324.6	324.6	324.6	324.6	324.6	324.2	323.3	322.5	321.7	320.8	320.6
122.5°	345.0	345.0	344.9	344.8	344.7	344.4	343.8	343.2	342.7	342.1	341.7
125°	373.9	373.7	373.5	373.2	373.1	372.8	372.6	372.4	372.2	372.0	371.6
127.5°	401.6	401.8	402.0	402.2	402.4	402.4	402.0	401.7	401.4	401.0	400.6
130°	419.5	419.6	419.9	420.0	420.3	420.1	419.7	419.3	418.9	418.5	418.1
132.5°	435.8	436.1	436.3	436.7	437.0	436.9	436.5	436.1	435.7	435.3	434.9
135°	460.8	461.1	461.5	461.8	462.0	462.0	461.8	461.5	461.1	460.8	460.4
137.5°	484.4	484.5	484.8	484.9	485.2	485.0	484.5	484.0	483.6	483.1	482.8
140°	498.5	498.7	498.9	499.1	499.3	499.2	498.8	498.4	498.0	497.6	497.3
142.5°	511.5	511.8	512.1	512.4	512.7	512.7	512.3	512.0	511.7	511.4	511.0
145°	531.5	531.5	531.5	531.5	531.5	531.4	531.2	531.0	530.8	530.6	530.4
147.5°	546.4	546.9	547.3	547.8	548.3	548.5	548.2	548.0	547.8	547.6	547.4
150°	557.6	557.8	558.2	558.5	558.8	558.8	558.6	558.4	558.2	558.0	557.8
152.5°	566.5	567.0	567.4	567.9	568.3	568.4	568.0	567.7	567.3	567.0	566.8
155°	578.9	579.6	580.2	580.8	581.4	581.5	581.0	580.4	579.9	579.4	579.3
157.5°	589.5	590.3	591.1	591.8	592.6	592.8	592.2	591.5	590.9	590.3	590.4
160°	596.1	596.9	597.6	598.3	599.0	599.1	598.4	597.9	597.2	596.6	596.7
162.5°	602.5	603.1	603.7	604.4	605.0	605.0	604.3	603.6	602.9	602.2	602.3
165°	610.1	610.8	611.6	612.3	613.0	612.9	612.1	611.3	610.5	609.6	609.8
167.5°	615.6	616.4	617.3	618.1	618.9	618.9	618.1	617.3	616.4	615.6	615.6
170°	618.9	619.8	620.6	621.4	622.2	622.2	621.4	620.6	619.8	618.9	618.9
172.5°	620.8	621.7	622.6	623.5	624.4	624.4	623.6	622.8	622.0	621.2	621.1
175°	623.5	624.4	625.3	626.1	626.9	627.0	626.2	625.5	624.8	624.0	623.9
177.5°	624.4	625.3	626.1	626.9	627.7	627.8	627.1	626.5	625.8	625.2	625.1
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1180.6	1177.0	1173.5	1167.3	1162.0	1154.5	1152.2	1149.6	1141.6	1134.5	1129.1
5°	1252.7	1239.4	1220.0	1202.2	1187.8	1168.4	1157.3	1145.7	1129.0	1114.0	1101.9
7.5°	1328.2	1302.0	1271.9	1239.2	1208.8	1179.5	1155.8	1134.8	1111.5	1089.4	1072.2
10°	1388.1	1350.4	1308.2	1262.7	1223.9	1186.2	1154.5	1126.8	1096.8	1070.7	1049.1
12.5°	1456.5	1400.5	1342.4	1287.1	1241.2	1188.9	1150.6	1115.2	1081.3	1049.9	1025.6
15°	1537.3	1466.3	1397.6	1321.5	1251.6	1186.2	1140.7	1096.3	1056.9	1024.7	993.7
17.5°	1611.0	1530.6	1439.9	1347.5	1263.1	1185.5	1121.9	1071.6	1022.4	983.0	952.0
20°	1652.8	1561.2	1458.6	1362.6	1269.4	1182.8	1113.0	1053.0	999.7	958.1	923.2
22.5°	1688.7	1581.6	1475.4	1372.8	1268.9	1175.7	1096.5	1034.9	977.1	936.4	899.2
25°	1726.0	1597.8	1491.3	1370.9	1255.0	1158.5	1069.7	999.7	942.1	894.4	856.1
27.5°	1757.9	1596.8	1470.3	1340.8	1233.0	1136.2	1041.5	966.5	905.2	853.4	814.6
30°	1779.2	1599.0	1448.6	1320.5	1211.7	1111.8	1019.7	944.3	880.0	827.2	790.6
32.5°	1792.6	1597.6	1428.6	1292.0	1177.9	1089.6	996.2	918.1	852.0	800.1	764.8
35°	1800.3	1587.9	1394.2	1233.3	1123.5	1037.5	959.3	878.2	808.9	760.7	720.7
37.5°	1784.8	1567.3	1354.3	1176.7	1056.5	971.8	906.0	837.0	770.6	717.5	683.1
40°	1760.4	1554.0	1323.2	1136.8	1010.3	928.7	872.7	805.0	739.6	689.1	656.9
42.5°	1713.8	1526.9	1289.1	1092.4	962.4	880.8	829.2	772.7	710.7	663.3	631.1
45°	1600.0	1468.0	1237.8	1025.8	891.5	807.2	761.7	720.7	664.6	618.6	590.8
47.5°	1442.3	1379.3	1163.7	955.6	817.7	736.5	689.3	656.2	615.3	578.1	551.5
50°	1332.6	1306.6	1113.5	907.7	768.4	689.1	643.6	613.6	584.2	547.1	522.6
52.5°	1206.2	1222.2	1054.9	857.9	718.3	640.3	597.5	573.6	546.9	516.4	495.1
55°	1028.1	1086.3	953.7	774.5	643.6	569.2	528.7	507.6	492.1	469.4	451.0
57.5°	861.3	935.4	844.3	688.5	570.2	506.1	467.2	444.3	434.3	422.4	408.0
60°	762.3	835.5	766.2	630.8	521.0	459.9	425.5	406.1	396.2	387.8	375.6
62.5°	674.0	748.1	689.8	572.3	472.5	416.0	386.0	367.0	359.3	355.0	344.5
65°	552.6	616.4	577.6	481.0	403.3	353.4	326.2	312.9	305.7	304.0	297.3
67.5°	449.7	498.3	470.0	399.0	337.9	294.7	271.7	260.3	254.8	254.2	249.2
70°	382.3	427.8	406.1	341.8	289.0	255.2	235.2	225.3	221.9	221.4	218.6
72.5°	329.9	361.6	344.4	290.7	250.0	219.2	204.6	194.2	190.4	191.2	189.3
75°	244.1	268.0	258.0	220.8	188.1	168.1	155.9	149.3	145.9	147.6	145.4
77.5°	175.6	190.8	181.7	156.0	135.8	121.4	112.4	108.3	105.3	105.2	104.2
80°	132.6	141.5	136.5	120.9	104.3	92.1	84.9	82.1	80.5	79.9	79.3
82.5°	94.4	102.0	96.1	85.4	74.1	66.8	62.7	59.0	57.8	58.1	57.6
85°	47.7	50.5	48.3	41.6	37.2	33.8	31.6	29.9	28.9	29.4	28.3
87.5°	18.1	18.3	16.7	14.7	13.6	12.1	11.8	10.8	10.0	10.3	10.0
90°	8.5	7.1	5.8	4.6	3.6	2.5	1.5	0.5	1.5	2.5	3.6
92.5°	9.9	8.9	7.8	7.5	7.7	8.1	8.4	8.6	8.4	8.1	7.7
95°	12.1	11.0	9.9	11.4	15.7	19.9	24.1	28.4	24.1	19.9	15.7
97.5°	29.8	37.3	44.8	49.4	51.3	53.2	55.1	57.0	55.1	53.2	51.3
100°	47.6	63.7	79.8	86.8	84.8	82.8	80.6	78.6	80.6	82.8	84.8
102.5°	65.8	83.4	101.0	109.1	107.6	106.2	104.6	103.1	104.6	106.2	107.6
105°	120.4	129.7	139.0	143.1	141.9	140.9	139.7	138.6	139.7	140.9	141.9
107.5°	183.7	182.2	180.8	179.6	178.7	177.8	176.8	175.9	176.8	177.8	178.7
110°	207.4	206.3	205.2	204.2	203.3	202.5	201.7	200.9	201.7	202.5	203.3



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	230.9	229.8	228.6	227.6	226.9	226.2	225.4	224.7	225.4	226.2	226.9
115°	265.1	264.2	263.2	262.4	261.8	261.1	260.6	259.9	260.6	261.1	261.8
117.5°	298.7	298.2	297.7	297.1	296.4	295.6	294.8	294.1	294.8	295.6	296.4
120°	320.2	319.9	319.6	319.0	318.0	317.2	316.2	315.3	316.2	317.2	318.0
122.5°	341.3	340.9	340.5	339.9	339.2	338.3	337.6	336.9	337.6	338.3	339.2
125°	371.2	370.8	370.4	369.7	368.9	368.1	367.3	366.4	367.3	368.1	368.9
127.5°	400.1	399.5	399.0	398.4	397.5	396.7	395.9	395.1	395.9	396.7	397.5
130°	417.7	417.3	416.9	416.2	415.4	414.6	413.8	412.9	413.8	414.6	415.4
132.5°	434.6	434.2	433.9	433.3	432.5	431.7	430.9	430.1	430.9	431.7	432.5
135°	460.0	459.6	459.2	458.7	458.0	457.4	456.8	456.2	456.8	457.4	458.0
137.5°	482.6	482.3	482.2	481.6	480.9	480.0	479.3	478.5	479.3	480.0	480.9
140°	496.9	496.6	496.4	495.9	495.2	494.6	494.0	493.3	494.0	494.6	495.2
142.5°	510.7	510.4	510.1	509.6	509.0	508.4	507.8	507.1	507.8	508.4	509.0
145°	530.2	529.9	529.8	529.3	528.6	527.8	527.1	526.4	527.1	527.8	528.6
147.5°	547.1	547.0	546.7	546.4	545.9	545.5	545.0	544.5	545.0	545.5	545.9
150°	557.6	557.4	557.2	556.9	556.6	556.3	556.0	555.7	556.0	556.3	556.6
152.5°	566.7	566.6	566.5	566.3	566.1	566.0	565.9	565.7	565.9	566.0	566.1
155°	579.2	579.1	579.0	579.0	579.3	579.4	579.7	579.8	579.7	579.4	579.3
157.5°	590.5	590.6	590.7	590.8	590.8	590.8	590.8	590.8	590.8	590.8	590.8
160°	596.8	596.9	597.0	597.1	597.2	597.4	597.5	597.5	597.5	597.4	597.2
162.5°	602.4	602.5	602.6	602.8	603.1	603.3	603.6	603.9	603.6	603.3	603.1
165°	609.8	609.9	610.0	610.3	610.6	610.9	611.1	611.5	611.1	610.9	610.6
167.5°	615.6	615.6	615.6	615.8	616.2	616.6	617.0	617.4	617.0	616.6	616.2
170°	618.9	618.9	618.9	619.1	619.5	620.0	620.4	620.8	620.4	620.0	619.5
172.5°	621.0	620.9	620.9	621.0	621.5	622.0	622.6	623.1	622.6	622.0	621.5
175°	623.9	623.7	623.6	623.9	624.4	624.8	625.4	625.9	625.4	624.8	624.4
177.5°	625.0	624.9	624.8	625.0	625.4	625.8	626.2	626.6	626.2	625.8	625.4
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1126.0	1122.9	1118.5	1111.8	1106.5	1098.0	1098.0	1099.4	1099.4	1098.9	1098.0
5°	1091.8	1083.5	1073.6	1061.9	1049.7	1037.5	1035.3	1030.9	1027.5	1025.2	1022.5
7.5°	1055.8	1041.1	1026.5	1010.2	995.3	983.0	974.4	967.4	962.8	957.9	954.4
10°	1031.4	1013.1	995.9	978.7	959.8	944.9	935.4	928.7	923.7	919.3	917.1
12.5°	1002.5	981.5	962.6	946.2	925.6	910.2	901.2	898.1	892.3	882.9	878.0
15°	960.3	940.9	918.2	893.2	883.2	864.4	853.9	848.9	845.5	838.3	836.1
17.5°	924.3	898.9	873.3	854.8	836.2	820.9	815.0	808.8	804.4	798.5	796.7
20°	895.4	872.7	849.4	829.4	810.0	793.4	788.4	783.9	779.5	776.7	774.5
22.5°	866.2	843.4	824.1	805.4	784.7	773.8	768.4	763.5	760.4	758.6	756.3
25°	825.0	805.0	783.4	766.7	750.1	742.9	739.6	736.8	734.6	731.8	731.2
27.5°	788.1	766.4	748.9	733.4	721.4	715.3	712.2	710.8	711.3	712.2	712.9
30°	760.7	740.7	726.3	712.9	701.8	696.3	695.7	695.7	698.0	698.5	699.6
32.5°	735.3	718.9	704.5	691.6	683.2	679.4	681.5	681.5	683.3	684.8	686.7
35°	698.5	684.0	672.9	661.9	654.7	656.3	657.5	658.5	661.3	664.6	666.9
37.5°	663.3	650.8	639.3	630.6	627.3	630.2	632.9	635.3	638.5	641.0	643.3
40°	638.1	628.6	617.5	609.8	610.8	612.5	614.7	617.5	620.3	621.9	624.2
42.5°	614.5	604.6	596.2	589.8	591.3	593.5	594.8	596.2	599.4	602.4	603.7
45°	578.7	570.9	563.1	559.2	560.4	561.5	562.6	564.3	567.0	569.2	569.8
47.5°	538.3	533.0	527.7	524.0	525.7	525.3	526.8	530.3	531.2	532.5	535.6
50°	512.7	507.6	501.6	500.4	500.4	500.4	501.0	505.4	505.4	507.6	509.9
52.5°	484.2	481.0	477.1	475.2	474.3	474.3	476.5	478.8	479.7	482.8	485.0
55°	442.2	438.9	435.5	433.8	432.8	433.8	438.3	439.4	442.2	443.8	445.5
57.5°	398.4	395.8	393.1	392.2	392.0	393.5	395.9	399.3	399.9	405.0	407.6
60°	369.5	365.6	363.4	363.4	362.3	367.3	366.2	371.7	372.8	376.2	380.0
62.5°	339.7	334.5	333.6	333.6	335.3	336.6	338.2	340.6	343.6	347.7	350.7
65°	291.8	289.0	292.9	292.4	291.3	294.6	294.6	297.3	300.7	304.6	310.7
67.5°	246.5	245.0	245.3	245.3	247.0	248.9	250.5	252.9	256.9	261.0	265.0
70°	215.8	217.5	214.7	217.0	218.6	219.2	220.3	223.6	228.0	230.8	235.2
72.5°	186.1	186.0	186.3	187.2	188.8	189.9	190.9	194.8	199.6	201.9	205.5
75°	143.2	142.6	144.2	144.2	147.0	148.1	149.3	150.9	155.3	158.7	161.4
77.5°	104.5	105.2	104.8	106.7	106.0	106.2	109.7	111.3	111.8	118.3	119.8
80°	78.8	79.9	80.5	81.0	81.5	80.5	84.3	86.0	86.0	89.8	92.6
82.5°	56.6	57.2	58.7	59.3	59.4	60.5	60.8	62.0	63.3	65.1	68.6
85°	28.3	29.9	30.5	29.9	30.5	29.4	31.1	31.6	32.2	32.2	32.2
87.5°	9.8	10.5	10.3	11.0	10.8	11.6	11.7	10.8	10.9	12.3	10.6
90°	4.6	5.8	7.1	8.5	9.8	11.2	11.6	12.0	12.4	12.8	13.1
92.5°	7.5	7.8	8.9	9.9	10.9	11.9	12.6	13.2	13.9	14.5	14.9
95°	11.4	9.9	11.0	12.1	13.3	14.4	15.2	15.9	16.6	17.3	17.7
97.5°	49.4	44.8	37.3	29.8	22.4	15.0	15.8	16.6	17.4	18.3	18.8
100°	86.8	79.8	63.7	47.6	31.5	15.3	16.1	17.0	17.9	18.7	19.1
102.5°	109.1	101.0	83.4	65.8	48.2	30.6	28.0	25.4	22.9	20.4	19.2
105°	143.1	139.0	129.7	120.4	111.1	101.8	83.6	65.2	47.0	28.7	19.6
107.5°	179.6	180.8	182.2	183.7	185.2	186.6	173.3	159.8	146.4	133.0	119.4
110°	204.2	205.2	206.3	207.4	208.6	209.7	206.3	202.9	199.5	196.1	186.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	227.6	228.6	229.8	230.9	232.0	233.2	233.3	233.3	233.3	233.4	231.9
115°	262.4	263.2	264.2	265.1	266.0	266.9	268.0	269.0	270.0	271.1	271.7
117.5°	297.1	297.7	298.2	298.7	299.2	299.6	300.5	301.3	302.1	303.0	303.5
120°	319.0	319.6	319.9	320.2	320.6	320.8	321.7	322.5	323.3	324.2	324.6
122.5°	339.9	340.5	340.9	341.3	341.7	342.1	342.7	343.2	343.8	344.4	344.7
125°	369.7	370.4	370.8	371.2	371.6	372.0	372.2	372.4	372.6	372.8	373.1
127.5°	398.4	399.0	399.5	400.1	400.6	401.0	401.4	401.7	402.0	402.4	402.4
130°	416.2	416.9	417.3	417.7	418.1	418.5	418.9	419.3	419.7	420.1	420.3
132.5°	433.3	433.9	434.2	434.6	434.9	435.3	435.7	436.1	436.5	436.9	437.0
135°	458.7	459.2	459.6	460.0	460.4	460.8	461.1	461.5	461.8	462.0	462.0
137.5°	481.6	482.2	482.3	482.6	482.8	483.1	483.6	484.0	484.5	485.0	485.2
140°	495.9	496.4	496.6	496.9	497.3	497.6	498.0	498.4	498.8	499.2	499.3
142.5°	509.6	510.1	510.4	510.7	511.0	511.4	511.7	512.0	512.3	512.7	512.7
145°	529.3	529.8	529.9	530.2	530.4	530.6	530.8	531.0	531.2	531.4	531.5
147.5°	546.4	546.7	547.0	547.1	547.4	547.6	547.8	548.0	548.2	548.5	548.3
150°	556.9	557.2	557.4	557.6	557.8	558.0	558.2	558.4	558.6	558.8	558.8
152.5°	566.3	566.5	566.6	566.7	566.8	567.0	567.3	567.7	568.0	568.4	568.3
155°	579.0	579.0	579.1	579.2	579.3	579.4	579.9	580.4	581.0	581.5	581.4
157.5°	590.8	590.7	590.6	590.5	590.4	590.3	590.9	591.5	592.2	592.8	592.6
160°	597.1	597.0	596.9	596.8	596.7	596.6	597.2	597.9	598.4	599.1	599.0
162.5°	602.8	602.6	602.5	602.4	602.3	602.2	602.9	603.6	604.3	605.0	605.0
165°	610.3	610.0	609.9	609.8	609.8	609.6	610.5	611.3	612.1	612.9	613.0
167.5°	615.8	615.6	615.6	615.6	615.6	615.6	616.4	617.3	618.1	618.9	618.9
170°	619.1	618.9	618.9	618.9	618.9	618.9	619.8	620.6	621.4	622.2	622.2
172.5°	621.0	620.9	620.9	621.0	621.1	621.2	622.0	622.8	623.6	624.4	624.4
175°	623.9	623.6	623.7	623.9	623.9	624.0	624.8	625.5	626.2	627.0	626.9
177.5°	625.0	624.8	624.9	625.0	625.1	625.2	625.8	626.5	627.1	627.8	627.7
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1094.9	1094.5	1097.6	1095.4	1097.6	1094.5	1094.9	1098.0	1098.9	1099.4	1099.4
5°	1019.2	1020.8	1015.3	1015.3	1015.3	1020.8	1019.2	1022.5	1025.2	1027.5	1030.9
7.5°	951.7	949.3	949.5	946.5	949.5	949.3	951.7	954.4	957.9	962.8	967.4
10°	910.4	907.1	906.0	906.5	906.0	907.1	910.4	917.1	919.3	923.7	928.7
12.5°	876.3	875.6	868.3	868.4	868.3	875.6	876.3	878.0	882.9	892.3	898.1
15°	836.1	825.6	824.4	827.8	824.4	825.6	836.1	836.1	838.3	845.5	848.9
17.5°	795.8	790.3	790.6	789.0	790.6	790.3	795.8	796.7	798.5	804.4	808.8
20°	774.5	771.2	770.6	766.7	770.6	771.2	774.5	774.5	776.7	779.5	783.9
22.5°	755.0	753.9	754.2	749.9	754.2	753.9	755.0	756.3	758.6	760.4	763.5
25°	730.7	733.4	731.2	731.2	731.2	733.4	730.7	731.2	731.8	734.6	736.8
27.5°	714.3	714.1	713.1	713.1	713.1	714.1	714.3	712.9	712.2	711.3	710.8
30°	701.8	701.2	702.4	702.4	702.4	701.2	701.8	699.6	698.5	698.0	695.7
32.5°	689.4	690.2	690.4	690.8	690.4	690.2	689.4	686.7	684.8	683.3	681.5
35°	670.2	670.7	672.5	671.3	672.5	670.7	670.2	666.9	664.6	661.3	658.5
37.5°	644.2	646.8	646.2	647.1	646.2	646.8	644.2	643.3	641.0	638.5	635.3
40°	624.7	626.4	625.8	625.8	625.8	626.4	624.7	624.2	621.9	620.3	617.5
42.5°	604.7	605.9	604.5	603.6	604.5	605.9	604.7	603.7	602.4	599.4	596.2
45°	572.0	570.9	572.6	570.3	572.6	570.9	572.0	569.8	569.2	567.0	564.3
47.5°	535.4	536.5	537.0	538.6	537.0	536.5	535.4	535.6	532.5	531.2	530.3
50°	510.9	514.3	514.3	513.7	514.3	514.3	510.9	509.9	507.6	505.4	505.4
52.5°	487.0	488.5	490.8	490.6	490.8	488.5	487.0	485.0	482.8	479.7	478.8
55°	450.0	451.0	452.2	452.7	452.2	451.0	450.0	445.5	443.8	442.2	439.4
57.5°	411.6	411.1	413.8	414.6	413.8	411.1	411.6	407.6	405.0	399.9	399.3
60°	384.5	384.5	388.9	390.6	388.9	384.5	384.5	380.0	376.2	372.8	371.7
62.5°	355.6	357.4	361.8	359.5	361.8	357.4	355.6	350.7	347.7	343.6	340.6
65°	313.5	317.9	317.3	319.6	317.3	317.9	313.5	310.7	304.6	300.7	297.3
67.5°	269.4	272.1	276.1	276.5	276.1	272.1	269.4	265.0	261.0	256.9	252.9
70°	239.7	242.5	244.7	246.3	244.7	242.5	239.7	235.2	230.8	228.0	223.6
72.5°	210.8	212.3	217.6	215.2	217.6	212.3	210.8	205.5	201.9	199.6	194.8
75°	165.3	169.2	172.5	170.9	172.5	169.2	165.3	161.4	158.7	155.3	150.9
77.5°	122.3	126.1	127.7	126.3	127.7	126.1	122.3	119.8	118.3	111.8	111.3
80°	96.5	96.0	99.3	98.7	99.3	96.0	96.5	92.6	89.8	86.0	86.0
82.5°	70.8	70.3	71.8	72.2	71.8	70.3	70.8	68.6	65.1	63.3	62.0
85°	34.4	36.0	33.8	33.3	33.8	36.0	34.4	32.2	32.2	32.2	31.6
87.5°	10.7	10.7	10.3	9.9	10.3	10.7	10.7	10.6	12.3	10.9	10.8
90°	13.4	13.5	13.8	13.9	13.8	13.5	13.4	13.1	12.8	12.4	12.0
92.5°	15.1	15.2	15.3	15.4	15.3	15.2	15.1	14.9	14.5	13.9	13.2
95°	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.3	16.6	15.9
97.5°	18.8	18.9	19.1	19.2	19.1	18.9	18.8	18.8	18.3	17.4	16.6
100°	19.2	19.3	19.4	19.6	19.4	19.3	19.2	19.1	18.7	17.9	17.0
102.5°	19.3	19.6	19.7	19.9	19.7	19.6	19.3	19.2	20.4	22.9	25.4
105°	19.8	20.1	20.2	20.5	20.2	20.1	19.8	19.6	28.7	47.0	65.2
107.5°	105.6	91.8	78.0	64.2	78.0	91.8	105.6	119.4	133.0	146.4	159.8
110°	172.2	157.4	142.7	127.8	142.7	157.4	172.2	186.9	196.1	199.5	202.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	228.8	225.6	222.5	219.4	222.5	225.6	228.8	231.9	233.4	233.3	233.3
115°	272.1	272.6	273.0	273.5	273.0	272.6	272.1	271.7	271.1	270.0	269.0
117.5°	303.5	303.6	303.7	303.8	303.7	303.6	303.5	303.5	303.0	302.1	301.3
120°	324.6	324.6	324.6	324.6	324.6	324.6	324.6	324.6	324.2	323.3	322.5
122.5°	344.8	344.9	345.0	345.0	345.0	344.9	344.8	344.7	344.4	343.8	343.2
125°	373.2	373.5	373.7	373.9	373.7	373.5	373.2	373.1	372.8	372.6	372.4
127.5°	402.2	402.0	401.8	401.6	401.8	402.0	402.2	402.4	402.4	402.0	401.7
130°	420.0	419.9	419.6	419.5	419.6	419.9	420.0	420.3	420.1	419.7	419.3
132.5°	436.7	436.3	436.1	435.8	436.1	436.3	436.7	437.0	436.9	436.5	436.1
135°	461.8	461.5	461.1	460.8	461.1	461.5	461.8	462.0	462.0	461.8	461.5
137.5°	484.9	484.8	484.5	484.4	484.5	484.8	484.9	485.2	485.0	484.5	484.0
140°	499.1	498.9	498.7	498.5	498.7	498.9	499.1	499.3	499.2	498.8	498.4
142.5°	512.4	512.1	511.8	511.5	511.8	512.1	512.4	512.7	512.7	512.3	512.0
145°	531.5	531.5	531.5	531.5	531.5	531.5	531.5	531.5	531.4	531.2	531.0
147.5°	547.8	547.3	546.9	546.4	546.9	547.3	547.8	548.3	548.5	548.2	548.0
150°	558.5	558.2	557.8	557.6	557.8	558.2	558.5	558.8	558.8	558.6	558.4
152.5°	567.9	567.4	567.0	566.5	567.0	567.4	567.9	568.3	568.4	568.0	567.7
155°	580.8	580.2	579.6	578.9	579.6	580.2	580.8	581.4	581.5	581.0	580.4
157.5°	591.8	591.1	590.3	589.5	590.3	591.1	591.8	592.6	592.8	592.2	591.5
160°	598.3	597.6	596.9	596.1	596.9	597.6	598.3	599.0	599.1	598.4	597.9
162.5°	604.4	603.7	603.1	602.5	603.1	603.7	604.4	605.0	605.0	604.3	603.6
165°	612.3	611.6	610.8	610.1	610.8	611.6	612.3	613.0	612.9	612.1	611.3
167.5°	618.1	617.3	616.4	615.6	616.4	617.3	618.1	618.9	618.9	618.1	617.3
170°	621.4	620.6	619.8	618.9	619.8	620.6	621.4	622.2	622.2	621.4	620.6
172.5°	623.5	622.6	621.7	620.8	621.7	622.6	623.5	624.4	624.4	623.6	622.8
175°	626.1	625.3	624.4	623.5	624.4	625.3	626.1	626.9	627.0	626.2	625.5
177.5°	626.9	626.1	625.3	624.4	625.3	626.1	626.9	627.7	627.8	627.1	626.5
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1098.0	1098.0	1106.5	1111.8	1118.5	1122.9	1126.0	1129.1	1134.5	1141.6	1149.6
5°	1035.3	1037.5	1049.7	1061.9	1073.6	1083.5	1091.8	1101.9	1114.0	1129.0	1145.7
7.5°	974.4	983.0	995.3	1010.2	1026.5	1041.1	1055.8	1072.2	1089.4	1111.5	1134.8
10°	935.4	944.9	959.8	978.7	995.9	1013.1	1031.4	1049.1	1070.7	1096.8	1126.8
12.5°	901.2	910.2	925.6	946.2	962.6	981.5	1002.5	1025.6	1049.9	1081.3	1115.2
15°	853.9	864.4	883.2	893.2	918.2	940.9	960.3	993.7	1024.7	1056.9	1096.3
17.5°	815.0	820.9	836.2	854.8	873.3	898.9	924.3	952.0	983.0	1022.4	1071.6
20°	788.4	793.4	810.0	829.4	849.4	872.7	895.4	923.2	958.1	999.7	1053.0
22.5°	768.4	773.8	784.7	805.4	824.1	843.4	866.2	899.2	936.4	977.1	1034.9
25°	739.6	742.9	750.1	766.7	783.4	805.0	825.0	856.1	894.4	942.1	999.7
27.5°	712.2	715.3	721.4	733.4	748.9	766.4	788.1	814.6	853.4	905.2	966.5
30°	695.7	696.3	701.8	712.9	726.3	740.7	760.7	790.6	827.2	880.0	944.3
32.5°	681.5	679.4	683.2	691.6	704.5	718.9	735.3	764.8	800.1	852.0	918.1
35°	657.5	656.3	654.7	661.9	672.9	684.0	698.5	720.7	760.7	808.9	878.2
37.5°	632.9	630.2	627.3	630.6	639.3	650.8	663.3	683.1	717.5	770.6	837.0
40°	614.7	612.5	610.8	609.8	617.5	628.6	638.1	656.9	689.1	739.6	805.0
42.5°	594.8	593.5	591.3	589.8	596.2	604.6	614.5	631.1	663.3	710.7	772.7
45°	562.6	561.5	560.4	559.2	563.1	570.9	578.7	590.8	618.6	664.6	720.7
47.5°	526.8	525.3	525.7	524.0	527.7	533.0	538.3	551.5	578.1	615.3	656.2
50°	501.0	500.4	500.4	500.4	501.6	507.6	512.7	522.6	547.1	584.2	613.6
52.5°	476.5	474.3	474.3	475.2	477.1	481.0	484.2	495.1	516.4	546.9	573.6
55°	438.3	433.8	432.8	433.8	435.5	438.9	442.2	451.0	469.4	492.1	507.6
57.5°	395.9	393.5	392.0	392.2	393.1	395.8	398.4	408.0	422.4	434.3	444.3
60°	366.2	367.3	362.3	363.4	363.4	365.6	369.5	375.6	387.8	396.2	406.1
62.5°	338.2	336.6	335.3	333.6	333.6	334.5	339.7	344.5	355.0	359.3	367.0
65°	294.6	294.6	291.3	292.4	292.9	289.0	291.8	297.3	304.0	305.7	312.9
67.5°	250.5	248.9	247.0	245.3	245.3	245.0	246.5	249.2	254.2	254.8	260.3
70°	220.3	219.2	218.6	217.0	214.7	217.5	215.8	218.6	221.4	221.9	225.3
72.5°	190.9	189.9	188.8	187.2	186.3	186.0	186.1	189.3	191.2	190.4	194.2
75°	149.3	148.1	147.0	144.2	144.2	142.6	143.2	145.4	147.6	145.9	149.3
77.5°	109.7	106.2	106.0	106.7	104.8	105.2	104.5	104.2	105.2	105.3	108.3
80°	84.3	80.5	81.5	81.0	80.5	79.9	78.8	79.3	79.9	80.5	82.1
82.5°	60.8	60.5	59.4	59.3	58.7	57.2	56.6	57.6	58.1	57.8	59.0
85°	31.1	29.4	30.5	29.9	30.5	29.9	28.3	28.3	29.4	28.9	29.9
87.5°	11.7	11.6	10.8	11.0	10.3	10.5	9.8	10.0	10.3	10.0	10.8
90°	11.6	11.2	9.8	8.5	7.1	5.8	4.6	3.6	2.5	1.5	0.5
92.5°	12.6	11.9	10.9	9.9	8.9	7.8	7.5	7.7	8.1	8.4	8.6
95°	15.2	14.4	13.3	12.1	11.0	9.9	11.4	15.7	19.9	24.1	28.4
97.5°	15.8	15.0	22.4	29.8	37.3	44.8	49.4	51.3	53.2	55.1	57.0
100°	16.1	15.3	31.5	47.6	63.7	79.8	86.8	84.8	82.8	80.6	78.6
102.5°	28.0	30.6	48.2	65.8	83.4	101.0	109.1	107.6	106.2	104.6	103.1
105°	83.6	101.8	111.1	120.4	129.7	139.0	143.1	141.9	140.9	139.7	138.6
107.5°	173.3	186.6	185.2	183.7	182.2	180.8	179.6	178.7	177.8	176.8	175.9
110°	206.3	209.7	208.6	207.4	206.3	205.2	204.2	203.3	202.5	201.7	200.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.3	233.2	232.0	230.9	229.8	228.6	227.6	226.9	226.2	225.4	224.7
115°	268.0	266.9	266.0	265.1	264.2	263.2	262.4	261.8	261.1	260.6	259.9
117.5°	300.5	299.6	299.2	298.7	298.2	297.7	297.1	296.4	295.6	294.8	294.1
120°	321.7	320.8	320.6	320.2	319.9	319.6	319.0	318.0	317.2	316.2	315.3
122.5°	342.7	342.1	341.7	341.3	340.9	340.5	339.9	339.2	338.3	337.6	336.9
125°	372.2	372.0	371.6	371.2	370.8	370.4	369.7	368.9	368.1	367.3	366.4
127.5°	401.4	401.0	400.6	400.1	399.5	399.0	398.4	397.5	396.7	395.9	395.1
130°	418.9	418.5	418.1	417.7	417.3	416.9	416.2	415.4	414.6	413.8	412.9
132.5°	435.7	435.3	434.9	434.6	434.2	433.9	433.3	432.5	431.7	430.9	430.1
135°	461.1	460.8	460.4	460.0	459.6	459.2	458.7	458.0	457.4	456.8	456.2
137.5°	483.6	483.1	482.8	482.6	482.3	482.2	481.6	480.9	480.0	479.3	478.5
140°	498.0	497.6	497.3	496.9	496.6	496.4	495.9	495.2	494.6	494.0	493.3
142.5°	511.7	511.4	511.0	510.7	510.4	510.1	509.6	509.0	508.4	507.8	507.1
145°	530.8	530.6	530.4	530.2	529.9	529.8	529.3	528.6	527.8	527.1	526.4
147.5°	547.8	547.6	547.4	547.1	547.0	546.7	546.4	545.9	545.5	545.0	544.5
150°	558.2	558.0	557.8	557.6	557.4	557.2	556.9	556.6	556.3	556.0	555.7
152.5°	567.3	567.0	566.8	566.7	566.6	566.5	566.3	566.1	566.0	565.9	565.7
155°	579.9	579.4	579.3	579.2	579.1	579.0	579.0	579.3	579.4	579.7	579.8
157.5°	590.9	590.3	590.4	590.5	590.6	590.7	590.8	590.8	590.8	590.8	590.8
160°	597.2	596.6	596.7	596.8	596.9	597.0	597.1	597.2	597.4	597.5	597.5
162.5°	602.9	602.2	602.3	602.4	602.5	602.6	602.8	603.1	603.3	603.6	603.9
165°	610.5	609.6	609.8	609.8	609.9	610.0	610.3	610.6	610.9	611.1	611.5
167.5°	616.4	615.6	615.6	615.6	615.6	615.6	615.8	616.2	616.6	617.0	617.4
170°	619.8	618.9	618.9	618.9	618.9	618.9	619.1	619.5	620.0	620.4	620.8
172.5°	622.0	621.2	621.1	621.0	620.9	620.9	621.0	621.5	622.0	622.6	623.1
175°	624.8	624.0	623.9	623.9	623.7	623.6	623.9	624.4	624.8	625.4	625.9
177.5°	625.8	625.2	625.1	625.0	624.9	624.8	625.0	625.4	625.8	626.2	626.6
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1152.2	1154.5	1162.0	1167.3	1173.5	1177.0	1180.6	1183.3	1186.8	1187.7	1200.6
5°	1157.3	1168.4	1187.8	1202.2	1220.0	1239.4	1252.7	1258.8	1275.0	1288.3	1314.9
7.5°	1155.8	1179.5	1208.8	1239.2	1271.9	1302.0	1328.2	1359.3	1381.4	1414.5	1447.2
10°	1154.5	1186.2	1223.9	1262.7	1308.2	1350.4	1388.1	1430.3	1465.3	1511.3	1550.7
12.5°	1150.6	1188.9	1241.2	1287.1	1342.4	1400.5	1456.5	1510.6	1541.6	1618.3	1654.6
15°	1140.7	1186.2	1251.6	1321.5	1397.6	1466.3	1537.3	1594.0	1685.5	1752.6	1795.4
17.5°	1121.9	1185.5	1263.1	1347.5	1439.9	1530.6	1611.0	1697.0	1794.0	1875.3	1961.8
20°	1113.0	1182.8	1269.4	1362.6	1458.6	1561.2	1652.8	1756.0	1861.9	1941.8	2052.8
22.5°	1096.5	1175.7	1268.9	1372.8	1475.4	1581.6	1688.7	1792.8	1915.2	2025.3	2130.9
25°	1069.7	1158.5	1255.0	1370.9	1491.3	1597.8	1726.0	1864.2	1991.8	2133.2	2238.6
27.5°	1041.5	1136.2	1233.0	1340.8	1470.3	1596.8	1757.9	1914.1	2070.0	2192.3	2270.3
30°	1019.7	1111.8	1211.7	1320.5	1448.6	1599.0	1779.2	1949.5	2101.6	2206.4	2250.3
32.5°	996.2	1089.6	1177.9	1292.0	1428.6	1597.6	1792.6	1970.4	2103.4	2173.2	2164.6
35°	959.3	1037.5	1123.5	1233.3	1394.2	1587.9	1800.3	1972.3	2053.9	2038.9	1925.7
37.5°	906.0	971.8	1056.5	1176.7	1354.3	1567.3	1784.8	1913.8	1908.5	1786.6	1622.6
40°	872.7	928.7	1010.3	1136.8	1323.2	1554.0	1760.4	1844.2	1773.2	1602.8	1406.4
42.5°	829.2	880.8	962.4	1092.4	1289.1	1526.9	1713.8	1738.1	1599.1	1403.1	1223.1
45°	761.7	807.2	891.5	1025.8	1237.8	1468.0	1600.0	1540.7	1353.7	1151.2	1014.2
47.5°	689.3	736.5	817.7	955.6	1163.7	1379.3	1442.3	1316.0	1124.1	959.8	834.0
50°	643.6	689.1	768.4	907.7	1113.5	1306.6	1332.6	1169.5	993.1	848.9	745.7
52.5°	597.5	640.3	718.3	857.9	1054.9	1222.2	1206.2	1039.9	877.7	754.7	673.8
55°	528.7	569.2	643.6	774.5	953.7	1086.3	1028.1	869.4	735.2	639.7	578.1
57.5°	467.2	506.1	570.2	688.5	844.3	935.4	861.3	727.6	620.9	547.4	501.4
60°	425.5	459.9	521.0	630.8	766.2	835.5	762.3	644.2	554.2	495.5	454.4
62.5°	386.0	416.0	472.5	572.3	689.8	748.1	674.0	574.0	497.4	445.3	410.4
65°	326.2	353.4	403.3	481.0	577.6	616.4	552.6	471.6	412.2	373.4	350.1
67.5°	271.7	294.7	337.9	399.0	470.0	498.3	449.7	387.0	342.3	311.1	292.6
70°	235.2	255.2	289.0	341.8	406.1	427.8	382.3	330.7	297.9	273.0	255.8
72.5°	204.6	219.2	250.0	290.7	344.4	361.6	329.9	284.5	254.0	235.2	221.6
75°	155.9	168.1	188.1	220.8	258.0	268.0	244.1	215.8	195.3	182.0	171.5
77.5°	112.4	121.4	135.8	156.0	181.7	190.8	175.6	156.8	141.8	132.8	126.9
80°	84.9	92.1	104.3	120.9	136.5	141.5	132.6	118.1	107.6	102.6	97.7
82.5°	62.7	66.8	74.1	85.4	96.1	102.0	94.4	85.8	80.1	75.6	73.7
85°	31.6	33.8	37.2	41.6	48.3	50.5	47.7	45.5	42.2	39.4	39.4
87.5°	11.8	12.1	13.6	14.7	16.7	18.3	18.1	17.5	17.3	17.0	16.6
90°	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6	12.0
92.5°	8.4	8.1	7.7	7.5	7.8	8.9	9.9	10.9	11.9	12.6	13.2
95°	24.1	19.9	15.7	11.4	9.9	11.0	12.1	13.3	14.4	15.2	15.9
97.5°	55.1	53.2	51.3	49.4	44.8	37.3	29.8	22.4	15.0	15.8	16.6
100°	80.6	82.8	84.8	86.8	79.8	63.7	47.6	31.5	15.3	16.1	17.0
102.5°	104.6	106.2	107.6	109.1	101.0	83.4	65.8	48.2	30.6	28.0	25.4
105°	139.7	140.9	141.9	143.1	139.0	129.7	120.4	111.1	101.8	83.6	65.2
107.5°	176.8	177.8	178.7	179.6	180.8	182.2	183.7	185.2	186.6	173.3	159.8
110°	201.7	202.5	203.3	204.2	205.2	206.3	207.4	208.6	209.7	206.3	202.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	225.4	226.2	226.9	227.6	228.6	229.8	230.9	232.0	233.2	233.3	233.3
115°	260.6	261.1	261.8	262.4	263.2	264.2	265.1	266.0	266.9	268.0	269.0
117.5°	294.8	295.6	296.4	297.1	297.7	298.2	298.7	299.2	299.6	300.5	301.3
120°	316.2	317.2	318.0	319.0	319.6	319.9	320.2	320.6	320.8	321.7	322.5
122.5°	337.6	338.3	339.2	339.9	340.5	340.9	341.3	341.7	342.1	342.7	343.2
125°	367.3	368.1	368.9	369.7	370.4	370.8	371.2	371.6	372.0	372.2	372.4
127.5°	395.9	396.7	397.5	398.4	399.0	399.5	400.1	400.6	401.0	401.4	401.7
130°	413.8	414.6	415.4	416.2	416.9	417.3	417.7	418.1	418.5	418.9	419.3
132.5°	430.9	431.7	432.5	433.3	433.9	434.2	434.6	434.9	435.3	435.7	436.1
135°	456.8	457.4	458.0	458.7	459.2	459.6	460.0	460.4	460.8	461.1	461.5
137.5°	479.3	480.0	480.9	481.6	482.2	482.3	482.6	482.8	483.1	483.6	484.0
140°	494.0	494.6	495.2	495.9	496.4	496.6	496.9	497.3	497.6	498.0	498.4
142.5°	507.8	508.4	509.0	509.6	510.1	510.4	510.7	511.0	511.4	511.7	512.0
145°	527.1	527.8	528.6	529.3	529.8	529.9	530.2	530.4	530.6	530.8	531.0
147.5°	545.0	545.5	545.9	546.4	546.7	547.0	547.1	547.4	547.6	547.8	548.0
150°	556.0	556.3	556.6	556.9	557.2	557.4	557.6	557.8	558.0	558.2	558.4
152.5°	565.9	566.0	566.1	566.3	566.5	566.6	566.7	566.8	567.0	567.3	567.7
155°	579.7	579.4	579.3	579.0	579.0	579.1	579.2	579.3	579.4	579.9	580.4
157.5°	590.8	590.8	590.8	590.8	590.7	590.6	590.5	590.4	590.3	590.9	591.5
160°	597.5	597.4	597.2	597.1	597.0	596.9	596.8	596.7	596.6	597.2	597.9
162.5°	603.6	603.3	603.1	602.8	602.6	602.5	602.4	602.3	602.2	602.9	603.6
165°	611.1	610.9	610.6	610.3	610.0	609.9	609.8	609.8	609.6	610.5	611.3
167.5°	617.0	616.6	616.2	615.8	615.6	615.6	615.6	615.6	615.6	616.4	617.3
170°	620.4	620.0	619.5	619.1	618.9	618.9	618.9	618.9	618.9	619.8	620.6
172.5°	622.6	622.0	621.5	621.0	620.9	620.9	621.0	621.1	621.2	622.0	622.8
175°	625.4	624.8	624.4	623.9	623.6	623.7	623.9	623.9	624.0	624.8	625.5
177.5°	626.2	625.8	625.4	625.0	624.8	624.9	625.0	625.1	625.2	625.8	626.5
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1	1145.1
2.5°	1205.0	1205.5	1210.4	1213.9	1212.1	1214.4	1215.2
5°	1316.5	1336.5	1347.0	1354.9	1355.4	1355.9	1360.4
7.5°	1474.6	1496.1	1511.7	1535.5	1542.5	1550.7	1548.3
10°	1590.1	1621.7	1648.9	1663.3	1678.9	1701.6	1683.3
12.5°	1697.9	1754.0	1795.4	1817.8	1832.4	1837.0	1828.0
15°	1875.8	1949.1	1988.4	1987.3	2037.3	2058.9	2025.0
17.5°	2038.9	2106.5	2160.6	2188.3	2230.0	2239.2	2235.0
20°	2138.8	2212.6	2254.7	2302.4	2324.1	2343.5	2346.8
22.5°	2224.9	2291.2	2336.4	2376.1	2394.2	2403.4	2409.0
25°	2313.5	2365.7	2392.9	2406.8	2411.7	2410.6	2403.4
27.5°	2307.5	2311.5	2281.5	2252.1	2225.8	2196.2	2185.9
30°	2247.5	2200.9	2117.7	2070.5	2001.2	1946.3	1968.5
32.5°	2089.9	1997.2	1903.7	1800.7	1715.3	1691.0	1666.6
35°	1783.7	1620.6	1525.2	1414.2	1369.8	1325.4	1294.9
37.5°	1443.1	1316.9	1203.7	1131.1	1086.6	1058.6	1043.5
40°	1247.7	1134.0	1040.8	982.0	948.2	916.6	912.1
42.5°	1091.9	986.2	916.1	869.3	836.7	823.3	813.6
45°	894.4	820.5	773.4	740.1	718.4	710.1	699.0
47.5°	757.0	704.8	669.4	646.8	630.5	624.3	623.4
50°	680.2	636.9	610.8	593.0	580.3	578.1	569.2
52.5°	622.5	585.0	564.7	549.2	540.0	533.7	531.1
55°	540.4	515.4	497.1	488.2	481.0	474.9	474.9
57.5°	472.8	451.9	439.9	432.3	430.1	425.7	423.0
60°	431.0	413.4	403.9	397.2	392.8	393.4	388.3
62.5°	390.3	378.7	369.7	363.1	357.8	357.8	358.2
65°	332.3	323.4	316.8	314.5	311.3	307.4	308.5
67.5°	281.6	273.3	268.1	264.3	263.2	261.1	264.3
70°	245.2	239.1	235.2	231.9	230.8	231.4	234.2
72.5°	211.9	207.6	205.0	203.5	201.1	201.1	203.1
75°	166.4	163.1	160.9	159.2	158.7	158.7	158.7
77.5°	122.3	121.5	120.5	118.1	118.1	118.9	119.0
80°	96.5	94.9	94.3	93.2	91.6	90.4	93.2
82.5°	72.2	70.4	69.9	69.7	67.1	66.9	69.2
85°	38.8	37.2	37.7	37.2	37.2	36.6	36.6
87.5°	16.2	15.9	15.5	16.0	15.6	15.2	16.1
90°	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	13.9	14.5	14.9	15.1	15.2	15.3	15.4
95°	16.6	17.3	17.7	17.7	17.7	17.7	17.7
97.5°	17.4	18.3	18.8	18.8	18.9	19.1	19.2
100°	17.9	18.7	19.1	19.2	19.3	19.4	19.6
102.5°	22.9	20.4	19.2	19.3	19.6	19.7	19.9
105°	47.0	28.7	19.6	19.8	20.1	20.2	20.5
107.5°	146.4	133.0	119.4	105.6	91.8	78.0	64.2
110°	199.5	196.1	186.9	172.2	157.4	142.7	127.8



TEST NUMBER: P332009-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.3	233.4	231.9	228.8	225.6	222.5	219.4
115°	270.0	271.1	271.7	272.1	272.6	273.0	273.5
117.5°	302.1	303.0	303.5	303.5	303.6	303.7	303.8
120°	323.3	324.2	324.6	324.6	324.6	324.6	324.6
122.5°	343.8	344.4	344.7	344.8	344.9	345.0	345.0
125°	372.6	372.8	373.1	373.2	373.5	373.7	373.9
127.5°	402.0	402.4	402.4	402.2	402.0	401.8	401.6
130°	419.7	420.1	420.3	420.0	419.9	419.6	419.5
132.5°	436.5	436.9	437.0	436.7	436.3	436.1	435.8
135°	461.8	462.0	462.0	461.8	461.5	461.1	460.8
137.5°	484.5	485.0	485.2	484.9	484.8	484.5	484.4
140°	498.8	499.2	499.3	499.1	498.9	498.7	498.5
142.5°	512.3	512.7	512.7	512.4	512.1	511.8	511.5
145°	531.2	531.4	531.5	531.5	531.5	531.5	531.5
147.5°	548.2	548.5	548.3	547.8	547.3	546.9	546.4
150°	558.6	558.8	558.8	558.5	558.2	557.8	557.6
152.5°	568.0	568.4	568.3	567.9	567.4	567.0	566.5
155°	581.0	581.5	581.4	580.8	580.2	579.6	578.9
157.5°	592.2	592.8	592.6	591.8	591.1	590.3	589.5
160°	598.4	599.1	599.0	598.3	597.6	596.9	596.1
162.5°	604.3	605.0	605.0	604.4	603.7	603.1	602.5
165°	612.1	612.9	613.0	612.3	611.6	610.8	610.1
167.5°	618.1	618.9	618.9	618.1	617.3	616.4	615.6
170°	621.4	622.2	622.2	621.4	620.6	619.8	618.9
172.5°	623.6	624.4	624.4	623.5	622.6	621.7	620.8
175°	626.2	627.0	626.9	626.1	625.3	624.4	623.5
177.5°	627.1	627.8	627.7	626.9	626.1	625.3	624.4
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9

(END OF REPORT)