

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332015-930

Luminaire Tested: **S123DIP-S1000D585U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332015-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5268.5 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332015-930
CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	32	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	2.3
10°-20°	343.3	6.5
20°-30°	507.0	9.6
30°-40°	592.3	11.2
40°-50°	595.5	11.3
50°-60°	523.1	9.9
60°-70°	389.7	7.4
70°-80°	222.0	4.2
80°-90°	65.5	1.2
90°-100°	22.8	0.4
100°-110°	108.4	2.1
110°-120°	260.5	4.9
120°-130°	331.7	6.3
130°-140°	354.4	6.7
140°-150°	331.4	6.3
150°-160°	267.4	5.1
160°-170°	172.6	3.3
170°-180°	59.5	1.1
0°-30°	971.9	18.4
0°-40°	1564.1	29.7
0°-60°	2682.6	50.9
0°-90°	3359.8	63.8
90°-120°	391.7	7.4
90°-150°	1409.3	26.8
90°-180°	1909.0	36.2
0°-180°	5268.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	0	5	11	13	14	4
95°	28	11	14	18	18	35
105°	139	141	102	24	20	147
115°	260	263	267	271	274	257
125°	366	370	372	373	374	327
135°	456	459	461	462	461	351
145°	526	530	531	531	532	329
155°	580	579	579	581	579	267
165°	612	610	610	613	610	173
175°	626	624	624	627	624	60
180°	626	626	626	626	626	



TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	22.8	22.4	22.0	21.6	21.4	21.5	21.6	21.7	21.8	21.7
90°	0.5	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6
92.5°	8.6	8.4	8.1	7.7	7.5	7.8	8.9	9.9	10.9	11.9	12.6
95°	28.4	24.1	19.9	15.7	11.4	9.9	11.0	12.1	13.3	14.4	15.2
97.5°	57.0	55.1	53.2	51.3	49.4	44.8	37.3	29.8	22.4	15.0	15.8
100°	78.6	80.6	82.8	84.8	86.8	79.8	63.7	47.6	31.5	15.3	16.1
102.5°	103.1	104.6	106.2	107.6	109.1	101.0	83.4	65.8	48.2	30.6	28.0
105°	138.6	139.7	140.9	141.9	143.1	139.0	129.7	120.4	111.1	101.8	83.6
107.5°	175.9	176.8	177.8	178.7	179.6	180.8	182.2	183.7	185.2	186.6	173.3
110°	200.9	201.7	202.5	203.3	204.2	205.2	206.3	207.4	208.6	209.7	206.3



TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.4	226.2	226.9	227.6	228.6	229.8	230.9	232.0	233.2	233.3
115°	259.9	260.6	261.1	261.8	262.4	263.2	264.2	265.1	266.0	266.9	268.0
117.5°	294.1	294.8	295.6	296.4	297.1	297.7	298.2	298.7	299.2	299.6	300.5
120°	315.3	316.2	317.2	318.0	319.0	319.6	319.9	320.2	320.6	320.8	321.7
122.5°	336.9	337.6	338.3	339.2	339.9	340.5	340.9	341.3	341.7	342.1	342.7
125°	366.4	367.3	368.1	368.9	369.7	370.4	370.8	371.2	371.6	372.0	372.2
127.5°	395.1	395.9	396.7	397.5	398.4	399.0	399.5	400.1	400.6	401.0	401.4
130°	412.9	413.8	414.6	415.4	416.2	416.9	417.3	417.7	418.1	418.5	418.9
132.5°	430.1	430.9	431.7	432.5	433.3	433.9	434.2	434.6	434.9	435.3	435.7
135°	456.2	456.8	457.4	458.0	458.7	459.2	459.6	460.0	460.4	460.8	461.1
137.5°	478.5	479.3	480.0	480.9	481.6	482.2	482.3	482.6	482.8	483.1	483.6
140°	493.3	494.0	494.6	495.2	495.9	496.4	496.6	496.9	497.3	497.6	498.0
142.5°	507.1	507.8	508.4	509.0	509.6	510.1	510.4	510.7	511.0	511.4	511.7
145°	526.4	527.1	527.8	528.6	529.3	529.8	529.9	530.2	530.4	530.6	530.8
147.5°	544.5	545.0	545.5	545.9	546.4	546.7	547.0	547.1	547.4	547.6	547.8
150°	555.7	556.0	556.3	556.6	556.9	557.2	557.4	557.6	557.8	558.0	558.2
152.5°	565.7	565.9	566.0	566.1	566.3	566.5	566.6	566.7	566.8	567.0	567.3
155°	579.8	579.7	579.4	579.3	579.0	579.0	579.1	579.2	579.3	579.4	579.9
157.5°	590.8	590.8	590.8	590.8	590.8	590.7	590.6	590.5	590.4	590.3	590.9
160°	597.5	597.5	597.4	597.2	597.1	597.0	596.9	596.8	596.7	596.6	597.2
162.5°	603.9	603.6	603.3	603.1	602.8	602.6	602.5	602.4	602.3	602.2	602.9
165°	611.5	611.1	610.9	610.6	610.3	610.0	609.9	609.8	609.8	609.6	610.5
167.5°	617.4	617.0	616.6	616.2	615.8	615.6	615.6	615.6	615.6	615.6	616.4
170°	620.8	620.4	620.0	619.5	619.1	618.9	618.9	618.9	618.9	618.9	619.8
172.5°	623.1	622.6	622.0	621.5	621.0	620.9	620.9	621.0	621.1	621.2	622.0
175°	625.9	625.4	624.8	624.4	623.9	623.6	623.7	623.9	623.9	624.0	624.8
177.5°	626.6	626.2	625.8	625.4	625.0	624.8	624.9	625.0	625.1	625.2	625.8
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	21.5	21.4	21.3	21.3	21.3	21.4	21.4	21.4
90°	12.0	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	13.2	13.9	14.5	14.9	15.1	15.2	15.3	15.4
95°	15.9	16.6	17.3	17.7	17.7	17.7	17.7	17.7
97.5°	16.6	17.4	18.3	18.8	18.8	18.9	19.1	19.2
100°	17.0	17.9	18.7	19.1	19.2	19.3	19.4	19.6
102.5°	25.4	22.9	20.4	19.2	19.3	19.6	19.7	19.9
105°	65.2	47.0	28.7	19.6	19.8	20.1	20.2	20.5
107.5°	159.8	146.4	133.0	119.4	105.6	91.8	78.0	64.2
110°	202.9	199.5	196.1	186.9	172.2	157.4	142.7	127.8



TEST NUMBER: P332015-930

CATALOG NUMBER: S123DIP-S1000D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.3	233.3	233.4	231.9	228.8	225.6	222.5	219.4
115°	269.0	270.0	271.1	271.7	272.1	272.6	273.0	273.5
117.5°	301.3	302.1	303.0	303.5	303.5	303.6	303.7	303.8
120°	322.5	323.3	324.2	324.6	324.6	324.6	324.6	324.6
122.5°	343.2	343.8	344.4	344.7	344.8	344.9	345.0	345.0
125°	372.4	372.6	372.8	373.1	373.2	373.5	373.7	373.9
127.5°	401.7	402.0	402.4	402.4	402.2	402.0	401.8	401.6
130°	419.3	419.7	420.1	420.3	420.0	419.9	419.6	419.5
132.5°	436.1	436.5	436.9	437.0	436.7	436.3	436.1	435.8
135°	461.5	461.8	462.0	462.0	461.8	461.5	461.1	460.8
137.5°	484.0	484.5	485.0	485.2	484.9	484.8	484.5	484.4
140°	498.4	498.8	499.2	499.3	499.1	498.9	498.7	498.5
142.5°	512.0	512.3	512.7	512.7	512.4	512.1	511.8	511.5
145°	531.0	531.2	531.4	531.5	531.5	531.5	531.5	531.5
147.5°	548.0	548.2	548.5	548.3	547.8	547.3	546.9	546.4
150°	558.4	558.6	558.8	558.8	558.5	558.2	557.8	557.6
152.5°	567.7	568.0	568.4	568.3	567.9	567.4	567.0	566.5
155°	580.4	581.0	581.5	581.4	580.8	580.2	579.6	578.9
157.5°	591.5	592.2	592.8	592.6	591.8	591.1	590.3	589.5
160°	597.9	598.4	599.1	599.0	598.3	597.6	596.9	596.1
162.5°	603.6	604.3	605.0	605.0	604.4	603.7	603.1	602.5
165°	611.3	612.1	612.9	613.0	612.3	611.6	610.8	610.1
167.5°	617.3	618.1	618.9	618.9	618.1	617.3	616.4	615.6
170°	620.6	621.4	622.2	622.2	621.4	620.6	619.8	618.9
172.5°	622.8	623.6	624.4	624.4	623.5	622.6	621.7	620.8
175°	625.5	626.2	627.0	626.9	626.1	625.3	624.4	623.5
177.5°	626.5	627.1	627.8	627.7	626.9	626.1	625.3	624.4
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9

(END OF REPORT)