

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332026-930

Luminaire Tested: **S123DIP-S1000D805U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332026-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5729.5 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332026-930
CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	57	55	54	49
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41
3	83	73	66	60	77	68	62	56	60	55	50	52	48	44	44	41	39	35
4	76	65	57	50	70	61	53	48	53	47	43	46	42	38	39	36	33	30
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23
7	59	47	39	33	55	44	37	31	39	33	29	34	29	26	29	26	23	20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	2.1
10°-20°	343.3	6.0
20°-30°	507.0	8.8
30°-40°	592.3	10.3
40°-50°	595.5	10.4
50°-60°	523.1	9.1
60°-70°	389.7	6.8
70°-80°	222.0	3.9
80°-90°	66.2	1.2
90°-100°	175.2	3.1
100°-110°	496.2	8.7
110°-120°	488.1	8.5
120°-130°	389.3	6.8
130°-140°	307.0	5.4
140°-150°	229.1	4.0
150°-160°	159.7	2.8
160°-170°	93.8	1.6
170°-180°	30.5	0.5
0°-30°	971.9	17.0
0°-40°	1564.1	27.3
0°-60°	2682.6	46.8
0°-90°	3360.5	58.7
90°-120°	1159.6	20.2
90°-150°	2085.0	36.4
90°-180°	2369.0	41.3
0°-180°	5729.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	8	16	18	18	5
95°	22	70	378	110	74	23
105°	74	109	512	896	811	79
115°	131	163	392	860	986	129
125°	182	214	366	663	778	161
135°	213	254	361	546	630	164
145°	243	278	356	448	493	152
155°	276	298	345	392	408	127
165°	302	310	330	350	356	85
175°	314	315	317	321	321	30
180°	315	315	315	315	315	



TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.3	23.0	22.7	22.4	22.1	22.0	22.2	22.3	22.5	22.7	22.4
90°	1.3	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3
92.5°	7.9	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9
95°	21.7	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6
97.5°	36.9	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7
100°	47.2	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2
102.5°	57.9	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3
105°	73.9	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5
107.5°	91.0	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4
110°	103.3	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5



TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.5	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3
115°	130.7	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3
117.5°	146.8	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2
120°	158.1	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9
122.5°	167.8	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1
125°	181.6	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1
127.5°	192.2	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9
130°	198.9	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7
132.5°	204.0	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1
135°	212.9	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4
137.5°	221.3	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9
140°	226.9	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3
142.5°	233.0	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2
145°	242.9	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7
147.5°	252.8	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4
150°	259.4	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8
152.5°	266.0	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7
155°	276.0	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6
157.5°	283.9	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7
160°	290.0	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1
162.5°	294.6	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5
165°	301.5	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3
167.5°	306.7	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3
170°	309.8	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7
172.5°	311.9	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1
175°	314.2	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0
177.5°	315.4	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	22.3	22.3	22.2	22.3	22.2	22.3	22.5	22.3
90°	15.9	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	53.6	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	229.5	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	572.0	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	751.5	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	811.1	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	828.7	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	778.4	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	730.5	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332026-930

CATALOG NUMBER: S123DIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.1	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	620.2	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	574.7	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	550.7	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	531.9	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	506.7	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	484.9	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	471.1	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	458.3	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	441.1	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	425.4	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	416.2	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	407.6	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	397.1	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	388.6	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	382.5	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	376.8	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	368.4	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	359.5	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	354.4	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	348.3	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	340.4	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	333.5	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	328.9	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	324.8	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	319.4	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	315.9	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)