

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332006-935

Luminaire Tested: **S123DIP-S1000D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332006-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4796.3 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	103	99	94	91	98	94	90	87	85	82	79	77	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55	52
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41	38
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	21
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.7
10°-20°	362.5	7.6
20°-30°	535.5	11.2
30°-40°	625.5	13.0
40°-50°	628.8	13.1
50°-60°	552.4	11.5
60°-70°	411.5	8.6
70°-80°	234.5	4.9
80°-90°	68.4	1.4
90°-100°	14.9	0.3
100°-110°	71.0	1.5
110°-120°	170.4	3.6
120°-130°	217.0	4.5
130°-140°	231.9	4.8
140°-150°	216.9	4.5
150°-160°	174.9	3.6
160°-170°	112.9	2.4
170°-180°	38.9	0.8
0°-30°	1026.3	21.4
0°-40°	1651.8	34.4
0°-60°	2833.0	59.1
0°-90°	3547.4	74.0
90°-120°	256.3	5.3
90°-150°	922.1	19.2
90°-180°	1249.0	26.0
0°-180°	4796.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	0	3	7	8	9	4
95°	19	7	10	11	12	23
105°	91	92	67	16	13	96
115°	170	172	175	178	179	168
125°	240	242	243	244	245	214
135°	298	300	302	302	302	230
145°	344	346	347	348	348	216
155°	379	379	379	380	379	175
165°	400	399	399	401	399	113
175°	410	408	408	410	408	39
180°	410	410	410	410	410	



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	23.9	23.4	23.0	22.5	22.2	22.2	22.1	22.1	22.1	22.0
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	5.7	5.5	5.3	5.1	4.9	5.2	5.8	6.5	7.1	7.7	8.2
95°	18.6	15.8	13.0	10.2	7.5	6.5	7.2	7.9	8.7	9.5	9.9
97.5°	37.3	36.1	34.8	33.6	32.3	29.3	24.4	19.5	14.6	9.8	10.3
100°	51.4	52.8	54.2	55.4	56.8	52.3	41.7	31.2	20.6	10.1	10.6
102.5°	67.5	68.4	69.4	70.4	71.4	66.1	54.6	43.0	31.5	20.1	18.3
105°	90.7	91.4	92.1	92.9	93.7	91.0	84.9	78.8	72.8	66.6	54.7
107.5°	115.1	115.7	116.3	116.9	117.5	118.3	119.2	120.2	121.1	122.1	113.3
110°	131.5	132.0	132.5	133.0	133.6	134.2	135.0	135.7	136.5	137.2	135.0



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	147.5	148.0	148.4	149.0	149.6	150.3	151.1	151.8	152.6	152.6
115°	170.0	170.5	170.9	171.3	171.7	172.2	172.8	173.4	174.0	174.6	175.3
117.5°	192.4	193.0	193.4	193.9	194.4	194.8	195.1	195.4	195.8	196.0	196.6
120°	206.3	206.9	207.5	208.1	208.7	209.1	209.3	209.6	209.7	209.9	210.5
122.5°	220.4	220.9	221.4	221.9	222.4	222.7	223.0	223.3	223.5	223.8	224.2
125°	239.8	240.3	240.8	241.3	241.9	242.3	242.6	242.9	243.1	243.4	243.6
127.5°	258.5	259.1	259.6	260.1	260.6	261.1	261.4	261.7	262.1	262.3	262.6
130°	270.2	270.7	271.2	271.8	272.3	272.8	273.0	273.3	273.5	273.8	274.1
132.5°	281.4	281.9	282.5	283.0	283.5	283.9	284.1	284.4	284.6	284.8	285.1
135°	298.5	298.9	299.3	299.7	300.1	300.4	300.7	301.0	301.3	301.5	301.7
137.5°	313.1	313.6	314.1	314.6	315.1	315.5	315.6	315.7	315.9	316.1	316.4
140°	322.8	323.2	323.6	324.0	324.4	324.8	324.9	325.1	325.4	325.5	325.8
142.5°	331.8	332.3	332.6	333.0	333.5	333.7	334.0	334.2	334.3	334.6	334.8
145°	344.4	344.9	345.3	345.9	346.3	346.6	346.7	346.9	347.0	347.2	347.3
147.5°	356.3	356.6	356.9	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
150°	363.6	363.8	363.9	364.2	364.4	364.5	364.7	364.8	365.0	365.1	365.2
152.5°	370.1	370.2	370.3	370.4	370.5	370.7	370.7	370.7	370.8	370.9	371.2
155°	379.4	379.3	379.1	379.0	378.8	378.8	378.9	378.9	379.0	379.1	379.4
157.5°	386.6	386.6	386.6	386.5	386.5	386.5	386.4	386.3	386.2	386.2	386.6
160°	391.0	390.9	390.8	390.7	390.7	390.6	390.5	390.5	390.5	390.4	390.7
162.5°	395.1	394.9	394.8	394.6	394.4	394.3	394.2	394.2	394.1	394.0	394.4
165°	400.1	399.8	399.7	399.5	399.2	399.2	399.1	399.0	398.9	398.9	399.4
167.5°	404.0	403.7	403.5	403.2	402.9	402.8	402.8	402.8	402.8	402.8	403.3
170°	406.1	405.9	405.6	405.4	405.1	404.9	404.9	404.9	404.9	404.9	405.5
172.5°	407.6	407.3	407.0	406.7	406.3	406.2	406.2	406.3	406.4	406.4	407.0
175°	409.5	409.1	408.8	408.5	408.2	408.0	408.1	408.2	408.2	408.3	408.8
177.5°	410.0	409.7	409.5	409.2	408.9	408.8	408.9	408.9	409.0	409.1	409.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	21.8	21.6	21.4	21.4	21.4	21.4	21.5	21.5
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	8.7	9.1	9.6	9.8	9.8	9.9	10.0	10.1
95°	10.4	10.8	11.4	11.5	11.5	11.5	11.5	11.5
97.5°	10.8	11.5	12.0	12.2	12.3	12.4	12.5	12.6
100°	11.1	11.6	12.2	12.5	12.6	12.7	12.7	12.7
102.5°	16.7	15.0	13.3	12.6	12.7	12.7	12.9	13.0
105°	42.7	30.7	18.8	12.8	13.0	13.1	13.3	13.3
107.5°	104.6	95.8	87.0	78.1	69.1	60.1	51.1	42.0
110°	132.8	130.5	128.3	122.3	112.7	103.0	93.3	83.7



TEST NUMBER: P332006-935

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.7	152.7	152.7	151.7	149.6	147.7	145.6	143.5
115°	176.0	176.7	177.4	177.8	178.1	178.4	178.7	178.9
117.5°	197.2	197.7	198.2	198.5	198.5	198.6	198.7	198.7
120°	211.0	211.5	212.1	212.4	212.4	212.4	212.4	212.4
122.5°	224.5	225.0	225.3	225.5	225.6	225.7	225.7	225.8
125°	243.7	243.8	243.9	244.1	244.2	244.4	244.5	244.6
127.5°	262.8	263.0	263.3	263.3	263.1	263.0	262.9	262.8
130°	274.4	274.7	274.9	275.0	274.8	274.7	274.6	274.4
132.5°	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.2
135°	302.0	302.1	302.3	302.3	302.1	302.0	301.7	301.5
137.5°	316.7	317.0	317.4	317.5	317.3	317.2	317.0	316.9
140°	326.1	326.3	326.7	326.7	326.6	326.4	326.3	326.1
142.5°	335.0	335.2	335.4	335.4	335.3	335.0	334.8	334.7
145°	347.4	347.6	347.7	347.8	347.8	347.8	347.8	347.8
147.5°	358.5	358.7	358.9	358.8	358.4	358.1	357.8	357.5
150°	365.4	365.5	365.7	365.6	365.4	365.2	365.0	364.8
152.5°	371.4	371.7	372.0	371.9	371.6	371.3	370.9	370.7
155°	379.8	380.1	380.5	380.4	380.0	379.6	379.2	378.8
157.5°	387.0	387.4	387.9	387.8	387.3	386.8	386.2	385.6
160°	391.2	391.6	392.0	391.9	391.5	391.0	390.5	390.0
162.5°	394.9	395.4	395.8	395.9	395.5	395.0	394.6	394.2
165°	399.9	400.5	401.1	401.1	400.6	400.1	399.7	399.2
167.5°	403.8	404.4	404.9	404.9	404.4	403.8	403.3	402.8
170°	406.0	406.6	407.1	407.1	406.6	406.0	405.5	404.9
172.5°	407.5	408.0	408.5	408.5	407.9	407.3	406.7	406.1
175°	409.2	409.7	410.2	410.2	409.7	409.1	408.5	408.0
177.5°	409.9	410.4	410.8	410.7	410.2	409.7	409.1	408.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5

(END OF REPORT)