

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831117

Luminaire Tested: S123DIP-S1000D365U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831117  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U935-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5218.6 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	80	80	80	76	
1	104	100	96	93	99	96	92	89	87	85	82	79	77	75	72	71	69	69	69	69	66	
2	96	89	83	77	91	85	79	75	77	73	69	71	67	64	64	62	60	60	60	60	56	
3	88	79	72	66	84	75	69	64	69	64	60	63	59	56	58	55	52	52	52	52	49	
4	81	71	63	57	77	68	61	55	62	56	52	57	53	49	53	49	46	46	46	46	43	
5	75	64	56	50	71	61	54	48	56	50	46	52	47	43	48	44	41	41	41	41	38	
6	70	58	50	44	66	56	48	43	51	45	41	48	42	39	44	40	36	36	36	36	34	
7	65	53	45	39	62	51	44	38	47	41	37	44	39	35	41	36	33	33	33	33	31	
8	61	48	41	35	58	47	40	35	44	37	33	41	35	32	38	33	30	30	30	30	28	
9	57	45	37	32	54	43	36	32	40	34	30	38	33	29	35	31	28	28	28	28	26	
10	54	42	34	30	51	40	33	29	38	32	28	35	30	27	33	29	25	25	25	25	24	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	26579	26579	26579	26579	26579
5°	33613	31726	26817	21610	19859
10°	33940	34967	26639	17227	15054
15°	25563	32465	26457	14588	12730
20°	17811	26270	26119	12757	11564
25°	13581	20202	25543	11738	10846
30°	11749	16051	24623	11016	10268
35°	10901	13550	23563	10494	9862
40°	10321	12156	22073	9999	9725
45°	9977	11251	20180	9611	9663
50°	9805	10535	17941	9259	9614
55°	9439	10010	15739	8923	9655
60°	9102	9449	13567	8609	9496
65°	8550	8917	11703	8273	9309
70°	7896	8239	9951	7717	8762
75°	7149	7386	8530	7170	8006
80°	5895	6465	6750	6248	6750
85°	4668	5236	4952	5311	5372

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 23041 cd/sqm



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.4	4.5
10°-20°	580.8	11.1
20°-30°	687.6	13.2
30°-40°	691.4	13.2
40°-50°	634.3	12.2
50°-60°	523.6	10.0
60°-70°	370.4	7.1
70°-80°	197.7	3.8
80°-90°	51.0	1.0
90°-100°	14.4	0.3
100°-110°	69.8	1.3
110°-120°	171.1	3.3
120°-130°	217.2	4.2
130°-140°	232.0	4.4
140°-150°	217.0	4.2
150°-160°	175.0	3.4
160°-170°	112.9	2.2
170°-180°	38.9	0.7
0°-30°	1501.8	28.8
0°-40°	2193.3	42.0
0°-60°	3351.2	64.2
0°-90°	3970.2	76.1
90°-120°	255.3	4.9
90°-150°	921.5	17.7
90°-180°	1248.0	23.9
0°-180°	5218.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2469	2469	2469	2469	2469	
5°	3111	2936	2482	2000	1838	296
15°	2294	2913	2374	1309	1142	634
25°	1144	1701	2151	988	913	540
35°	830	1031	1793	799	750	521
45°	655	739	1326	631	635	508
55°	503	533	839	476	514	450
65°	336	350	460	325	366	334
75°	172	178	205	172	192	181
85°	38	42	40	43	44	42
90°	9	7	0	7	9	6
95°	12	9	19	9	12	10
105°	13	67	91	67	13	28
115°	179	175	170	175	179	168
125°	245	243	240	243	245	219
135°	302	302	298	302	302	233
145°	348	347	344	347	348	217
155°	379	379	379	379	379	175
165°	399	399	400	399	399	113
175°	408	408	410	408	408	39
180°	410	410	410	410	410	



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2783.2	2780.4	2777.5	2763.2	2748.8	2742.0	2735.1	2714.5	2693.8	2670.9	2648.0
5°	3110.9	3119.0	3127.0	3117.8	3108.6	3080.6	3052.5	3015.3	2978.0	2936.2	2894.4
7.5°	3262.2	3266.8	3271.3	3265.6	3259.9	3252.4	3245.0	3211.8	3178.5	3135.6	3092.6
10°	3105.2	3115.5	3125.8	3148.2	3170.5	3195.7	3220.9	3216.3	3211.8	3199.2	3186.6
12.5°	2760.3	2772.9	2785.5	2830.2	2874.9	2932.2	2989.5	3038.7	3088.0	3122.4	3156.8
15°	2294.0	2328.9	2363.8	2404.5	2445.2	2529.4	2613.6	2717.3	2821.0	2913.3	3005.5
17.5°	1889.5	1902.7	1915.8	1959.4	2002.9	2108.9	2214.9	2334.6	2454.4	2607.3	2760.3
20°	1554.9	1566.9	1579.0	1636.2	1693.5	1776.6	1859.7	1994.3	2129.0	2293.4	2457.8
22.5°	1306.2	1325.2	1344.1	1376.1	1408.2	1487.9	1567.5	1687.2	1807.0	1988.6	2170.2
25°	1143.5	1157.3	1171.0	1190.5	1210.0	1273.6	1337.2	1435.7	1534.3	1701.0	1867.7
27.5°	1032.4	1038.1	1043.9	1063.3	1082.8	1124.1	1165.3	1250.1	1334.9	1476.4	1617.9
30°	945.3	949.3	953.3	970.5	987.7	1015.8	1043.9	1105.2	1166.5	1291.4	1416.2
32.5°	884.6	887.4	890.3	903.5	916.7	936.7	956.8	1001.5	1046.1	1149.3	1252.4
35°	829.6	831.3	833.0	842.8	852.5	867.4	882.3	916.1	949.9	1031.2	1112.6
37.5°	781.5	783.7	786.0	791.8	797.5	810.7	823.9	850.8	877.7	940.2	1002.6
40°	734.5	738.5	742.5	746.5	750.5	761.4	772.3	792.9	813.5	865.1	916.7
42.5°	694.4	698.4	702.4	704.1	705.8	712.1	718.4	737.3	756.2	794.6	833.0
45°	655.4	657.1	658.9	660.6	662.3	667.4	672.6	689.2	705.8	739.1	772.3
47.5°	619.9	619.9	619.9	621.0	622.2	626.8	631.4	643.4	655.4	681.2	707.0
50°	585.5	585.5	585.5	583.8	582.1	584.9	587.8	597.0	606.1	629.1	652.0
52.5°	544.3	544.3	544.3	544.8	545.4	545.4	545.4	553.4	561.5	582.1	602.7
55°	503.0	505.3	507.6	505.9	504.2	505.3	506.5	511.6	516.8	533.4	550.0
57.5°	461.8	462.9	464.1	463.5	462.9	463.5	464.1	468.6	473.2	485.8	498.4
60°	422.8	422.8	422.8	421.7	420.5	421.7	422.8	425.1	427.4	438.9	450.3
62.5°	379.3	379.8	380.4	381.0	381.6	380.4	379.3	382.1	385.0	393.6	402.2
65°	335.7	336.3	336.9	338.6	340.3	339.2	338.0	340.9	343.7	350.1	356.4
67.5°	296.8	295.6	294.5	295.1	295.6	297.3	299.1	299.6	300.2	307.1	314.0
70°	250.9	252.1	253.2	252.7	252.1	252.7	253.2	254.9	256.7	261.8	267.0
72.5°	209.7	210.3	210.8	210.8	210.8	212.0	213.1	214.8	216.6	219.4	222.3
75°	171.9	171.9	171.9	173.0	174.2	174.7	175.3	175.3	175.3	177.6	179.9
77.5°	130.6	133.5	136.4	135.8	135.2	136.4	137.5	139.2	140.9	142.1	143.2
80°	95.1	95.1	95.1	95.7	96.2	98.0	99.7	100.8	102.0	104.3	106.6
82.5°	60.7	61.3	61.9	63.6	65.3	66.5	67.6	69.3	71.0	71.0	71.0
85°	37.8	36.7	35.5	36.7	37.8	39.0	40.1	40.7	41.2	42.4	43.5
87.5°	18.3	18.3	18.3	18.3	18.3	18.9	19.5	19.5	19.5	19.5	19.5
90°	9.1	9.0	8.9	8.7	8.6	8.4	8.1	7.8	7.6	7.3	6.4
92.5°	10.3	10.3	10.2	10.1	10.1	9.8	9.3	8.9	8.4	7.9	7.3
95°	11.6	11.6	11.6	11.6	11.6	11.3	10.9	10.4	9.9	9.4	8.7
97.5°	12.5	12.4	12.3	12.3	12.2	11.9	11.4	10.8	10.3	9.7	13.2
100°	12.8	12.7	12.6	12.6	12.5	12.2	11.7	11.1	10.6	10.0	20.6
102.5°	13.1	12.9	12.8	12.7	12.5	13.6	15.8	18.1	20.3	22.5	34.3
105°	13.4	13.3	13.1	13.0	12.8	18.8	30.7	42.7	54.7	66.6	72.7
107.5°	31.6	40.5	49.4	58.2	67.1	76.7	87.1	97.5	107.9	118.4	117.3
110°	83.7	93.3	103.0	112.7	122.3	128.3	130.5	132.8	135.0	137.2	136.5



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	158.5	158.6	158.8	158.9	159.1	158.8	158.2	157.6	157.0	156.4	155.6
115°	178.9	178.6	178.4	178.1	177.8	177.3	176.7	176.0	175.3	174.6	174.0
117.5°	195.3	195.3	195.2	195.1	195.1	194.8	194.2	193.7	193.1	192.6	192.3
120°	212.4	212.4	212.4	212.4	212.4	212.1	211.6	211.0	210.5	209.9	209.7
122.5°	229.1	229.0	229.0	228.9	228.8	228.6	228.3	228.0	227.6	227.3	227.0
125°	244.6	244.5	244.3	244.2	244.1	243.9	243.8	243.7	243.5	243.4	243.1
127.5°	259.8	260.0	260.1	260.2	260.4	260.3	260.1	259.9	259.7	259.5	259.2
130°	274.4	274.6	274.7	274.8	275.0	274.9	274.6	274.4	274.1	273.8	273.6
132.5°	287.8	288.0	288.2	288.4	288.6	288.6	288.3	288.1	287.8	287.5	287.3
135°	301.5	301.7	301.9	302.1	302.3	302.3	302.1	301.9	301.7	301.5	301.2
137.5°	314.6	314.7	314.9	315.0	315.1	315.0	314.7	314.4	314.0	313.7	313.5
140°	326.2	326.3	326.4	326.6	326.7	326.6	326.4	326.1	325.8	325.5	325.3
142.5°	336.8	337.0	337.2	337.4	337.6	337.6	337.4	337.2	337.0	336.8	336.6
145°	347.8	347.8	347.8	347.8	347.8	347.7	347.6	347.4	347.3	347.1	347.0
147.5°	355.7	356.0	356.3	356.7	357.0	357.1	357.0	356.9	356.7	356.6	356.4
150°	364.8	365.0	365.2	365.4	365.6	365.6	365.5	365.4	365.2	365.1	365.0
152.5°	372.1	372.4	372.8	373.1	373.5	373.5	373.2	372.9	372.7	372.4	372.3
155°	378.8	379.2	379.6	380.0	380.4	380.4	380.1	379.8	379.4	379.1	379.0
157.5°	384.6	385.1	385.7	386.2	386.7	386.8	386.4	386.0	385.6	385.2	385.2
160°	390.0	390.5	391.0	391.5	391.9	392.0	391.6	391.2	390.8	390.4	390.4
162.5°	395.2	395.6	396.0	396.4	396.8	396.8	396.3	395.9	395.4	394.9	395.0
165°	399.2	399.6	400.1	400.6	401.1	401.0	400.5	400.0	399.4	398.9	398.9
167.5°	402.2	402.8	403.3	403.8	404.4	404.4	403.8	403.3	402.8	402.2	402.2
170°	405.0	405.5	406.0	406.6	407.1	407.1	406.6	406.0	405.5	405.0	405.0
172.5°	406.5	407.1	407.7	408.3	408.9	408.9	408.4	407.9	407.3	406.8	406.7
175°	408.0	408.5	409.1	409.6	410.2	410.2	409.7	409.3	408.8	408.3	408.2
177.5°	408.3	409.0	409.7	410.3	411.0	411.1	410.5	410.0	409.5	408.9	408.8
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2641.1	2634.3	2609.1	2583.8	2555.2	2526.6	2505.4	2484.2	2452.7	2421.1	2395.4
5°	2862.3	2830.2	2776.9	2723.6	2651.5	2579.3	2530.6	2481.9	2416.6	2351.2	2299.1
7.5°	3037.6	2982.6	2908.1	2833.6	2739.1	2644.6	2555.2	2465.8	2366.1	2266.5	2185.1
10°	3149.3	3112.1	3026.1	2940.2	2813.6	2687.0	2562.1	2437.2	2308.8	2180.5	2072.8
12.5°	3160.2	3163.6	3084.6	3005.5	2862.3	2719.1	2567.2	2415.4	2253.8	2092.3	1966.8
15°	3064.5	3123.5	3080.0	3036.5	2892.1	2747.7	2560.9	2374.2	2188.0	2001.8	1856.8
17.5°	2886.9	3013.5	3019.8	3026.1	2881.8	2737.4	2530.6	2323.7	2112.9	1902.1	1749.7
20°	2644.6	2831.3	2895.5	2959.7	2842.2	2724.8	2502.5	2280.2	2044.2	1808.1	1648.3
22.5°	2397.1	2624.0	2741.4	2858.8	2771.8	2684.7	2448.1	2211.5	1962.2	1713.0	1550.9
25°	2115.2	2362.7	2543.2	2723.6	2670.4	2617.1	2383.9	2150.7	1885.5	1620.2	1454.6
27.5°	1869.4	2120.9	2338.6	2556.3	2544.9	2533.4	2302.0	2070.5	1799.0	1527.4	1367.5
30°	1650.6	1884.9	2128.4	2371.9	2399.9	2428.0	2204.6	1981.1	1709.0	1436.9	1282.8
32.5°	1456.9	1661.5	1922.7	2184.0	2239.0	2294.0	2092.3	1890.6	1621.4	1352.1	1203.7
35°	1298.2	1483.9	1745.1	2006.3	2075.1	2143.8	1968.5	1793.2	1530.8	1268.4	1126.9
37.5°	1157.9	1313.1	1568.1	1823.0	1907.2	1991.5	1834.5	1677.5	1431.7	1185.9	1055.9
40°	1041.6	1166.5	1400.8	1635.1	1732.5	1829.9	1700.4	1570.9	1337.8	1104.6	984.8
42.5°	944.2	1055.3	1267.9	1480.4	1573.8	1667.2	1557.8	1448.3	1240.9	1033.5	924.1
45°	861.1	949.9	1143.0	1336.0	1424.8	1513.6	1419.7	1325.7	1143.0	960.2	858.2
47.5°	783.2	859.4	1024.4	1189.4	1268.4	1347.5	1274.2	1200.8	1046.1	891.5	799.2
50°	713.3	774.6	919.0	1063.3	1132.1	1200.8	1136.1	1071.4	944.2	817.0	736.8
52.5°	652.6	702.4	823.3	944.2	1003.2	1062.2	1006.6	951.0	850.2	749.4	679.5
55°	592.4	634.8	739.6	844.5	884.6	924.7	881.7	838.7	757.4	676.0	617.0
57.5°	536.2	574.1	660.0	745.9	776.9	807.8	768.9	729.9	668.6	607.3	558.0
60°	481.2	512.2	583.8	655.4	674.3	693.2	661.7	630.2	587.2	544.3	500.2
62.5°	430.3	458.3	511.6	564.9	577.5	590.1	566.0	542.0	509.3	476.7	442.3
65°	377.6	398.7	442.3	485.8	493.9	501.9	480.7	459.5	434.8	410.2	385.0
67.5°	328.9	343.7	379.3	414.8	415.4	415.9	398.7	381.6	367.8	354.1	334.0
70°	281.3	295.6	319.1	342.6	343.2	343.7	330.0	316.2	305.9	295.6	280.7
72.5°	232.6	242.9	260.7	278.4	277.3	276.1	267.6	259.0	250.9	242.9	232.0
75°	188.5	197.1	209.1	221.1	217.7	214.3	209.7	205.1	198.2	191.4	184.5
77.5°	148.4	153.5	160.4	167.3	165.0	162.7	158.7	154.7	149.5	144.4	141.5
80°	108.9	111.1	115.7	120.3	119.2	118.0	113.4	108.9	107.7	106.6	102.6
82.5°	73.9	76.8	77.9	79.1	78.5	77.9	74.5	71.0	69.9	68.7	68.2
85°	44.1	44.7	45.3	45.8	44.1	42.4	41.2	40.1	40.1	40.1	39.5
87.5°	20.1	20.6	20.6	20.6	20.1	19.5	18.3	17.2	17.8	18.3	18.3
90°	5.5	4.7	3.8	3.0	2.3	1.7	1.0	0.3	1.0	1.7	2.3
92.5°	6.7	6.1	5.5	5.4	5.8	6.2	6.6	7.0	6.6	6.2	5.8
95°	7.9	7.2	6.5	7.5	10.2	13.0	15.8	18.6	15.8	13.0	10.2
97.5°	16.6	20.1	23.5	26.2	28.1	30.0	31.9	33.8	31.9	30.0	28.1
100°	31.1	41.7	52.2	56.8	55.5	54.1	52.8	51.4	52.8	54.1	55.5
102.5°	46.0	57.8	69.6	75.0	74.1	73.3	72.4	71.5	72.4	73.3	74.1
105°	78.8	84.9	91.0	93.6	92.9	92.2	91.4	90.7	91.4	92.2	92.9
107.5°	116.3	115.3	114.3	113.5	112.9	112.3	111.7	111.1	111.7	112.3	112.9
110°	135.7	135.0	134.2	133.6	133.1	132.5	132.0	131.4	132.0	132.5	133.1





TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.9	154.2	153.4	152.8	152.3	151.9	151.4	150.9	151.4	151.9	152.3
115°	173.4	172.8	172.2	171.7	171.3	170.9	170.5	170.1	170.5	170.9	171.3
117.5°	191.9	191.6	191.2	190.8	190.4	189.9	189.4	188.9	189.4	189.9	190.4
120°	209.5	209.3	209.1	208.7	208.1	207.5	206.9	206.3	206.9	207.5	208.1
122.5°	226.7	226.5	226.2	225.8	225.3	224.9	224.4	223.9	224.4	224.9	225.3
125°	242.9	242.6	242.3	241.9	241.4	240.8	240.3	239.7	240.3	240.8	241.4
127.5°	258.8	258.5	258.2	257.7	257.2	256.7	256.1	255.6	256.1	256.7	257.2
130°	273.3	273.0	272.7	272.3	271.8	271.3	270.7	270.2	270.7	271.3	271.8
132.5°	287.1	286.9	286.7	286.3	285.8	285.3	284.7	284.2	284.7	285.3	285.8
135°	301.0	300.7	300.4	300.1	299.7	299.3	298.9	298.5	298.9	299.3	299.7
137.5°	313.4	313.3	313.1	312.8	312.3	311.7	311.2	310.6	311.2	311.7	312.3
140°	325.1	324.9	324.7	324.4	324.0	323.6	323.2	322.8	323.2	323.6	324.0
142.5°	336.4	336.2	336.0	335.7	335.3	334.9	334.5	334.1	334.5	334.9	335.3
145°	346.9	346.7	346.6	346.3	345.8	345.4	344.9	344.4	344.9	345.4	345.8
147.5°	356.3	356.2	356.0	355.8	355.5	355.1	354.8	354.5	354.8	355.1	355.5
150°	364.8	364.7	364.6	364.4	364.2	364.0	363.8	363.6	363.8	364.0	364.2
152.5°	372.3	372.2	372.1	372.1	372.0	371.9	371.9	371.8	371.9	371.9	372.0
155°	379.0	378.9	378.8	378.9	379.0	379.1	379.3	379.4	379.3	379.1	379.0
157.5°	385.3	385.4	385.5	385.5	385.5	385.5	385.5	385.5	385.5	385.5	385.5
160°	390.5	390.6	390.6	390.7	390.8	390.8	390.9	391.0	390.9	390.8	390.8
162.5°	395.1	395.1	395.2	395.3	395.5	395.7	395.9	396.1	395.9	395.7	395.5
165°	399.0	399.1	399.1	399.3	399.5	399.7	399.9	400.1	399.9	399.7	399.5
167.5°	402.2	402.2	402.2	402.4	402.6	402.9	403.2	403.4	403.2	402.9	402.6
170°	405.0	405.0	405.0	405.1	405.4	405.6	405.9	406.2	405.9	405.6	405.4
172.5°	406.6	406.6	406.5	406.6	407.0	407.3	407.7	408.0	407.7	407.3	407.0
175°	408.2	408.1	408.0	408.2	408.5	408.8	409.2	409.5	409.2	408.8	408.5
177.5°	408.8	408.7	408.6	408.8	409.1	409.5	409.8	410.1	409.8	409.5	409.1
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3	2469.3
2.5°	2369.6	2347.2	2324.9	2307.7	2290.5	2261.3	2232.1	2225.2	2218.3	2208.6	2198.8
5°	2247.0	2192.0	2137.0	2087.7	2038.4	2000.0	1961.7	1936.5	1911.2	1892.9	1874.6
7.5°	2103.7	2021.2	1938.7	1880.3	1821.9	1766.3	1710.7	1693.0	1675.2	1651.1	1627.1
10°	1965.1	1874.0	1782.9	1706.7	1630.5	1576.1	1521.7	1499.9	1478.1	1447.8	1417.4
12.5°	1841.4	1741.7	1642.0	1565.2	1488.4	1435.7	1383.0	1351.5	1320.0	1302.8	1285.6
15°	1711.9	1605.3	1498.7	1427.7	1356.7	1309.1	1261.6	1234.1	1206.6	1189.9	1173.3
17.5°	1597.3	1491.9	1386.5	1318.3	1250.1	1206.6	1163.0	1139.0	1114.9	1102.3	1089.7
20°	1488.4	1385.3	1282.2	1215.7	1149.3	1113.7	1078.2	1062.8	1047.3	1037.0	1026.7
22.5°	1388.7	1287.3	1185.9	1129.2	1072.5	1043.9	1015.2	1004.3	993.4	984.8	976.2
25°	1289.1	1198.5	1108.0	1059.9	1011.8	988.3	964.8	953.9	943.0	934.4	925.8
27.5°	1207.7	1121.2	1034.7	993.4	952.2	933.9	915.5	906.9	898.3	890.3	882.3
30°	1128.6	1051.3	974.0	938.4	902.9	886.3	869.7	861.1	852.5	845.1	837.6
32.5°	1055.3	988.9	922.4	889.7	857.1	843.3	829.6	819.3	809.0	803.2	797.5
35°	985.4	925.8	866.2	839.3	812.4	798.6	784.9	776.3	767.7	763.1	758.5
37.5°	925.8	872.6	819.3	793.5	767.7	754.5	741.4	733.9	726.5	724.7	723.0
40°	865.1	819.3	773.4	748.2	723.0	711.6	700.1	695.5	690.9	689.8	688.6
42.5°	814.7	770.0	725.3	702.4	679.5	669.7	660.0	657.7	655.4	657.1	658.9
45°	756.2	719.0	681.8	660.6	639.4	631.4	623.3	621.6	619.9	623.3	626.8
47.5°	707.0	672.6	638.2	618.2	598.1	592.4	586.7	586.1	585.5	590.1	594.7
50°	656.6	623.3	590.1	574.1	558.0	552.9	547.7	549.4	551.1	558.6	566.0
52.5°	609.6	578.6	547.7	532.8	517.9	514.5	511.0	515.1	519.1	527.1	535.1
55°	558.0	529.9	501.9	490.4	479.0	475.5	472.1	480.1	488.1	495.6	503.0
57.5°	508.7	484.1	459.5	449.2	438.9	438.3	437.7	445.2	452.6	460.6	468.6
60°	456.0	435.4	414.8	406.8	398.7	399.9	401.0	409.6	418.2	424.5	430.8
62.5°	407.9	390.7	373.5	366.1	358.6	361.5	364.4	373.0	381.6	389.0	396.5
65°	359.8	345.5	331.1	326.0	320.8	324.8	328.9	336.3	343.7	348.9	354.1
67.5°	314.0	301.9	289.9	285.9	281.9	285.9	289.9	297.3	304.8	309.9	315.1
70°	265.8	256.1	246.4	243.5	240.6	245.2	249.8	256.1	262.4	267.6	272.7
72.5°	221.1	213.7	206.2	205.7	205.1	209.1	213.1	219.4	225.7	229.2	232.6
75°	177.6	173.6	169.6	169.0	168.4	172.4	176.5	179.9	183.3	186.2	189.1
77.5°	138.6	135.2	131.8	132.3	132.9	135.8	138.6	142.1	145.5	147.2	149.0
80°	98.5	97.4	96.2	97.4	98.5	100.8	103.1	105.4	107.7	108.9	110.0
82.5°	67.6	66.5	65.3	67.0	68.7	70.5	72.2	73.9	75.6	76.2	76.8
85°	39.0	40.7	42.4	42.4	42.4	43.0	43.5	44.1	44.7	44.1	43.5
87.5°	18.3	18.9	19.5	19.5	19.5	20.1	20.6	20.6	20.6	20.1	19.5
90°	3.0	3.8	4.7	5.5	6.4	7.3	7.6	7.8	8.1	8.4	8.6
92.5°	5.4	5.5	6.1	6.7	7.3	7.9	8.4	8.9	9.3	9.8	10.1
95°	7.5	6.5	7.2	7.9	8.7	9.4	9.9	10.4	10.9	11.3	11.6
97.5°	26.2	23.5	20.1	16.6	13.2	9.7	10.3	10.8	11.4	11.9	12.2
100°	56.8	52.2	41.7	31.1	20.6	10.0	10.6	11.1	11.7	12.2	12.5
102.5°	75.0	69.6	57.8	46.0	34.3	22.5	20.3	18.1	15.8	13.6	12.5
105°	93.6	91.0	84.9	78.8	72.7	66.6	54.7	42.7	30.7	18.8	12.8
107.5°	113.5	114.3	115.3	116.3	117.3	118.4	107.9	97.5	87.1	76.7	67.1
110°	133.6	134.2	135.0	135.7	136.5	137.2	135.0	132.8	130.5	128.3	122.3

TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	152.8	153.4	154.2	154.9	155.6	156.4	157.0	157.6	158.2	158.8	159.1
115°	171.7	172.2	172.8	173.4	174.0	174.6	175.3	176.0	176.7	177.3	177.8
117.5°	190.8	191.2	191.6	191.9	192.3	192.6	193.1	193.7	194.2	194.8	195.1
120°	208.7	209.1	209.3	209.5	209.7	209.9	210.5	211.0	211.6	212.1	212.4
122.5°	225.8	226.2	226.5	226.7	227.0	227.3	227.6	228.0	228.3	228.6	228.8
125°	241.9	242.3	242.6	242.9	243.1	243.4	243.5	243.7	243.8	243.9	244.1
127.5°	257.7	258.2	258.5	258.8	259.2	259.5	259.7	259.9	260.1	260.3	260.4
130°	272.3	272.7	273.0	273.3	273.6	273.8	274.1	274.4	274.6	274.9	275.0
132.5°	286.3	286.7	286.9	287.1	287.3	287.5	287.8	288.1	288.3	288.6	288.6
135°	300.1	300.4	300.7	301.0	301.2	301.5	301.7	301.9	302.1	302.3	302.3
137.5°	312.8	313.1	313.3	313.4	313.5	313.7	314.0	314.4	314.7	315.0	315.1
140°	324.4	324.7	324.9	325.1	325.3	325.5	325.8	326.1	326.4	326.6	326.7
142.5°	335.7	336.0	336.2	336.4	336.6	336.8	337.0	337.2	337.4	337.6	337.6
145°	346.3	346.6	346.7	346.9	347.0	347.1	347.3	347.4	347.6	347.7	347.8
147.5°	355.8	356.0	356.2	356.3	356.4	356.6	356.7	356.9	357.0	357.1	357.0
150°	364.4	364.6	364.7	364.8	365.0	365.1	365.2	365.4	365.5	365.6	365.6
152.5°	372.1	372.1	372.2	372.3	372.3	372.4	372.7	372.9	373.2	373.5	373.5
155°	378.9	378.8	378.9	379.0	379.0	379.1	379.4	379.8	380.1	380.4	380.4
157.5°	385.5	385.5	385.4	385.3	385.2	385.2	385.6	386.0	386.4	386.8	386.7
160°	390.7	390.6	390.6	390.5	390.4	390.4	390.8	391.2	391.6	392.0	391.9
162.5°	395.3	395.2	395.1	395.1	395.0	394.9	395.4	395.9	396.3	396.8	396.8
165°	399.3	399.1	399.1	399.0	398.9	398.9	399.4	400.0	400.5	401.0	401.1
167.5°	402.4	402.2	402.2	402.2	402.2	402.2	402.8	403.3	403.8	404.4	404.4
170°	405.1	405.0	405.0	405.0	405.0	405.0	405.5	406.0	406.6	407.1	407.1
172.5°	406.6	406.5	406.6	406.6	406.7	406.8	407.3	407.9	408.4	408.9	408.9
175°	408.2	408.0	408.1	408.2	408.2	408.3	408.8	409.3	409.7	410.2	410.2
177.5°	408.8	408.6	408.7	408.8	408.8	408.9	409.5	410.0	410.5	411.1	411.0
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2469.3	2469.3	2469.3	2469.3
2.5°	2194.8	2190.8	2174.8	2158.7
5°	1860.8	1847.1	1842.5	1837.9
7.5°	1625.9	1624.8	1600.7	1576.7
10°	1419.1	1420.8	1399.1	1377.3
12.5°	1271.3	1257.0	1255.3	1253.5
15°	1160.2	1147.0	1144.7	1142.4
17.5°	1081.7	1073.6	1071.4	1069.1
20°	1022.1	1017.5	1013.5	1009.5
22.5°	970.5	964.8	961.4	957.9
25°	920.7	915.5	914.4	913.2
27.5°	876.0	869.7	869.7	869.7
30°	833.6	829.6	827.9	826.1
32.5°	794.1	790.6	790.6	790.6
35°	756.8	755.1	752.8	750.5
37.5°	723.0	723.0	721.9	720.7
40°	690.4	692.1	692.1	692.1
42.5°	660.6	662.3	662.3	662.3
45°	629.6	632.5	633.6	634.8
47.5°	599.3	603.9	605.0	606.1
50°	569.5	572.9	573.5	574.1
52.5°	539.1	543.1	546.0	548.9
55°	507.0	511.0	512.8	514.5
57.5°	472.7	476.7	477.2	477.8
60°	434.8	438.9	440.0	441.1
62.5°	398.7	401.0	402.2	403.3
65°	357.5	360.9	363.2	365.5
67.5°	318.0	320.8	320.8	320.8
70°	273.9	275.0	276.7	278.4
72.5°	233.2	233.7	233.7	233.7
75°	190.2	191.4	191.9	192.5
77.5°	149.5	150.1	150.1	150.1
80°	109.4	108.9	108.9	108.9
82.5°	75.1	73.3	73.3	73.3
85°	43.0	42.4	43.0	43.5
87.5°	19.5	19.5	19.5	19.5
90°	8.7	8.9	9.0	9.1
92.5°	10.1	10.2	10.3	10.3
95°	11.6	11.6	11.6	11.6
97.5°	12.3	12.3	12.4	12.5
100°	12.6	12.6	12.7	12.8
102.5°	12.7	12.8	12.9	13.1
105°	13.0	13.1	13.3	13.4
107.5°	58.2	49.4	40.5	31.6
110°	112.7	103.0	93.3	83.7



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	158.9	158.8	158.6	158.5
115°	178.1	178.4	178.6	178.9
117.5°	195.1	195.2	195.3	195.3
120°	212.4	212.4	212.4	212.4
122.5°	228.9	229.0	229.0	229.1
125°	244.2	244.3	244.5	244.6
127.5°	260.2	260.1	260.0	259.8
130°	274.8	274.7	274.6	274.4
132.5°	288.4	288.2	288.0	287.8
135°	302.1	301.9	301.7	301.5
137.5°	315.0	314.9	314.7	314.6
140°	326.6	326.4	326.3	326.2
142.5°	337.4	337.2	337.0	336.8
145°	347.8	347.8	347.8	347.8
147.5°	356.7	356.3	356.0	355.7
150°	365.4	365.2	365.0	364.8
152.5°	373.1	372.8	372.4	372.1
155°	380.0	379.6	379.2	378.8
157.5°	386.2	385.7	385.1	384.6
160°	391.5	391.0	390.5	390.0
162.5°	396.4	396.0	395.6	395.2
165°	400.6	400.1	399.6	399.2
167.5°	403.8	403.3	402.8	402.2
170°	406.6	406.0	405.5	405.0
172.5°	408.3	407.7	407.1	406.5
175°	409.6	409.1	408.5	408.0
177.5°	410.3	409.7	409.0	408.3
180°	409.5	409.5	409.5	409.5



TEST NUMBER: P831117

CATALOG NUMBER: S123DIP-S1000D365U935-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.13	18.22	17.83	18.94	19.78	19.36	20.46	20.07	21.17	22.02
	3H	18.79	19.77	19.51	20.50	21.38	20.80	21.78	21.52	22.51	23.39
	4H	19.38	20.30	20.11	21.04	21.93	21.26	22.19	22.00	22.92	23.82
	6H	19.76	20.61	20.51	21.36	22.26	21.55	22.40	22.30	23.15	24.05
	8H	19.86	20.67	20.62	21.44	22.34	21.62	22.43	22.38	23.20	24.10
	12H	19.92	20.69	20.68	21.45	22.38	21.65	22.42	22.41	23.18	24.11
4H	2H	17.73	18.65	18.47	19.39	20.28	19.55	20.48	20.29	21.21	22.10
	3H	19.58	20.34	20.33	21.12	22.03	21.19	21.96	21.94	22.73	23.64
	4H	20.28	20.98	21.05	21.75	22.69	21.78	22.48	22.55	23.25	24.19
	6H	20.77	21.37	21.56	22.17	23.12	22.20	22.80	22.99	23.60	24.55
	8H	20.91	21.47	21.70	22.27	23.23	22.32	22.88	23.11	23.67	24.63
	12H	20.99	21.49	21.80	22.31	23.27	22.37	22.88	23.18	23.69	24.66
8H	4H	20.57	21.13	21.35	21.92	22.88	21.91	22.47	22.70	23.26	24.22
	6H	21.16	21.63	21.98	22.47	23.42	22.42	22.88	23.24	23.72	24.68
	8H	21.37	21.78	22.20	22.62	23.60	22.60	23.01	23.43	23.85	24.82
	12H	21.51	21.87	22.34	22.69	23.73	22.71	23.07	23.54	23.90	24.93
12H	4H	20.58	21.08	21.39	21.90	22.86	21.89	22.40	22.70	23.21	24.18
	6H	21.21	21.63	22.04	22.46	23.44	22.43	22.85	23.26	23.68	24.66
	8H	21.46	21.82	22.29	22.65	23.68	22.64	23.01	23.47	23.83	24.86