

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332082-930

Luminaire Tested: **S123DIP-S1165D1195U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332082-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7336.3 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332082-930
CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14235	14235	14235	14235
5°	16977	14296	12670	14296
10°	21249	14224	11444	14224
15°	26063	14110	10653	14110
20°	31047	13931	10143	13931
25°	32967	13713	10030	13713
30°	28256	13554	10082	13554
35°	19651	13328	10188	13328
40°	14802	13065	10156	13065
45°	12291	12670	10027	12670
50°	11010	11868	9937	11868
55°	10293	11003	9813	11003
60°	9655	10097	9711	10097
65°	9075	9205	9401	9205
70°	8510	8189	8954	8189
75°	7623	7170	8210	7170
80°	6670	5876	7073	5876
85°	5224	4273	4755	4273



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	1.8
10°-20°	417.7	5.7
20°-30°	701.1	9.6
30°-40°	793.9	10.8
40°-50°	711.9	9.7
50°-60°	574.5	7.8
60°-70°	400.3	5.5
70°-80°	210.4	2.9
80°-90°	55.0	0.8
90°-100°	78.6	1.1
100°-110°	235.1	3.2
110°-120°	399.9	5.5
120°-130°	526.0	7.2
130°-140°	591.2	8.1
140°-150°	581.2	7.9
150°-160°	489.3	6.7
160°-170°	325.7	4.4
170°-180°	114.0	1.6
0°-30°	1249.1	17.0
0°-40°	2043.0	27.8
0°-60°	3329.4	45.4
0°-90°	3995.2	54.5
90°-120°	713.6	9.7
90°-150°	2412.1	32.9
90°-180°	3341.0	45.5
0°-180°	7336.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1571	1323	1173	1323	1571	163
15°	2339	1266	956	1266	2339	675
25°	2776	1155	844	1155	2776	1217
35°	1496	1014	775	1014	1496	972
45°	807	832	659	832	807	639
55°	548	586	523	586	548	492
65°	356	361	369	361	356	355
75°	183	172	197	172	183	196
85°	42	35	38	35	42	51
90°	28	1	28	1	28	16
95°	74	56	74	56	74	76
105°	225	213	225	213	225	239
115°	404	403	404	403	404	400
125°	583	589	583	589	583	521
135°	764	764	764	764	764	587
145°	927	927	927	927	927	579
155°	1060	1062	1060	1062	1060	488
165°	1153	1157	1153	1157	1153	325
175°	1198	1203	1198	1203	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332082-930
 CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1403.5	1402.5	1400.0	1402.0	1397.9	1392.2	1391.7	1386.6	1371.7	1370.7	1366.6
5°	1571.2	1566.0	1565.4	1564.7	1555.8	1543.6	1520.5	1518.6	1487.8	1472.4	1453.9
7.5°	1788.2	1790.9	1781.6	1773.4	1746.0	1727.9	1703.2	1671.5	1633.7	1595.4	1569.9
10°	1944.1	1965.2	1938.9	1921.0	1904.4	1872.9	1836.5	1790.9	1745.4	1692.2	1651.9
12.5°	2111.2	2121.6	2116.3	2099.4	2073.5	2025.7	1961.0	1910.9	1869.0	1780.5	1744.7
15°	2338.8	2377.9	2352.9	2295.2	2296.5	2251.0	2166.4	2073.5	2024.1	1946.6	1840.9
17.5°	2581.2	2586.1	2575.4	2527.4	2495.4	2432.9	2354.8	2265.7	2165.8	2072.0	1959.8
20°	2710.4	2706.5	2684.1	2659.2	2604.1	2555.4	2470.1	2370.8	2242.6	2150.4	2028.0
22.5°	2782.2	2775.8	2765.2	2744.2	2698.4	2646.1	2569.6	2461.1	2339.0	2211.9	2070.5
25°	2775.8	2784.1	2785.4	2779.6	2763.6	2732.2	2672.0	2585.5	2463.8	2300.4	2153.0
27.5°	2524.6	2536.4	2570.6	2601.0	2635.0	2669.5	2664.9	2622.0	2531.9	2390.8	2210.6
30°	2273.4	2247.8	2311.2	2391.4	2445.8	2541.9	2595.7	2598.9	2548.3	2427.2	2251.6
32.5°	1924.8	1953.0	1981.1	2079.7	2198.7	2306.6	2413.8	2500.0	2509.9	2429.3	2275.7
35°	1495.5	1530.8	1582.0	1633.3	1761.5	1871.7	2060.0	2224.1	2354.8	2372.1	2277.9
37.5°	1205.2	1222.5	1255.0	1306.4	1390.2	1520.9	1666.6	1874.0	2063.4	2204.2	2210.4
40°	1053.4	1058.5	1095.0	1134.2	1202.1	1309.7	1441.0	1624.3	1851.1	2047.9	2129.9
42.5°	939.6	950.9	966.4	1004.0	1058.0	1139.1	1261.2	1412.6	1620.5	1846.9	2007.3
45°	807.4	820.2	829.8	854.8	893.2	947.7	1032.9	1171.3	1329.6	1563.4	1779.4
47.5°	720.0	721.0	728.1	747.0	773.1	814.0	874.2	963.2	1108.5	1298.2	1519.9
50°	657.5	667.6	670.3	684.9	705.5	735.6	785.5	861.2	980.4	1147.0	1350.7
52.5°	613.3	616.4	623.6	634.2	652.2	675.6	718.9	778.1	871.7	1013.7	1201.0
55°	548.5	548.5	555.5	563.9	574.1	595.3	624.1	667.6	738.8	849.0	1004.0
57.5°	488.5	491.7	496.7	499.3	508.0	522.0	546.1	579.1	632.2	717.0	840.3
60°	448.5	454.3	453.6	458.8	466.5	477.4	497.9	524.8	572.2	640.1	744.0
62.5°	413.7	413.3	413.2	419.3	427.0	437.4	450.7	474.0	514.3	574.5	662.9
65°	356.3	355.0	359.5	363.3	365.9	373.6	383.8	404.3	431.2	476.1	544.6
67.5°	305.2	301.6	303.9	305.2	309.7	315.6	325.2	337.9	359.3	395.3	447.0
70°	270.4	267.2	266.5	267.8	271.7	276.1	283.2	295.4	315.3	344.1	381.9
72.5°	234.5	232.4	232.2	235.1	236.8	239.8	244.8	255.9	271.7	293.3	328.6
75°	183.3	183.3	183.3	183.9	185.8	188.4	192.2	198.0	210.2	225.5	249.2
77.5°	137.4	137.2	136.5	136.3	139.2	140.3	141.2	146.6	153.4	163.8	181.1
80°	107.6	104.4	105.7	107.6	108.9	109.6	111.5	112.8	118.5	124.3	136.5
82.5°	80.0	77.3	77.5	80.5	80.7	81.4	83.3	85.1	87.2	92.5	99.1
85°	42.3	42.3	43.0	43.0	43.5	43.0	44.8	45.5	45.5	48.7	52.5
87.5°	21.0	20.0	20.4	20.8	20.2	20.6	21.0	21.3	21.6	22.0	21.9
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5	23.6	22.7	20.0
92.5°	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7	37.0	36.4	34.8
95°	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7	70.9	70.1	68.4
97.5°	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6	110.6	109.7	108.4
100°	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5	139.9	139.3	138.2
102.5°	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8	173.3	172.6	171.2
105°	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6	223.6	223.6	221.7
107.5°	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4	276.7	276.1	275.2
110°	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3	312.5	311.7	311.2



TEST NUMBER: P332082-930
 CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3	348.3	347.2	347.2
115°	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6	404.0
117.5°	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2	459.2	459.3	459.8
120°	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9	496.2	496.4	497.4
122.5°	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2	533.7	534.3	534.8
125°	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5	589.3	590.2	590.6
127.5°	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1	644.3	645.5	646.0
130°	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4	680.3	681.1	681.8
132.5°	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7	715.7	716.7	717.1
135°	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5	768.3	769.2	769.4
137.5°	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1	820.0	820.9	820.4
140°	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9	885.1	885.3	884.9
145°	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7	931.9	932.1	931.5
147.5°	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1	1003.1	1003.1	1002.7
152.5°	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1	1027.8	1027.4	1027.2
155°	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5	1063.7	1062.8	1062.7
157.5°	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8	1095.0	1094.1	1094.0
160°	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2	1114.1	1113.0	1113.0
162.5°	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3	1132.3	1131.2	1131.1
165°	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3	1155.0	1153.8	1153.8
167.5°	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3	1172.2
170°	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2	1182.2
172.5°	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2	1191.9	1190.6	1190.6
175°	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8	1200.5	1199.2	1199.2
177.5°	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7	1204.6	1203.6	1203.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1363.5	1359.4	1355.4	1348.2	1342.0	1333.3	1330.7	1327.6	1318.4	1310.3	1304.1
5°	1446.8	1431.4	1409.0	1388.5	1371.9	1349.5	1336.6	1323.1	1303.9	1286.6	1272.5
7.5°	1534.0	1503.7	1468.8	1431.2	1396.1	1362.3	1335.0	1310.6	1283.7	1258.2	1238.4
10°	1603.2	1559.6	1510.9	1458.4	1413.5	1369.9	1333.4	1301.4	1266.8	1236.6	1211.7
12.5°	1682.1	1617.6	1550.4	1486.5	1433.5	1373.0	1328.8	1288.1	1248.9	1212.6	1184.5
15°	1775.6	1693.5	1614.0	1526.3	1445.5	1369.9	1317.4	1266.2	1220.7	1183.5	1147.6
17.5°	1860.7	1767.7	1663.0	1556.2	1458.9	1369.2	1295.6	1237.7	1180.8	1135.3	1099.5
20°	1908.9	1803.1	1684.6	1573.7	1466.1	1366.1	1285.4	1216.2	1154.6	1106.6	1066.2
22.5°	1950.4	1826.7	1704.1	1585.5	1465.6	1357.9	1266.4	1195.1	1128.5	1081.5	1038.5
25°	1993.4	1845.4	1722.4	1583.3	1449.4	1337.9	1235.4	1154.6	1088.0	1032.9	988.7
27.5°	2030.3	1844.1	1698.1	1548.6	1424.0	1312.3	1202.8	1116.2	1045.5	985.6	940.8
30°	2054.9	1846.7	1673.0	1525.0	1399.5	1284.1	1177.7	1090.5	1016.3	955.4	913.1
32.5°	2070.3	1845.1	1649.9	1492.2	1360.5	1258.4	1150.6	1060.3	984.0	924.1	883.4
35°	2079.3	1833.9	1610.2	1424.4	1297.5	1198.2	1107.9	1014.3	934.3	878.5	832.3
37.5°	2061.3	1810.1	1564.1	1359.0	1220.2	1122.3	1046.4	966.6	890.0	828.7	788.9
40°	2033.1	1794.8	1528.2	1313.0	1166.9	1072.6	1008.0	929.8	854.1	795.8	758.6
42.5°	1979.3	1763.5	1488.7	1261.7	1111.5	1017.2	957.7	892.3	820.8	766.1	729.0
45°	1848.0	1695.4	1429.5	1184.8	1029.7	932.3	879.8	832.3	767.6	714.4	682.4
47.5°	1665.7	1593.1	1343.9	1103.7	944.4	850.7	796.1	757.9	710.6	667.6	636.9
50°	1539.1	1509.0	1286.0	1048.3	887.5	795.8	743.3	708.7	674.7	631.8	603.6
52.5°	1393.0	1411.6	1218.4	990.8	829.6	739.5	690.0	662.5	631.7	596.4	571.9
55°	1187.3	1254.6	1101.5	894.5	743.3	657.5	610.7	586.3	568.3	542.1	521.0
57.5°	994.7	1080.4	975.1	795.2	658.6	584.5	539.6	513.1	501.6	487.9	471.2
60°	880.4	965.0	884.9	728.6	601.7	531.2	491.5	469.0	457.5	447.9	433.8
62.5°	778.4	864.0	796.7	660.9	545.8	480.5	445.8	424.0	415.0	409.9	397.9
65°	638.2	711.9	667.0	555.5	465.9	408.1	376.7	361.4	353.0	351.1	343.5
67.5°	519.4	575.5	542.8	460.8	390.2	340.4	313.7	300.7	294.2	293.6	287.8
70°	441.5	494.0	469.0	394.7	333.9	294.7	271.7	260.2	256.3	255.7	252.5
72.5°	381.0	417.7	397.8	335.7	288.7	253.2	236.3	224.3	219.9	220.8	218.7
75°	281.9	309.5	298.0	255.0	217.2	194.1	180.0	172.4	168.5	170.5	167.9
77.5°	202.8	220.3	209.9	180.2	156.9	140.2	129.8	125.1	121.6	121.5	120.3
80°	153.1	163.4	157.6	139.7	120.5	106.4	98.0	94.8	92.9	92.3	91.6
82.5°	109.1	117.8	111.0	98.7	85.6	77.1	72.4	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.0	43.0	39.1	36.5	34.6	33.3	34.0	32.7
87.5°	22.4	22.4	20.3	17.8	16.3	14.3	13.9	12.5	11.9	12.3	12.2
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9	24.4	25.8	27.2
95°	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9	57.4	58.9	60.3
97.5°	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3	100.4	101.5	102.6
100°	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8	130.1	131.3	132.6
102.5°	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9	163.7	164.4	165.2
105°	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1	213.5	214.0	214.4
107.5°	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5	271.7	272.0	272.2
110°	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9	308.3	308.7	309.2



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8	346.0	346.3	346.5
115°	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6	403.2	403.8	404.5
117.5°	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8	460.2	460.6	461.1
120°	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5	496.7	498.0	499.2
122.5°	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6	533.5	534.4	535.3
125°	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2	589.9	590.4	591.1
127.5°	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5	642.9	644.2	645.6
130°	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4	678.0	679.7	681.4
132.5°	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2	712.9	714.6	716.2
135°	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4	765.7	767.0	768.3
137.5°	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8	814.7	815.8	816.8
140°	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8	848.9	849.9	851.0
142.5°	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9	880.0	881.0	882.1
145°	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4	927.8	928.2	928.6
147.5°	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8	970.6	971.3	972.1
150°	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4	999.8	1000.2	1000.6
152.5°	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6	1024.3	1024.8	1025.4
155°	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5	1094.2	1094.0	1093.7
160°	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9	1114.5	1114.1	1113.7
162.5°	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1	1132.5	1132.0	1131.4
165°	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7	1156.0	1155.4	1154.7
167.5°	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4	1174.5	1173.7	1172.9
170°	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0	1185.1	1184.3	1183.5
172.5°	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3	1193.5	1192.6	1191.8
175°	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1	1202.2	1201.3	1200.5
177.5°	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6	1206.0	1205.3	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1300.5	1296.9	1291.8	1284.1	1277.9	1268.2	1268.2	1269.7	1269.7	1269.3	1268.2
5°	1261.0	1251.4	1239.9	1226.5	1212.4	1198.2	1195.6	1190.5	1186.7	1184.1	1181.0
7.5°	1219.4	1202.3	1185.5	1166.7	1149.5	1135.3	1125.4	1117.2	1112.0	1106.4	1102.2
10°	1191.2	1170.0	1150.1	1130.3	1108.5	1091.2	1080.4	1072.6	1066.9	1061.8	1059.2
12.5°	1157.9	1133.7	1111.7	1092.9	1069.0	1051.2	1040.9	1037.2	1030.5	1019.7	1014.1
15°	1109.1	1086.7	1060.5	1031.6	1020.1	998.3	986.1	980.4	976.5	968.2	965.6
17.5°	1067.5	1038.1	1008.7	987.2	965.7	948.0	941.3	934.1	929.0	922.2	920.1
20°	1034.2	1008.0	981.0	958.0	935.5	916.3	910.5	905.4	900.3	897.1	894.5
22.5°	1000.4	974.1	951.8	930.3	906.3	893.7	887.5	881.8	878.2	876.0	873.5
25°	952.8	929.8	904.7	885.5	866.3	857.9	854.1	850.9	848.4	845.1	844.5
27.5°	910.3	885.2	864.9	846.9	833.2	826.2	822.5	820.9	821.5	822.6	823.4
30°	878.5	855.4	838.8	823.4	810.6	804.1	803.5	803.5	806.1	806.7	808.0
32.5°	849.3	830.3	813.7	798.7	789.0	784.6	787.1	787.1	789.1	790.8	793.1
35°	806.7	790.0	777.2	764.4	756.1	758.0	759.3	760.6	763.8	767.6	770.2
37.5°	766.1	751.6	738.3	728.3	724.5	727.9	731.0	733.7	737.4	740.4	742.9
40°	736.9	725.9	713.1	704.2	705.5	707.4	710.0	713.1	716.4	718.3	720.9
42.5°	709.7	698.3	688.6	681.1	682.9	685.3	686.9	688.6	692.3	695.8	697.2
45°	668.3	659.3	650.4	645.9	647.2	648.5	649.7	651.7	654.8	657.5	658.0
47.5°	621.8	615.6	609.5	605.1	607.2	606.7	608.4	612.5	613.4	615.0	618.6
50°	592.1	586.3	579.3	578.0	578.0	578.0	578.6	583.8	583.8	586.3	588.9
52.5°	559.3	555.5	551.1	548.8	547.7	547.7	550.4	553.0	554.0	557.6	560.2
55°	510.7	506.9	503.0	501.1	499.8	501.1	506.2	507.4	510.7	512.6	514.5
57.5°	460.1	457.1	454.0	453.0	452.7	454.4	457.2	461.1	461.9	467.7	470.7
60°	426.7	422.2	419.7	419.7	418.4	424.2	422.9	429.3	430.6	434.5	439.0
62.5°	392.4	386.4	385.4	385.4	387.2	388.8	390.6	393.5	396.7	401.6	405.1
65°	337.0	333.9	338.3	337.7	336.4	340.2	340.2	343.5	347.3	351.8	358.8
67.5°	284.6	283.0	283.3	283.3	285.3	287.5	289.3	292.0	296.7	301.4	306.1
70°	249.2	251.2	248.0	250.5	252.5	253.1	254.4	258.2	263.3	266.5	271.7
72.5°	214.9	214.7	215.2	216.2	218.1	219.2	220.5	224.9	230.6	233.3	237.3
75°	165.3	164.7	166.6	166.6	169.8	171.0	172.4	174.3	179.4	183.3	186.5
77.5°	120.7	121.5	121.1	123.3	122.4	122.6	126.6	128.6	129.1	136.6	138.3
80°	91.0	92.3	92.9	93.5	94.2	92.9	97.4	99.3	99.3	103.8	107.0
82.5°	65.4	66.1	67.8	68.4	68.6	69.9	70.2	71.7	73.2	75.1	79.3
85°	32.7	34.6	35.2	34.6	35.2	34.0	35.9	36.5	37.2	37.2	37.2
87.5°	12.1	13.1	13.1	14.2	14.3	15.3	15.5	14.6	14.8	16.5	14.6
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5	25.3	26.1	26.7
92.5°	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7	38.4	39.1	39.3
95°	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7	72.6	73.5	73.9
97.5°	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6	112.6	113.6	114.0
100°	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5	141.1	141.8	142.3
102.5°	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8	174.5	175.1	175.4
105°	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6	223.6	223.6	223.8
107.5°	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4	278.1	278.8	278.9
110°	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3	314.2	315.0	315.2



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3	350.3	351.3	351.8
115°	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0	404.1	404.4	404.4
117.5°	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2	459.1	459.1	458.8
120°	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9	495.8	495.5	495.2
122.5°	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2	532.6	532.1	531.5
125°	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5	587.7	586.8	586.0
127.5°	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1	642.0	640.7	639.7
130°	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4	678.6	677.8	676.5
132.5°	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7	713.7	712.7	711.6
135°	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5	766.6	765.8	765.2
137.5°	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1	818.2	817.3	816.5
140°	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0	852.9	852.6	851.8
142.5°	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9	884.7	884.5	883.8
145°	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7	931.5	931.3	930.7
147.5°	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1	1003.1	1003.1	1002.6
152.5°	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1	1028.4	1028.7	1028.4
155°	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5	1065.4	1066.2	1065.9
157.5°	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8	1096.7	1097.6	1097.5
160°	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2	1116.2	1117.3	1117.4
162.5°	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3	1134.4	1135.5	1135.3
165°	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3	1157.6	1158.9	1158.7
167.5°	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5
170°	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1
172.5°	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2	1194.5	1195.8	1195.7
175°	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8	1203.1	1204.3	1204.2
177.5°	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7	1206.6	1207.6	1207.5
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930
 CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1264.6	1264.1	1267.7	1265.1	1267.7	1264.1	1264.6	1268.2	1269.3	1269.7	1269.7
5°	1177.0	1179.0	1172.6	1172.6	1172.6	1179.0	1177.0	1181.0	1184.1	1186.7	1190.5
7.5°	1099.2	1096.3	1096.6	1093.2	1096.6	1096.3	1099.2	1102.2	1106.4	1112.0	1117.2
10°	1051.5	1047.7	1046.4	1047.0	1046.4	1047.7	1051.5	1059.2	1061.8	1066.9	1072.6
12.5°	1012.0	1011.2	1002.8	1002.9	1002.8	1011.2	1012.0	1014.1	1019.7	1030.5	1037.2
15°	965.6	953.5	952.2	956.0	952.2	953.5	965.6	965.6	968.2	976.5	980.4
17.5°	919.1	912.7	913.1	911.2	913.1	912.7	919.1	920.1	922.2	929.0	934.1
20°	894.5	890.6	890.0	885.5	890.0	890.6	894.5	894.5	897.1	900.3	905.4
22.5°	872.0	870.7	871.1	866.1	871.1	870.7	872.0	873.5	876.0	878.2	881.8
25°	843.9	847.1	844.5	844.5	844.5	847.1	843.9	844.5	845.1	848.4	850.9
27.5°	824.9	824.8	823.5	823.5	823.5	824.8	824.9	823.4	822.6	821.5	820.9
30°	810.6	809.9	811.2	811.2	811.2	809.9	810.6	808.0	806.7	806.1	803.5
32.5°	796.2	797.1	797.4	797.9	797.4	797.1	796.2	793.1	790.8	789.1	787.1
35°	774.0	774.7	776.6	775.3	776.6	774.7	774.0	770.2	767.6	763.8	760.6
37.5°	744.0	747.0	746.3	747.4	746.3	747.0	744.0	742.9	740.4	737.4	733.7
40°	721.5	723.4	722.8	722.8	722.8	723.4	721.5	720.9	718.3	716.4	713.1
42.5°	698.5	699.9	698.1	697.2	698.1	699.9	698.5	697.2	695.8	692.3	688.6
45°	660.6	659.3	661.3	658.7	661.3	659.3	660.6	658.0	657.5	654.8	651.7
47.5°	618.3	619.6	620.1	622.1	620.1	619.6	618.3	618.6	615.0	613.4	612.5
50°	590.1	593.9	593.9	593.4	593.9	593.9	590.1	588.9	586.3	583.8	583.8
52.5°	562.5	564.3	566.8	566.7	566.8	564.3	562.5	560.2	557.6	554.0	553.0
55°	519.7	521.0	522.2	522.9	522.2	521.0	519.7	514.5	512.6	510.7	507.4
57.5°	475.3	474.8	477.8	478.7	477.8	474.8	475.3	470.7	467.7	461.9	461.1
60°	444.0	444.0	449.1	451.1	449.1	444.0	444.0	439.0	434.5	430.6	429.3
62.5°	410.7	412.8	417.9	415.2	417.9	412.8	410.7	405.1	401.6	396.7	393.5
65°	362.0	367.1	366.5	369.1	366.5	367.1	362.0	358.8	351.8	347.3	343.5
67.5°	311.1	314.4	318.9	319.4	318.9	314.4	311.1	306.1	301.4	296.7	292.0
70°	276.8	280.0	282.6	284.5	282.6	280.0	276.8	271.7	266.5	263.3	258.2
72.5°	243.5	245.2	251.3	248.6	251.3	245.2	243.5	237.3	233.3	230.6	224.9
75°	190.9	195.4	199.3	197.4	199.3	195.4	190.9	186.5	183.3	179.4	174.3
77.5°	141.2	145.7	147.5	145.9	147.5	145.7	141.2	138.3	136.6	129.1	128.6
80°	111.5	110.9	114.7	114.1	114.7	110.9	111.5	107.0	103.8	99.3	99.3
82.5°	81.8	81.1	82.9	83.3	82.9	81.1	81.8	79.3	75.1	73.2	71.7
85°	39.7	41.7	39.1	38.5	39.1	41.7	39.7	37.2	37.2	37.2	36.5
87.5°	14.7	14.8	14.3	13.9	14.3	14.8	14.7	14.6	16.5	14.8	14.6
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5
92.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7
95°	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7
97.5°	113.9	113.8	113.7	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6
100°	142.8	143.2	143.6	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5
102.5°	175.3	175.2	175.1	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8
105°	224.2	224.6	225.0	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6
107.5°	278.7	278.4	278.2	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4
110°	314.8	314.4	314.0	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	351.7	351.6	351.6	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3
115°	404.1	404.0	403.7	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0
117.5°	458.2	457.5	457.0	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2
120°	494.8	494.4	494.0	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9
122.5°	530.9	530.4	529.7	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2
125°	585.1	584.2	583.4	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5
127.5°	638.7	637.7	636.7	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1
130°	675.1	673.6	672.1	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4
132.5°	710.5	709.3	708.2	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7
135°	764.8	764.3	763.9	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5
137.5°	815.7	815.0	814.2	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1
140°	850.4	848.9	847.4	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0
142.5°	882.6	881.5	880.4	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9
145°	929.9	929.0	928.2	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7
147.5°	974.0	972.7	971.4	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9
150°	1001.3	1000.0	998.7	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1
152.5°	1027.3	1026.2	1025.1	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1
155°	1064.5	1063.0	1061.5	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5
157.5°	1096.3	1095.1	1094.0	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8
160°	1116.6	1115.7	1114.8	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2
162.5°	1133.9	1132.6	1131.2	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3
165°	1157.2	1155.8	1154.3	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3
167.5°	1176.2	1174.9	1173.6	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9
170°	1186.7	1185.1	1183.7	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1
172.5°	1194.2	1192.7	1191.2	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2
175°	1202.7	1201.3	1199.8	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8
177.5°	1206.4	1205.2	1204.0	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1268.2	1268.2	1277.9	1284.1	1291.8	1296.9	1300.5	1304.1	1310.3	1318.4	1327.6
5°	1195.6	1198.2	1212.4	1226.5	1239.9	1251.4	1261.0	1272.5	1286.6	1303.9	1323.1
7.5°	1125.4	1135.3	1149.5	1166.7	1185.5	1202.3	1219.4	1238.4	1258.2	1283.7	1310.6
10°	1080.4	1091.2	1108.5	1130.3	1150.1	1170.0	1191.2	1211.7	1236.6	1266.8	1301.4
12.5°	1040.9	1051.2	1069.0	1092.9	1111.7	1133.7	1157.9	1184.5	1212.6	1248.9	1288.1
15°	986.1	998.3	1020.1	1031.6	1060.5	1086.7	1109.1	1147.6	1183.5	1220.7	1266.2
17.5°	941.3	948.0	965.7	987.2	1008.7	1038.1	1067.5	1099.5	1135.3	1180.8	1237.7
20°	910.5	916.3	935.5	958.0	981.0	1008.0	1034.2	1066.2	1106.6	1154.6	1216.2
22.5°	887.5	893.7	906.3	930.3	951.8	974.1	1000.4	1038.5	1081.5	1128.5	1195.1
25°	854.1	857.9	866.3	885.5	904.7	929.8	952.8	988.7	1032.9	1088.0	1154.6
27.5°	822.5	826.2	833.2	846.9	864.9	885.2	910.3	940.8	985.6	1045.5	1116.2
30°	803.5	804.1	810.6	823.4	838.8	855.4	878.5	913.1	955.4	1016.3	1090.5
32.5°	787.1	784.6	789.0	798.7	813.7	830.3	849.3	883.4	924.1	984.0	1060.3
35°	759.3	758.0	756.1	764.4	777.2	790.0	806.7	832.3	878.5	934.3	1014.3
37.5°	731.0	727.9	724.5	728.3	738.3	751.6	766.1	788.9	828.7	890.0	966.6
40°	710.0	707.4	705.5	704.2	713.1	725.9	736.9	758.6	795.8	854.1	929.8
42.5°	686.9	685.3	682.9	681.1	688.6	698.3	709.7	729.0	766.1	820.8	892.3
45°	649.7	648.5	647.2	645.9	650.4	659.3	668.3	682.4	714.4	767.6	832.3
47.5°	608.4	606.7	607.2	605.1	609.5	615.6	621.8	636.9	667.6	710.6	757.9
50°	578.6	578.0	578.0	578.0	579.3	586.3	592.1	603.6	631.8	674.7	708.7
52.5°	550.4	547.7	547.7	548.8	551.1	555.5	559.3	571.9	596.4	631.7	662.5
55°	506.2	501.1	499.8	501.1	503.0	506.9	510.7	521.0	542.1	568.3	586.3
57.5°	457.2	454.4	452.7	453.0	454.0	457.1	460.1	471.2	487.9	501.6	513.1
60°	422.9	424.2	418.4	419.7	419.7	422.2	426.7	433.8	447.9	457.5	469.0
62.5°	390.6	388.8	387.2	385.4	385.4	386.4	392.4	397.9	409.9	415.0	424.0
65°	340.2	340.2	336.4	337.7	338.3	333.9	337.0	343.5	351.1	353.0	361.4
67.5°	289.3	287.5	285.3	283.3	283.3	283.0	284.6	287.8	293.6	294.2	300.7
70°	254.4	253.1	252.5	250.5	248.0	251.2	249.2	252.5	255.7	256.3	260.2
72.5°	220.5	219.2	218.1	216.2	215.2	214.7	214.9	218.7	220.8	219.9	224.3
75°	172.4	171.0	169.8	166.6	166.6	164.7	165.3	167.9	170.5	168.5	172.4
77.5°	126.6	122.6	122.4	123.3	121.1	121.5	120.7	120.3	121.5	121.6	125.1
80°	97.4	92.9	94.2	93.5	92.9	92.3	91.0	91.6	92.3	92.9	94.8
82.5°	70.2	69.9	68.6	68.4	67.8	66.1	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.2	34.6	35.2	34.6	32.7	32.7	34.0	33.3	34.6
87.5°	15.5	15.3	14.3	14.2	13.1	13.1	12.1	12.2	12.3	11.9	12.5
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	37.0	36.4	34.8	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9
95°	70.9	70.1	68.4	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9
97.5°	110.6	109.7	108.4	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3
100°	139.9	139.3	138.2	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8
102.5°	173.3	172.6	171.2	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9
105°	223.6	223.6	221.7	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1
107.5°	276.7	276.1	275.2	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5
110°	312.5	311.7	311.2	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.3	347.2	347.2	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8
115°	403.7	403.6	404.0	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6
117.5°	459.2	459.3	459.8	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8
120°	496.2	496.4	497.4	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5
122.5°	533.7	534.3	534.8	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6
125°	589.3	590.2	590.6	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2
127.5°	644.3	645.5	646.0	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5
130°	680.3	681.1	681.8	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4
132.5°	715.7	716.7	717.1	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2
135°	768.3	769.2	769.4	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4
137.5°	820.0	820.9	820.4	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8
140°	853.3	853.5	853.3	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8
142.5°	885.1	885.3	884.9	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9
145°	931.9	932.1	931.5	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4
147.5°	975.9	975.9	975.3	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8
150°	1003.1	1003.1	1002.7	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4
152.5°	1027.8	1027.4	1027.2	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6
155°	1063.7	1062.8	1062.7	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1095.0	1094.1	1094.0	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5
160°	1114.1	1113.0	1113.0	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9
162.5°	1132.3	1131.2	1131.1	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1
165°	1155.0	1153.8	1153.8	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7
167.5°	1173.6	1172.3	1172.2	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4
170°	1183.7	1182.2	1182.2	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0
172.5°	1191.9	1190.6	1190.6	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3
175°	1200.5	1199.2	1199.2	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1
177.5°	1204.6	1203.6	1203.6	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930
 CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1330.7	1333.3	1342.0	1348.2	1355.4	1359.4	1363.5	1366.6	1370.7	1371.7	1386.6
5°	1336.6	1349.5	1371.9	1388.5	1409.0	1431.4	1446.8	1453.9	1472.4	1487.8	1518.6
7.5°	1335.0	1362.3	1396.1	1431.2	1468.8	1503.7	1534.0	1569.9	1595.4	1633.7	1671.5
10°	1333.4	1369.9	1413.5	1458.4	1510.9	1559.6	1603.2	1651.9	1692.2	1745.4	1790.9
12.5°	1328.8	1373.0	1433.5	1486.5	1550.4	1617.6	1682.1	1744.7	1780.5	1869.0	1910.9
15°	1317.4	1369.9	1445.5	1526.3	1614.0	1693.5	1775.6	1840.9	1946.6	2024.1	2073.5
17.5°	1295.6	1369.2	1458.9	1556.2	1663.0	1767.7	1860.7	1959.8	2072.0	2165.8	2265.7
20°	1285.4	1366.1	1466.1	1573.7	1684.6	1803.1	1908.9	2028.0	2150.4	2242.6	2370.8
22.5°	1266.4	1357.9	1465.6	1585.5	1704.1	1826.7	1950.4	2070.5	2211.9	2339.0	2461.1
25°	1235.4	1337.9	1449.4	1583.3	1722.4	1845.4	1993.4	2153.0	2300.4	2463.8	2585.5
27.5°	1202.8	1312.3	1424.0	1548.6	1698.1	1844.1	2030.3	2210.6	2390.8	2531.9	2622.0
30°	1177.7	1284.1	1399.5	1525.0	1673.0	1846.7	2054.9	2251.6	2427.2	2548.3	2598.9
32.5°	1150.6	1258.4	1360.5	1492.2	1649.9	1845.1	2070.3	2275.7	2429.3	2509.9	2500.0
35°	1107.9	1198.2	1297.5	1424.4	1610.2	1833.9	2079.3	2277.9	2372.1	2354.8	2224.1
37.5°	1046.4	1122.3	1220.2	1359.0	1564.1	1810.1	2061.3	2210.4	2204.2	2063.4	1874.0
40°	1008.0	1072.6	1166.9	1313.0	1528.2	1794.8	2033.1	2129.9	2047.9	1851.1	1624.3
42.5°	957.7	1017.2	1111.5	1261.7	1488.7	1763.5	1979.3	2007.3	1846.9	1620.5	1412.6
45°	879.8	932.3	1029.7	1184.8	1429.5	1695.4	1848.0	1779.4	1563.4	1329.6	1171.3
47.5°	796.1	850.7	944.4	1103.7	1343.9	1593.1	1665.7	1519.9	1298.2	1108.5	963.2
50°	743.3	795.8	887.5	1048.3	1286.0	1509.0	1539.1	1350.7	1147.0	980.4	861.2
52.5°	690.0	739.5	829.6	990.8	1218.4	1411.6	1393.0	1201.0	1013.7	871.7	778.1
55°	610.7	657.5	743.3	894.5	1101.5	1254.6	1187.3	1004.0	849.0	738.8	667.6
57.5°	539.6	584.5	658.6	795.2	975.1	1080.4	994.7	840.3	717.0	632.2	579.1
60°	491.5	531.2	601.7	728.6	884.9	965.0	880.4	744.0	640.1	572.2	524.8
62.5°	445.8	480.5	545.8	660.9	796.7	864.0	778.4	662.9	574.5	514.3	474.0
65°	376.7	408.1	465.9	555.5	667.0	711.9	638.2	544.6	476.1	431.2	404.3
67.5°	313.7	340.4	390.2	460.8	542.8	575.5	519.4	447.0	395.3	359.3	337.9
70°	271.7	294.7	333.9	394.7	469.0	494.0	441.5	381.9	344.1	315.3	295.4
72.5°	236.3	253.2	288.7	335.7	397.8	417.7	381.0	328.6	293.3	271.7	255.9
75°	180.0	194.1	217.2	255.0	298.0	309.5	281.9	249.2	225.5	210.2	198.0
77.5°	129.8	140.2	156.9	180.2	209.9	220.3	202.8	181.1	163.8	153.4	146.6
80°	98.0	106.4	120.5	139.7	157.6	163.4	153.1	136.5	124.3	118.5	112.8
82.5°	72.4	77.1	85.6	98.7	111.0	117.8	109.1	99.1	92.5	87.2	85.1
85°	36.5	39.1	43.0	48.0	55.8	58.3	55.1	52.5	48.7	45.5	45.5
87.5°	13.9	14.3	16.3	17.8	20.3	22.4	22.4	21.9	22.0	21.6	21.3
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5
92.5°	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7
95°	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7
97.5°	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6
100°	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5
102.5°	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8
105°	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6
107.5°	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4
110°	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3
115°	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0
117.5°	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2
120°	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9
122.5°	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2
125°	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5
127.5°	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1
130°	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4
132.5°	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7
135°	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5
137.5°	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1
140°	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0
142.5°	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9
145°	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7
147.5°	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9
150°	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1
152.5°	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1
155°	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5
157.5°	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8
160°	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2
162.5°	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3
165°	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3
167.5°	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9
170°	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1
172.5°	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2
175°	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8
177.5°	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1391.7	1392.2	1397.9	1402.0	1400.0	1402.5	1403.5
5°	1520.5	1543.6	1555.8	1564.7	1565.4	1566.0	1571.2
7.5°	1703.2	1727.9	1746.0	1773.4	1781.6	1790.9	1788.2
10°	1836.5	1872.9	1904.4	1921.0	1938.9	1965.2	1944.1
12.5°	1961.0	2025.7	2073.5	2099.4	2116.3	2121.6	2111.2
15°	2166.4	2251.0	2296.5	2295.2	2352.9	2377.9	2338.8
17.5°	2354.8	2432.9	2495.4	2527.4	2575.4	2586.1	2581.2
20°	2470.1	2555.4	2604.1	2659.2	2684.1	2706.5	2710.4
22.5°	2569.6	2646.1	2698.4	2744.2	2765.2	2775.8	2782.2
25°	2672.0	2732.2	2763.6	2779.6	2785.4	2784.1	2775.8
27.5°	2664.9	2669.5	2635.0	2601.0	2570.6	2536.4	2524.6
30°	2595.7	2541.9	2445.8	2391.4	2311.2	2247.8	2273.4
32.5°	2413.8	2306.6	2198.7	2079.7	1981.1	1953.0	1924.8
35°	2060.0	1871.7	1761.5	1633.3	1582.0	1530.8	1495.5
37.5°	1666.6	1520.9	1390.2	1306.4	1255.0	1222.5	1205.2
40°	1441.0	1309.7	1202.1	1134.2	1095.0	1058.5	1053.4
42.5°	1261.2	1139.1	1058.0	1004.0	966.4	950.9	939.6
45°	1032.9	947.7	893.2	854.8	829.8	820.2	807.4
47.5°	874.2	814.0	773.1	747.0	728.1	721.0	720.0
50°	785.5	735.6	705.5	684.9	670.3	667.6	657.5
52.5°	718.9	675.6	652.2	634.2	623.6	616.4	613.3
55°	624.1	595.3	574.1	563.9	555.5	548.5	548.5
57.5°	546.1	522.0	508.0	499.3	496.7	491.7	488.5
60°	497.9	477.4	466.5	458.8	453.6	454.3	448.5
62.5°	450.7	437.4	427.0	419.3	413.2	413.3	413.7
65°	383.8	373.6	365.9	363.3	359.5	355.0	356.3
67.5°	325.2	315.6	309.7	305.2	303.9	301.6	305.2
70°	283.2	276.1	271.7	267.8	266.5	267.2	270.4
72.5°	244.8	239.8	236.8	235.1	232.2	232.4	234.5
75°	192.2	188.4	185.8	183.9	183.3	183.3	183.3
77.5°	141.2	140.3	139.2	136.3	136.5	137.2	137.4
80°	111.5	109.6	108.9	107.6	105.7	104.4	107.6
82.5°	83.3	81.4	80.7	80.5	77.5	77.3	80.0
85°	44.8	43.0	43.5	43.0	43.0	42.3	42.3
87.5°	21.0	20.6	20.2	20.8	20.4	20.0	21.0
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P332082-930

CATALOG NUMBER: S123DIP-S1165D1195U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)