

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332080-935

Luminaire Tested: **S123DIP-S1165D1025U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332080-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7293.2 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.0
10°-20°	418.7	5.7
20°-30°	618.4	8.5
30°-40°	722.4	9.9
40°-50°	726.3	10.0
50°-60°	638.0	8.7
60°-70°	475.3	6.5
70°-80°	270.8	3.7
80°-90°	81.0	1.1
90°-100°	236.3	3.2
100°-110°	669.0	9.2
110°-120°	658.1	9.0
120°-130°	525.0	7.2
130°-140°	413.9	5.7
140°-150°	308.9	4.2
150°-160°	215.3	3.0
160°-170°	126.5	1.7
170°-180°	41.2	0.6
0°-30°	1185.3	16.3
0°-40°	1907.7	26.2
0°-60°	3272.0	44.9
0°-90°	4099.0	56.2
90°-120°	1563.5	21.4
90°-150°	2811.2	38.5
90°-180°	3194.0	43.8
0°-180°	7293.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	2	10	22	24	25	6
95°	29	95	510	149	100	32
105°	100	147	691	1208	1093	106
115°	176	220	529	1159	1330	174
125°	245	289	493	894	1048	217
135°	287	342	486	736	850	222
145°	327	375	480	604	664	205
155°	372	401	465	529	551	171
165°	406	418	445	472	480	115
175°	424	424	427	433	432	40
180°	425	425	425	425	425	



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.5	28.2	27.7	27.6	27.1	27.0	27.3	27.6	27.8	28.2	27.7
90°	1.7	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7
92.5°	10.7	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7
95°	29.2	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4
97.5°	49.9	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0
100°	63.6	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2
102.5°	78.0	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1
105°	99.7	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6
107.5°	122.7	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8
110°	139.2	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	154.4	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9
115°	176.2	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3
117.5°	198.0	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6
120°	213.1	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4
122.5°	226.2	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5
125°	245.0	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3
127.5°	259.2	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4
130°	268.1	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8
132.5°	275.0	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8
135°	287.1	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2
137.5°	298.4	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0
140°	306.0	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8
142.5°	314.2	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3
145°	327.4	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9
147.5°	340.9	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7
150°	349.8	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8
152.5°	358.7	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4
155°	372.1	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2
157.5°	382.8	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9
160°	391.1	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7
162.5°	397.3	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5
165°	406.5	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0
167.5°	413.5	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0
170°	417.7	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2
172.5°	420.4	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4
175°	423.7	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9
177.5°	425.2	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	27.6	27.6	27.5	27.7	27.6	27.7	27.9	27.7
90°	21.5	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	72.3	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	309.4	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	771.3	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	1013.3	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1093.7	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1117.2	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1049.6	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	984.9	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P332080-935

CATALOG NUMBER: S123DIP-S1165D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	920.9	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	836.2	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	774.9	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	742.5	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	717.1	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	683.3	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	653.7	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	635.2	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	617.9	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	594.7	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	573.6	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	561.2	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	549.5	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	535.5	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	523.9	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	515.7	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	508.1	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	496.7	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	484.7	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	477.9	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	469.6	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	458.9	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	449.6	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	443.5	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	438.0	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	430.6	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	425.9	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)