

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332051-930

Luminaire Tested: **S123DIP-S1165D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332051-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5062.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332051-930
CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	38	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.8
10°-20°	396.4	7.8
20°-30°	585.6	11.6
30°-40°	684.0	13.5
40°-50°	687.7	13.6
50°-60°	604.1	11.9
60°-70°	450.0	8.9
70°-80°	256.4	5.1
80°-90°	74.7	1.5
90°-100°	14.1	0.3
100°-110°	67.2	1.3
110°-120°	161.4	3.2
120°-130°	205.5	4.1
130°-140°	219.6	4.3
140°-150°	205.4	4.1
150°-160°	165.6	3.3
160°-170°	106.9	2.1
170°-180°	36.8	0.7
0°-30°	1122.4	22.2
0°-40°	1806.5	35.7
0°-60°	3098.3	61.2
0°-90°	3879.4	76.6
90°-120°	242.7	4.8
90°-150°	873.2	17.2
90°-180°	1183.0	23.4
0°-180°	5062.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	0	3	7	8	9	4
95°	18	7	9	11	11	22
105°	86	87	63	15	13	91
115°	161	163	165	168	169	159
125°	227	229	230	231	232	203
135°	283	284	286	286	286	217
145°	326	328	329	329	329	204
155°	359	359	359	360	359	165
165°	379	378	378	380	378	107
175°	388	386	387	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.7	26.2	25.6	25.0	24.5	24.2	24.1	24.1	24.0	24.0	23.7
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	5.4	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7
95°	17.6	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4
97.5°	35.3	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8
100°	48.7	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0
102.5°	63.9	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4
105°	85.9	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8
107.5°	109.0	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3
110°	124.5	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8



TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.2	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5
115°	161.0	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0
117.5°	182.2	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1
120°	195.3	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3
122.5°	208.7	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3
125°	227.1	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6
127.5°	244.8	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7
130°	255.8	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5
132.5°	266.4	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9
135°	282.7	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7
137.5°	296.4	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6
140°	305.7	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5
142.5°	314.2	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0
145°	326.1	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9
147.5°	337.4	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4
150°	344.3	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8
152.5°	350.5	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5
155°	359.3	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3
157.5°	366.1	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1
160°	370.2	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0
162.5°	374.1	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5
165°	378.9	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2
167.5°	382.5	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9
170°	384.6	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0
172.5°	386.0	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4
175°	387.8	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1
177.5°	388.2	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	23.6	23.4	23.2	23.2	23.2	23.2	23.2	23.2
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.2	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	9.9	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.3	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	10.5	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	15.8	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	40.4	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	99.1	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	125.7	123.6	121.5	115.9	106.7	97.5	88.4	79.2



TEST NUMBER: P332051-930

CATALOG NUMBER: S123DIP-S1165D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	144.6	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	166.6	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	186.7	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	199.8	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	212.6	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.7	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	248.8	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	259.8	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.2	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	299.9	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	308.8	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.2	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.0	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.5	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.0	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	351.7	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	359.6	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.5	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.4	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.0	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	378.7	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	385.9	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	387.5	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.2	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)