

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332065-930

Luminaire Tested: **S123DIP-S1165D805U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332065-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6363.1 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	84	80	77	75	70	68	66	61	59	58	54
2	92	85	79	74	86	80	74	70	70	66	63	62	59	56	54	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	77	66	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	39	33	41	35	31	36	32	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	32	27	33	29	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14235	14235	14235	14235
5°	16977	14296	12670	14296
10°	21249	14224	11444	14224
15°	26063	14110	10653	14110
20°	31047	13931	10143	13931
25°	32967	13713	10030	13713
30°	28256	13554	10082	13554
35°	19651	13328	10188	13328
40°	14802	13065	10156	13065
45°	12291	12670	10027	12670
50°	11010	11868	9937	11868
55°	10293	11003	9813	11003
60°	9655	10097	9711	10097
65°	9075	9205	9401	9205
70°	8510	8189	8954	8189
75°	7623	7170	8210	7170
80°	6670	5876	7073	5876
85°	5224	4273	4755	4273



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.0
10°-20°	417.7	6.6
20°-30°	701.1	11.0
30°-40°	793.9	12.5
40°-50°	711.9	11.2
50°-60°	574.5	9.0
60°-70°	400.3	6.3
70°-80°	210.4	3.3
80°-90°	53.9	0.8
90°-100°	175.2	2.8
100°-110°	496.2	7.8
110°-120°	488.1	7.7
120°-130°	389.3	6.1
130°-140°	307.0	4.8
140°-150°	229.1	3.6
150°-160°	159.7	2.5
160°-170°	93.8	1.5
170°-180°	30.5	0.5
0°-30°	1249.1	19.6
0°-40°	2043.0	32.1
0°-60°	3329.4	52.3
0°-90°	3994.1	62.8
90°-120°	1159.6	18.2
90°-150°	2085.0	32.8
90°-180°	2369.0	37.2
0°-180°	6363.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1571	1323	1173	1323	1571	163
15°	2339	1266	956	1266	2339	675
25°	2776	1155	844	1155	2776	1217
35°	1496	1014	775	1014	1496	972
45°	807	832	659	832	807	639
55°	548	586	523	586	548	492
65°	356	361	369	361	356	355
75°	183	172	197	172	183	196
85°	42	35	38	35	42	50
90°	18	1	18	1	18	12
95°	74	22	74	22	74	133
105°	811	74	811	74	811	800
115°	986	131	986	131	986	958
125°	778	182	778	182	778	705
135°	630	213	630	213	630	489
145°	493	243	493	243	493	313
155°	408	276	408	276	408	191
165°	356	302	356	302	356	102
175°	321	314	321	314	321	31
180°	315	315	315	315	315	



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1403.5	1402.5	1400.0	1402.0	1397.9	1392.2	1391.7	1386.6	1371.7	1370.7	1366.6
5°	1571.2	1566.0	1565.4	1564.7	1555.8	1543.6	1520.5	1518.6	1487.8	1472.4	1453.9
7.5°	1788.2	1790.9	1781.6	1773.4	1746.0	1727.9	1703.2	1671.5	1633.7	1595.4	1569.9
10°	1944.1	1965.2	1938.9	1921.0	1904.4	1872.9	1836.5	1790.9	1745.4	1692.2	1651.9
12.5°	2111.2	2121.6	2116.3	2099.4	2073.5	2025.7	1961.0	1910.9	1869.0	1780.5	1744.7
15°	2338.8	2377.9	2352.9	2295.2	2296.5	2251.0	2166.4	2073.5	2024.1	1946.6	1840.9
17.5°	2581.2	2586.1	2575.4	2527.4	2495.4	2432.9	2354.8	2265.7	2165.8	2072.0	1959.8
20°	2710.4	2706.5	2684.1	2659.2	2604.1	2555.4	2470.1	2370.8	2242.6	2150.4	2028.0
22.5°	2782.2	2775.8	2765.2	2744.2	2698.4	2646.1	2569.6	2461.1	2339.0	2211.9	2070.5
25°	2775.8	2784.1	2785.4	2779.6	2763.6	2732.2	2672.0	2585.5	2463.8	2300.4	2153.0
27.5°	2524.6	2536.4	2570.6	2601.0	2635.0	2669.5	2664.9	2622.0	2531.9	2390.8	2210.6
30°	2273.4	2247.8	2311.2	2391.4	2445.8	2541.9	2595.7	2598.9	2548.3	2427.2	2251.6
32.5°	1924.8	1953.0	1981.1	2079.7	2198.7	2306.6	2413.8	2500.0	2509.9	2429.3	2275.7
35°	1495.5	1530.8	1582.0	1633.3	1761.5	1871.7	2060.0	2224.1	2354.8	2372.1	2277.9
37.5°	1205.2	1222.5	1255.0	1306.4	1390.2	1520.9	1666.6	1874.0	2063.4	2204.2	2210.4
40°	1053.4	1058.5	1095.0	1134.2	1202.1	1309.7	1441.0	1624.3	1851.1	2047.9	2129.9
42.5°	939.6	950.9	966.4	1004.0	1058.0	1139.1	1261.2	1412.6	1620.5	1846.9	2007.3
45°	807.4	820.2	829.8	854.8	893.2	947.7	1032.9	1171.3	1329.6	1563.4	1779.4
47.5°	720.0	721.0	728.1	747.0	773.1	814.0	874.2	963.2	1108.5	1298.2	1519.9
50°	657.5	667.6	670.3	684.9	705.5	735.6	785.5	861.2	980.4	1147.0	1350.7
52.5°	613.3	616.4	623.6	634.2	652.2	675.6	718.9	778.1	871.7	1013.7	1201.0
55°	548.5	548.5	555.5	563.9	574.1	595.3	624.1	667.6	738.8	849.0	1004.0
57.5°	488.5	491.7	496.7	499.3	508.0	522.0	546.1	579.1	632.2	717.0	840.3
60°	448.5	454.3	453.6	458.8	466.5	477.4	497.9	524.8	572.2	640.1	744.0
62.5°	413.7	413.3	413.2	419.3	427.0	437.4	450.7	474.0	514.3	574.5	662.9
65°	356.3	355.0	359.5	363.3	365.9	373.6	383.8	404.3	431.2	476.1	544.6
67.5°	305.2	301.6	303.9	305.2	309.7	315.6	325.2	337.9	359.3	395.3	447.0
70°	270.4	267.2	266.5	267.8	271.7	276.1	283.2	295.4	315.3	344.1	381.9
72.5°	234.5	232.4	232.2	235.1	236.8	239.8	244.8	255.9	271.7	293.3	328.6
75°	183.3	183.3	183.3	183.9	185.8	188.4	192.2	198.0	210.2	225.5	249.2
77.5°	137.4	137.2	136.5	136.3	139.2	140.3	141.2	146.6	153.4	163.8	181.1
80°	107.6	104.4	105.7	107.6	108.9	109.6	111.5	112.8	118.5	124.3	136.5
82.5°	80.0	77.3	77.5	80.5	80.7	81.4	83.3	85.1	87.2	92.5	99.1
85°	42.3	42.3	43.0	43.0	43.5	43.0	44.8	45.5	45.5	48.7	52.5
87.5°	19.1	18.2	18.6	18.9	18.6	18.8	19.2	19.6	20.0	20.6	20.7
90°	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6	73.9	98.0	107.9
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5	306.6	378.0	336.6
97.5°	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0	626.7	585.8	428.8
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	408.0
102.5°	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1	734.3	570.5	377.3
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7	695.5	512.5	339.7
107.5°	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4	627.4	461.2	315.8
110°	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5	584.5	432.2	306.6



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1	547.3	412.8	301.5
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7	475.2	379.8	300.8
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7	460.9	374.1	302.8
122.5°	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9	449.1	370.6	306.3
125°	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7	434.1	365.9	311.7
127.5°	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9	420.9	363.6	317.8
130°	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1	413.7	362.1	321.9
132.5°	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3	407.1	361.5	325.0
135°	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1	398.4	360.8	329.5
137.5°	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4	390.9	359.4	332.6
140°	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.7
142.5°	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6	382.2	357.8	336.1
145°	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1	376.7	356.3	337.2
147.5°	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6	371.4	353.9	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5	367.8	351.9	337.2
152.5°	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8	363.7	349.3	335.7
155°	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4	357.6	344.9	334.0
157.5°	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5	350.7	340.9	331.8
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.9	330.8
162.5°	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3	341.5	334.8	328.8
165°	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5	329.3	325.6	322.7
170°	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9	325.7	322.5	320.7
172.5°	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8	322.1	320.0	319.1
175°	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4	318.0	316.8	316.8
177.5°	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1363.5	1359.4	1355.4	1348.2	1342.0	1333.3	1330.7	1327.6	1318.4	1310.3	1304.1
5°	1446.8	1431.4	1409.0	1388.5	1371.9	1349.5	1336.6	1323.1	1303.9	1286.6	1272.5
7.5°	1534.0	1503.7	1468.8	1431.2	1396.1	1362.3	1335.0	1310.6	1283.7	1258.2	1238.4
10°	1603.2	1559.6	1510.9	1458.4	1413.5	1369.9	1333.4	1301.4	1266.8	1236.6	1211.7
12.5°	1682.1	1617.6	1550.4	1486.5	1433.5	1373.0	1328.8	1288.1	1248.9	1212.6	1184.5
15°	1775.6	1693.5	1614.0	1526.3	1445.5	1369.9	1317.4	1266.2	1220.7	1183.5	1147.6
17.5°	1860.7	1767.7	1663.0	1556.2	1458.9	1369.2	1295.6	1237.7	1180.8	1135.3	1099.5
20°	1908.9	1803.1	1684.6	1573.7	1466.1	1366.1	1285.4	1216.2	1154.6	1106.6	1066.2
22.5°	1950.4	1826.7	1704.1	1585.5	1465.6	1357.9	1266.4	1195.1	1128.5	1081.5	1038.5
25°	1993.4	1845.4	1722.4	1583.3	1449.4	1337.9	1235.4	1154.6	1088.0	1032.9	988.7
27.5°	2030.3	1844.1	1698.1	1548.6	1424.0	1312.3	1202.8	1116.2	1045.5	985.6	940.8
30°	2054.9	1846.7	1673.0	1525.0	1399.5	1284.1	1177.7	1090.5	1016.3	955.4	913.1
32.5°	2070.3	1845.1	1649.9	1492.2	1360.5	1258.4	1150.6	1060.3	984.0	924.1	883.4
35°	2079.3	1833.9	1610.2	1424.4	1297.5	1198.2	1107.9	1014.3	934.3	878.5	832.3
37.5°	2061.3	1810.1	1564.1	1359.0	1220.2	1122.3	1046.4	966.6	890.0	828.7	788.9
40°	2033.1	1794.8	1528.2	1313.0	1166.9	1072.6	1008.0	929.8	854.1	795.8	758.6
42.5°	1979.3	1763.5	1488.7	1261.7	1111.5	1017.2	957.7	892.3	820.8	766.1	729.0
45°	1848.0	1695.4	1429.5	1184.8	1029.7	932.3	879.8	832.3	767.6	714.4	682.4
47.5°	1665.7	1593.1	1343.9	1103.7	944.4	850.7	796.1	757.9	710.6	667.6	636.9
50°	1539.1	1509.0	1286.0	1048.3	887.5	795.8	743.3	708.7	674.7	631.8	603.6
52.5°	1393.0	1411.6	1218.4	990.8	829.6	739.5	690.0	662.5	631.7	596.4	571.9
55°	1187.3	1254.6	1101.5	894.5	743.3	657.5	610.7	586.3	568.3	542.1	521.0
57.5°	994.7	1080.4	975.1	795.2	658.6	584.5	539.6	513.1	501.6	487.9	471.2
60°	880.4	965.0	884.9	728.6	601.7	531.2	491.5	469.0	457.5	447.9	433.8
62.5°	778.4	864.0	796.7	660.9	545.8	480.5	445.8	424.0	415.0	409.9	397.9
65°	638.2	711.9	667.0	555.5	465.9	408.1	376.7	361.4	353.0	351.1	343.5
67.5°	519.4	575.5	542.8	460.8	390.2	340.4	313.7	300.7	294.2	293.6	287.8
70°	441.5	494.0	469.0	394.7	333.9	294.7	271.7	260.2	256.3	255.7	252.5
72.5°	381.0	417.7	397.8	335.7	288.7	253.2	236.3	224.3	219.9	220.8	218.7
75°	281.9	309.5	298.0	255.0	217.2	194.1	180.0	172.4	168.5	170.5	167.9
77.5°	202.8	220.3	209.9	180.2	156.9	140.2	129.8	125.1	121.6	121.5	120.3
80°	153.1	163.4	157.6	139.7	120.5	106.4	98.0	94.8	92.9	92.3	91.6
82.5°	109.1	117.8	111.0	98.7	85.6	77.1	72.4	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.0	43.0	39.1	36.5	34.6	33.3	34.0	32.7
87.5°	21.4	21.5	19.6	17.3	16.0	14.1	13.9	12.6	11.8	12.1	11.9
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9	11.7	17.1	22.1
95°	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9	37.6	43.1	52.5
100°	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9	59.0	62.9	71.4
105°	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9	75.8	79.7	87.3
107.5°	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0	92.9	96.6	104.1
110°	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5	116.4	119.6	126.6
115°	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7	133.2	137.1	143.4
117.5°	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8	149.8	153.0	158.8
120°	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1	160.0	163.1	169.6
122.5°	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8	169.7	172.8	179.8
125°	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6	183.0	186.8	193.8
127.5°	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2	194.1	198.9	206.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0	206.4	212.6	221.8
135°	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9	215.5	222.5	232.0
137.5°	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3	224.0	230.9	241.1
140°	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0	235.7	242.6	251.8
145°	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8	254.0	259.6	267.8
150°	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4	260.1	265.1	273.5
152.5°	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0	266.2	271.3	278.6
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9	284.4	287.5	293.1
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6	294.6	296.7	300.8
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5	300.8	302.1	305.3
167.5°	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7	306.0	306.6	309.0
170°	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8	308.5	309.2	311.0
172.5°	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9	311.0	311.2	312.6
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4	314.9	314.4	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1300.5	1296.9	1291.8	1284.1	1277.9	1268.2	1268.2	1269.7	1269.7	1269.3	1268.2
5°	1261.0	1251.4	1239.9	1226.5	1212.4	1198.2	1195.6	1190.5	1186.7	1184.1	1181.0
7.5°	1219.4	1202.3	1185.5	1166.7	1149.5	1135.3	1125.4	1117.2	1112.0	1106.4	1102.2
10°	1191.2	1170.0	1150.1	1130.3	1108.5	1091.2	1080.4	1072.6	1066.9	1061.8	1059.2
12.5°	1157.9	1133.7	1111.7	1092.9	1069.0	1051.2	1040.9	1037.2	1030.5	1019.7	1014.1
15°	1109.1	1086.7	1060.5	1031.6	1020.1	998.3	986.1	980.4	976.5	968.2	965.6
17.5°	1067.5	1038.1	1008.7	987.2	965.7	948.0	941.3	934.1	929.0	922.2	920.1
20°	1034.2	1008.0	981.0	958.0	935.5	916.3	910.5	905.4	900.3	897.1	894.5
22.5°	1000.4	974.1	951.8	930.3	906.3	893.7	887.5	881.8	878.2	876.0	873.5
25°	952.8	929.8	904.7	885.5	866.3	857.9	854.1	850.9	848.4	845.1	844.5
27.5°	910.3	885.2	864.9	846.9	833.2	826.2	822.5	820.9	821.5	822.6	823.4
30°	878.5	855.4	838.8	823.4	810.6	804.1	803.5	803.5	806.1	806.7	808.0
32.5°	849.3	830.3	813.7	798.7	789.0	784.6	787.1	787.1	789.1	790.8	793.1
35°	806.7	790.0	777.2	764.4	756.1	758.0	759.3	760.6	763.8	767.6	770.2
37.5°	766.1	751.6	738.3	728.3	724.5	727.9	731.0	733.7	737.4	740.4	742.9
40°	736.9	725.9	713.1	704.2	705.5	707.4	710.0	713.1	716.4	718.3	720.9
42.5°	709.7	698.3	688.6	681.1	682.9	685.3	686.9	688.6	692.3	695.8	697.2
45°	668.3	659.3	650.4	645.9	647.2	648.5	649.7	651.7	654.8	657.5	658.0
47.5°	621.8	615.6	609.5	605.1	607.2	606.7	608.4	612.5	613.4	615.0	618.6
50°	592.1	586.3	579.3	578.0	578.0	578.0	578.6	583.8	583.8	586.3	588.9
52.5°	559.3	555.5	551.1	548.8	547.7	547.7	550.4	553.0	554.0	557.6	560.2
55°	510.7	506.9	503.0	501.1	499.8	501.1	506.2	507.4	510.7	512.6	514.5
57.5°	460.1	457.1	454.0	453.0	452.7	454.4	457.2	461.1	461.9	467.7	470.7
60°	426.7	422.2	419.7	419.7	418.4	424.2	422.9	429.3	430.6	434.5	439.0
62.5°	392.4	386.4	385.4	385.4	387.2	388.8	390.6	393.5	396.7	401.6	405.1
65°	337.0	333.9	338.3	337.7	336.4	340.2	340.2	343.5	347.3	351.8	358.8
67.5°	284.6	283.0	283.3	283.3	285.3	287.5	289.3	292.0	296.7	301.4	306.1
70°	249.2	251.2	248.0	250.5	252.5	253.1	254.4	258.2	263.3	266.5	271.7
72.5°	214.9	214.7	215.2	216.2	218.1	219.2	220.5	224.9	230.6	233.3	237.3
75°	165.3	164.7	166.6	166.6	169.8	171.0	172.4	174.3	179.4	183.3	186.5
77.5°	120.7	121.5	121.1	123.3	122.4	122.6	126.6	128.6	129.1	136.6	138.3
80°	91.0	92.3	92.9	93.5	94.2	92.9	97.4	99.3	99.3	103.8	107.0
82.5°	65.4	66.1	67.8	68.4	68.6	69.9	70.2	71.7	73.2	75.1	79.3
85°	32.7	34.6	35.2	34.6	35.2	34.0	35.9	36.5	37.2	37.2	37.2
87.5°	11.7	12.4	12.3	13.2	13.0	13.9	13.9	13.0	13.0	14.8	13.0
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6	42.6	37.6	34.3
95°	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5	155.6	121.7	98.8
97.5°	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0	458.2	375.9	299.7
100°	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1	809.5	766.1	708.7
105°	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7	892.3	904.5	887.9
107.5°	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4	881.9	937.8	960.4
110°	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5	847.7	928.1	972.7



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1	802.9	892.9	950.2
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7	670.4	754.6	825.1
120°	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7	636.7	713.3	777.6
122.5°	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9	609.8	680.6	740.5
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.3	637.4	688.4
127.5°	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9	546.7	602.0	648.4
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.1	623.4
132.5°	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3	511.1	559.1	600.5
135°	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1	486.3	527.7	564.1
137.5°	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4	462.5	498.2	529.7
140°	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6	435.5	462.0	485.8
145°	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1	418.2	438.5	457.1
147.5°	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6	405.3	421.8	434.9
150°	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5	397.1	410.5	422.6
152.5°	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8	389.5	401.3	411.4
155°	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4	378.6	388.2	395.8
157.5°	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5	368.0	375.4	381.4
160°	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4	361.4	367.8	372.3
162.5°	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3	354.2	360.1	364.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5	336.4	339.0	341.3
170°	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9	330.8	333.4	334.7
172.5°	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8	326.2	328.2	329.1
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4	320.0	321.2	321.2
177.5°	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9	316.4	316.9	316.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1264.6	1264.1	1267.7	1265.1	1267.7	1264.1	1264.6	1268.2	1269.3	1269.7	1269.7
5°	1177.0	1179.0	1172.6	1172.6	1172.6	1179.0	1177.0	1181.0	1184.1	1186.7	1190.5
7.5°	1099.2	1096.3	1096.6	1093.2	1096.6	1096.3	1099.2	1102.2	1106.4	1112.0	1117.2
10°	1051.5	1047.7	1046.4	1047.0	1046.4	1047.7	1051.5	1059.2	1061.8	1066.9	1072.6
12.5°	1012.0	1011.2	1002.8	1002.9	1002.8	1011.2	1012.0	1014.1	1019.7	1030.5	1037.2
15°	965.6	953.5	952.2	956.0	952.2	953.5	965.6	965.6	968.2	976.5	980.4
17.5°	919.1	912.7	913.1	911.2	913.1	912.7	919.1	920.1	922.2	929.0	934.1
20°	894.5	890.6	890.0	885.5	890.0	890.6	894.5	894.5	897.1	900.3	905.4
22.5°	872.0	870.7	871.1	866.1	871.1	870.7	872.0	873.5	876.0	878.2	881.8
25°	843.9	847.1	844.5	844.5	844.5	847.1	843.9	844.5	845.1	848.4	850.9
27.5°	824.9	824.8	823.5	823.5	823.5	824.8	824.9	823.4	822.6	821.5	820.9
30°	810.6	809.9	811.2	811.2	811.2	809.9	810.6	808.0	806.7	806.1	803.5
32.5°	796.2	797.1	797.4	797.9	797.4	797.1	796.2	793.1	790.8	789.1	787.1
35°	774.0	774.7	776.6	775.3	776.6	774.7	774.0	770.2	767.6	763.8	760.6
37.5°	744.0	747.0	746.3	747.4	746.3	747.0	744.0	742.9	740.4	737.4	733.7
40°	721.5	723.4	722.8	722.8	722.8	723.4	721.5	720.9	718.3	716.4	713.1
42.5°	698.5	699.9	698.1	697.2	698.1	699.9	698.5	697.2	695.8	692.3	688.6
45°	660.6	659.3	661.3	658.7	661.3	659.3	660.6	658.0	657.5	654.8	651.7
47.5°	618.3	619.6	620.1	622.1	620.1	619.6	618.3	618.6	615.0	613.4	612.5
50°	590.1	593.9	593.9	593.4	593.9	593.9	590.1	588.9	586.3	583.8	583.8
52.5°	562.5	564.3	566.8	566.7	566.8	564.3	562.5	560.2	557.6	554.0	553.0
55°	519.7	521.0	522.2	522.9	522.2	521.0	519.7	514.5	512.6	510.7	507.4
57.5°	475.3	474.8	477.8	478.7	477.8	474.8	475.3	470.7	467.7	461.9	461.1
60°	444.0	444.0	449.1	451.1	449.1	444.0	444.0	439.0	434.5	430.6	429.3
62.5°	410.7	412.8	417.9	415.2	417.9	412.8	410.7	405.1	401.6	396.7	393.5
65°	362.0	367.1	366.5	369.1	366.5	367.1	362.0	358.8	351.8	347.3	343.5
67.5°	311.1	314.4	318.9	319.4	318.9	314.4	311.1	306.1	301.4	296.7	292.0
70°	276.8	280.0	282.6	284.5	282.6	280.0	276.8	271.7	266.5	263.3	258.2
72.5°	243.5	245.2	251.3	248.6	251.3	245.2	243.5	237.3	233.3	230.6	224.9
75°	190.9	195.4	199.3	197.4	199.3	195.4	190.9	186.5	183.3	179.4	174.3
77.5°	141.2	145.7	147.5	145.9	147.5	145.7	141.2	138.3	136.6	129.1	128.6
80°	111.5	110.9	114.7	114.1	114.7	110.9	111.5	107.0	103.8	99.3	99.3
82.5°	81.8	81.1	82.9	83.3	82.9	81.1	81.8	79.3	75.1	73.2	71.7
85°	39.7	41.7	39.1	38.5	39.1	41.7	39.7	37.2	37.2	37.2	36.5
87.5°	12.8	13.0	12.6	11.9	12.6	13.0	12.8	13.0	14.8	13.0	13.0
90°	17.9	18.5	19.2	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9
92.5°	33.2	31.2	31.9	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6
95°	86.7	81.0	76.5	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5
97.5°	252.7	224.0	206.8	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0
100°	470.4	423.9	399.0	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5
102.5°	658.6	621.7	601.0	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1
105°	858.6	834.4	814.0	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7
107.5°	961.0	952.8	945.9	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4
110°	990.5	995.6	994.3	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	982.9	998.7	1003.6	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1
115°	942.1	970.1	982.9	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2
117.5°	874.9	907.0	925.4	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7
120°	828.0	863.7	879.0	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7
122.5°	785.1	817.3	834.1	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9
125°	729.2	757.2	773.1	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7
127.5°	684.7	708.7	723.1	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9
130°	657.2	680.1	693.5	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1
132.5°	632.2	655.2	667.0	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3
135°	595.3	614.5	625.9	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1
137.5°	556.0	575.4	585.1	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4
140°	531.0	548.8	559.1	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2
142.5°	506.5	522.3	531.5	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6
145°	473.0	486.3	491.5	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1
147.5°	446.9	456.0	460.9	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6
150°	432.2	439.2	443.0	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5
152.5°	418.9	425.4	427.7	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8
155°	401.5	406.7	408.0	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4
157.5°	386.4	390.2	391.3	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5
160°	376.7	380.5	380.5	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4
162.5°	367.0	370.3	370.3	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3
165°	354.4	356.9	356.3	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4
167.5°	342.4	344.2	343.6	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5
170°	335.3	336.6	335.9	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9
172.5°	329.1	330.4	329.3	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8
175°	321.2	321.9	321.2	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4
177.5°	316.4	316.9	315.9	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1268.2	1268.2	1277.9	1284.1	1291.8	1296.9	1300.5	1304.1	1310.3	1318.4	1327.6
5°	1195.6	1198.2	1212.4	1226.5	1239.9	1251.4	1261.0	1272.5	1286.6	1303.9	1323.1
7.5°	1125.4	1135.3	1149.5	1166.7	1185.5	1202.3	1219.4	1238.4	1258.2	1283.7	1310.6
10°	1080.4	1091.2	1108.5	1130.3	1150.1	1170.0	1191.2	1211.7	1236.6	1266.8	1301.4
12.5°	1040.9	1051.2	1069.0	1092.9	1111.7	1133.7	1157.9	1184.5	1212.6	1248.9	1288.1
15°	986.1	998.3	1020.1	1031.6	1060.5	1086.7	1109.1	1147.6	1183.5	1220.7	1266.2
17.5°	941.3	948.0	965.7	987.2	1008.7	1038.1	1067.5	1099.5	1135.3	1180.8	1237.7
20°	910.5	916.3	935.5	958.0	981.0	1008.0	1034.2	1066.2	1106.6	1154.6	1216.2
22.5°	887.5	893.7	906.3	930.3	951.8	974.1	1000.4	1038.5	1081.5	1128.5	1195.1
25°	854.1	857.9	866.3	885.5	904.7	929.8	952.8	988.7	1032.9	1088.0	1154.6
27.5°	822.5	826.2	833.2	846.9	864.9	885.2	910.3	940.8	985.6	1045.5	1116.2
30°	803.5	804.1	810.6	823.4	838.8	855.4	878.5	913.1	955.4	1016.3	1090.5
32.5°	787.1	784.6	789.0	798.7	813.7	830.3	849.3	883.4	924.1	984.0	1060.3
35°	759.3	758.0	756.1	764.4	777.2	790.0	806.7	832.3	878.5	934.3	1014.3
37.5°	731.0	727.9	724.5	728.3	738.3	751.6	766.1	788.9	828.7	890.0	966.6
40°	710.0	707.4	705.5	704.2	713.1	725.9	736.9	758.6	795.8	854.1	929.8
42.5°	686.9	685.3	682.9	681.1	688.6	698.3	709.7	729.0	766.1	820.8	892.3
45°	649.7	648.5	647.2	645.9	650.4	659.3	668.3	682.4	714.4	767.6	832.3
47.5°	608.4	606.7	607.2	605.1	609.5	615.6	621.8	636.9	667.6	710.6	757.9
50°	578.6	578.0	578.0	578.0	579.3	586.3	592.1	603.6	631.8	674.7	708.7
52.5°	550.4	547.7	547.7	548.8	551.1	555.5	559.3	571.9	596.4	631.7	662.5
55°	506.2	501.1	499.8	501.1	503.0	506.9	510.7	521.0	542.1	568.3	586.3
57.5°	457.2	454.4	452.7	453.0	454.0	457.1	460.1	471.2	487.9	501.6	513.1
60°	422.9	424.2	418.4	419.7	419.7	422.2	426.7	433.8	447.9	457.5	469.0
62.5°	390.6	388.8	387.2	385.4	385.4	386.4	392.4	397.9	409.9	415.0	424.0
65°	340.2	340.2	336.4	337.7	338.3	333.9	337.0	343.5	351.1	353.0	361.4
67.5°	289.3	287.5	285.3	283.3	283.3	283.0	284.6	287.8	293.6	294.2	300.7
70°	254.4	253.1	252.5	250.5	248.0	251.2	249.2	252.5	255.7	256.3	260.2
72.5°	220.5	219.2	218.1	216.2	215.2	214.7	214.9	218.7	220.8	219.9	224.3
75°	172.4	171.0	169.8	166.6	166.6	164.7	165.3	167.9	170.5	168.5	172.4
77.5°	126.6	122.6	122.4	123.3	121.1	121.5	120.7	120.3	121.5	121.6	125.1
80°	97.4	92.9	94.2	93.5	92.9	92.3	91.0	91.6	92.3	92.9	94.8
82.5°	70.2	69.9	68.6	68.4	67.8	66.1	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.2	34.6	35.2	34.6	32.7	32.7	34.0	33.3	34.6
87.5°	13.9	13.9	13.0	13.2	12.3	12.4	11.7	11.9	12.1	11.8	12.6
90°	15.3	15.9	14.0	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3
92.5°	73.9	98.0	107.9	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9
95°	306.6	378.0	336.6	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7
97.5°	626.7	585.8	428.8	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9
100°	729.2	603.6	408.0	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2
102.5°	734.3	570.5	377.3	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9
105°	695.5	512.5	339.7	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9
107.5°	627.4	461.2	315.8	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0
110°	584.5	432.2	306.6	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	547.3	412.8	301.5	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5
115°	502.3	392.0	299.6	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7
117.5°	475.2	379.8	300.8	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8
120°	460.9	374.1	302.8	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1
122.5°	449.1	370.6	306.3	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8
125°	434.1	365.9	311.7	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6
127.5°	420.9	363.6	317.8	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2
130°	413.7	362.1	321.9	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9
132.5°	407.1	361.5	325.0	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0
135°	398.4	360.8	329.5	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9
137.5°	390.9	359.4	332.6	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3
140°	386.3	358.9	334.7	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9
142.5°	382.2	357.8	336.1	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0
145°	376.7	356.3	337.2	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9
147.5°	371.4	353.9	337.2	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8
150°	367.8	351.9	337.2	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4
152.5°	363.7	349.3	335.7	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0
155°	357.6	344.9	334.0	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0
157.5°	350.7	340.9	331.8	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9
160°	346.1	337.9	330.8	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0
162.5°	341.5	334.8	328.8	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6
165°	335.3	330.2	325.7	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5
167.5°	329.3	325.6	322.7	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7
170°	325.7	322.5	320.7	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8
172.5°	322.1	320.0	319.1	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9
175°	318.0	316.8	316.8	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2
177.5°	315.4	314.9	315.4	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1330.7	1333.3	1342.0	1348.2	1355.4	1359.4	1363.5	1366.6	1370.7	1371.7	1386.6
5°	1336.6	1349.5	1371.9	1388.5	1409.0	1431.4	1446.8	1453.9	1472.4	1487.8	1518.6
7.5°	1335.0	1362.3	1396.1	1431.2	1468.8	1503.7	1534.0	1569.9	1595.4	1633.7	1671.5
10°	1333.4	1369.9	1413.5	1458.4	1510.9	1559.6	1603.2	1651.9	1692.2	1745.4	1790.9
12.5°	1328.8	1373.0	1433.5	1486.5	1550.4	1617.6	1682.1	1744.7	1780.5	1869.0	1910.9
15°	1317.4	1369.9	1445.5	1526.3	1614.0	1693.5	1775.6	1840.9	1946.6	2024.1	2073.5
17.5°	1295.6	1369.2	1458.9	1556.2	1663.0	1767.7	1860.7	1959.8	2072.0	2165.8	2265.7
20°	1285.4	1366.1	1466.1	1573.7	1684.6	1803.1	1908.9	2028.0	2150.4	2242.6	2370.8
22.5°	1266.4	1357.9	1465.6	1585.5	1704.1	1826.7	1950.4	2070.5	2211.9	2339.0	2461.1
25°	1235.4	1337.9	1449.4	1583.3	1722.4	1845.4	1993.4	2153.0	2300.4	2463.8	2585.5
27.5°	1202.8	1312.3	1424.0	1548.6	1698.1	1844.1	2030.3	2210.6	2390.8	2531.9	2622.0
30°	1177.7	1284.1	1399.5	1525.0	1673.0	1846.7	2054.9	2251.6	2427.2	2548.3	2598.9
32.5°	1150.6	1258.4	1360.5	1492.2	1649.9	1845.1	2070.3	2275.7	2429.3	2509.9	2500.0
35°	1107.9	1198.2	1297.5	1424.4	1610.2	1833.9	2079.3	2277.9	2372.1	2354.8	2224.1
37.5°	1046.4	1122.3	1220.2	1359.0	1564.1	1810.1	2061.3	2210.4	2204.2	2063.4	1874.0
40°	1008.0	1072.6	1166.9	1313.0	1528.2	1794.8	2033.1	2129.9	2047.9	1851.1	1624.3
42.5°	957.7	1017.2	1111.5	1261.7	1488.7	1763.5	1979.3	2007.3	1846.9	1620.5	1412.6
45°	879.8	932.3	1029.7	1184.8	1429.5	1695.4	1848.0	1779.4	1563.4	1329.6	1171.3
47.5°	796.1	850.7	944.4	1103.7	1343.9	1593.1	1665.7	1519.9	1298.2	1108.5	963.2
50°	743.3	795.8	887.5	1048.3	1286.0	1509.0	1539.1	1350.7	1147.0	980.4	861.2
52.5°	690.0	739.5	829.6	990.8	1218.4	1411.6	1393.0	1201.0	1013.7	871.7	778.1
55°	610.7	657.5	743.3	894.5	1101.5	1254.6	1187.3	1004.0	849.0	738.8	667.6
57.5°	539.6	584.5	658.6	795.2	975.1	1080.4	994.7	840.3	717.0	632.2	579.1
60°	491.5	531.2	601.7	728.6	884.9	965.0	880.4	744.0	640.1	572.2	524.8
62.5°	445.8	480.5	545.8	660.9	796.7	864.0	778.4	662.9	574.5	514.3	474.0
65°	376.7	408.1	465.9	555.5	667.0	711.9	638.2	544.6	476.1	431.2	404.3
67.5°	313.7	340.4	390.2	460.8	542.8	575.5	519.4	447.0	395.3	359.3	337.9
70°	271.7	294.7	333.9	394.7	469.0	494.0	441.5	381.9	344.1	315.3	295.4
72.5°	236.3	253.2	288.7	335.7	397.8	417.7	381.0	328.6	293.3	271.7	255.9
75°	180.0	194.1	217.2	255.0	298.0	309.5	281.9	249.2	225.5	210.2	198.0
77.5°	129.8	140.2	156.9	180.2	209.9	220.3	202.8	181.1	163.8	153.4	146.6
80°	98.0	106.4	120.5	139.7	157.6	163.4	153.1	136.5	124.3	118.5	112.8
82.5°	72.4	77.1	85.6	98.7	111.0	117.8	109.1	99.1	92.5	87.2	85.1
85°	36.5	39.1	43.0	48.0	55.8	58.3	55.1	52.5	48.7	45.5	45.5
87.5°	13.9	14.1	16.0	17.3	19.6	21.5	21.4	20.7	20.6	20.0	19.6
90°	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9
92.5°	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6
95°	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5
97.5°	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0
100°	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5
102.5°	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1
105°	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7
107.5°	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4
110°	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1
115°	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2
117.5°	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7
120°	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7
122.5°	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9
125°	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7
127.5°	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9
130°	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1
132.5°	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3
135°	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1
137.5°	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4
140°	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2
142.5°	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6
145°	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1
147.5°	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6
150°	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5
152.5°	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8
155°	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4
157.5°	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5
160°	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4
162.5°	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3
165°	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4
167.5°	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5
170°	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9
172.5°	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8
175°	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4
177.5°	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5	1322.5
2.5°	1391.7	1392.2	1397.9	1402.0	1400.0	1402.5	1403.5
5°	1520.5	1543.6	1555.8	1564.7	1565.4	1566.0	1571.2
7.5°	1703.2	1727.9	1746.0	1773.4	1781.6	1790.9	1788.2
10°	1836.5	1872.9	1904.4	1921.0	1938.9	1965.2	1944.1
12.5°	1961.0	2025.7	2073.5	2099.4	2116.3	2121.6	2111.2
15°	2166.4	2251.0	2296.5	2295.2	2352.9	2377.9	2338.8
17.5°	2354.8	2432.9	2495.4	2527.4	2575.4	2586.1	2581.2
20°	2470.1	2555.4	2604.1	2659.2	2684.1	2706.5	2710.4
22.5°	2569.6	2646.1	2698.4	2744.2	2765.2	2775.8	2782.2
25°	2672.0	2732.2	2763.6	2779.6	2785.4	2784.1	2775.8
27.5°	2664.9	2669.5	2635.0	2601.0	2570.6	2536.4	2524.6
30°	2595.7	2541.9	2445.8	2391.4	2311.2	2247.8	2273.4
32.5°	2413.8	2306.6	2198.7	2079.7	1981.1	1953.0	1924.8
35°	2060.0	1871.7	1761.5	1633.3	1582.0	1530.8	1495.5
37.5°	1666.6	1520.9	1390.2	1306.4	1255.0	1222.5	1205.2
40°	1441.0	1309.7	1202.1	1134.2	1095.0	1058.5	1053.4
42.5°	1261.2	1139.1	1058.0	1004.0	966.4	950.9	939.6
45°	1032.9	947.7	893.2	854.8	829.8	820.2	807.4
47.5°	874.2	814.0	773.1	747.0	728.1	721.0	720.0
50°	785.5	735.6	705.5	684.9	670.3	667.6	657.5
52.5°	718.9	675.6	652.2	634.2	623.6	616.4	613.3
55°	624.1	595.3	574.1	563.9	555.5	548.5	548.5
57.5°	546.1	522.0	508.0	499.3	496.7	491.7	488.5
60°	497.9	477.4	466.5	458.8	453.6	454.3	448.5
62.5°	450.7	437.4	427.0	419.3	413.2	413.3	413.7
65°	383.8	373.6	365.9	363.3	359.5	355.0	356.3
67.5°	325.2	315.6	309.7	305.2	303.9	301.6	305.2
70°	283.2	276.1	271.7	267.8	266.5	267.2	270.4
72.5°	244.8	239.8	236.8	235.1	232.2	232.4	234.5
75°	192.2	188.4	185.8	183.9	183.3	183.3	183.3
77.5°	141.2	140.3	139.2	136.3	136.5	137.2	137.4
80°	111.5	109.6	108.9	107.6	105.7	104.4	107.6
82.5°	83.3	81.4	80.7	80.5	77.5	77.3	80.0
85°	44.8	43.0	43.5	43.0	43.0	42.3	42.3
87.5°	19.2	18.8	18.6	18.9	18.6	18.2	19.1
90°	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332065-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)