

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332082-935

Luminaire Tested: **S123DIP-S1165D1195U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332082-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7747.6 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	1.8
10°-20°	441.2	5.7
20°-30°	740.4	9.6
30°-40°	838.4	10.8
40°-50°	751.8	9.7
50°-60°	606.7	7.8
60°-70°	422.8	5.5
70°-80°	222.2	2.9
80°-90°	58.1	0.8
90°-100°	83.0	1.1
100°-110°	248.3	3.2
110°-120°	422.3	5.5
120°-130°	555.5	7.2
130°-140°	624.4	8.1
140°-150°	613.8	7.9
150°-160°	516.7	6.7
160°-170°	343.9	4.4
170°-180°	120.4	1.6
0°-30°	1319.2	17.0
0°-40°	2157.5	27.8
0°-60°	3516.1	45.4
0°-90°	4219.2	54.5
90°-120°	753.6	9.7
90°-150°	2547.3	32.9
90°-180°	3528.0	45.5
0°-180°	7747.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	54
90°	30	1	30	1	30	17
95°	78	59	78	59	78	80
105°	238	225	238	225	238	253
115°	426	425	426	425	426	422
125°	615	622	615	622	615	550
135°	806	807	806	807	806	620
145°	979	979	979	979	979	611
155°	1119	1122	1119	1122	1119	515
165°	1218	1222	1218	1222	1218	343
175°	1266	1270	1266	1270	1266	120
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	22.2	21.1	21.5	22.0	21.4	21.8	22.1	22.5	22.8	23.2	23.2
90°	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.8	24.9	24.0	21.1
92.5°	40.4	40.6	41.0	41.2	41.5	41.2	40.6	39.9	39.1	38.4	36.8
95°	78.0	78.0	78.0	78.0	78.0	77.6	76.7	75.8	74.9	74.0	72.2
97.5°	120.0	120.1	120.2	120.3	120.4	119.9	118.9	117.9	116.8	115.8	114.5
100°	152.1	151.6	151.2	150.8	150.2	149.7	149.0	148.4	147.7	147.1	145.9
102.5°	184.9	184.9	185.0	185.1	185.2	184.9	184.3	183.6	183.0	182.3	180.8
105°	238.1	237.6	237.2	236.8	236.3	236.1	236.1	236.1	236.1	236.1	234.1
107.5°	293.5	293.8	294.0	294.3	294.5	294.4	293.7	292.9	292.2	291.5	290.7
110°	331.1	331.6	332.0	332.4	332.9	332.7	331.8	330.9	330.0	329.2	328.6



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	371.2	371.3	371.3	371.4	371.5	371.0	370.0	368.9	367.8	366.7	366.6
115°	426.2	426.4	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2	426.6
117.5°	482.0	482.6	483.2	483.9	484.5	484.8	484.8	484.9	484.9	485.0	485.6
120°	521.2	521.7	522.1	522.5	523.0	523.3	523.6	523.7	524.0	524.2	525.3
122.5°	558.8	559.4	560.1	560.7	561.3	561.9	562.5	563.1	563.6	564.2	564.8
125°	615.3	616.1	617.0	617.9	618.8	619.7	620.6	621.5	622.3	623.3	623.7
127.5°	671.5	672.4	673.5	674.5	675.5	676.7	678.0	679.2	680.4	681.7	682.2
130°	708.3	709.8	711.4	712.9	714.5	715.7	716.6	717.5	718.4	719.3	720.0
132.5°	746.7	747.9	749.1	750.3	751.5	752.6	753.7	754.8	755.8	756.9	757.3
135°	806.3	806.8	807.2	807.6	808.0	808.7	809.6	810.5	811.4	812.3	812.5
137.5°	858.9	859.8	860.7	861.4	862.3	863.2	864.1	865.0	866.0	866.9	866.3
140°	893.4	894.9	896.5	898.0	899.6	900.4	900.7	900.9	901.1	901.4	901.1
142.5°	928.6	929.8	930.9	932.1	933.3	934.1	934.3	934.5	934.7	935.0	934.5
145°	979.4	980.2	981.1	982.1	982.9	983.5	983.7	984.0	984.1	984.4	983.7
147.5°	1024.6	1025.9	1027.3	1028.6	1029.9	1030.6	1030.6	1030.6	1030.6	1030.6	1029.9
150°	1053.4	1054.7	1056.1	1057.4	1058.8	1059.4	1059.4	1059.4	1059.4	1059.4	1058.9
152.5°	1081.4	1082.5	1083.7	1084.9	1086.1	1086.4	1086.1	1085.7	1085.4	1085.0	1084.8
155°	1119.4	1121.0	1122.6	1124.1	1125.7	1126.0	1125.1	1124.2	1123.3	1122.4	1122.2
157.5°	1154.0	1155.3	1156.5	1157.8	1159.0	1159.2	1158.2	1157.3	1156.4	1155.5	1155.3
160°	1176.5	1177.3	1178.2	1179.1	1180.0	1179.9	1178.8	1177.7	1176.6	1175.4	1175.4
162.5°	1193.3	1194.6	1196.1	1197.5	1198.9	1199.1	1198.0	1196.9	1195.8	1194.6	1194.5
165°	1217.5	1219.0	1220.6	1222.1	1223.7	1223.8	1222.4	1221.2	1219.8	1218.5	1218.5
167.5°	1238.0	1239.4	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0	1237.9
170°	1248.4	1250.0	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4	1248.4
172.5°	1256.5	1258.0	1259.6	1261.1	1262.7	1262.8	1261.5	1260.1	1258.7	1257.3	1257.3
175°	1265.5	1267.0	1268.6	1270.1	1271.7	1271.8	1270.5	1269.1	1267.8	1266.4	1266.4
177.5°	1270.3	1271.5	1272.7	1274.0	1275.2	1275.3	1274.3	1273.2	1272.1	1271.1	1271.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	23.7	23.7	21.4	18.8	17.2	15.2	14.7	13.2	12.6	13.0	12.9
90°	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	35.1	33.5	31.9	30.2	28.8	27.2	25.7	24.2	25.7	27.2	28.8
95°	70.4	68.7	66.9	65.3	63.7	62.2	60.6	59.1	60.6	62.2	63.7
97.5°	113.3	112.0	110.7	109.4	108.3	107.2	106.0	104.9	106.0	107.2	108.3
100°	144.8	143.7	142.6	141.4	140.1	138.7	137.4	136.0	137.4	138.7	140.1
102.5°	179.3	177.9	176.4	175.3	174.4	173.7	172.9	172.0	172.9	173.7	174.4
105°	232.1	230.1	228.1	226.9	226.4	226.0	225.5	225.1	225.5	226.0	226.4
107.5°	289.9	289.1	288.3	287.7	287.5	287.2	287.0	286.7	287.0	287.2	287.5
110°	328.2	327.8	327.4	326.9	326.5	326.0	325.5	325.1	325.5	326.0	326.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.5	366.4	366.4	366.2	365.9	365.7	365.4	365.2	365.4	365.7	365.9
115°	427.1	427.5	427.9	427.8	427.1	426.5	425.9	425.2	425.9	426.5	427.1
117.5°	486.1	486.7	487.3	487.3	486.9	486.5	486.0	485.6	486.0	486.5	486.9
120°	526.4	527.5	528.7	528.6	527.2	525.9	524.5	523.2	524.5	525.9	527.2
122.5°	565.3	565.9	566.5	566.4	565.3	564.4	563.4	562.4	563.4	564.4	565.3
125°	624.1	624.6	625.0	624.9	624.2	623.5	622.9	622.2	622.9	623.5	624.2
127.5°	682.6	683.1	683.6	683.1	681.7	680.3	678.9	677.4	678.9	680.3	681.7
130°	720.6	721.3	721.9	721.3	719.6	717.8	716.0	714.3	716.0	717.8	719.6
132.5°	757.9	758.4	758.9	758.2	756.4	754.7	752.9	751.1	752.9	754.7	756.4
135°	812.8	813.0	813.2	812.6	811.3	809.9	808.7	807.3	808.7	809.9	811.3
137.5°	865.7	865.2	864.6	863.8	862.6	861.5	860.4	859.4	860.4	861.5	862.6
140°	900.9	900.7	900.4	899.7	898.7	897.6	896.5	895.4	896.5	897.6	898.7
142.5°	934.2	933.8	933.3	932.6	931.5	930.4	929.3	928.2	929.3	930.4	931.5
145°	983.0	982.4	981.7	981.1	980.7	980.2	979.8	979.4	979.8	980.2	980.7
147.5°	1029.3	1028.7	1028.1	1027.4	1026.6	1025.8	1025.0	1024.2	1025.0	1025.8	1026.6
150°	1058.5	1058.1	1057.7	1057.2	1056.7	1056.3	1055.8	1055.4	1055.8	1056.3	1056.7
152.5°	1084.5	1084.2	1083.9	1083.5	1082.9	1082.3	1081.7	1081.0	1081.7	1082.3	1082.9
155°	1122.0	1121.8	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
157.5°	1155.1	1154.9	1154.7	1154.8	1155.0	1155.3	1155.5	1155.8	1155.5	1155.3	1155.0
160°	1175.4	1175.4	1175.4	1175.7	1176.1	1176.6	1177.0	1177.4	1177.0	1176.6	1176.1
162.5°	1194.3	1194.1	1193.9	1194.2	1194.8	1195.4	1196.0	1196.6	1196.0	1195.4	1194.8
165°	1218.5	1218.5	1218.5	1218.8	1219.4	1220.1	1220.8	1221.5	1220.8	1220.1	1219.4
167.5°	1237.7	1237.5	1237.3	1237.7	1238.6	1239.5	1240.4	1241.3	1240.4	1239.5	1238.6
170°	1248.4	1248.4	1248.4	1248.9	1249.8	1250.7	1251.5	1252.5	1251.5	1250.7	1249.8
172.5°	1257.3	1257.3	1257.3	1257.7	1258.6	1259.5	1260.4	1261.3	1260.4	1259.5	1258.6
175°	1266.4	1266.4	1266.4	1267.0	1267.8	1268.7	1269.6	1270.5	1269.6	1268.7	1267.8
177.5°	1271.1	1271.1	1271.1	1271.4	1272.1	1272.9	1273.6	1274.3	1273.6	1272.9	1272.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	12.8	13.9	13.9	15.0	15.1	16.2	16.4	15.4	15.6	17.4	15.4
90°	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.8	26.7	27.6	28.2
92.5°	30.2	31.9	33.5	35.1	36.8	38.4	39.1	39.9	40.6	41.2	41.5
95°	65.3	66.9	68.7	70.4	72.2	74.0	74.9	75.8	76.7	77.6	78.0
97.5°	109.4	110.7	112.0	113.3	114.5	115.8	116.8	117.9	118.9	119.9	120.4
100°	141.4	142.6	143.7	144.8	145.9	147.1	147.7	148.4	149.0	149.7	150.2
102.5°	175.3	176.4	177.9	179.3	180.8	182.3	183.0	183.6	184.3	184.9	185.2
105°	226.9	228.1	230.1	232.1	234.1	236.1	236.1	236.1	236.1	236.1	236.3
107.5°	287.7	288.3	289.1	289.9	290.7	291.5	292.2	292.9	293.7	294.4	294.5
110°	326.9	327.4	327.8	328.2	328.6	329.2	330.0	330.9	331.8	332.7	332.9



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	366.2	366.4	366.4	366.5	366.6	366.7	367.8	368.9	370.0	371.0	371.5
115°	427.8	427.9	427.5	427.1	426.6	426.2	426.4	426.6	426.8	427.1	427.1
117.5°	487.3	487.3	486.7	486.1	485.6	485.0	484.9	484.9	484.8	484.8	484.5
120°	528.6	528.7	527.5	526.4	525.3	524.2	524.0	523.7	523.6	523.3	523.0
122.5°	566.4	566.5	565.9	565.3	564.8	564.2	563.6	563.1	562.5	561.9	561.3
125°	624.9	625.0	624.6	624.1	623.7	623.3	622.3	621.5	620.6	619.7	618.8
127.5°	683.1	683.6	683.1	682.6	682.2	681.7	680.4	679.2	678.0	676.7	675.5
130°	721.3	721.9	721.3	720.6	720.0	719.3	718.4	717.5	716.6	715.7	714.5
132.5°	758.2	758.9	758.4	757.9	757.3	756.9	755.8	754.8	753.7	752.6	751.5
135°	812.6	813.2	813.0	812.8	812.5	812.3	811.4	810.5	809.6	808.7	808.0
137.5°	863.8	864.6	865.2	865.7	866.3	866.9	866.0	865.0	864.1	863.2	862.3
140°	899.7	900.4	900.7	900.9	901.1	901.4	901.1	900.9	900.7	900.4	899.6
142.5°	932.6	933.3	933.8	934.2	934.5	935.0	934.7	934.5	934.3	934.1	933.3
145°	981.1	981.7	982.4	983.0	983.7	984.4	984.1	984.0	983.7	983.5	982.9
147.5°	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6	1030.6	1030.6	1030.6	1029.9
150°	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4	1059.4	1059.4	1059.4	1058.8
152.5°	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4	1085.7	1086.1	1086.4	1086.1
155°	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3	1124.2	1125.1	1126.0	1125.7
157.5°	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4	1157.3	1158.2	1159.2	1159.0
160°	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6	1177.7	1178.8	1179.9	1180.0
162.5°	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8	1196.9	1198.0	1199.1	1198.9
165°	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8	1221.2	1222.4	1223.8	1223.7
167.5°	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4	1240.8	1242.2	1243.5	1243.5
170°	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0	1251.5	1253.2	1254.7	1254.7
172.5°	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7	1260.1	1261.5	1262.8	1262.7
175°	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8	1269.1	1270.5	1271.8	1271.7
177.5°	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1	1273.2	1274.3	1275.3	1275.2
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	15.5	15.6	15.2	14.6	15.2	15.6	15.5	15.4	17.4	15.6	15.4
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.8
92.5°	41.2	41.0	40.6	40.4	40.6	41.0	41.2	41.5	41.2	40.6	39.9
95°	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	77.6	76.7	75.8
97.5°	120.3	120.2	120.1	120.0	120.1	120.2	120.3	120.4	119.9	118.9	117.9
100°	150.8	151.2	151.6	152.1	151.6	151.2	150.8	150.2	149.7	149.0	148.4
102.5°	185.1	185.0	184.9	184.9	184.9	185.0	185.1	185.2	184.9	184.3	183.6
105°	236.8	237.2	237.6	238.1	237.6	237.2	236.8	236.3	236.1	236.1	236.1
107.5°	294.3	294.0	293.8	293.5	293.8	294.0	294.3	294.5	294.4	293.7	292.9
110°	332.4	332.0	331.6	331.1	331.6	332.0	332.4	332.9	332.7	331.8	330.9



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	371.4	371.3	371.3	371.2	371.3	371.3	371.4	371.5	371.0	370.0	368.9
115°	426.8	426.6	426.4	426.2	426.4	426.6	426.8	427.1	427.1	426.8	426.6
117.5°	483.9	483.2	482.6	482.0	482.6	483.2	483.9	484.5	484.8	484.8	484.9
120°	522.5	522.1	521.7	521.2	521.7	522.1	522.5	523.0	523.3	523.6	523.7
122.5°	560.7	560.1	559.4	558.8	559.4	560.1	560.7	561.3	561.9	562.5	563.1
125°	617.9	617.0	616.1	615.3	616.1	617.0	617.9	618.8	619.7	620.6	621.5
127.5°	674.5	673.5	672.4	671.5	672.4	673.5	674.5	675.5	676.7	678.0	679.2
130°	712.9	711.4	709.8	708.3	709.8	711.4	712.9	714.5	715.7	716.6	717.5
132.5°	750.3	749.1	747.9	746.7	747.9	749.1	750.3	751.5	752.6	753.7	754.8
135°	807.6	807.2	806.8	806.3	806.8	807.2	807.6	808.0	808.7	809.6	810.5
137.5°	861.4	860.7	859.8	858.9	859.8	860.7	861.4	862.3	863.2	864.1	865.0
140°	898.0	896.5	894.9	893.4	894.9	896.5	898.0	899.6	900.4	900.7	900.9
142.5°	932.1	930.9	929.8	928.6	929.8	930.9	932.1	933.3	934.1	934.3	934.5
145°	982.1	981.1	980.2	979.4	980.2	981.1	982.1	982.9	983.5	983.7	984.0
147.5°	1028.6	1027.3	1025.9	1024.6	1025.9	1027.3	1028.6	1029.9	1030.6	1030.6	1030.6
150°	1057.4	1056.1	1054.7	1053.4	1054.7	1056.1	1057.4	1058.8	1059.4	1059.4	1059.4
152.5°	1084.9	1083.7	1082.5	1081.4	1082.5	1083.7	1084.9	1086.1	1086.4	1086.1	1085.7
155°	1124.1	1122.6	1121.0	1119.4	1121.0	1122.6	1124.1	1125.7	1126.0	1125.1	1124.2
157.5°	1157.8	1156.5	1155.3	1154.0	1155.3	1156.5	1157.8	1159.0	1159.2	1158.2	1157.3
160°	1179.1	1178.2	1177.3	1176.5	1177.3	1178.2	1179.1	1180.0	1179.9	1178.8	1177.7
162.5°	1197.5	1196.1	1194.6	1193.3	1194.6	1196.1	1197.5	1198.9	1199.1	1198.0	1196.9
165°	1222.1	1220.6	1219.0	1217.5	1219.0	1220.6	1222.1	1223.7	1223.8	1222.4	1221.2
167.5°	1242.2	1240.8	1239.4	1238.0	1239.4	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8
170°	1253.2	1251.5	1250.0	1248.4	1250.0	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5
172.5°	1261.1	1259.6	1258.0	1256.5	1258.0	1259.6	1261.1	1262.7	1262.8	1261.5	1260.1
175°	1270.1	1268.6	1267.0	1265.5	1267.0	1268.6	1270.1	1271.7	1271.8	1270.5	1269.1
177.5°	1274.0	1272.7	1271.5	1270.3	1271.5	1272.7	1274.0	1275.2	1275.3	1274.3	1273.2
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	16.4	16.2	15.1	15.0	13.9	13.9	12.8	12.9	13.0	12.6	13.2
90°	24.9	24.0	21.1	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0
92.5°	39.1	38.4	36.8	35.1	33.5	31.9	30.2	28.8	27.2	25.7	24.2
95°	74.9	74.0	72.2	70.4	68.7	66.9	65.3	63.7	62.2	60.6	59.1
97.5°	116.8	115.8	114.5	113.3	112.0	110.7	109.4	108.3	107.2	106.0	104.9
100°	147.7	147.1	145.9	144.8	143.7	142.6	141.4	140.1	138.7	137.4	136.0
102.5°	183.0	182.3	180.8	179.3	177.9	176.4	175.3	174.4	173.7	172.9	172.0
105°	236.1	236.1	234.1	232.1	230.1	228.1	226.9	226.4	226.0	225.5	225.1
107.5°	292.2	291.5	290.7	289.9	289.1	288.3	287.7	287.5	287.2	287.0	286.7
110°	330.0	329.2	328.6	328.2	327.8	327.4	326.9	326.5	326.0	325.5	325.1



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	367.8	366.7	366.6	366.5	366.4	366.4	366.2	365.9	365.7	365.4	365.2
115°	426.4	426.2	426.6	427.1	427.5	427.9	427.8	427.1	426.5	425.9	425.2
117.5°	484.9	485.0	485.6	486.1	486.7	487.3	487.3	486.9	486.5	486.0	485.6
120°	524.0	524.2	525.3	526.4	527.5	528.7	528.6	527.2	525.9	524.5	523.2
122.5°	563.6	564.2	564.8	565.3	565.9	566.5	566.4	565.3	564.4	563.4	562.4
125°	622.3	623.3	623.7	624.1	624.6	625.0	624.9	624.2	623.5	622.9	622.2
127.5°	680.4	681.7	682.2	682.6	683.1	683.6	683.1	681.7	680.3	678.9	677.4
130°	718.4	719.3	720.0	720.6	721.3	721.9	721.3	719.6	717.8	716.0	714.3
132.5°	755.8	756.9	757.3	757.9	758.4	758.9	758.2	756.4	754.7	752.9	751.1
135°	811.4	812.3	812.5	812.8	813.0	813.2	812.6	811.3	809.9	808.7	807.3
137.5°	866.0	866.9	866.3	865.7	865.2	864.6	863.8	862.6	861.5	860.4	859.4
140°	901.1	901.4	901.1	900.9	900.7	900.4	899.7	898.7	897.6	896.5	895.4
142.5°	934.7	935.0	934.5	934.2	933.8	933.3	932.6	931.5	930.4	929.3	928.2
145°	984.1	984.4	983.7	983.0	982.4	981.7	981.1	980.7	980.2	979.8	979.4
147.5°	1030.6	1030.6	1029.9	1029.3	1028.7	1028.1	1027.4	1026.6	1025.8	1025.0	1024.2
150°	1059.4	1059.4	1058.9	1058.5	1058.1	1057.7	1057.2	1056.7	1056.3	1055.8	1055.4
152.5°	1085.4	1085.0	1084.8	1084.5	1084.2	1083.9	1083.5	1082.9	1082.3	1081.7	1081.0
155°	1123.3	1122.4	1122.2	1122.0	1121.8	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5
157.5°	1156.4	1155.5	1155.3	1155.1	1154.9	1154.7	1154.8	1155.0	1155.3	1155.5	1155.8
160°	1176.6	1175.4	1175.4	1175.4	1175.4	1175.4	1175.7	1176.1	1176.6	1177.0	1177.4
162.5°	1195.8	1194.6	1194.5	1194.3	1194.1	1193.9	1194.2	1194.8	1195.4	1196.0	1196.6
165°	1219.8	1218.5	1218.5	1218.5	1218.5	1218.5	1218.8	1219.4	1220.1	1220.8	1221.5
167.5°	1239.4	1238.0	1237.9	1237.7	1237.5	1237.3	1237.7	1238.6	1239.5	1240.4	1241.3
170°	1250.0	1248.4	1248.4	1248.4	1248.4	1248.4	1248.9	1249.8	1250.7	1251.5	1252.5
172.5°	1258.7	1257.3	1257.3	1257.3	1257.3	1257.3	1257.7	1258.6	1259.5	1260.4	1261.3
175°	1267.8	1266.4	1266.4	1266.4	1266.4	1266.4	1267.0	1267.8	1268.7	1269.6	1270.5
177.5°	1272.1	1271.1	1271.1	1271.1	1271.1	1271.1	1271.4	1272.1	1272.9	1273.6	1274.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.7	15.2	17.2	18.8	21.4	23.7	23.7	23.2	23.2	22.8	22.5
90°	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.8
92.5°	25.7	27.2	28.8	30.2	31.9	33.5	35.1	36.8	38.4	39.1	39.9
95°	60.6	62.2	63.7	65.3	66.9	68.7	70.4	72.2	74.0	74.9	75.8
97.5°	106.0	107.2	108.3	109.4	110.7	112.0	113.3	114.5	115.8	116.8	117.9
100°	137.4	138.7	140.1	141.4	142.6	143.7	144.8	145.9	147.1	147.7	148.4
102.5°	172.9	173.7	174.4	175.3	176.4	177.9	179.3	180.8	182.3	183.0	183.6
105°	225.5	226.0	226.4	226.9	228.1	230.1	232.1	234.1	236.1	236.1	236.1
107.5°	287.0	287.2	287.5	287.7	288.3	289.1	289.9	290.7	291.5	292.2	292.9
110°	325.5	326.0	326.5	326.9	327.4	327.8	328.2	328.6	329.2	330.0	330.9



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	365.4	365.7	365.9	366.2	366.4	366.4	366.5	366.6	366.7	367.8	368.9
115°	425.9	426.5	427.1	427.8	427.9	427.5	427.1	426.6	426.2	426.4	426.6
117.5°	486.0	486.5	486.9	487.3	487.3	486.7	486.1	485.6	485.0	484.9	484.9
120°	524.5	525.9	527.2	528.6	528.7	527.5	526.4	525.3	524.2	524.0	523.7
122.5°	563.4	564.4	565.3	566.4	566.5	565.9	565.3	564.8	564.2	563.6	563.1
125°	622.9	623.5	624.2	624.9	625.0	624.6	624.1	623.7	623.3	622.3	621.5
127.5°	678.9	680.3	681.7	683.1	683.6	683.1	682.6	682.2	681.7	680.4	679.2
130°	716.0	717.8	719.6	721.3	721.9	721.3	720.6	720.0	719.3	718.4	717.5
132.5°	752.9	754.7	756.4	758.2	758.9	758.4	757.9	757.3	756.9	755.8	754.8
135°	808.7	809.9	811.3	812.6	813.2	813.0	812.8	812.5	812.3	811.4	810.5
137.5°	860.4	861.5	862.6	863.8	864.6	865.2	865.7	866.3	866.9	866.0	865.0
140°	896.5	897.6	898.7	899.7	900.4	900.7	900.9	901.1	901.4	901.1	900.9
142.5°	929.3	930.4	931.5	932.6	933.3	933.8	934.2	934.5	935.0	934.7	934.5
145°	979.8	980.2	980.7	981.1	981.7	982.4	983.0	983.7	984.4	984.1	984.0
147.5°	1025.0	1025.8	1026.6	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6	1030.6
150°	1055.8	1056.3	1056.7	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4	1059.4
152.5°	1081.7	1082.3	1082.9	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4	1085.7
155°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3	1124.2
157.5°	1155.5	1155.3	1155.0	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4	1157.3
160°	1177.0	1176.6	1176.1	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6	1177.7
162.5°	1196.0	1195.4	1194.8	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8	1196.9
165°	1220.8	1220.1	1219.4	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8	1221.2
167.5°	1240.4	1239.5	1238.6	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4	1240.8
170°	1251.5	1250.7	1249.8	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0	1251.5
172.5°	1260.4	1259.5	1258.6	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7	1260.1
175°	1269.6	1268.7	1267.8	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8	1269.1
177.5°	1273.6	1272.9	1272.1	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1	1273.2
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	22.1	21.8	21.4	22.0	21.5	21.1	22.2
90°	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	40.6	41.2	41.5	41.2	41.0	40.6	40.4
95°	76.7	77.6	78.0	78.0	78.0	78.0	78.0
97.5°	118.9	119.9	120.4	120.3	120.2	120.1	120.0
100°	149.0	149.7	150.2	150.8	151.2	151.6	152.1
102.5°	184.3	184.9	185.2	185.1	185.0	184.9	184.9
105°	236.1	236.1	236.3	236.8	237.2	237.6	238.1
107.5°	293.7	294.4	294.5	294.3	294.0	293.8	293.5
110°	331.8	332.7	332.9	332.4	332.0	331.6	331.1



TEST NUMBER: P332082-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	370.0	371.0	371.5	371.4	371.3	371.3	371.2
115°	426.8	427.1	427.1	426.8	426.6	426.4	426.2
117.5°	484.8	484.8	484.5	483.9	483.2	482.6	482.0
120°	523.6	523.3	523.0	522.5	522.1	521.7	521.2
122.5°	562.5	561.9	561.3	560.7	560.1	559.4	558.8
125°	620.6	619.7	618.8	617.9	617.0	616.1	615.3
127.5°	678.0	676.7	675.5	674.5	673.5	672.4	671.5
130°	716.6	715.7	714.5	712.9	711.4	709.8	708.3
132.5°	753.7	752.6	751.5	750.3	749.1	747.9	746.7
135°	809.6	808.7	808.0	807.6	807.2	806.8	806.3
137.5°	864.1	863.2	862.3	861.4	860.7	859.8	858.9
140°	900.7	900.4	899.6	898.0	896.5	894.9	893.4
142.5°	934.3	934.1	933.3	932.1	930.9	929.8	928.6
145°	983.7	983.5	982.9	982.1	981.1	980.2	979.4
147.5°	1030.6	1030.6	1029.9	1028.6	1027.3	1025.9	1024.6
150°	1059.4	1059.4	1058.8	1057.4	1056.1	1054.7	1053.4
152.5°	1086.1	1086.4	1086.1	1084.9	1083.7	1082.5	1081.4
155°	1125.1	1126.0	1125.7	1124.1	1122.6	1121.0	1119.4
157.5°	1158.2	1159.2	1159.0	1157.8	1156.5	1155.3	1154.0
160°	1178.8	1179.9	1180.0	1179.1	1178.2	1177.3	1176.5
162.5°	1198.0	1199.1	1198.9	1197.5	1196.1	1194.6	1193.3
165°	1222.4	1223.8	1223.7	1222.1	1220.6	1219.0	1217.5
167.5°	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0
170°	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4
172.5°	1261.5	1262.8	1262.7	1261.1	1259.6	1258.0	1256.5
175°	1270.5	1271.8	1271.7	1270.1	1268.6	1267.0	1265.5
177.5°	1274.3	1275.3	1275.2	1274.0	1272.7	1271.5	1270.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5

(END OF REPORT)