

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332069-930

Luminaire Tested: **S123DIP-S1165D805U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332069-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6497.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	95	91	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	21
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.2
10°-20°	396.4	6.1
20°-30°	585.6	9.0
30°-40°	684.0	10.5
40°-50°	687.7	10.6
50°-60°	604.1	9.3
60°-70°	450.0	6.9
70°-80°	256.4	3.9
80°-90°	76.0	1.2
90°-100°	31.2	0.5
100°-110°	148.7	2.3
110°-120°	357.1	5.5
120°-130°	454.7	7.0
130°-140°	485.8	7.5
140°-150°	454.3	7.0
150°-160°	366.5	5.6
160°-170°	236.5	3.6
170°-180°	81.5	1.3
0°-30°	1122.4	17.3
0°-40°	1806.5	27.8
0°-60°	3098.3	47.7
0°-90°	3880.7	59.7
90°-120°	536.9	8.3
90°-150°	1931.8	29.7
90°-180°	2616.0	40.3
0°-180°	6497.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	7	15	18	19	5
95°	39	15	20	24	24	48
105°	190	193	140	33	28	201
115°	356	360	366	372	375	352
125°	502	507	510	511	512	448
135°	625	629	632	633	632	481
145°	722	726	727	728	729	451
155°	795	794	794	797	794	366
165°	838	836	836	840	836	237
175°	858	855	855	859	855	82
180°	858	858	858	858	858	



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.8	26.4	26.0	25.6	25.2	25.0	25.2	25.4	25.4	25.6	25.5
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	11.8	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2
95°	38.9	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8
97.5°	78.1	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7
100°	107.7	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2
102.5°	141.4	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4
105°	190.0	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5
107.5°	241.2	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5
110°	275.3	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7
115°	356.3	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3
117.5°	403.1	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9
120°	432.2	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9
122.5°	461.7	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7
125°	502.3	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2
127.5°	541.5	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2
130°	566.0	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2
132.5°	589.5	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2
135°	625.3	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1
137.5°	655.9	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8
140°	676.3	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6
142.5°	695.1	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3
145°	721.5	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6
147.5°	746.4	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9
150°	761.7	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2
152.5°	775.4	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6
155°	794.8	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9
157.5°	809.8	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0
160°	819.0	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6
162.5°	827.7	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4
165°	838.2	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7
167.5°	846.4	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9
170°	850.9	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5
172.5°	853.9	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6
175°	857.9	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4
177.5°	858.9	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	25.4	25.3	25.2	25.1	25.2	25.3	25.3	25.4
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	18.1	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	21.8	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	22.8	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	23.3	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	34.9	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	89.4	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	219.1	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	278.1	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332069-930

CATALOG NUMBER: S123DIP-S1165D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	368.7	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	413.0	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	442.1	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	470.4	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.5	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	550.6	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	574.8	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	597.7	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	663.5	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.1	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	701.8	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	727.8	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.1	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.4	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.1	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	795.7	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	810.8	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	819.5	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	827.4	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	837.9	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	853.7	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	857.4	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	858.8	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)