

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332088-935

Luminaire Tested: **S123DIP-S1165D1195U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332088-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7627.9 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50	45
2	90	82	76	71	83	76	71	66	66	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	37	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	38	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	1.9
10°-20°	418.7	5.5
20°-30°	618.4	8.1
30°-40°	722.4	9.5
40°-50°	726.3	9.5
50°-60°	638.0	8.4
60°-70°	475.3	6.2
70°-80°	270.8	3.5
80°-90°	81.5	1.1
90°-100°	83.0	1.1
100°-110°	248.3	3.3
110°-120°	422.3	5.5
120°-130°	555.5	7.3
130°-140°	624.4	8.2
140°-150°	613.8	8.0
150°-160°	516.7	6.8
160°-170°	343.9	4.5
170°-180°	120.4	1.6
0°-30°	1185.3	15.5
0°-40°	1907.7	25.0
0°-60°	3272.0	42.9
0°-90°	4099.5	53.7
90°-120°	753.6	9.9
90°-150°	2547.3	33.4
90°-180°	3528.0	46.3
0°-180°	7627.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	11	24	28	30	7
95°	59	66	74	78	78	66
105°	225	228	236	236	238	241
115°	425	428	426	427	426	421
125°	622	625	623	619	615	555
135°	807	813	812	808	806	622
145°	979	981	984	983	979	612
155°	1122	1122	1122	1126	1119	516
165°	1222	1219	1218	1224	1218	344
175°	1270	1267	1266	1272	1266	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.3	28.1	27.8	27.6	27.2	27.3	27.6	28.0	28.3	28.6	28.6
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	24.2	25.7	27.2	28.8	30.2	31.9	33.5	35.1	36.8	38.4	39.1
95°	59.1	60.6	62.2	63.7	65.3	66.9	68.7	70.4	72.2	74.0	74.9
97.5°	104.9	106.0	107.2	108.3	109.4	110.7	112.0	113.3	114.5	115.8	116.8
100°	136.0	137.4	138.7	140.1	141.4	142.6	143.7	144.8	145.9	147.1	147.7
102.5°	172.0	172.9	173.7	174.4	175.3	176.4	177.9	179.3	180.8	182.3	183.0
105°	225.1	225.5	226.0	226.4	226.9	228.1	230.1	232.1	234.1	236.1	236.1
107.5°	286.7	287.0	287.2	287.5	287.7	288.3	289.1	289.9	290.7	291.5	292.2
110°	325.1	325.5	326.0	326.5	326.9	327.4	327.8	328.2	328.6	329.2	330.0



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	365.2	365.4	365.7	365.9	366.2	366.4	366.4	366.5	366.6	366.7	367.8
115°	425.2	425.9	426.5	427.1	427.8	427.9	427.5	427.1	426.6	426.2	426.4
117.5°	485.6	486.0	486.5	486.9	487.3	487.3	486.7	486.1	485.6	485.0	484.9
120°	523.2	524.5	525.9	527.2	528.6	528.7	527.5	526.4	525.3	524.2	524.0
122.5°	562.4	563.4	564.4	565.3	566.4	566.5	565.9	565.3	564.8	564.2	563.6
125°	622.2	622.9	623.5	624.2	624.9	625.0	624.6	624.1	623.7	623.3	622.3
127.5°	677.4	678.9	680.3	681.7	683.1	683.6	683.1	682.6	682.2	681.7	680.4
130°	714.3	716.0	717.8	719.6	721.3	721.9	721.3	720.6	720.0	719.3	718.4
132.5°	751.1	752.9	754.7	756.4	758.2	758.9	758.4	757.9	757.3	756.9	755.8
135°	807.3	808.7	809.9	811.3	812.6	813.2	813.0	812.8	812.5	812.3	811.4
137.5°	859.4	860.4	861.5	862.6	863.8	864.6	865.2	865.7	866.3	866.9	866.0
140°	895.4	896.5	897.6	898.7	899.7	900.4	900.7	900.9	901.1	901.4	901.1
142.5°	928.2	929.3	930.4	931.5	932.6	933.3	933.8	934.2	934.5	935.0	934.7
145°	979.4	979.8	980.2	980.7	981.1	981.7	982.4	983.0	983.7	984.4	984.1
147.5°	1024.2	1025.0	1025.8	1026.6	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6
150°	1055.4	1055.8	1056.3	1056.7	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4
152.5°	1081.0	1081.7	1082.3	1082.9	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4
155°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3
157.5°	1155.8	1155.5	1155.3	1155.0	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4
160°	1177.4	1177.0	1176.6	1176.1	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6
162.5°	1196.6	1196.0	1195.4	1194.8	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8
165°	1221.5	1220.8	1220.1	1219.4	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8
167.5°	1241.3	1240.4	1239.5	1238.6	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4
170°	1252.5	1251.5	1250.7	1249.8	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0
172.5°	1261.3	1260.4	1259.5	1258.6	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7
175°	1270.5	1269.6	1268.7	1267.8	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8
177.5°	1274.3	1273.6	1272.9	1272.1	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	28.5	28.4	28.4	28.4	28.5	28.6	28.7	28.8
90°	25.8	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	39.9	40.6	41.2	41.5	41.2	41.0	40.6	40.4
95°	75.8	76.7	77.6	78.0	78.0	78.0	78.0	78.0
97.5°	117.9	118.9	119.9	120.4	120.3	120.2	120.1	120.0
100°	148.4	149.0	149.7	150.2	150.8	151.2	151.6	152.1
102.5°	183.6	184.3	184.9	185.2	185.1	185.0	184.9	184.9
105°	236.1	236.1	236.1	236.3	236.8	237.2	237.6	238.1
107.5°	292.9	293.7	294.4	294.5	294.3	294.0	293.8	293.5
110°	330.9	331.8	332.7	332.9	332.4	332.0	331.6	331.1



TEST NUMBER: P332088-935

CATALOG NUMBER: S123DIP-S1165D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.9	370.0	371.0	371.5	371.4	371.3	371.3	371.2
115°	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2
117.5°	484.9	484.8	484.8	484.5	483.9	483.2	482.6	482.0
120°	523.7	523.6	523.3	523.0	522.5	522.1	521.7	521.2
122.5°	563.1	562.5	561.9	561.3	560.7	560.1	559.4	558.8
125°	621.5	620.6	619.7	618.8	617.9	617.0	616.1	615.3
127.5°	679.2	678.0	676.7	675.5	674.5	673.5	672.4	671.5
130°	717.5	716.6	715.7	714.5	712.9	711.4	709.8	708.3
132.5°	754.8	753.7	752.6	751.5	750.3	749.1	747.9	746.7
135°	810.5	809.6	808.7	808.0	807.6	807.2	806.8	806.3
137.5°	865.0	864.1	863.2	862.3	861.4	860.7	859.8	858.9
140°	900.9	900.7	900.4	899.6	898.0	896.5	894.9	893.4
142.5°	934.5	934.3	934.1	933.3	932.1	930.9	929.8	928.6
145°	984.0	983.7	983.5	982.9	982.1	981.1	980.2	979.4
147.5°	1030.6	1030.6	1030.6	1029.9	1028.6	1027.3	1025.9	1024.6
150°	1059.4	1059.4	1059.4	1058.8	1057.4	1056.1	1054.7	1053.4
152.5°	1085.7	1086.1	1086.4	1086.1	1084.9	1083.7	1082.5	1081.4
155°	1124.2	1125.1	1126.0	1125.7	1124.1	1122.6	1121.0	1119.4
157.5°	1157.3	1158.2	1159.2	1159.0	1157.8	1156.5	1155.3	1154.0
160°	1177.7	1178.8	1179.9	1180.0	1179.1	1178.2	1177.3	1176.5
162.5°	1196.9	1198.0	1199.1	1198.9	1197.5	1196.1	1194.6	1193.3
165°	1221.2	1222.4	1223.8	1223.7	1222.1	1220.6	1219.0	1217.5
167.5°	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0
170°	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4
172.5°	1260.1	1261.5	1262.8	1262.7	1261.1	1259.6	1258.0	1256.5
175°	1269.1	1270.5	1271.8	1271.7	1270.1	1268.6	1267.0	1265.5
177.5°	1273.2	1274.3	1275.3	1275.2	1274.0	1272.7	1271.5	1270.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5

(END OF REPORT)