

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331899-930

Luminaire Tested: **S123DIP-S340D1025U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331899-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1025U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4023.2 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	71	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	15
5	65	53	45	40	58	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.6	1.0
10°-20°	117.5	2.9
20°-30°	173.6	4.3
30°-40°	202.8	5.0
40°-50°	203.9	5.1
50°-60°	179.1	4.5
60°-70°	133.4	3.3
70°-80°	76.0	1.9
80°-90°	24.9	0.6
90°-100°	67.5	1.7
100°-110°	202.0	5.0
110°-120°	343.6	8.5
120°-130°	451.9	11.2
130°-140°	508.0	12.6
140°-150°	499.3	12.4
150°-160°	420.4	10.4
160°-170°	279.8	7.0
170°-180°	98.0	2.4
0°-30°	332.7	8.3
0°-40°	535.5	13.3
0°-60°	918.4	22.8
0°-90°	1152.7	28.7
90°-120°	613.1	15.2
90°-150°	2072.3	51.5
90°-180°	2870.0	71.3
0°-180°	4023.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	9	20	23	24	4
95°	48	54	60	63	64	54
105°	183	185	192	192	194	196
115°	346	348	347	347	347	342
125°	506	508	507	504	500	451
135°	657	661	661	658	656	506
145°	797	798	801	800	797	497
155°	912	912	913	916	911	420
165°	994	991	991	996	990	280
175°	1034	1030	1030	1035	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.1	8.2	8.4	8.6	8.7	9.0	9.4	9.8	10.2	10.6	10.7
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	19.7	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8
95°	48.0	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0
97.5°	85.3	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1
100°	110.7	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2
102.5°	140.0	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8
105°	183.1	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1
107.5°	233.3	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7
110°	264.5	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5



TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.0	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2
115°	345.8	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9
117.5°	395.0	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5
120°	425.7	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2
122.5°	457.5	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5
125°	506.2	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3
127.5°	551.1	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5
130°	581.1	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4
132.5°	611.1	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9
135°	656.8	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1
137.5°	699.1	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5
140°	728.4	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.0	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4
145°	796.7	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6
147.5°	833.2	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5
150°	858.6	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9
152.5°	879.5	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0
155°	912.3	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9
157.5°	940.3	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8
160°	957.9	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2
162.5°	973.5	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8
165°	993.7	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3
167.5°	1009.8	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4
170°	1019.0	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9
172.5°	1026.1	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9
175°	1033.6	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4
177.5°	1036.7	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	10.8	10.8	10.9	11.0	11.1	11.1	11.2	11.3
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	32.4	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	61.6	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	95.9	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	120.7	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.4	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.3	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.2	269.9	270.7	270.8	270.4	270.1	269.8	269.4





TEST NUMBER: P331899-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.1	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	426.1	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	458.0	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	505.6	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	552.5	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	583.7	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	614.0	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	659.4	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.8	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.9	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.3	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.5	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.3	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	914.6	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	941.5	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	958.1	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	973.7	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	993.4	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1025.1	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1032.5	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1035.8	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)