

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331900-930

Luminaire Tested: **S123DIP-S340D1025U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331900-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4177.4 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	36	36	36	28
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	31	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	52	46	63	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	20	18	16	12
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.0
10°-20°	117.5	2.8
20°-30°	173.6	4.2
30°-40°	202.8	4.9
40°-50°	203.9	4.9
50°-60°	179.1	4.3
60°-70°	133.4	3.2
70°-80°	76.0	1.8
80°-90°	24.9	0.6
90°-100°	223.7	5.4
100°-110°	633.5	15.2
110°-120°	623.2	14.9
120°-130°	497.1	11.9
130°-140°	391.9	9.4
140°-150°	292.5	7.0
150°-160°	203.9	4.9
160°-170°	119.8	2.9
170°-180°	39.0	0.9
0°-30°	332.7	8.0
0°-40°	535.5	12.8
0°-60°	918.4	22.0
0°-90°	1152.8	27.6
90°-120°	1480.5	35.4
90°-150°	2662.0	63.7
90°-180°	3025.0	72.4
0°-180°	4177.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	2	10	20	23	24	3
95°	28	90	483	141	94	30
105°	94	140	654	1144	1035	100
115°	167	208	500	1097	1259	165
125°	232	274	467	846	993	206
135°	272	324	461	697	805	210
145°	310	355	455	572	629	194
155°	352	380	440	500	522	162
165°	385	396	422	447	455	108
175°	401	402	404	410	409	38
180°	402	402	402	402	402	



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.2	8.3	8.5	8.7	8.9	9.0	9.5	9.9	10.4	10.8	10.5
90°	1.6	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6
92.5°	10.1	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4
95°	27.6	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4
97.5°	47.2	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1
100°	60.3	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0
102.5°	73.9	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5
105°	94.4	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9
107.5°	116.2	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0
110°	131.8	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.2	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7
115°	166.8	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3
117.5°	187.5	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6
120°	201.8	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4
122.5°	214.2	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4
125°	232.0	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2
127.5°	245.5	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3
130°	253.9	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2
132.5°	260.4	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7
135°	271.8	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7
137.5°	282.6	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0
140°	289.8	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2
142.5°	297.5	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0
145°	310.1	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9
147.5°	322.8	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1
150°	331.3	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5
152.5°	339.7	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4
155°	352.4	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6
157.5°	362.5	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8
160°	370.3	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9
162.5°	376.2	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0
165°	384.9	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0
167.5°	391.6	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4
170°	395.5	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9
172.5°	398.1	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3
175°	401.2	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1
177.5°	402.7	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	10.6	10.7	10.8	11.1	10.9	11.1	11.3	11.1
90°	20.4	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	68.5	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	292.9	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	730.3	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	959.5	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1035.7	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1057.9	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	993.8	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	932.6	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P331900-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.0	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	791.8	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	733.8	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	703.1	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	679.1	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	647.0	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	619.0	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	601.4	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	585.1	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	563.1	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	543.2	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	531.4	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	520.3	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	507.0	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	496.1	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	488.3	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	481.1	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	470.3	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	459.0	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	452.5	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	444.7	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	434.6	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	425.7	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	420.0	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	414.7	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	407.7	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	403.3	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)