

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332053-935

Luminaire Tested: **S123DIP-S1165D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332053-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5227.7 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	73	71	69
2	95	87	80	75	90	83	77	72	76	72	67	70	66	63	64	61	58
3	86	76	69	62	82	73	66	61	67	61	57	62	57	53	57	53	50
4	79	68	59	53	75	65	57	51	60	53	48	55	50	46	51	46	43
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	46	41	37
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	37	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29
8	58	45	37	31	55	43	36	30	40	34	29	37	32	28	35	30	26
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.8
10°-20°	418.7	8.0
20°-30°	618.4	11.8
30°-40°	722.4	13.8
40°-50°	726.3	13.9
50°-60°	638.0	12.2
60°-70°	475.3	9.1
70°-80°	270.8	5.2
80°-90°	78.9	1.5
90°-100°	83.7	1.6
100°-110°	236.9	4.5
110°-120°	233.0	4.5
120°-130°	185.8	3.6
130°-140°	146.5	2.8
140°-150°	109.4	2.1
150°-160°	76.2	1.5
160°-170°	44.8	0.9
170°-180°	14.6	0.3
0°-30°	1185.3	22.7
0°-40°	1907.7	36.5
0°-60°	3272.0	62.6
0°-90°	4096.9	78.4
90°-120°	553.5	10.6
90°-150°	995.3	19.0
90°-180°	1131.0	21.6
0°-180°	5227.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	4	8	8	9	5
95°	10	34	180	53	35	11
105°	35	52	245	428	387	38
115°	62	78	187	410	471	62
125°	87	102	175	316	371	77
135°	102	121	172	261	301	79
145°	116	133	170	214	235	73
155°	132	142	165	187	195	61
165°	144	148	158	167	170	41
175°	150	150	151	153	153	14
180°	150	150	150	150	150	



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.2	27.6	27.0	26.5	25.9	25.6	25.5	25.5	25.4	25.3	25.1
90°	0.6	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3
92.5°	3.8	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3
95°	10.3	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4
97.5°	17.7	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1
100°	22.6	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1
102.5°	27.6	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5
105°	35.3	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9
107.5°	43.5	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5
110°	49.2	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.7	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2
115°	62.3	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8
117.5°	70.1	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8
120°	75.4	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0
122.5°	80.1	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4
125°	86.7	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2
127.5°	91.8	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9
130°	95.0	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4
132.5°	97.4	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3
135°	101.6	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2
137.5°	105.6	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6
140°	108.3	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3
142.5°	111.2	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4
145°	115.9	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8
147.5°	120.7	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3
150°	123.8	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6
152.5°	127.0	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6
155°	131.7	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7
157.5°	135.5	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4
160°	138.4	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2
162.5°	140.6	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0
165°	143.9	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1
167.5°	146.4	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2
170°	147.8	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5
172.5°	148.9	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8
175°	150.0	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8
177.5°	150.6	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	24.9	24.7	24.5	24.5	24.5	24.5	24.5	24.5
90°	7.6	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	25.7	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	109.5	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	273.0	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	358.7	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	387.2	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	395.5	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	371.5	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	348.7	404.7	443.0	464.3	472.9	475.3	474.7	474.1



TEST NUMBER: P332053-935

CATALOG NUMBER: S123DIP-S1165D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.1	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	296.0	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	274.3	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	262.9	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	253.9	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	241.9	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	231.4	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	224.8	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	218.8	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	210.5	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	203.0	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	198.7	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	194.6	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	189.6	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	185.5	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	182.5	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	179.9	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	175.9	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	171.6	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	169.2	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	166.3	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	162.5	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	159.2	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.0	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.1	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.4	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	150.8	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)