

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332061-935

Luminaire Tested: **S123DIP-S1165D585U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332061-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5829.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27
7	61	48	40	34	58	46	38	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	32	27	50	39	31	26	35	29	25	32	27	23	29	25	22	19
10	50	37	30	25	47	35	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.5
10°-20°	418.7	7.2
20°-30°	618.4	10.6
30°-40°	722.4	12.4
40°-50°	726.3	12.5
50°-60°	638.0	10.9
60°-70°	475.3	8.2
70°-80°	270.8	4.6
80°-90°	79.6	1.4
90°-100°	40.7	0.7
100°-110°	121.9	2.1
110°-120°	207.3	3.6
120°-130°	272.7	4.7
130°-140°	306.5	5.3
140°-150°	301.3	5.2
150°-160°	253.7	4.4
160°-170°	168.9	2.9
170°-180°	59.1	1.0
0°-30°	1185.3	20.3
0°-40°	1907.7	32.7
0°-60°	3272.0	56.1
0°-90°	4097.6	70.3
90°-120°	370.0	6.3
90°-150°	1250.5	21.5
90°-180°	1732.0	29.7
0°-180°	5829.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	0	5	12	14	15	6
95°	29	32	36	38	38	33
105°	110	112	116	116	117	118
115°	209	210	209	210	209	206
125°	306	307	306	304	302	272
135°	396	399	399	397	396	305
145°	481	482	483	483	481	300
155°	550	551	551	553	550	253
165°	600	598	598	601	598	169
175°	624	622	622	624	621	59
180°	625	625	625	625	625	



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.2	27.7	27.2	26.8	26.3	26.0	26.1	26.1	26.2	26.2	26.0
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	11.9	12.7	13.3	14.1	14.9	15.7	16.4	17.2	18.1	18.9	19.2
95°	29.0	29.7	30.5	31.3	32.0	32.9	33.8	34.6	35.5	36.3	36.8
97.5°	51.5	52.0	52.6	53.2	53.7	54.3	54.9	55.6	56.2	56.9	57.3
100°	66.8	67.4	68.1	68.8	69.4	70.0	70.5	71.1	71.6	72.2	72.5
102.5°	84.5	84.9	85.2	85.7	86.0	86.6	87.3	88.1	88.8	89.5	89.8
105°	110.5	110.7	110.9	111.2	111.4	111.9	113.0	113.9	114.9	115.9	115.9
107.5°	140.8	140.9	141.0	141.1	141.3	141.5	141.9	142.3	142.8	143.1	143.4
110°	159.6	159.8	160.1	160.2	160.5	160.7	160.9	161.2	161.4	161.6	162.0



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	179.3	179.5	179.6	179.8	179.9	179.9	179.9	180.0	180.0	180.6
115°	208.7	209.1	209.4	209.7	210.0	210.1	209.8	209.7	209.4	209.2	209.3
117.5°	238.4	238.6	238.8	239.0	239.3	239.2	238.9	238.7	238.4	238.1	238.1
120°	256.8	257.5	258.1	258.8	259.5	259.5	259.0	258.5	257.9	257.4	257.3
122.5°	276.1	276.6	277.1	277.5	278.0	278.1	277.8	277.6	277.2	277.0	276.7
125°	305.5	305.8	306.1	306.4	306.8	306.9	306.6	306.4	306.2	306.0	305.5
127.5°	332.6	333.3	334.0	334.7	335.4	335.6	335.4	335.1	334.8	334.7	334.1
130°	350.7	351.5	352.4	353.3	354.1	354.4	354.1	353.8	353.4	353.1	352.7
132.5°	368.7	369.6	370.5	371.3	372.2	372.6	372.3	372.0	371.8	371.6	371.0
135°	396.3	397.0	397.6	398.3	398.9	399.2	399.1	399.0	398.9	398.8	398.4
137.5°	421.9	422.4	422.9	423.5	424.0	424.5	424.7	425.0	425.3	425.6	425.2
140°	439.5	440.1	440.7	441.2	441.7	442.0	442.1	442.3	442.4	442.5	442.4
142.5°	455.6	456.2	456.8	457.3	457.8	458.2	458.4	458.6	458.8	459.0	458.9
145°	480.8	481.0	481.2	481.5	481.6	481.9	482.2	482.6	482.9	483.3	483.1
147.5°	502.8	503.2	503.6	503.9	504.4	504.7	505.1	505.3	505.7	505.9	505.9
150°	518.1	518.3	518.6	518.8	519.0	519.2	519.4	519.6	519.9	520.0	520.0
152.5°	530.7	531.0	531.3	531.6	531.9	532.1	532.3	532.4	532.5	532.6	532.8
155°	550.5	550.5	550.5	550.5	550.5	550.6	550.7	550.8	551.0	551.0	551.5
157.5°	567.4	567.3	567.1	567.1	566.9	566.9	567.0	567.1	567.1	567.2	567.7
160°	578.0	577.8	577.6	577.4	577.1	577.0	577.0	577.0	577.0	577.0	577.6
162.5°	587.5	587.1	586.9	586.5	586.3	586.2	586.3	586.3	586.4	586.5	587.0
165°	599.6	599.3	599.0	598.7	598.3	598.1	598.1	598.1	598.1	598.1	598.8
167.5°	609.3	608.9	608.5	608.0	607.6	607.4	607.5	607.6	607.7	607.8	608.5
170°	614.8	614.4	614.0	613.5	613.1	612.9	612.9	612.9	612.9	612.9	613.6
172.5°	619.1	618.7	618.3	617.9	617.4	617.3	617.3	617.3	617.3	617.3	617.9
175°	623.7	623.3	622.8	622.4	622.0	621.7	621.7	621.7	621.7	621.7	622.4
177.5°	625.6	625.3	624.9	624.5	624.1	624.0	624.0	624.0	624.0	624.0	624.5
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	25.8	25.7	25.6	25.5	25.6	25.6	25.7	25.7
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	19.5	19.9	20.2	20.4	20.2	20.1	20.0	19.8
95°	37.2	37.6	38.1	38.3	38.3	38.3	38.3	38.3
97.5°	57.9	58.4	58.9	59.1	59.1	59.0	59.0	58.9
100°	72.8	73.2	73.5	73.8	74.0	74.2	74.4	74.6
102.5°	90.1	90.5	90.7	90.9	90.9	90.8	90.8	90.7
105°	115.9	115.9	115.9	116.0	116.2	116.4	116.7	116.9
107.5°	143.8	144.1	144.5	144.6	144.5	144.4	144.2	144.1
110°	162.5	162.9	163.3	163.4	163.2	163.0	162.8	162.6



TEST NUMBER: P332061-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.1	181.6	182.1	182.4	182.4	182.3	182.3	182.2
115°	209.4	209.6	209.7	209.7	209.6	209.4	209.3	209.2
117.5°	238.1	238.0	238.0	237.8	237.5	237.2	236.9	236.6
120°	257.1	257.0	256.9	256.8	256.5	256.3	256.1	255.9
122.5°	276.4	276.1	275.9	275.5	275.3	274.9	274.7	274.3
125°	305.1	304.6	304.2	303.8	303.3	302.9	302.5	302.0
127.5°	333.4	332.8	332.2	331.7	331.1	330.6	330.1	329.6
130°	352.2	351.8	351.4	350.8	350.0	349.2	348.4	347.7
132.5°	370.5	370.0	369.5	368.9	368.3	367.7	367.1	366.5
135°	397.9	397.4	397.0	396.7	396.5	396.2	396.1	395.8
137.5°	424.6	424.2	423.8	423.4	422.9	422.5	422.1	421.6
140°	442.3	442.1	442.0	441.6	440.8	440.1	439.3	438.6
142.5°	458.7	458.7	458.6	458.2	457.6	457.0	456.4	455.8
145°	483.0	482.9	482.8	482.5	482.1	481.6	481.2	480.8
147.5°	505.9	505.9	505.9	505.6	505.0	504.3	503.7	503.0
150°	520.0	520.0	520.0	519.8	519.1	518.4	517.8	517.1
152.5°	533.0	533.2	533.4	533.1	532.6	532.0	531.5	530.9
155°	551.9	552.3	552.8	552.6	551.8	551.0	550.4	549.6
157.5°	568.2	568.6	569.0	568.9	568.3	567.7	567.1	566.5
160°	578.2	578.7	579.2	579.3	578.9	578.4	578.0	577.6
162.5°	587.5	588.1	588.7	588.6	587.9	587.2	586.5	585.8
165°	599.5	600.1	600.8	600.7	599.9	599.2	598.5	597.7
167.5°	609.2	609.8	610.5	610.5	609.8	609.2	608.5	607.8
170°	614.4	615.2	616.0	616.0	615.2	614.4	613.6	612.9
172.5°	618.5	619.2	619.9	619.9	619.1	618.4	617.6	616.8
175°	623.0	623.7	624.4	624.3	623.5	622.8	622.0	621.2
177.5°	625.1	625.6	626.1	626.0	625.4	624.8	624.2	623.6
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2

(END OF REPORT)