

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332062-935

Luminaire Tested: **S123DIP-S1165D585U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332062-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D585U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5922.8 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	102	98	93	90	96	92	89	85	82	80	77	73	71	69	65	64	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52	49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33	31
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.3	2.5
10°-20°	418.7	7.1
20°-30°	618.4	10.4
30°-40°	722.4	12.2
40°-50°	726.3	12.3
50°-60°	638.0	10.8
60°-70°	475.3	8.0
70°-80°	270.8	4.6
80°-90°	79.6	1.3
90°-100°	135.0	2.3
100°-110°	382.3	6.5
110°-120°	376.1	6.3
120°-130°	300.0	5.1
130°-140°	236.5	4.0
140°-150°	176.5	3.0
150°-160°	123.0	2.1
160°-170°	72.3	1.2
170°-180°	23.5	0.4
0°-30°	1185.3	20.0
0°-40°	1907.7	32.2
0°-60°	3272.0	55.2
0°-90°	4097.6	69.2
90°-120°	893.4	15.1
90°-150°	1606.4	27.1
90°-180°	1825.0	30.8
0°-180°	5922.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	6	12	14	14	5
95°	17	54	291	85	57	18
105°	57	84	395	690	625	61
115°	101	125	302	662	760	100
125°	140	165	282	511	599	124
135°	164	196	278	421	486	127
145°	187	214	274	345	380	117
155°	213	229	266	302	315	98
165°	232	239	254	270	274	65
175°	242	242	244	248	247	23
180°	243	243	243	243	243	



TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.3	27.8	27.3	26.9	26.3	26.1	26.1	26.2	26.3	26.3	25.9
90°	0.9	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8
92.5°	6.1	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0
95°	16.7	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2
97.5°	28.5	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8
100°	36.3	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8
102.5°	44.6	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8
105°	57.0	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8
107.5°	70.1	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4
110°	79.6	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3



TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.2	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6
115°	100.7	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0
117.5°	113.1	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1
120°	121.8	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1
122.5°	129.2	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0
125°	140.0	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4
127.5°	148.1	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3
130°	153.3	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7
132.5°	157.1	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6
135°	164.0	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9
137.5°	170.5	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2
140°	174.9	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6
142.5°	179.5	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5
145°	187.1	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2
147.5°	194.8	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1
150°	199.8	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4
152.5°	205.0	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3
155°	212.7	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5
157.5°	218.7	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2
160°	223.4	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7
162.5°	227.0	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1
165°	232.3	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3
167.5°	236.3	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7
170°	238.7	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0
172.5°	240.2	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2
175°	242.1	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0
177.5°	243.0	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	25.8	25.7	25.5	25.6	25.5	25.6	25.7	25.6
90°	12.3	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	41.3	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	176.8	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	440.7	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	579.0	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	625.0	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	638.4	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	599.7	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	562.7	653.2	715.1	749.4	763.2	767.1	766.1	765.1





TEST NUMBER: P332062-935

CATALOG NUMBER: S123DIP-S1165D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	526.2	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	477.9	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	442.7	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	424.3	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	409.7	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	390.4	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	373.5	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	362.9	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	353.1	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	339.8	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	327.8	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	320.7	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	314.0	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	305.9	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	299.4	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	294.6	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	290.3	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	283.9	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	277.0	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	273.0	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	268.4	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	262.3	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	256.9	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	253.4	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	250.3	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.1	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.4	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)