

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331893-935

Luminaire Tested: **S123DIP-S340D1025U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331893-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1025U935-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4284.1 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.8	1.0
10°-20°	130.8	3.1
20°-30°	219.5	5.1
30°-40°	248.5	5.8
40°-50°	222.9	5.2
50°-60°	179.8	4.2
60°-70°	125.3	2.9
70°-80°	65.9	1.5
80°-90°	19.3	0.5
90°-100°	71.3	1.7
100°-110°	213.3	5.0
110°-120°	362.8	8.5
120°-130°	477.3	11.1
130°-140°	536.4	12.5
140°-150°	527.3	12.3
150°-160°	443.9	10.4
160°-170°	295.5	6.9
170°-180°	103.5	2.4
0°-30°	391.0	9.1
0°-40°	639.5	14.9
0°-60°	1042.2	24.3
0°-90°	1252.8	29.2
90°-120°	647.5	15.1
90°-150°	2188.5	51.1
90°-180°	3031.0	70.7
0°-180°	4284.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	16
90°	26	1	26	1	26	13
95°	67	51	67	51	67	69
105°	205	193	205	193	205	217
115°	366	365	366	365	366	362
125°	529	535	529	535	529	473
135°	693	694	693	694	693	533
145°	841	841	841	841	841	525
155°	962	964	962	964	962	443
165°	1046	1049	1046	1049	1046	295
175°	1087	1092	1087	1092	1087	103
180°	1094	1094	1094	1094	1094	



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	10.0	9.6	9.6	9.7	9.5	9.6	9.6	9.6	9.6	9.6	9.2
90°	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1	21.4	20.7	18.2
92.5°	34.7	35.0	35.2	35.4	35.6	35.5	34.9	34.3	33.6	33.0	31.6
95°	67.1	67.1	67.1	67.1	67.1	66.6	65.9	65.1	64.4	63.6	62.1
97.5°	103.1	103.2	103.3	103.4	103.4	103.1	102.2	101.3	100.4	99.5	98.4
100°	130.6	130.3	129.8	129.5	129.2	128.6	128.0	127.5	126.9	126.3	125.4
102.5°	158.9	158.9	158.9	159.0	159.1	158.9	158.3	157.7	157.1	156.6	155.3
105°	204.6	204.1	203.8	203.4	203.0	202.9	202.9	202.9	202.9	202.9	201.1
107.5°	252.2	252.4	252.6	252.9	253.0	252.9	252.3	251.7	251.1	250.5	249.8
110°	284.5	284.9	285.2	285.6	286.0	285.9	285.1	284.3	283.5	282.8	282.4



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	318.8	318.9	319.0	319.1	319.2	318.7	317.8	316.9	316.0	315.0	315.0
115°	366.1	366.4	366.5	366.7	366.9	366.9	366.7	366.5	366.4	366.1	366.5
117.5°	414.1	414.7	415.2	415.7	416.2	416.6	416.6	416.6	416.6	416.6	417.2
120°	447.8	448.2	448.6	448.9	449.3	449.6	449.8	450.0	450.1	450.4	451.3
122.5°	480.1	480.6	481.1	481.7	482.2	482.8	483.3	483.7	484.2	484.7	485.3
125°	528.6	529.3	530.1	530.9	531.6	532.4	533.1	533.9	534.7	535.5	535.8
127.5°	576.9	577.7	578.6	579.5	580.4	581.3	582.5	583.5	584.5	585.7	586.1
130°	608.5	609.8	611.1	612.5	613.8	614.9	615.6	616.4	617.2	617.9	618.5
132.5°	641.5	642.6	643.6	644.6	645.7	646.6	647.6	648.4	649.4	650.2	650.7
135°	692.8	693.1	693.4	693.9	694.2	694.8	695.6	696.4	697.2	697.8	698.1
137.5°	738.0	738.7	739.3	740.1	740.8	741.6	742.4	743.2	744.0	744.8	744.3
140°	767.5	768.9	770.2	771.5	772.8	773.6	773.8	774.0	774.2	774.4	774.2
142.5°	797.7	798.7	799.8	800.8	801.8	802.5	802.7	802.9	803.1	803.2	802.9
145°	841.4	842.1	842.9	843.7	844.5	844.9	845.2	845.3	845.5	845.7	845.2
147.5°	880.3	881.4	882.5	883.7	884.8	885.5	885.5	885.5	885.5	885.5	884.8
150°	905.0	906.1	907.3	908.4	909.6	910.2	910.2	910.2	910.2	910.2	909.8
152.5°	929.1	930.1	931.1	932.0	933.1	933.4	933.1	932.8	932.5	932.2	931.9
155°	961.7	963.0	964.4	965.8	967.1	967.3	966.6	965.9	965.1	964.3	964.1
157.5°	991.4	992.6	993.6	994.7	995.7	995.9	995.1	994.3	993.5	992.6	992.6
160°	1010.7	1011.5	1012.3	1013.1	1013.7	1013.7	1012.7	1011.8	1010.8	1009.9	1009.9
162.5°	1025.2	1026.4	1027.6	1028.8	1030.0	1030.2	1029.2	1028.3	1027.3	1026.4	1026.2
165°	1045.9	1047.3	1048.6	1050.0	1051.3	1051.4	1050.2	1049.1	1047.9	1046.8	1046.8
167.5°	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7	1063.5
170°	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6	1072.6
172.5°	1079.4	1080.8	1082.2	1083.5	1084.9	1084.9	1083.7	1082.5	1081.3	1080.1	1080.1
175°	1087.2	1088.6	1089.9	1091.2	1092.5	1092.7	1091.5	1090.4	1089.3	1088.0	1088.0
177.5°	1091.3	1092.4	1093.5	1094.6	1095.6	1095.7	1094.8	1093.9	1093.0	1092.0	1092.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	9.0	8.7	7.7	6.7	5.9	5.1	4.7	4.0	4.0	4.5	4.6
90°	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9	2.8	4.6	6.6
92.5°	30.1	28.8	27.4	26.0	24.7	23.4	22.1	20.8	22.1	23.4	24.7
95°	60.5	59.0	57.5	56.1	54.8	53.4	52.0	50.7	52.0	53.4	54.8
97.5°	97.3	96.2	95.1	94.0	93.1	92.0	91.1	90.1	91.1	92.0	93.1
100°	124.4	123.5	122.5	121.5	120.3	119.2	118.0	116.9	118.0	119.2	120.3
102.5°	154.0	152.8	151.5	150.6	149.9	149.2	148.5	147.8	148.5	149.2	149.9
105°	199.4	197.7	196.0	194.9	194.5	194.2	193.7	193.4	193.7	194.2	194.5
107.5°	249.1	248.4	247.7	247.3	247.0	246.8	246.6	246.3	246.6	246.8	247.0
110°	282.0	281.6	281.2	280.9	280.4	280.1	279.7	279.3	279.7	280.1	280.4





TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.0	314.9	314.8	314.6	314.4	314.2	313.9	313.7	313.9	314.2	314.4
115°	366.9	367.3	367.6	367.6	367.0	366.4	365.8	365.2	365.8	366.4	367.0
117.5°	417.7	418.2	418.6	418.7	418.4	417.9	417.6	417.2	417.6	417.9	418.4
120°	452.3	453.2	454.2	454.1	453.0	451.8	450.6	449.5	450.6	451.8	453.0
122.5°	485.7	486.2	486.7	486.6	485.7	484.8	484.1	483.2	484.1	484.8	485.7
125°	536.2	536.6	537.0	536.8	536.3	535.7	535.2	534.6	535.2	535.7	536.3
127.5°	586.5	586.9	587.3	586.9	585.7	584.4	583.2	582.0	583.2	584.4	585.7
130°	619.1	619.7	620.3	619.7	618.2	616.7	615.2	613.6	615.2	616.7	618.2
132.5°	651.1	651.5	651.9	651.4	649.9	648.3	646.8	645.3	646.8	648.3	649.9
135°	698.3	698.4	698.6	698.2	697.0	695.9	694.7	693.6	694.7	695.9	697.0
137.5°	743.8	743.3	742.8	742.1	741.1	740.2	739.3	738.3	739.3	740.2	741.1
140°	774.0	773.8	773.6	773.0	772.1	771.1	770.2	769.2	770.2	771.1	772.1
142.5°	802.5	802.2	801.8	801.2	800.3	799.4	798.3	797.4	798.3	799.4	800.3
145°	844.6	844.0	843.4	842.9	842.6	842.1	841.8	841.4	841.8	842.1	842.6
147.5°	884.3	883.8	883.3	882.7	882.0	881.3	880.6	879.9	880.6	881.3	882.0
150°	909.4	909.0	908.6	908.3	907.8	907.5	907.1	906.7	907.1	907.5	907.8
152.5°	931.7	931.5	931.3	930.8	930.3	929.8	929.3	928.8	929.3	929.8	930.3
155°	963.9	963.7	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
157.5°	992.4	992.2	992.0	992.1	992.3	992.6	992.8	993.0	992.8	992.6	992.3
160°	1009.9	1009.9	1009.9	1010.0	1010.5	1010.8	1011.2	1011.6	1011.2	1010.8	1010.5
162.5°	1026.1	1025.9	1025.8	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
165°	1046.8	1046.8	1046.8	1047.1	1047.7	1048.3	1048.8	1049.4	1048.8	1048.3	1047.7
167.5°	1063.3	1063.2	1063.1	1063.3	1064.1	1064.9	1065.7	1066.4	1065.7	1064.9	1064.1
170°	1072.6	1072.6	1072.6	1073.0	1073.8	1074.5	1075.3	1076.1	1075.3	1074.5	1073.8
172.5°	1080.1	1080.1	1080.1	1080.6	1081.3	1082.1	1082.9	1083.6	1082.9	1082.1	1081.3
175°	1088.0	1088.0	1088.0	1088.5	1089.3	1089.9	1090.7	1091.5	1090.7	1089.9	1089.3
177.5°	1092.0	1092.0	1092.0	1092.4	1093.0	1093.6	1094.2	1094.8	1094.2	1093.6	1093.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	4.9	5.5	5.9	6.5	6.8	7.5	7.7	7.5	7.7	8.3	7.7
90°	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1	22.9	23.7	24.3
92.5°	26.0	27.4	28.8	30.1	31.6	33.0	33.6	34.3	34.9	35.5	35.6
95°	56.1	57.5	59.0	60.5	62.1	63.6	64.4	65.1	65.9	66.6	67.1
97.5°	94.0	95.1	96.2	97.3	98.4	99.5	100.4	101.3	102.2	103.1	103.4
100°	121.5	122.5	123.5	124.4	125.4	126.3	126.9	127.5	128.0	128.6	129.2
102.5°	150.6	151.5	152.8	154.0	155.3	156.6	157.1	157.7	158.3	158.9	159.1
105°	194.9	196.0	197.7	199.4	201.1	202.9	202.9	202.9	202.9	202.9	203.0
107.5°	247.3	247.7	248.4	249.1	249.8	250.5	251.1	251.7	252.3	252.9	253.0
110°	280.9	281.2	281.6	282.0	282.4	282.8	283.5	284.3	285.1	285.9	286.0



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	314.6	314.8	314.9	315.0	315.0	315.0	316.0	316.9	317.8	318.7	319.2
115°	367.6	367.6	367.3	366.9	366.5	366.1	366.4	366.5	366.7	366.9	366.9
117.5°	418.7	418.6	418.2	417.7	417.2	416.6	416.6	416.6	416.6	416.6	416.2
120°	454.1	454.2	453.2	452.3	451.3	450.4	450.1	450.0	449.8	449.6	449.3
122.5°	486.6	486.7	486.2	485.7	485.3	484.7	484.2	483.7	483.3	482.8	482.2
125°	536.8	537.0	536.6	536.2	535.8	535.5	534.7	533.9	533.1	532.4	531.6
127.5°	586.9	587.3	586.9	586.5	586.1	585.7	584.5	583.5	582.5	581.3	580.4
130°	619.7	620.3	619.7	619.1	618.5	617.9	617.2	616.4	615.6	614.9	613.8
132.5°	651.4	651.9	651.5	651.1	650.7	650.2	649.4	648.4	647.6	646.6	645.7
135°	698.2	698.6	698.4	698.3	698.1	697.8	697.2	696.4	695.6	694.8	694.2
137.5°	742.1	742.8	743.3	743.8	744.3	744.8	744.0	743.2	742.4	741.6	740.8
140°	773.0	773.6	773.8	774.0	774.2	774.4	774.2	774.0	773.8	773.6	772.8
142.5°	801.2	801.8	802.2	802.5	802.9	803.2	803.1	802.9	802.7	802.5	801.8
145°	842.9	843.4	844.0	844.6	845.2	845.7	845.5	845.3	845.2	844.9	844.5
147.5°	882.7	883.3	883.8	884.3	884.8	885.5	885.5	885.5	885.5	885.5	884.8
150°	908.3	908.6	909.0	909.4	909.8	910.2	910.2	910.2	910.2	910.2	909.6
152.5°	930.8	931.3	931.5	931.7	931.9	932.2	932.5	932.8	933.1	933.4	933.1
155°	963.5	963.5	963.7	963.9	964.1	964.3	965.1	965.9	966.6	967.3	967.1
157.5°	992.1	992.0	992.2	992.4	992.6	992.6	993.5	994.3	995.1	995.9	995.7
160°	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8	1011.8	1012.7	1013.7	1013.7
162.5°	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3	1028.3	1029.2	1030.2	1030.0
165°	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9	1049.1	1050.2	1051.4	1051.3
167.5°	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4
170°	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0
172.5°	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3	1082.5	1083.7	1084.9	1084.9
175°	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3	1090.4	1091.5	1092.7	1092.5
177.5°	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0	1093.9	1094.8	1095.7	1095.6
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	7.8	7.9	7.8	7.7	7.8	7.9	7.8	7.7	8.3	7.7	7.5
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1
92.5°	35.4	35.2	35.0	34.7	35.0	35.2	35.4	35.6	35.5	34.9	34.3
95°	67.1	67.1	67.1	67.1	67.1	67.1	67.1	67.1	66.6	65.9	65.1
97.5°	103.4	103.3	103.2	103.1	103.2	103.3	103.4	103.4	103.1	102.2	101.3
100°	129.5	129.8	130.3	130.6	130.3	129.8	129.5	129.2	128.6	128.0	127.5
102.5°	159.0	158.9	158.9	158.9	158.9	158.9	159.0	159.1	158.9	158.3	157.7
105°	203.4	203.8	204.1	204.6	204.1	203.8	203.4	203.0	202.9	202.9	202.9
107.5°	252.9	252.6	252.4	252.2	252.4	252.6	252.9	253.0	252.9	252.3	251.7
110°	285.6	285.2	284.9	284.5	284.9	285.2	285.6	286.0	285.9	285.1	284.3



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	319.1	319.0	318.9	318.8	318.9	319.0	319.1	319.2	318.7	317.8	316.9
115°	366.7	366.5	366.4	366.1	366.4	366.5	366.7	366.9	366.9	366.7	366.5
117.5°	415.7	415.2	414.7	414.1	414.7	415.2	415.7	416.2	416.6	416.6	416.6
120°	448.9	448.6	448.2	447.8	448.2	448.6	448.9	449.3	449.6	449.8	450.0
122.5°	481.7	481.1	480.6	480.1	480.6	481.1	481.7	482.2	482.8	483.3	483.7
125°	530.9	530.1	529.3	528.6	529.3	530.1	530.9	531.6	532.4	533.1	533.9
127.5°	579.5	578.6	577.7	576.9	577.7	578.6	579.5	580.4	581.3	582.5	583.5
130°	612.5	611.1	609.8	608.5	609.8	611.1	612.5	613.8	614.9	615.6	616.4
132.5°	644.6	643.6	642.6	641.5	642.6	643.6	644.6	645.7	646.6	647.6	648.4
135°	693.9	693.4	693.1	692.8	693.1	693.4	693.9	694.2	694.8	695.6	696.4
137.5°	740.1	739.3	738.7	738.0	738.7	739.3	740.1	740.8	741.6	742.4	743.2
140°	771.5	770.2	768.9	767.5	768.9	770.2	771.5	772.8	773.6	773.8	774.0
142.5°	800.8	799.8	798.7	797.7	798.7	799.8	800.8	801.8	802.5	802.7	802.9
145°	843.7	842.9	842.1	841.4	842.1	842.9	843.7	844.5	844.9	845.2	845.3
147.5°	883.7	882.5	881.4	880.3	881.4	882.5	883.7	884.8	885.5	885.5	885.5
150°	908.4	907.3	906.1	905.0	906.1	907.3	908.4	909.6	910.2	910.2	910.2
152.5°	932.0	931.1	930.1	929.1	930.1	931.1	932.0	933.1	933.4	933.1	932.8
155°	965.8	964.4	963.0	961.7	963.0	964.4	965.8	967.1	967.3	966.6	965.9
157.5°	994.7	993.6	992.6	991.4	992.6	993.6	994.7	995.7	995.9	995.1	994.3
160°	1013.1	1012.3	1011.5	1010.7	1011.5	1012.3	1013.1	1013.7	1013.7	1012.7	1011.8
162.5°	1028.8	1027.6	1026.4	1025.2	1026.4	1027.6	1028.8	1030.0	1030.2	1029.2	1028.3
165°	1050.0	1048.6	1047.3	1045.9	1047.3	1048.6	1050.0	1051.3	1051.4	1050.2	1049.1
167.5°	1067.2	1066.0	1064.9	1063.7	1064.9	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0
170°	1076.6	1075.3	1073.9	1072.6	1073.9	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3
172.5°	1083.5	1082.2	1080.8	1079.4	1080.8	1082.2	1083.5	1084.9	1084.9	1083.7	1082.5
175°	1091.2	1089.9	1088.6	1087.2	1088.6	1089.9	1091.2	1092.5	1092.7	1091.5	1090.4
177.5°	1094.6	1093.5	1092.4	1091.3	1092.4	1093.5	1094.6	1095.6	1095.7	1094.8	1093.9
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	7.7	7.5	6.8	6.5	5.9	5.5	4.9	4.6	4.5	4.0	4.0
90°	21.4	20.7	18.2	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9
92.5°	33.6	33.0	31.6	30.1	28.8	27.4	26.0	24.7	23.4	22.1	20.8
95°	64.4	63.6	62.1	60.5	59.0	57.5	56.1	54.8	53.4	52.0	50.7
97.5°	100.4	99.5	98.4	97.3	96.2	95.1	94.0	93.1	92.0	91.1	90.1
100°	126.9	126.3	125.4	124.4	123.5	122.5	121.5	120.3	119.2	118.0	116.9
102.5°	157.1	156.6	155.3	154.0	152.8	151.5	150.6	149.9	149.2	148.5	147.8
105°	202.9	202.9	201.1	199.4	197.7	196.0	194.9	194.5	194.2	193.7	193.4
107.5°	251.1	250.5	249.8	249.1	248.4	247.7	247.3	247.0	246.8	246.6	246.3
110°	283.5	282.8	282.4	282.0	281.6	281.2	280.9	280.4	280.1	279.7	279.3



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	316.0	315.0	315.0	315.0	314.9	314.8	314.6	314.4	314.2	313.9	313.7
115°	366.4	366.1	366.5	366.9	367.3	367.6	367.6	367.0	366.4	365.8	365.2
117.5°	416.6	416.6	417.2	417.7	418.2	418.6	418.7	418.4	417.9	417.6	417.2
120°	450.1	450.4	451.3	452.3	453.2	454.2	454.1	453.0	451.8	450.6	449.5
122.5°	484.2	484.7	485.3	485.7	486.2	486.7	486.6	485.7	484.8	484.1	483.2
125°	534.7	535.5	535.8	536.2	536.6	537.0	536.8	536.3	535.7	535.2	534.6
127.5°	584.5	585.7	586.1	586.5	586.9	587.3	586.9	585.7	584.4	583.2	582.0
130°	617.2	617.9	618.5	619.1	619.7	620.3	619.7	618.2	616.7	615.2	613.6
132.5°	649.4	650.2	650.7	651.1	651.5	651.9	651.4	649.9	648.3	646.8	645.3
135°	697.2	697.8	698.1	698.3	698.4	698.6	698.2	697.0	695.9	694.7	693.6
137.5°	744.0	744.8	744.3	743.8	743.3	742.8	742.1	741.1	740.2	739.3	738.3
140°	774.2	774.4	774.2	774.0	773.8	773.6	773.0	772.1	771.1	770.2	769.2
142.5°	803.1	803.2	802.9	802.5	802.2	801.8	801.2	800.3	799.4	798.3	797.4
145°	845.5	845.7	845.2	844.6	844.0	843.4	842.9	842.6	842.1	841.8	841.4
147.5°	885.5	885.5	884.8	884.3	883.8	883.3	882.7	882.0	881.3	880.6	879.9
150°	910.2	910.2	909.8	909.4	909.0	908.6	908.3	907.8	907.5	907.1	906.7
152.5°	932.5	932.2	931.9	931.7	931.5	931.3	930.8	930.3	929.8	929.3	928.8
155°	965.1	964.3	964.1	963.9	963.7	963.5	963.5	963.5	963.5	963.5	963.5
157.5°	993.5	992.6	992.6	992.4	992.2	992.0	992.1	992.3	992.6	992.8	993.0
160°	1010.8	1009.9	1009.9	1009.9	1009.9	1009.9	1010.0	1010.5	1010.8	1011.2	1011.6
162.5°	1027.3	1026.4	1026.2	1026.1	1025.9	1025.8	1026.0	1026.5	1027.0	1027.5	1028.1
165°	1047.9	1046.8	1046.8	1046.8	1046.8	1046.8	1047.1	1047.7	1048.3	1048.8	1049.4
167.5°	1064.9	1063.7	1063.5	1063.3	1063.2	1063.1	1063.3	1064.1	1064.9	1065.7	1066.4
170°	1073.9	1072.6	1072.6	1072.6	1072.6	1072.6	1073.0	1073.8	1074.5	1075.3	1076.1
172.5°	1081.3	1080.1	1080.1	1080.1	1080.1	1080.1	1080.6	1081.3	1082.1	1082.9	1083.6
175°	1089.3	1088.0	1088.0	1088.0	1088.0	1088.0	1088.5	1089.3	1089.9	1090.7	1091.5
177.5°	1093.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.4	1093.0	1093.6	1094.2	1094.8
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	4.7	5.1	5.9	6.7	7.7	8.7	9.0	9.2	9.6	9.6	9.6
90°	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1
92.5°	22.1	23.4	24.7	26.0	27.4	28.8	30.1	31.6	33.0	33.6	34.3
95°	52.0	53.4	54.8	56.1	57.5	59.0	60.5	62.1	63.6	64.4	65.1
97.5°	91.1	92.0	93.1	94.0	95.1	96.2	97.3	98.4	99.5	100.4	101.3
100°	118.0	119.2	120.3	121.5	122.5	123.5	124.4	125.4	126.3	126.9	127.5
102.5°	148.5	149.2	149.9	150.6	151.5	152.8	154.0	155.3	156.6	157.1	157.7
105°	193.7	194.2	194.5	194.9	196.0	197.7	199.4	201.1	202.9	202.9	202.9
107.5°	246.6	246.8	247.0	247.3	247.7	248.4	249.1	249.8	250.5	251.1	251.7
110°	279.7	280.1	280.4	280.9	281.2	281.6	282.0	282.4	282.8	283.5	284.3





TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	313.9	314.2	314.4	314.6	314.8	314.9	315.0	315.0	315.0	316.0	316.9
115°	365.8	366.4	367.0	367.6	367.6	367.3	366.9	366.5	366.1	366.4	366.5
117.5°	417.6	417.9	418.4	418.7	418.6	418.2	417.7	417.2	416.6	416.6	416.6
120°	450.6	451.8	453.0	454.1	454.2	453.2	452.3	451.3	450.4	450.1	450.0
122.5°	484.1	484.8	485.7	486.6	486.7	486.2	485.7	485.3	484.7	484.2	483.7
125°	535.2	535.7	536.3	536.8	537.0	536.6	536.2	535.8	535.5	534.7	533.9
127.5°	583.2	584.4	585.7	586.9	587.3	586.9	586.5	586.1	585.7	584.5	583.5
130°	615.2	616.7	618.2	619.7	620.3	619.7	619.1	618.5	617.9	617.2	616.4
132.5°	646.8	648.3	649.9	651.4	651.9	651.5	651.1	650.7	650.2	649.4	648.4
135°	694.7	695.9	697.0	698.2	698.6	698.4	698.3	698.1	697.8	697.2	696.4
137.5°	739.3	740.2	741.1	742.1	742.8	743.3	743.8	744.3	744.8	744.0	743.2
140°	770.2	771.1	772.1	773.0	773.6	773.8	774.0	774.2	774.4	774.2	774.0
142.5°	798.3	799.4	800.3	801.2	801.8	802.2	802.5	802.9	803.2	803.1	802.9
145°	841.8	842.1	842.6	842.9	843.4	844.0	844.6	845.2	845.7	845.5	845.3
147.5°	880.6	881.3	882.0	882.7	883.3	883.8	884.3	884.8	885.5	885.5	885.5
150°	907.1	907.5	907.8	908.3	908.6	909.0	909.4	909.8	910.2	910.2	910.2
152.5°	929.3	929.8	930.3	930.8	931.3	931.5	931.7	931.9	932.2	932.5	932.8
155°	963.5	963.5	963.5	963.5	963.5	963.7	963.9	964.1	964.3	965.1	965.9
157.5°	992.8	992.6	992.3	992.1	992.0	992.2	992.4	992.6	992.6	993.5	994.3
160°	1011.2	1010.8	1010.5	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8	1011.8
162.5°	1027.5	1027.0	1026.5	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3	1028.3
165°	1048.8	1048.3	1047.7	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9	1049.1
167.5°	1065.7	1064.9	1064.1	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9	1066.0
170°	1075.3	1074.5	1073.8	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9	1075.3
172.5°	1082.9	1082.1	1081.3	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3	1082.5
175°	1090.7	1089.9	1089.3	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3	1090.4
177.5°	1094.2	1093.6	1093.0	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0	1093.9
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	9.6	9.6	9.5	9.7	9.6	9.6	10.0
90°	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	34.9	35.5	35.6	35.4	35.2	35.0	34.7
95°	65.9	66.6	67.1	67.1	67.1	67.1	67.1
97.5°	102.2	103.1	103.4	103.4	103.3	103.2	103.1
100°	128.0	128.6	129.2	129.5	129.8	130.3	130.6
102.5°	158.3	158.9	159.1	159.0	158.9	158.9	158.9
105°	202.9	202.9	203.0	203.4	203.8	204.1	204.6
107.5°	252.3	252.9	253.0	252.9	252.6	252.4	252.2
110°	285.1	285.9	286.0	285.6	285.2	284.9	284.5



TEST NUMBER: P331893-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	317.8	318.7	319.2	319.1	319.0	318.9	318.8
115°	366.7	366.9	366.9	366.7	366.5	366.4	366.1
117.5°	416.6	416.6	416.2	415.7	415.2	414.7	414.1
120°	449.8	449.6	449.3	448.9	448.6	448.2	447.8
122.5°	483.3	482.8	482.2	481.7	481.1	480.6	480.1
125°	533.1	532.4	531.6	530.9	530.1	529.3	528.6
127.5°	582.5	581.3	580.4	579.5	578.6	577.7	576.9
130°	615.6	614.9	613.8	612.5	611.1	609.8	608.5
132.5°	647.6	646.6	645.7	644.6	643.6	642.6	641.5
135°	695.6	694.8	694.2	693.9	693.4	693.1	692.8
137.5°	742.4	741.6	740.8	740.1	739.3	738.7	738.0
140°	773.8	773.6	772.8	771.5	770.2	768.9	767.5
142.5°	802.7	802.5	801.8	800.8	799.8	798.7	797.7
145°	845.2	844.9	844.5	843.7	842.9	842.1	841.4
147.5°	885.5	885.5	884.8	883.7	882.5	881.4	880.3
150°	910.2	910.2	909.6	908.4	907.3	906.1	905.0
152.5°	933.1	933.4	933.1	932.0	931.1	930.1	929.1
155°	966.6	967.3	967.1	965.8	964.4	963.0	961.7
157.5°	995.1	995.9	995.7	994.7	993.6	992.6	991.4
160°	1012.7	1013.7	1013.7	1013.1	1012.3	1011.5	1010.7
162.5°	1029.2	1030.2	1030.0	1028.8	1027.6	1026.4	1025.2
165°	1050.2	1051.4	1051.3	1050.0	1048.6	1047.3	1045.9
167.5°	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7
170°	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6
172.5°	1083.7	1084.9	1084.9	1083.5	1082.2	1080.8	1079.4
175°	1091.5	1092.7	1092.5	1091.2	1089.9	1088.6	1087.2
177.5°	1094.8	1095.7	1095.6	1094.6	1093.5	1092.4	1091.3
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1

(END OF REPORT)