

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331898-935

Luminaire Tested: **S123DIP-S340D1025U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331898-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4744.9 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	101	101	101	101	90	90	90	90	70	70	70		51	51	51		34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57		45	43	42		30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47		39	37	35		26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39		35	32	30		23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34		31	28	25		21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29		28	24	22		19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25		25	22	19		17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22		22	19	17		15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19		20	17	15		14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17		19	16	13		13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15		17	14	12		12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.9
10°-20°	124.1	2.6
20°-30°	183.3	3.9
30°-40°	214.1	4.5
40°-50°	215.3	4.5
50°-60°	189.1	4.0
60°-70°	140.9	3.0
70°-80°	80.3	1.7
80°-90°	26.3	0.6
90°-100°	42.1	0.9
100°-110°	200.4	4.2
110°-120°	481.5	10.1
120°-130°	613.1	12.9
130°-140°	655.1	13.8
140°-150°	612.6	12.9
150°-160°	494.1	10.4
160°-170°	318.9	6.7
170°-180°	109.9	2.3
0°-30°	351.4	7.4
0°-40°	565.5	11.9
0°-60°	969.9	20.4
0°-90°	1217.3	25.7
90°-120°	724.0	15.3
90°-150°	2604.6	54.9
90°-180°	3528.0	74.4
0°-180°	4744.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	1	10	21	24	26	4
95°	52	20	27	32	33	65
105°	256	261	188	45	38	272
115°	480	486	493	502	505	474
125°	677	684	688	689	691	605
135°	843	848	852	854	852	649
145°	973	979	981	982	982	609
155°	1072	1070	1071	1075	1070	494
165°	1130	1128	1127	1133	1128	319
175°	1157	1153	1153	1159	1152	110
180°	1157	1157	1157	1157	1157	



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.5	8.7	8.9	9.0	9.2	9.5	9.9	10.3	10.8	11.2	11.3
90°	0.9	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4
92.5°	16.0	15.4	14.9	14.4	13.9	14.6	16.4	18.3	20.1	22.0	23.2
95°	52.4	44.6	36.8	28.9	21.1	18.3	20.3	22.5	24.5	26.6	28.0
97.5°	105.4	101.9	98.3	94.8	91.3	82.7	69.0	55.2	41.4	27.6	29.2
100°	145.3	149.0	152.9	156.7	160.5	147.5	117.7	87.9	58.1	28.3	29.9
102.5°	190.6	193.4	196.1	198.9	201.6	186.8	154.2	121.7	89.1	56.6	51.8
105°	256.1	258.2	260.3	262.4	264.5	256.9	239.8	222.6	205.4	188.2	154.4
107.5°	325.2	326.9	328.6	330.3	331.9	334.2	336.8	339.6	342.2	345.0	320.2
110°	371.3	372.8	374.3	375.8	377.4	379.2	381.3	383.4	385.5	387.6	381.3



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.6	418.0	419.4	420.8	422.5	424.6	426.7	428.8	430.9	431.0
115°	480.4	481.6	482.7	483.9	485.0	486.5	488.1	489.8	491.5	493.3	495.2
117.5°	543.5	544.9	546.3	547.8	549.1	550.3	551.1	552.1	552.9	553.8	555.3
120°	582.6	584.4	586.1	587.8	589.5	590.7	591.2	591.9	592.5	593.0	594.5
122.5°	622.6	624.0	625.3	626.8	628.2	629.3	630.0	630.8	631.5	632.1	633.3
125°	677.2	678.7	680.3	681.8	683.3	684.5	685.3	686.0	686.7	687.5	687.9
127.5°	730.1	731.7	733.2	734.7	736.2	737.4	738.4	739.3	740.2	741.1	741.8
130°	763.2	764.7	766.2	767.8	769.3	770.4	771.2	772.0	772.7	773.4	774.2
132.5°	794.8	796.3	797.8	799.4	800.9	801.9	802.5	803.1	803.8	804.4	805.2
135°	843.1	844.2	845.3	846.5	847.7	848.6	849.4	850.2	850.9	851.7	852.2
137.5°	884.3	885.8	887.3	888.7	890.1	891.0	891.5	891.9	892.3	892.8	893.6
140°	911.8	913.0	914.1	915.2	916.4	917.3	917.8	918.4	919.0	919.5	920.3
142.5°	937.3	938.4	939.5	940.7	941.8	942.7	943.3	943.8	944.4	945.0	945.6
145°	972.8	974.2	975.5	976.9	978.2	979.0	979.5	979.8	980.2	980.6	980.9
147.5°	1006.3	1007.3	1008.1	1009.0	1009.9	1010.5	1010.9	1011.2	1011.7	1012.0	1012.4
150°	1027.0	1027.6	1028.1	1028.7	1029.2	1029.8	1030.1	1030.5	1030.9	1031.3	1031.7
152.5°	1045.5	1045.9	1046.1	1046.4	1046.6	1046.9	1047.1	1047.3	1047.6	1047.8	1048.4
155°	1071.7	1071.3	1070.9	1070.6	1070.1	1070.1	1070.2	1070.4	1070.7	1070.8	1071.8
157.5°	1091.9	1091.9	1091.9	1091.8	1091.8	1091.7	1091.5	1091.3	1091.1	1090.9	1092.1
160°	1104.3	1104.1	1104.0	1103.8	1103.5	1103.4	1103.2	1103.0	1102.8	1102.6	1103.8
162.5°	1116.0	1115.5	1115.0	1114.6	1114.0	1113.7	1113.5	1113.3	1113.1	1112.9	1114.2
165°	1130.1	1129.5	1128.9	1128.4	1127.8	1127.5	1127.2	1127.0	1126.9	1126.7	1128.2
167.5°	1141.1	1140.4	1139.6	1138.8	1138.1	1137.6	1137.6	1137.6	1137.6	1137.6	1139.2
170°	1147.3	1146.5	1145.8	1145.0	1144.3	1143.8	1143.8	1143.8	1143.8	1143.8	1145.4
172.5°	1151.4	1150.6	1149.6	1148.7	1147.8	1147.4	1147.5	1147.7	1147.8	1148.0	1149.5
175°	1156.8	1155.8	1154.9	1153.9	1153.0	1152.5	1152.7	1153.0	1153.1	1153.3	1154.7
177.5°	1158.1	1157.4	1156.6	1155.8	1155.1	1154.8	1154.9	1155.1	1155.2	1155.4	1156.6
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	11.4	11.5	11.5	11.6	11.7	11.7	11.8	11.9
90°	22.1	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	24.5	25.7	26.9	27.6	27.8	28.1	28.3	28.5
95°	29.3	30.7	32.0	32.6	32.6	32.6	32.6	32.6
97.5°	30.7	32.3	33.8	34.6	34.9	35.0	35.2	35.4
100°	31.4	33.0	34.4	35.3	35.6	35.7	35.9	36.1
102.5°	47.1	42.4	37.6	35.4	35.7	36.1	36.4	36.8
105°	120.6	86.8	53.0	36.2	36.7	37.0	37.5	37.8
107.5°	295.4	270.6	245.8	220.7	195.2	169.7	144.2	118.7
110°	375.0	368.7	362.4	345.6	318.2	290.9	263.6	236.3



TEST NUMBER: P331898-935

CATALOG NUMBER: S123DIP-S340D1025U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	431.1	431.3	431.4	428.5	422.8	417.0	411.2	405.4
115°	497.1	499.0	500.9	502.3	503.0	503.8	504.5	505.3
117.5°	556.9	558.4	559.9	560.8	560.9	561.0	561.2	561.4
120°	596.1	597.5	599.1	599.9	599.9	599.9	599.9	599.9
122.5°	634.3	635.4	636.5	637.1	637.2	637.4	637.5	637.7
125°	688.3	688.6	689.1	689.4	689.8	690.2	690.6	691.0
127.5°	742.4	743.0	743.6	743.7	743.3	743.0	742.5	742.2
130°	775.0	775.8	776.5	776.7	776.4	775.9	775.6	775.2
132.5°	805.9	806.7	807.4	807.5	807.0	806.5	806.0	805.5
135°	852.8	853.4	853.9	853.9	853.4	852.8	852.2	851.7
137.5°	894.6	895.5	896.4	896.6	896.3	896.0	895.5	895.2
140°	921.1	921.9	922.6	922.8	922.4	922.0	921.7	921.3
142.5°	946.2	946.8	947.4	947.4	946.9	946.4	945.9	945.4
145°	981.4	981.7	982.1	982.3	982.3	982.3	982.3	982.3
147.5°	1012.8	1013.1	1013.6	1013.3	1012.4	1011.6	1010.6	1009.8
150°	1032.1	1032.4	1032.9	1032.7	1032.2	1031.6	1031.0	1030.4
152.5°	1049.1	1049.8	1050.5	1050.4	1049.6	1048.7	1047.8	1046.9
155°	1072.7	1073.7	1074.6	1074.5	1073.4	1072.3	1071.1	1070.0
157.5°	1093.2	1094.3	1095.5	1095.4	1093.8	1092.4	1090.9	1089.4
160°	1104.9	1106.0	1107.2	1107.1	1105.8	1104.4	1103.1	1101.7
162.5°	1115.5	1116.8	1118.1	1118.2	1117.0	1115.8	1114.7	1113.4
165°	1129.7	1131.3	1132.8	1132.9	1131.5	1130.2	1128.9	1127.6
167.5°	1140.7	1142.3	1143.8	1143.8	1142.3	1140.7	1139.2	1137.6
170°	1146.9	1148.5	1150.0	1150.0	1148.5	1146.9	1145.4	1143.8
172.5°	1151.1	1152.5	1154.1	1154.0	1152.4	1150.6	1149.0	1147.3
175°	1156.0	1157.4	1158.6	1158.6	1157.0	1155.5	1154.0	1152.4
177.5°	1157.8	1159.1	1160.3	1160.1	1158.6	1157.1	1155.5	1154.0
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8

(END OF REPORT)