

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331903-935

Luminaire Tested: **S123DIP-S340D1195U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331903-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4971.3 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	21
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	0.8
10°-20°	130.8	2.6
20°-30°	219.5	4.4
30°-40°	248.5	5.0
40°-50°	222.9	4.5
50°-60°	179.8	3.6
60°-70°	125.3	2.5
70°-80°	65.9	1.3
80°-90°	19.9	0.4
90°-100°	275.0	5.5
100°-110°	778.7	15.7
110°-120°	766.1	15.4
120°-130°	611.0	12.3
130°-140°	481.8	9.7
140°-150°	359.6	7.2
150°-160°	250.6	5.0
160°-170°	147.2	3.0
170°-180°	47.9	1.0
0°-30°	391.0	7.9
0°-40°	639.5	12.9
0°-60°	1042.2	21.0
0°-90°	1253.4	25.2
90°-120°	1819.8	36.6
90°-150°	3272.2	65.8
90°-180°	3718.0	74.8
0°-180°	4971.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	16
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1272	116	1272	116	1272	1255
115°	1548	205	1548	205	1548	1504
125°	1220	285	1220	285	1220	1106
135°	989	334	989	334	989	767
145°	773	381	773	381	773	492
155°	641	433	641	433	641	299
165°	559	473	559	473	559	160
175°	503	493	503	493	503	49
180°	494	494	494	494	494	



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	10.6	10.5	10.4	10.4	10.4	10.2	10.2	10.2	10.1	10.4	10.0
90°	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2	116.1	153.9	169.3
95°	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2	481.1	593.2	528.2
97.5°	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7	983.5	919.3	673.0
100°	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4	1144.4	947.4	640.2
102.5°	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1	1152.4	895.4	592.2
105°	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5	1091.4	804.3	533.2
107.5°	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6	984.6	723.8	495.6
110°	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4	917.3	678.2	481.1



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9	858.9	647.8	473.2
115°	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4	788.2	615.2	470.2
117.5°	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9	745.6	596.0	472.0
120°	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3	723.2	587.2	475.2
122.5°	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7	704.8	581.6	480.8
125°	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3	681.2	574.2	489.1
127.5°	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9	660.5	570.6	498.8
130°	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3	649.2	568.2	505.1
132.5°	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3	638.9	567.4	510.0
135°	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2	625.3	566.2	517.2
137.5°	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6	613.4	564.0	522.0
140°	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2	606.2	563.2	525.2
142.5°	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6	599.8	561.6	527.6
145°	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2	591.2	559.2	529.2
147.5°	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8	582.8	555.4	529.2
150°	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2	577.2	552.2	529.2
152.5°	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4	570.8	548.2	526.8
155°	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2	561.2	541.2	524.2
157.5°	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2	550.4	535.0	520.8
160°	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2	543.2	530.2	519.2
162.5°	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6	536.0	525.4	516.0
165°	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2	526.2	518.1	511.2
167.5°	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4	516.8	511.0	506.4
170°	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2	511.2	506.2	503.2
172.5°	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8	505.6	502.1	500.8
175°	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2	499.2	497.1	497.1
177.5°	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	9.7	9.3	8.2	7.1	6.5	5.3	5.0	4.2	4.3	4.7	5.2
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4	18.4	26.8	34.6
95°	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0	37.0	48.0	65.0
97.5°	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0	59.0	67.6	82.4
100°	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0	75.0	82.1	96.0
102.5°	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8	92.6	98.8	112.0
105°	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1	119.1	125.0	137.1
107.5°	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8	145.9	151.6	163.4
110°	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0	165.1	170.0	181.1



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7	182.7	187.7	198.6
115°	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1	209.1	215.1	225.1
117.5°	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5	235.1	240.0	249.3
120°	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1	251.1	256.1	266.1
122.5°	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3	266.3	271.3	282.1
125°	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1	287.1	293.1	304.1
127.5°	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7	304.7	312.1	323.3
130°	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1	315.1	324.1	336.1
132.5°	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1	323.9	333.7	348.1
135°	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2	338.1	349.1	364.1
137.5°	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3	351.5	362.3	378.3
140°	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1	361.1	371.1	387.1
142.5°	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8	370.0	380.7	395.1
145°	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2	384.1	393.1	408.1
147.5°	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7	398.6	407.3	420.3
150°	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2	408.1	416.1	429.1
152.5°	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6	417.8	425.8	437.1
155°	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2	433.2	439.2	449.2
157.5°	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6	446.3	451.2	459.9
160°	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1	455.1	459.2	467.2
162.5°	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4	462.4	465.5	472.0
165°	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2	472.2	474.2	479.1
167.5°	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4	480.2	481.1	485.0
170°	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2	484.1	485.2	488.2
172.5°	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4	488.2	488.4	490.6
175°	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2	492.1	491.2	493.2
177.5°	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0	494.2	493.4	494.2
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	5.4	5.9	6.4	7.1	7.6	8.4	8.2	8.1	8.3	9.0	8.7
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	29.0
92.5°	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2	66.8	59.0	53.8
95°	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2	244.1	191.1	155.1
97.5°	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7	719.0	590.0	470.4
100°	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4	1098.4	981.4	839.3
102.5°	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1	1270.4	1202.2	1112.2
105°	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5	1400.5	1419.5	1393.5
107.5°	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6	1384.1	1471.7	1507.4
110°	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4	1330.5	1456.6	1526.6



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9	1260.1	1401.3	1491.3
115°	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4	1147.4	1294.4	1403.5
117.5°	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9	1052.1	1184.2	1294.9
120°	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3	999.4	1119.4	1220.5
122.5°	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7	956.9	1068.2	1162.0
125°	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3	904.3	1000.3	1080.4
127.5°	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9	858.1	944.7	1017.5
130°	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3	829.3	910.3	978.4
132.5°	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3	802.1	877.5	942.4
135°	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2	763.3	828.3	885.3
137.5°	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6	725.8	781.9	831.3
140°	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2	704.2	752.3	795.3
142.5°	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6	683.5	725.0	762.5
145°	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2	656.3	688.3	717.2
147.5°	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8	636.0	661.9	682.4
150°	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2	623.2	644.2	663.2
152.5°	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4	611.2	629.8	645.7
155°	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2	594.2	609.2	621.2
157.5°	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2	577.6	589.2	598.6
160°	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2	567.2	577.2	584.2
162.5°	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6	556.0	565.2	571.4
165°	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2	540.2	547.2	552.2
167.5°	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4	528.0	532.0	535.6
170°	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2	519.2	523.1	525.2
172.5°	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8	512.0	515.2	516.3
175°	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2	502.1	504.2	504.2
177.5°	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8	496.5	497.4	497.4
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	8.5	8.7	8.7	8.4	8.7	8.7	8.5	8.7	9.0	8.3	8.1
90°	28.0	29.0	30.0	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0
92.5°	52.0	49.0	50.0	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2
95°	136.0	127.1	120.0	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2
97.5°	396.6	351.5	324.5	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7
100°	738.2	665.2	626.2	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4
102.5°	1033.5	975.8	943.1	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1
105°	1347.5	1309.5	1277.5	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5
107.5°	1508.1	1495.3	1484.5	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6
110°	1554.5	1562.5	1560.6	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1542.6	1567.4	1574.9	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9
115°	1478.5	1522.5	1542.6	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4
117.5°	1373.1	1423.5	1452.3	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9
120°	1299.4	1355.5	1379.5	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3
122.5°	1232.3	1282.6	1309.1	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7
125°	1144.4	1188.4	1213.4	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3
127.5°	1074.6	1112.2	1134.8	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9
130°	1031.4	1067.4	1088.4	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3
132.5°	992.1	1028.1	1046.8	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3
135°	934.4	964.3	982.3	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2
137.5°	872.5	902.9	918.1	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6
140°	833.3	861.3	877.3	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2
142.5°	794.9	819.7	834.1	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6
145°	742.3	763.3	771.3	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2
147.5°	701.5	715.7	723.2	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8
150°	678.2	689.2	695.3	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2
152.5°	657.5	667.6	671.2	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4
155°	630.3	638.3	640.2	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2
157.5°	606.4	612.4	614.0	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2
160°	591.2	597.2	597.2	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2
162.5°	576.0	581.2	581.2	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6
165°	556.2	560.2	559.2	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2
167.5°	537.4	540.2	539.2	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4
170°	526.2	528.2	527.2	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2
172.5°	516.6	518.6	516.8	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8
175°	504.2	505.1	504.2	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2
177.5°	496.5	497.4	495.8	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	8.2	8.4	7.6	7.1	6.4	5.9	5.4	5.2	4.7	4.3	4.2
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	116.1	153.9	169.3	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4
95°	481.1	593.2	528.2	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0
97.5°	983.5	919.3	673.0	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0
100°	1144.4	947.4	640.2	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0
102.5°	1152.4	895.4	592.2	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8
105°	1091.4	804.3	533.2	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1
107.5°	984.6	723.8	495.6	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8
110°	917.3	678.2	481.1	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	858.9	647.8	473.2	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7
115°	788.2	615.2	470.2	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1
117.5°	745.6	596.0	472.0	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5
120°	723.2	587.2	475.2	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1
122.5°	704.8	581.6	480.8	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3
125°	681.2	574.2	489.1	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1
127.5°	660.5	570.6	498.8	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7
130°	649.2	568.2	505.1	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1
132.5°	638.9	567.4	510.0	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1
135°	625.3	566.2	517.2	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2
137.5°	613.4	564.0	522.0	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3
140°	606.2	563.2	525.2	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1
142.5°	599.8	561.6	527.6	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8
145°	591.2	559.2	529.2	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2
147.5°	582.8	555.4	529.2	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7
150°	577.2	552.2	529.2	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2
152.5°	570.8	548.2	526.8	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6
155°	561.2	541.2	524.2	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2
157.5°	550.4	535.0	520.8	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6
160°	543.2	530.2	519.2	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1
162.5°	536.0	525.4	516.0	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4
165°	526.2	518.1	511.2	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2
167.5°	516.8	511.0	506.4	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4
170°	511.2	506.2	503.2	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2
172.5°	505.6	502.1	500.8	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4
175°	499.2	497.1	497.1	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2
177.5°	495.0	494.2	495.0	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	5.0	5.3	6.5	7.1	8.2	9.3	9.7	10.0	10.4	10.1	10.2
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2
95°	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2
97.5°	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7
100°	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4
102.5°	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1
105°	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5
107.5°	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6
110°	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9
115°	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4
117.5°	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9
120°	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3
122.5°	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7
125°	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3
127.5°	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9
130°	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3
132.5°	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3
135°	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2
137.5°	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6
140°	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2
142.5°	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6
145°	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2
147.5°	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8
150°	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2
152.5°	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4
155°	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2
157.5°	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2
160°	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2
162.5°	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6
165°	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2
167.5°	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4
170°	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2
172.5°	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8
175°	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2
177.5°	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	10.2	10.2	10.4	10.4	10.4	10.5	10.6
90°	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6



TEST NUMBER: P331903-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)